

Plastično crevo PUN-V0-6X2-WS-C

Broj artikla: 561714

FESTO

nezapaljivo



Tehnički podaci

| Svojstvo | Vrednost |
|---|---|
| Spoljašnji prečnik | 6 mm |
| Radius savijanja, merodavan za protok | 24 mm |
| Unutrašnji prečnik | 2 mm |
| Min. radius savijanja | 7 mm |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0,095 ... 1,6 MPa |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 16 bar |
| Operating pressure for entire temperature range | -13,775 ... 232 psi |
| Temperature-dependent operating pressure | -0,095 ... 3 MPa |
| Pogonski pritisak zavisn od temperature | -0,95 ... 30 bar |
| Temperature-dependent operating pressure | -13,775 ... 435 psi |
| Napomena za pogonski pritisak | Water: max. 0.6 MPa at max. 50°C For applications with welding spatter: max. 1 MPa at 20°C, max. 0.9 MPa at 40°C, max. 0.7 MPa at 60°C |
| Dozvola | TÜV |
| Mesto izdavanja sertifikata | B 013277 0506 00 |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| Material fire test | UL94 V-0 (3mm) UL94 V-2 (0,75mm) |
| PWIS conformity | VDMA24364-B2-L |
| Temperatura okoline | -35 ... 60 °C |
| Note on ambient temperature | For unpressurised use up to 90 °C |
| Težina proizvoda prema dužini | 0,032 kg/m |
| Pneumatski priključak | For push-in connector outside diameter 6 mm for barbed connector internal diameter 2 mm with nut |
| Boja | belo |
| Napomena za boju | odstupanje prema standardnoj boji zbog vatrozaštite |
| Tvrdoća po Shoreu | D 54 +/-3 |
| Materijal - napomena | RoHS komformnost |
| Material tubing | TPE-U(PU) |