

Spojni vod NEBC-M9W5-K-2-N-LE3

Broj artikla: 563711

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	sa priborom
Težina proizvoda	108 g
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	Kabl
Electrical connection 1, connection technology	otvoreni kraj
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	M9x0,5
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	3
Electrical connection 2, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	1,6 A
Note on acceptable current load at 40°C	2.3 A for 0.34 mm ² 3.6 A for 0.49 mm ²
Čvrstoća na udarno naprezanje	0,5 kV
Dužina kabla	2 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, flexible cable installation	≥ 75 mm
Prečnik kabla	5,5 mm
Struktura kabla	2x0,25+2x0,34+0,49 zaslonjeno
Nazivni presek provodnika	0,25 mm ² 0,34 mm ² 0,49 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-20 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	1
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	svetlo sivo
Material housing	PA PBT

Svojstvo	Vrednost
	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	TPE-U(PUR)