

Plastično crevo PUN-H-1/4-SW-500-HA

Broj artikla: 568018

FESTO

dopušteno u prehrambenom području (postojano na hidrolizu).



Tehnički podaci

| Svojstvo | Vrednost |
|---|--|
| Spoljašnji prečnik, col | 1/4 |
| Radius savijanja, merodavan za protok | 0,085 ft |
| Min. radius savijanja | 0,032 ft |
| Uputstva za korišćenje | TPE-U Ether basiert |
| Tubing characteristics | Suitable for energy chains |
| Pogonski pritisak zavisn od temperature | -14,4 ... 145 Psi |
| Napomena za pogonski pritisak | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7::-] Water (liquid, free of ice) |
| Material fire test | UL94 HB |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See Supplementary material information |
| Temperatura okoline | -31 ... 145 °F |
| Težina proizvoda prema dužini | 0,23 oz/ft |
| Pneumatski priključak | za utični priključak spoljašnji prečnik 1/4" |
| Boja | crno |
| Tvrdoća po Shoreu | D 52 +/-3 |
| Materijal - napomena | RoHS komformnost |
| Material tubing | TPE-U(PU) |