

# Plastično crevo

## PUN-H-5/16-NT-500-HA

Broj artikla: 8003127

FESTO



### Tehnički podaci

| Svojstvo                                 | Vrednost   |
|--|--|
| Spoljašnji prečnik, col                  | 5/16   |
| Radius savijanja, merodavan za protok    | 0,123 ft   |
| Min. radius savijanja                    | 0,066 ft   |
| Uputstva za korišćenje                   | TPE-U Ether basiert  |
| Tubing characteristics                   | Suitable for energy chains   |
| Pogonski pritisak zavisao od temperature | -14,4 ... 145 Psi  |
| Napomena za pogonski pritisak            | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C   |
| Pogonski medijum                         | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-]<br>Water (liquid, free of ice)   |
| Material fire test                       | UL94 HB  |
| PWIS conformity                          | VDMA24364-B2-L   |
| RSBP classification to CD-0033           | F1a  |
| Cleanroom class                          | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe                                | See Supplementary material information   |
| Temperatura okoline                      | -31 ... 145 °F   |
| Težina proizvoda prema dužini            | 0,31 oz/ft   |
| Pneumatski priključak                    | For push-in connector outside diameter 5/16"   |
| Boja                                     | prirodno   |
| Tvrdoća po Shoreu                        | D 52 +/-3  |
| Materijal - napomena                     | RoHS komfornost  |
| Material tubing                          | TPE-U(PU)  |