



Adapter

NEFV-V12-M12W8-0.6-M12QG5

Broj artikla: 4787544

FESTO



Tehnički podaci

Svojstvo	Vrednost
Vrsta pričvršćenja	sa prolaznim otvorom
Težina proizvoda	157 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Analogue output module (green), digital input module (white), analogue input module (yellow), digital output module (red) Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	4x plugs
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Pogonski napon DC napon opterećenja	0 ... 30 V
Nazivni pogonski napon DC, napon opterećenja	24 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	60 V
Dužina kabla	0,623 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
PWIS conformity	VDMA24364-B1/B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material of union nut	Nickel-plated die-cast zinc
Material electrical contact	Mesing Niklovano
Material insulation	PP