


Mrežna priključna utičnica NECU-M-PPG5PP-C1-PN

Broj artikla: 5195383

FESTO



Tehnički podaci

Svojstvo	Vrednost
Protokol	PROFINET
Dozvola	c UL us - Recognized (OL)
Mesto izdavanja sertifikata	UL E328433
Dodatne funkcije	Fulfils requirements according to AIDA
Frekvencija priključivanja	100
Cable outlet	Ravno
Težina proizvoda	109 g
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, connection technology	Connection pattern PP, coding to pin 2 and 5
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Push-pull with interlock against unintentional pulling
Electrical connection 2, connection technology	Opružna stezaljka
Područje pogonskog napona DC	0 ... 24 V
Strujna opteretivost kod 40°C	16 A
Čvrstoća na udarno naprezanje	4 kV
Navojni spoj kabla	Pg13.5 hex A/F 22
Prečnik kabla	9 ... 13 mm
Nazivni presek provodnika	0,75 ... 2,5 mm ²
Nominal conductor cross section (AWG)	AWG18 - 13
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 85 °C
Temperatura ležaja	-40 ... 85 °C
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Fire test	UL94 V-0
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material housing	Nickel-plated die-cast zinc
Boja kućišta	srebrno
Material seals	NBR TPE-V
Material electrical contact	Nickel-plated and gold-plated copper alloy