


Spojni vod NEBV-C1SW3-K-2.5-N-LE3-S9

Broj artikla: 8032628

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	125 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Socket, slim
Electrical connection 1, cable outlet	Angled
Electrical connection 1, note about the cable outlet	180° rotatable
Electrical connection 1, connection technology	Plug pattern type C to EN 175301-803
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	na elektromagnetnom ventilu sa središnjim vijkom M2,5
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Područje pogonskog napona DC	0 ... 230 V
Područje pogonskog napona AC	0 ... 230 V
Strujna opteretivost kod 40°C	6 A
Čvrstoća na udarno naprezanje	4 kV
Zaštita od zamene polova	bipolarno
Priključak uzemljenja	postoji
Dužina kabla	2,5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, flexible cable installation	≥ 52 mm
Prečnik kabela	5,2 mm
Odstupanje prečnika kabla	± 0,1 mm
Struktura kabla	3x0,5
Nazivni presek provodnika	0,5 mm ²
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-20 ... 70 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	3 - High corrosion stress
Material cable sheath	PVC
Boja izolacije	sivo

Svojstvo	Vrednost
Material housing	TPE-U(PU)
Boja kućišta	crno
Material screws	Nerđajući čelik
Material seals	HNBR
Material electrical contact	Legura bakra, kalajisana
Material insulation	PVC