


Spojni vod NEBC-D12G4-ES-5-S-D12G4-ET

Broj artikla: 8040449

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	With inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	331,5 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, D-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hex A/F 13 mm and longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, D-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw-type lock with hex A/F 13 mm and longitudinal knurl
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	4 A
Čvrstoća na udarno naprezanje	0,8 kV
Note on surge resistance	Due to screening, a leakage flow of up to 20 mA is permissible.
Svojstva prenošenja	In accordance with category 5, EN 50173, class D In accordance with category 5, ISO/IEC 11801, class D
Specifikacija ethernet kabla	Tip: CAT.5
Dužina kabla	5 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Energy chain > 2 million cycles, bending radius 100 mm
Bending radius, fixed cable installation	>= 40 mm
Bending radius, flexible cable installation	>= 100 mm
Prečnik kabla	6,7 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	4 x 0.34 mm ² (star quad)
Nazivni presek provodnika	0,34 mm ²
Nominal conductor cross section (AWG)	AWG22
Mehanička zaštita	IP65 IP67
Posebne karakteristike	postojano na ulje
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-20 ... 60 °C
Temperatura ležaja	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive

Svojstvo	Vrednost
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	zeleno
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Mesing pozlačeno
Material insulation	PE
Material threaded sleeve	Cink