



# Hauba VMPA-KMS-H

Broj artikla: 533198

FESTO

za multipol priključak na ventilski blok MPA-S.



## Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	DIN 41652
Frekvencija priključivanja	50
Težina proizvoda	71 g
Električni priključak	Utikači / utičnice
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, type of mounting	3x M3 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection technology	Crimp contacts
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Nazivni pogonski napon AC	3 V
Čvrstoća na udarno naprezanje	1 kV
Prečnik kabela	6 ... 12 mm
Mehanička zaštita	IP65 prema IEC 60529
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material housing	PA
Boja kućišta	sivo
Material of union nut	PA
Material seals	CR NBR
Material electrical contact	Gold-plated copper alloy