



Osovina konzole ELCC-TB-KF-60- -

Broj artikla: 8060571

FESTO



Prikaz primera



Tehnički podaci

Ukupni list podataka - Pojedinačne vrednosti zavise od Vaše konfiguracije.

Svojstvo	Vrednost
Pogonski manji zupčanik, efektivni prečnik	30,558 mm
Radni hod	50 ... 1.300 mm
Veličina	60
Rezerva hoda	0 ... 1.300 mm
Zupčasti kaiš, podela	3 mm
Položaj ugradnje	proizvoljno
Vođica	Kuglično vođenje
Konstruktivna struktura	Elektromehanička osa prečke
Maks. ubrzanje	50 m/s ²
Maks. brzina	5 m/s
Tačnost ponavljanja	±0,05 mm
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Mehanička zaštita	IP20
Temperatura okoline	-10 ... 60 °C
Moment inercije 2. stepena Iy	240,6E+03 mm ⁴
Moment inercije 2. stepena Iz	304,21E+03 mm ⁴
Maks. pogonski moment	5,2 Nm
Maks. sila Fy	4.216 N
Maks. sila Fz	4.119 N
Maks. moment Mx	36 Nm
Maks. moment My	293 Nm
Maks. moment Mz	288 Nm
Maks. Ulazna sila Fx	300 N
Moment inercije, JH po metru hoda	8,9 kgcm ²
Moment inercije, JL po kg korisnog tereta	2,3 kgcm ²
Moment inercije JO	5,9 kgcm ²
Konstanta posmaka	96 mm/U
Referentna veličina snage kretanja	5.000 km
Interval podmazivanja zavisao od puta	1.000 km
Pokretna masa kod 0 mm hoda sa drugom pogonskom glavom	2.738 g
Pokretna masa kod hoda 0 mm	1.636 g
Dodatni faktor mase po 10 mm hoda	38 g
Težina dodatnog klizača	805 g
Osnovna težina kod hoda 0 mm	4.146 g
Dodatna težine po 10 mm hoda	38 g
Osnovna težina kod 0 mm hoda sa drugom pogonskom glavom	6.053 g
Material of end caps	Anodised wrought aluminium alloy
Material of profile	Anodised wrought aluminium alloy
Materijal - napomena	RoHS komformnost
Material drive head	Anodised wrought aluminium alloy
Material guide rail	Rolled steel, Corrotect coated
Material housing	visokolegirani čelik, nerdajući
Material slide	Cast aluminium, anodised
Material toothed belt clamping piece	Anodised wrought aluminium alloy
Material toothed belt	Polihiropren sa staklenom vrpcom i najlonskom oblogom Polyurethane with steel cord and fabric coating Polyurethane with steel cord