


dispense head

VTOE-8-D9-T3-M22C-08-V-S-PC-M

Broj artikla: 8063636

FESTO



Tehnički podaci

Svojstvo	Vrednost
Funkcija ventila	2/2 zatvoren, monostabilan
Operating pressure MPa	0 ... 0,05 MPa
Pogonski pritisak	0 ... 0,5 bar
Operating pressure	0 ... 7,25 psi
Internal volume	113 µl valve with fluid connections
Nazivni prečnik	0,8 mm
Nominal width of dosing needle	1 mm
Length of dosing needle	30 mm
Mera mreže	9 mm
Princip zaptivanja	mekano
Položaj ugradnje	proizvoljno
Vrsta resetovanja	mehanička opruga
Vrsta upravljanja	direktno
Water flow rate at max. operating pressure	2000 µl/s
Min. dosing volume	5 µl
Note on dosing volume	Depending on the configuration, environment and application
Typical dosing precision	<1% CV for volumes >5 µl <2.5% CV for volumes between 1-5 µl
Note on dosing precision	Depending on the configuration, environment and application
Maks. frekvencija prekidača	4 Hz
Note on switching frequency	Dependent on the ambient temperature and installation state
Vreme uključenja	7 ms
Note on switching time on	Depending on the configuration, environment and application
Vreme isključenja	2 ms
Note on switching time off	Depending on the configuration, environment and application
Trajanje uključenosti	50% (max. switch-on time 1s)
Električna primljena snaga	1,8 W
Napomena uz primljenu snagu	Specification per valve
Nazivni pogonski napon DC	24 V
Dozvoljena kolebanja napona	+/- 10 %
Medijum	Tečni mediji
Note on the medium	Observe resistance of materials that come into contact with media
Uputstva za korišćenje	See application note (available on the Support Portal at festo.com)
Otpornost na vibracije	Ispitivanje transporta sa stepenom težine 2 prema FN 942017-4 i EN 60068-2-6
Udarna čvrstoća	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364-B2-L
Temperatura ležaja	-20 ... 70 °C
Temperatura medijuma	5 ... 50 °C
Mehanička zaštita	IP30
Note on degree of protection	u montiranom stanju
Temperatura okoline	5 ... 40 °C
Težina proizvoda	220 g
Električni priključak	9-polno

Svojstvo	Vrednost
	Utikači Sub-D
Vrsta pričvršćenja	With through-hole for M3 screw With female thread and centring sleeve po izboru:
Fluid connection	8x UNF1/4-28
Note on fluid connection	Fitting provided for tubing with an outside diameter of 3 mm
Material of dosing needle	visokolegirani čelik, nerđajući
Material number of dosing needle	1.4301
Materijal - napomena	RoHS komfornost
materijali u dodiru sa medijumom	ETFE FPM PC PEEK PPS visokolegirani čelik, nerđajući
Način aktiviranja	električno
Nominal altitude of use	≤ 2000 m NHN
Relativna vlažnost vazduha	0 - 95 % ne kondenzira se
Stepen zagađenja	2