

Osovina konzole

ELCC-TB-KF-90-500-0H-P0-CR

Broj artikla: 8082401

FESTO



Tehnički podaci

Svojstvo	Vrednost
Pogonski manji zupčanik, efektivni prečnik	50,93 mm
Radni hod	500 mm
Veličina	90
Rezerva hoda	0 mm
Zupčasti kaiš, podela	5 mm
Položaj ugradnje	proizvoljno
Vođica	Kuglično vođenje
Konstruktivna struktura	Elektromehanička osa prečke
Maks. ubrzanje	30 m/s ²
Maks. brzina	5 m/s
Tačnost ponavljanja	±0,05 mm
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Mehanička zaštita	IP20
Temperatura okoline	-10 ... 60 °C
Moment inercije 2. stepena ly	2.667,9E+03 mm ⁴
Moment inercije 2. stepena lz	2.049,49E+03 mm ⁴
Maks. pogonski moment	33 Nm
Maks. sila Fy	13.957 N
Maks. sila Fz	13.523 N
Maks. moment Mx	167 Nm
Maks. moment My	1.300 Nm
Maks. moment Mz	1.233 Nm
Maks. Ulazna sila Fx	1.200 N
Moment inercije, JH po metru hoda	62,9 kgcm ²
Moment inercije, JL po kg korisnog tereta	6,5 kgcm ²
Moment inercije JO	55,2 kgcm ²
Konstanta posmaka	160 mm/U
Referentna veličina snage kretanja	5.000 km
Interval podmazivanja zavisao od puta	1.000 km
Pokretna masa kod hoda 0 mm	5.487 g
Dodatni faktor mase po 10 mm hoda	97 g
Osnovna težina kod hoda 0 mm	14.787 g
Dodatna težine po 10 mm hoda	97 g
Material of end caps	Anodised wrought aluminium alloy
Material of profile	Anodised wrought aluminium alloy
Materijal - napomena	RoHS komfornost
Material drive head	Anodised wrought aluminium alloy
Material guide rail	Rolled steel, Corrotect coated
Material housing	visokolegirani čelik, nerđajući
Material slide	Cast aluminium, anodised
Material toothed belt clamping piece	Anodised wrought aluminium alloy
Material toothed belt	Polihloropren sa staklenom vrpcom i najlonskom oblogom