


Spojni vod NEBC-D8G4-ES-0.3-N-S-D8G4-ET

Broj artikla: 8082902

★ Kernprogramm

FESTO



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-114
Dozvola	c UL us (OL)
Mesto izdavanja sertifikata	UL E520706
Cable identification	Without inscription label holder
Frekvencija priključivanja	100
Težina proizvoda	31 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1, D-coded to EN 61076-2-114
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M8x1, D-coded to EN 61076-2-114
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw-type lock with longitudinal knurl
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Strujna opteretivost kod 40°C	3 A
Čvrstoća na udarno naprezanje	1,5 kV
Zaštita od zamene polova	ne
Priključak uzemljenja	ne postoji
Shielding	Da
Svojstva prenošenja	as per system communication AP
Dužina kabla	0,3 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 20 mm
Bending radius, flexible cable installation	≥ 75 mm
Prečnik kabla	6,3 mm
Odstupanje prečnika kabla	± 0,2 mm
Struktura kabla	1x(4xAWG22)
Nominal conductor cross section (AWG)	AWG22
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Posebne karakteristike	postojano na ulje
Temperatura okoline	-20 ... 60 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 60 °C
Temperatura ležaja	-40 ... 70 °C

Svojstvo	Vrednost
CE znak (vidi izjavu o uskladenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost Bez halogena
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	Silver-grey with sky blue stripe
Material housing	PA TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulation	PP