

Spojni vod NEBU-M8G3-R-5-LE3

Broj artikla: 569846

FESTO



Tehnički podaci

| Svojstvo | Vrednost |
|--|---|
| Odgovara standardu | Core colours and connection numbers to EN 60947-5-2 EN 61076-2-104 |
| Cable identification | with 2x label holders |
| Težina proizvoda | 123 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | okruglo |
| Electrical connection 1, connection type | Utičnica |
| Electrical connection 1, cable outlet | Ravno |
| Electrical connection 1, connection technology | M8x1, A-coded to EN 61076-2-104 |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, occupied pins/wires | 3 |
| Electrical connection 1, type of mounting | Screw lock |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | Kabl |
| Electrical connection 2, connection technology | otvoreni kraj |
| Electrical connection 2, number of pins/wires | 3 |
| Electrical connection 2, occupied pins/wires | 3 |
| Područje pogonskog napona DC | 0 ... 60 V |
| Područje pogonskog napona AC | 0 ... 60 V |
| Strujna opteretivost kod 40°C | 3 A |
| Čvrstoća na udarno naprezanje | 1,5 kV |
| Dužina kabla | 5 m |
| Svojstvo kabla | prikladno za robot |
| Uslovi ispitivanja kabla | Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Čvrstoća na torziju: > 300 000 ciklusa, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm |
| Bending radius, fixed cable installation | 12 mm |
| Bending radius, flexible cable installation | 39 mm |
| Prečnik kabla | 3,8 mm |
| Odstupanje prečnika kabla | ± 0,1 mm |
| Struktura kabla | 3x0,25 |
| Nazivni presek provodnika | 0,25 mm ² |
| Mehanička zaštita | IP65 IP68 IP69K |
| Note on degree of protection | u montiranom stanju |
| Posebne karakteristike | postojano na ulje |
| Temperatura okoline | -25 ... 80 °C |
| Temperatura okoline kod pokretnog postepenja kablova | -5 ... 80 °C |
| CE znak (vidi izjavu o usklađenosti) | prema EU-niski napon-smernica in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |

| Svojstvo | Vrednost |
|--------------------------------|--|
| Materijal - napomena | RoHS komfornost Bez halogena Free of phosphoric acid ester |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| Boja izolacije | sivo |
| Material housing | TPE-U(PUR) |
| Boja kućišta | crno |
| Material screw-type lock | Nickel-plated brass |
| Material seals | NBR |
| Material electrical contact | Gold-plated copper alloy |
| Material insulation | PP |