



# Spojni vod NEBV-S1WA25-K-5-N-LE25-S9

Broj artikla: 575424

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	DIN 47100
Cable identification	Without inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	950 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, occupied pins/wires	25
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	25
Electrical connection 2, occupied pins/wires	25
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	2,6 A
Čvrstoća na udarno naprezanje	2,4 kV
Zaštita od zamene polova	Da
Dužina kabla	5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 42 mm
Bending radius, flexible cable installation	≥ 126 mm
Navojni spoj kabla	M20x1,5
Prečnik kabela	10,2 mm
Odstupanje prečnika kabla	± 0,25 mm
Struktura kabla	25x0,34
Nazivni presek provodnika	0,34 mm <sup>2</sup>
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-35 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
Temperatura ležaja	-35 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	PVC
Boja izolacije	sivo

Svojstvo	Vrednost
Material housing	PA66-GF30
Boja kućišta	crno
Material screws	Čelik
Material seals	NBR
Material electrical contact	Bronza pozlačeno
Material insulation	PVC