



# Razdelnik NEDY-L2R1-V1-M8G3-N-M8G4

Broj artikla: 8005312

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-104
Konstruktivna struktura	Y-distributor without cable
Distributor type	2 to 1
Cable identification	Without inscription label holder
Vrsta pričvršćenja	With through-hole for M2 screw sa priborom
Težina proizvoda	10,5 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Field device side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	2 x utičnica
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	3 A
Čvrstoća na udarno naprezanje	0,8 kV
Mehanička zaštita	IP65 IP68 IP69K
Temperatura okoline	-25 ... 85 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
Temperatura ležaja	-25 ... 85 °C
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost Bez halogena Free of phosphoric acid ester
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	PC TPE-U(PUR)
Boja kućišta	crno
Material of union nut	Mesing niklovan
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material threaded sleeve	Mesing niklovan