



# Razdelnik NEDY-L2R1-V1-B2W3L-U-0.3L-M12G4-5R

Broj artikla: 8035780

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-101
Konstruktivna struktura	Y-distributor with cables on both sides
Distributor type	2 to 1
Signal status display	LED žuti
Cable identification	With inscription label holder
Vrsta pričvršćenja	With through-hole for M2 screw sa priborom
Težina proizvoda	173 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	2 x utičnica
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Plug pattern type B to industry standard, 11 mm
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	2
Područje pogonskog napona DC	20,4 ... 27,6 V
Strujna opteretivost kod 40°C	4 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabela 1	5 m
Dužina kabela 2	0,3 m
Svojstvo kabela	Suitable for energy chains/robot applications
Uslovi ispitivanja kabela	Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Čvrstoća na torziju: > 300 000 ciklusa, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Minimum bending radius with freely moveable use 1	39 mm
Minimum bending radius with freely moveable use 2	39 mm
Prečnik kabela 1	3,8 mm
Prečnik kabela 2	3,8 mm
Nazivni presek provodnika	0,25 mm <sup>2</sup>
Mehanička zaštita	IP65 IP67
Temperatura okoline	-20 ... 80 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
Temperatura okoline kod pokretnog postepenja kablova	-20 ... 80 °C
Temperatura ležaja	-20 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions

Svojstvo	Vrednost
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena Free of phosphoric acid ester
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	PA PC TPE-U(PUR)
Boja kućišta	crno
Material of union nut	Mesing niklovan
Material seals	NBR
Material electrical contact	Gold-plated copper alloy Silver-plated copper alloy
Material threaded sleeve	Mesing niklovan