


# Ulazni modul CTMM-S1-D-8E-M8-3

Broj artikla: 8047505

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Dimenzije Š x D x V	27 mm x 123 mm x 40 mm
Mera mreže	28 mm
Težina proizvoda	75 g
Temperatura medijuma	-5 ... 50 °C
Temperatura okoline	-5 ... 50 °C
Temperatura ležaja	-20 ... 40 °C
Mehanička zaštita	IP65 IP67
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Otpornost na vibracije	Ispitivanje transporta sa stepenom težine 2 prema FN 942017-4 i EN 60068-2-6
Udarna čvrstoća	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Maks. dužina voda	30 m
PWIS conformity	VDMA24364-B1/B2-L
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici
Materijal - napomena	RoHS komformnost
Material housing	PA ojačan
Diagnostics via LED	Error per module Status per channel
Broj izlaza	0
Nazivni pogonski napon DC	24 V
Nominal operating voltage DC for electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typical 12 mA
Electrical connection, input, function	Digitaleingang
Electrical connection, input, connection type	8 x utičnica
Electrical connection, input, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection, input, number of pins/wires	3
Broj ulaza	8
Karakteristike, ulazi	to IEC 61131-2, type 3
Sklopna razina	Signal 0: ≤ 5 V Signal 1: ≥ 11 V
Sklopna logika, ulazi	PNP (plus sklapanje)
Vreme ulaznog odskoka	0,1 ms
Maks. ukupna struja ulaza po modulu	0,2 A
Izolacija kanal - kanal	ne
Naponsko odvajanje kanal - interna sabirnica	ne
Osiguranje (kratki spoj)	interni elektronski osigurač