

Electrical connection technology, for multi-pin plug connection

FESTO

Product range overview

Overview of multi-pin plug connections for valve terminals									
Connecting cable/plug	Valve terminal								→ Page
	Type 04	Type 10	Type 12	Type 32	Type 03	Type 02	Type 80	Type 82	
KEA-1-25P-5	–	■	■	–	■	–	–	–	4 / 5.1-67
KEA-1-25P-10	–	■	■	–	■	–	–	–	4 / 5.1-67
KEA-1-25P-...	–	■	■	–	■	–	–	–	4 / 5.1-67
KMP1-02-VI-16-X	■	–	–	–	–	–	–	–	4 / 5.1-51
KMP1-02-VI-6-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-VI-12-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-VI-16-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-VI-6-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-VI-12-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-VI-16-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-4-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-8-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-10-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-14-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-16-5	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-4-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-8-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-10-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-14-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP1-02-II-16-10	–	–	–	–	–	■	–	–	4 / 5.1-51
KMP2-03-E-10-26	–	–	–	–	■	–	–	–	4 / 5.1-57
KMP2-03-E-X-26	–	–	–	–	■	–	–	–	4 / 5.1-57
KMP2-03-V-10-26	–	–	–	–	■	–	–	–	4 / 5.1-57
KMP2-03-V-X-26	–	–	–	–	■	–	–	–	4 / 5.1-57
KMP3-9P-08-5	–	■	–	–	■	–	–	–	4 / 5.1-59
KMP3-9P-08-5-FD	–	■	–	–	–	–	–	–	4 / 5.1-59
KMP3-9P-08-10	–	■	–	–	–	–	–	–	4 / 5.1-59
KMP3-9P-08-10-FD	–	■	–	–	–	–	–	–	4 / 5.1-59
KMP3-25P-16-5	–	■	–	–	–	–	–	–	4 / 5.1-59
KMP3-25P-16-10	–	■	–	–	–	–	–	–	4 / 5.1-59
KMP4-9-P-5-PVC	–	■	–	–	–	–	–	–	4 / 5.1-61
KMP4-9-P-10-PVC	–	■	–	–	–	–	–	–	4 / 5.1-61
KMP4-9-P-5-PUR	–	■	–	–	–	–	–	–	4 / 5.1-61
KMP4-9-P-10-PUR	–	■	–	–	–	–	–	–	4 / 5.1-61
KMP4-25-P-5-PVC	–	■	■	–	–	–	–	–	4 / 5.1-61
KMP4-25-P-10-PVC	–	■	■	–	–	–	–	–	4 / 5.1-61
KMP4-25-P-5-PUR	–	■	■	–	–	–	–	–	4 / 5.1-61
KMP4-25-P-10-PUR	–	■	■	–	–	–	–	–	4 / 5.1-61

Electrical connection technology, for multi-pin plug connection

Product range overview

FESTO


Overview of multi-pin plug connections for valve terminals									
Connecting cable/plug	Valve terminal								→ Page
	Type 04	Type 10	Type 12	Type 32	Type 03	Type 02	Type 80	Type 82	
KMP6-09P-8-2,5	–	■	–	–	–	–	–	–	4 / 5.1-63
KMP6-09P-8-5	–	■	–	–	–	–	–	–	4 / 5.1-63
KMP6-09P-8-10	–	■	–	–	–	–	–	–	4 / 5.1-63
KMP6-15P-12-2,5	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-15P-12-5	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-15P-12-10	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-26P-16-2,5	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-26P-16-5	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-26P-16-10	–	–	–	–	–	–	■	–	4 / 5.1-63
KMP6-25P-12-2,5	–	–	–	–	–	–	–	■	4 / 5.1-63
KMP6-25P-12-5	–	–	–	–	–	–	–	■	4 / 5.1-63
KMP6-25P-12-10	–	–	–	–	–	–	–	■	4 / 5.1-63
KMP6-25P-20-2,5	–	■	■	–	–	–	–	■	4 / 5.1-63
KMP6-25P-20-5	–	■	■	–	–	–	–	■	4 / 5.1-63
KMP6-25P-20-10	–	■	■	–	–	–	–	■	4 / 5.1-63
SD-SUB-D-BU9	–	■	■	–	–	–	–	–	4 / 5.1-71
SD-SUB-D-BU25	–	■	■	–	■	–	–	–	4 / 5.1-71
IMP1-SD-25	–	–	–	–	–	■	–	–	4 / 5.1-47
IMP1-SD-40	–	–	–	–	–	■	–	–	4 / 5.1-47
IMP1-SD-72	–	–	–	–	–	■	–	–	4 / 5.1-47
IMP1-SD-25-0,75	–	–	–	–	–	■	–	–	4 / 5.1-47
IMP1-SD-40-0,75	■	–	–	–	–	■	–	–	4 / 5.1-47
IMP1-SD-72-0,75	–	–	–	–	–	■	–	–	4 / 5.1-47
IMP2-SD-26-V	–	–	–	–	■	–	–	–	4 / 5.1-49
IMP2-SD-26-EA	–	–	–	–	■	–	–	–	4 / 5.1-49
VMPA-KMS-H	–	–	–	■	–	–	–	–	4 / 5.1-44
VMPA-KMS1-8-2,5	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS1-8-5	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS1-8-10	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS1-24-2,5	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS1-24-5	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS1-24-10	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-8-2,5-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-8-5-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-8-10-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-24-2,5-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-24-5-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45
VMPA-KMS2-24-10-PUR	–	–	–	■	–	–	–	–	4 / 5.1-45

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type 04A, ISO 5599-2




Accessories		
	Brief description	→ Page
1	IMP1-SD-40-0,75 Multi-pin plug socket	4 / 5.1-47
2	KMP1-02-VI-16-X Connecting cable, IP65	4 / 5.1-51
3	Round plug from Electrivert Inc.	

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type 10 CPV




Accessories		
	Brief description	→ Page
[1]	KMP6-09P-8-... KMP6-25P-20-... KEA-1-...	Connecting cable for chain link trunking with 9-pin Sub-D plug, IP40 Connecting cable for chain link trunking with 25-pin Sub-D plug, IP40 Connecting cable, IP40
[2]	SD-SUB-D-BU9 SD-SUB-D-BU25...	Plug socket, 9-pin, IP65 Plug socket, 25-pin, IP65
[3]	KMP3-... KMP4-9P-...-PVC KMP4-9P-...-PUR KMP4-25P-...-PVC KMP4-25P-...-PUR	Connecting cable, IP65 Connecting cable, 9-pin, polyvinyl chloride, for chain link trunking, IP65 Connecting cable, 9-pin, polyurethane, for chain link trunking, IP65 Connecting cable, 25-pin, polyvinyl chloride, for chain link trunking, IP65 Connecting cable, 25-pin, polyurethane, for chain link trunking, IP65

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type 12 CPA




Accessories		
	Brief description	→ Page
1	KEA-1-25P-...	Connecting cable, IP65
	KMP3-25P-...	Connecting cable, 25-pin, for chain link trunking, IP65
	KMP4-25P-...-PVC	Connecting cable, 25-pin, for chain link trunking, IP65
	KMP4-25P-...-PUR	Connecting cable, 25-pin, for chain link trunking, IP65
	SD-SUB-D-BU25	Plug socket
2	KMP6-25P-20-...	Connecting cable for chain link trunking with 25-pin Sub-D plug

Electrical connection technology, for multi-pin plug connection

Peripherals overview




Valve terminal type 32 MPA



Accessories		
	Brief description	→ Page
1	Type 32 MPA Valve terminal	Info 227 Ventil- insel MPA
2	VMPA-KMS-H Cover plug, without connecting cable, IP65	4 / 5.1-44
3	VMPA-KMS1-... Connecting cable, IP65	4 / 5.1-45
	VMPA-KMS2-...-PUR Connecting cable, polyurethane, for chain link trunking, IP65	4 / 5.1-45

Valve terminal type 80 CPVSC1




Accessories		
	Brief description	→ Page
1	Type 80 CPVSC1 Valve terminal	4 / 3.1-1
2	KMP6-15P-12-... Connecting cable, with Sub-D plug, 15-pin, IP40	4 / 5.1-63
3	KMP6-26P-16-... Connecting cable, with Sub-D plug, 26-pin, IP40	4 / 5.1-63

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type 82 CPASC1




Accessories		
	Brief description	→ Page
1	Type 82 CPASC1 Valve terminal	4 / 3.1-27
2	KMP6-25P-... Connecting cable, with Sub-D plug, 25-pin, IP40	4 / 5.1-63

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type VIMP-03 MIDI/MAXI



Electrical connection technology, for multi-pin plug connection

FESTO

Peripherals overview

Accessories		
	Brief description	→ Page
1	KMP2-03-V-...-26	Connecting cable, straight socket
2	IMP2-SD-...-V	Multi-pin plug socket
3	KMP2-03-E-...-26	Connecting cable, straight socket
4	IMP2-SD-...-E	Multi-pin plug socket
5	SD-SUB-D-BU25	Plug socket, 25-pin, angled outlet
6	KEA-1-25P-...	Connecting cable

Accessories for valve terminals
Electrical connector systems


5.1

Electrical connection technology, for multi-pin plug connection

Peripherals overview

FESTO

Valve terminal type 02 VIMP/IIMP



Accessories		
	Brief description	→ Page
1	IIMP-02-...	Valve/sensor terminal type 02
2	VIMP02-...	Valve terminal type 02
3	IMP1-SD-...	Multi-pin plug socket (contacts 1.5 mm ²)
	IMP1-SD-...-0,75	Multi-pin plug socket (contacts 0.75 mm ²)
4	KMP1-02-...	Connecting cable with plug socket, pre-assembled

Electrical connection technology, for multi-pin plug connection


Technical data – VMPA-KMS-H

FESTO

- Plug socket for multi-pin connection (to valve terminal type 32 MPA)
- Can be fabricated with any cable lengths
- 25-pin
- Sub-D




General technical data	
Type	VMPA-KMS-H
Type of mounting	3 M3x22 screws
Mounting position	Any
Cable gland connection	M20x1.5
Operating voltage range [V DC]	24
Current-carrying capacity [A]	3
Protection class to EN 60 529	IP65 (assembled)
Material of housing	Fibreglass reinforced polyamide
Material of contacts	Gold-plated copper base alloy
Material of seal	Polyurethane
Ambient temperature [°C]	–30 ... +80

Ordering data				
	Electrical connection	Perm. cable diameter [mm]	Type	Part No.
	25-pin Sub-D socket	6 ... 12	VMPA-KMS-H	533 198

Dimensions

Download CAD data → www.festo.com/en/engineering

VMPA-KMS-H



1 Cable gland fitting M20x1.5

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – VMPA-...

- Plug socket with cable for multi-pin connection (to valve terminal type 32 MPA)
- Pre-assembled
- Cable lengths 2.5 m, 5 m or 10 m
- For 8 or 24 solenoid coils
- Sub-D
- VMPA-KMS2 as a design suitable for chain link trunking



Accessories for valve terminals
Electrical connector systems

5.1

General technical data		
Type	VMPA-...	
Type of mounting	3 M3x22 screws	
Mounting position	Any	
Operating voltage range	[V DC]	24
Current-carrying capacity	[A]	3
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Fibreglass reinforced polyamide	
Material of contacts	Gold-plated copper base alloy	
Material of seal	Polyurethane	
Ambient temperature	[°C]	−30 ... +80
Ambient temperature of flexible cable installation	[°C]	−5 ... +70

Ordering data							
	Electrical connection	Cable composition [mm ²]	Material of cable sheath	Cable diameter [mm]	Cable length [m]	Type	Part No.
	25-pin Sub-D socket	10x0.34	Polyvinyl chloride	6.9	2.5	VMPA-KMS1-8-2,5	533 195
		10x0.34	Polyvinyl chloride	6.9	5	VMPA-KMS1-8-5	533 196
		10x0.34	Polyvinyl chloride	6.9	10	VMPA-KMS1-8-10	533 197
		25x0.34	Polyvinyl chloride	11.4	2.5	VMPA-KMS1-24-2,5	533 192
		25x0.34	Polyvinyl chloride	11.4	5	VMPA-KMS1-24-5	533 193
		25x0.34	Polyvinyl chloride	11.4	10	VMPA-KMS1-24-10	533 194
	25-pin Sub-D socket	10x0.25	Polyurethane	8.3	2.5	VMPA-KMS2-8-2,5-PUR	533 504
		10x0.25	Polyurethane	8.3	5	VMPA-KMS2-8-5-PUR	533 505
		10x0.25	Polyurethane	8.3	10	VMPA-KMS2-8-10-PUR	533 506
		25x0.25	Polyurethane	11.2	2.5	VMPA-KMS2-24-2,5-PUR	533 501
		25x0.25	Polyurethane	11.2	5	VMPA-KMS2-24-5-PUR	533 502
		25x0.25	Polyurethane	11.2	10	VMPA-KMS2-24-10-PUR	533 503

Electrical connection technology, for multi-pin plug connection

Technical data – VMPA-...



Dimensions

Download CAD data → www.festo.com/en/engineering

VMPA-...

D1 Length according to type
(2.5 m, 5 m or 10 m)
L1 Diameter according to type
(6.9 mm, 8.3 mm, 11.2 mm or 11.4 m)

Wiring allocation (socket view)				
VMPA-KMS...-24-...				
	Pin	Core colour	Pin	Core colour
	1	White	14	Yellow-brown
	2	Green	15	White-grey
	3	Yellow	16	Grey-brown
	4	Grey	17	White-pink
	5	Pink	18	Pink-brown
	6	Blue	19	White-blue
	7	Red	20	Brown-blue
	8	Purple	21	White-red
	9	Grey-pink	22	Brown-red
	10	Red-blue	23	White-black
	11	White-green	24	Brown
	12	Brown-green	25	Black
	13	White-yellow		

Electrical connection technology, for multi-pin plug connection

Technical data – IMP1

FESTO


- Plug socket for multi-pin cable connection (to valve terminal type 02)
- Can be fabricated with any cable lengths
- 25-pin, 40-pin or 72-pin socket
- Wire cross section 0.75 and 1.5 mm² can be used



Accessories for valve terminals
Electrical connector systems

5.1

General technical data		
Type	IMP1-SD-...	
Type of mounting	Clamping strap	
Mounting position	Any	
Operating voltage range	[V]	300 AC
	[V]	250 DC
Current-carrying capacity	[A]	10
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Die-cast light metal alloy	
Material of contacts	Silver-plated copper base alloy	
Material of plug	Fibreglass reinforced thermoplastic moulded material	
Ambient temperature	[°C]	-40 ... +125

Ordering data							
	Electrical connection	Cable gland connection	Perm. cable diameter [mm]	Max. wire cross section [mm ²]	Product weight [g]	Type	Part No.
	25-pin plug socket	Pg21	11 ... 21	1.5	315	IMP1-SD-25	18 317
	25-pin plug socket	Pg16	7.5 ... 15	0.75	210	IMP1-SD-25-0,75	18 321
	40-pin plug socket	Pg29	18 ... 27	1.5	395	IMP1-SD-40	18 318
	40-pin plug socket	Pg21	10 ... 19	0.75	325	IMP1-SD-40-0,75	18 322
	72-pin plug socket	Pg29	18 ... 27	1.5	401	IMP1-SD-72	18 319
	72-pin plug socket	Pg29	18 ... 27	0.75	417	IMP1-SD-72-0,75	18 323
	72-pin plug socket	Sg50	22 ... 32	1.75	550	IMP1-SD-72-36	18 320

Electrical connection technology, for multi-pin plug connection

Technical data – IMP1


FESTO

Dimensions


Download CAD data → www.festo.com/en/engineering

IMP1-...

Cable assembled




Housing




	25-pin	25-pin	40-pin	72-pin
L1	79.5 mm	79.5 mm	93.5 mm	93.5 mm
B1	29.5 mm	36 mm	43 mm	43 mm
H1	54.5 mm	70.5 mm	60 mm	76 mm
Pg	16	21	21	29


Socket insert, 72-pin



Socket insert, 40-pin



Socket insert, 25-pin



Electrical connection technology, for multi-pin plug connection

Technical data – IMP2

FESTO

- Plug socket for electrical inputs or valves
- Can be fabricated with any cable lengths
- 26-pin plug socket
- Wire cross section of up to 0.75 mm²



Note


The only difference between IMP2-...-EA (variant for inputs/outputs) and IMP2-...-V (variant for valves) lies in the different reverse polarity protection.



Accessories for valve terminals
Electrical connector systems

5.1

General technical data	
Type	IMP2-SD-...
Type of mounting	Knurled ring
Mounting position	Any
Operating voltage range [V]	250 AC
Current-carrying capacity [A]	7.5
Protection class to EN 60 529	IP65 (assembled)
Material of housing	Nickel-plated copper base alloy
Material of seal	Neoprene, light and oil resistant
Material of contacts	Gold-plated copper base alloy
Ambient temperature [°C]	–40 ... +125

Ordering data							
	Electrical connection	Cable gland connection	Perm. cable diameter [mm]	Coding	Product weight [g]	Type	Part No.
	26-pin plug socket	Pg16	13.5 ... 15	Y (for inputs/outputs)	97	IMP2-SD-26-EA	18 665
	26-pin plug socket	Pg16	13.5 ... 15	N (for valves)	96	IMP2-SD-26-V	18 664

Electrical connection technology, for multi-pin plug connection

Technical data – IMP2

FESTO




Dimensions

Download CAD data → www.festo.com/en/engineering

IMP2-...

Socket insert, N-coded
(IMP2-SD-26-V)

Socket insert, Y-coded
(IMP2-SD-26-EA)



Electrical connection technology, for multi-pin plug connection

Technical data – KMP1-...



- Plug socket with cable for multi-pin connection (to valve terminal type 02)
- Pre-assembled
- Cable lengths of 5 m, 10 m or by customer request
- 25-pin, 40-pin or 72-pin socket
- Not suitable for chain link trunking




General technical data		
Type	KMP1-...	
Type of mounting	Clamping strap	
Mounting position	Any	
Operating voltage range	[V]	300 AC
	[V]	250 DC
Current-carrying capacity	[A]	4
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Die-cast light metal alloy	
Material of contacts	Silver-plated copper base alloy	
Material of cable sheath	Polyethylene	
Ambient temperature	[°C]	–30 ... +70
Ambient temperature of flexible cable installation	[°C]	+5 ... +70

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP1-...

Ordering data								
	Electrical connection	Cable composition [mm ²]	Cable diameter [mm]	Product weight		Cable length [m]	Type	Part No.
				Cable [g/m]	Total [g]			
	25-pin plug socket	25x0.75	13		1,933	5	KMP1-02-II-4-5	175 654
	25-pin plug socket	25x0.75	13		3,676	10	KMP1-02-II-4-10	175 655
	25-pin plug socket	25x0.75	13	Approx. 370	Acc. to length	Any	KMP1-02-II-4-X	158 988
	40-pin plug socket	39x0.75	17		2,995	5	KMP1-02-II-8-5	175 656
	40-pin plug socket	39x0.75	17		5,672	10	KMP1-02-II-8-10	175 657
	40-pin plug socket	39x0.75	17	Approx. 570	Acc. to length	Any	KMP1-02-II-8-X	158 989
	72-pin plug socket	50x0.75	19		3,908	5	KMP1-02-II-10-5	175 658
	72-pin plug socket	50x0.75	19		7,300	10	KMP1-02-II-10-10	175 659
	72-pin plug socket	50x0.75	19	Approx. 700	Acc. to length	Any	KMP1-02-II-10-X	158 990
	72-pin plug socket	65x0.75	22		6,000	5	KMP1-02-II-14-5	175 660
	72-pin plug socket	65x0.75	22		11,300	10	KMP1-02-II-14-10	175 661
	72-pin plug socket	65x0.75	22	Approx. 930	Acc. to length	Any	KMP1-02-II-14-X	158 991
	72-pin plug socket	80x0.75	24		5,326	5	KMP1-02-II-16-5	175 662
	72-pin plug socket	80x0.75	24		10,650	10	KMP1-02-II-16-10	175 663
	72-pin plug socket	80x0.75	24	Approx. 1160	Acc. to length	Any	KMP1-02-II-16-X	158 992
	25-pin plug socket	13x0.75	10		1,200	5	KMP1-02-VI-6-5	175 585
	25-pin plug socket	13x0.75	10		2,188	10	KMP1-02-VI-6-10	175 586
	25-pin plug socket	13x0.75	10	Approx. 180	Acc. to length	Any	KMP1-02-VI-6-X	158 984
	25-pin plug socket	25x0.75	13		1,967	5	KMP1-02-VI-12-5	175 587
	25-pin plug socket	25x0.75	13		3,667	10	KMP1-02-VI-12-10	175 588
	25-pin plug socket	25x0.75	13	Approx. 370	Acc. to length	Any	KMP1-02-VI-12-X	158 986
	40-pin plug socket	39x0.75	17		3,016	5	KMP1-02-VI-16-5	175 589
	40-pin plug socket	39x0.75	17		5,800	10	KMP1-02-VI-16-10	175 590
	40-pin plug socket	39x0.75	17	Approx. 570	Acc. to length	Any	KMP1-02-VI-16-X	158 987

Electrical connection technology, for multi-pin plug connection


Technical data – KMP1-...

FESTO

Dimensions Download CAD data → www.festo.com/en/engineering


KMP1-...

Cable assembled




- 1 Housing
- 2 Socket insert with protective earth connection
- 3 Cable gland fitting with sealing set
- 4 Label with part number, type and cable length
- 5 Cable

Housing




	25-pin	40-pin	72-pin
L1	79.5 mm	93.5 mm	93.5 mm
B1	29.5 mm	43 mm	43 mm
H1	54.5 mm	60 mm	76 mm
Pg	16	21	29


Socket insert, 72-pin



Socket insert, 40-pin



Socket insert, 25-pin



Electrical connection technology, for multi-pin plug connection

Technical data – KMP1-...



FESTO

Wiring allocation (socket view)						
KMP1-02-II-4-...						
	Pin Row A	Wire number	Pin Row B	Wire number	Pin Row C	Wire number
	1	4			1	20
	2	5	2	13	2	21
	3	6	3	14	3	22
	4	7	4	15	4	23
	5	8	5	16	5	24
	6	9	6	17	6	25
	7	10	7	18	7	1
	8	11	8	19	8	2
	9	12			9	3
KMP1-02-VI-6-...						
	Pin Row A	Wire number	Pin Row B	Wire number	Pin Row C	Wire number
	1	2			1	–
	2	3	2	11	2	–
	3	4	3	12	3	–
	4	5	4	13	4	–
	5	6	5	–	5	–
	6	7	6	–	6	–
	7	8	7	–	7	–
	8	9	8	–	8	–
	9	10			9	1
KMP1-02-VI-12-...						
	Pin Row A	Wire number	Pin Row B	Wire number	Pin Row C	Wire number
	1	2			1	18
	2	3	2	11	2	19
	3	4	3	12	3	20
	4	5	4	13	4	21
	5	6	5	14	5	22
	6	7	6	15	6	23
	7	8	7	16	7	24
	8	9	8	17	8	25
	9	10			9	1

Electrical connection technology, for multi-pin plug connection

FESTO




Technical data – KMP1-...

Wiring allocation (socket view)								
KMP1-02-II-8-...								
	Pin Row A	Wire number	Pin Row B	Wire number	Pin Row C	Wire number	Pin Row D	Wire number
	1	4	1	14	1	22	1	32
	2	5	2	15	2	23	2	33
	3	6	3	16	3	24	3	34
	4	7	4	17	4	25	4	35
	5	8	5	18	5	26	5	36
	6	9	6	19	6	27	6	37
	7	10	7	2	7	28	7	38
	8	11	8	21	8	29	8	39
	9	12	9	–	9	30	9	2
	10	13	10	1	10	31	10	3
KMP1-02-VI-16-...								
	Pin Row A	Wire number	Pin Row B	Wire number	Pin Row C	Wire number	Pin Row D	Wire number
	1	3	1	13	1	23	1	33
	2	4	2	14	2	24	2	34
	3	5	3	15	3	25	3	35
	4	6	4	16	4	26	4	36
	5	7	5	17	5	27	5	37
	6	8	6	18	6	28	6	38
	7	9	7	19	7	29	7	39
	8	10	8	20	8	30	8	–
	9	11	9	21	9	31	9	1
	10	12	10	22	10	32	10	2

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP1-...


Wiring allocation (socket view)												
KMP1-02-II-10-...												
	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number
	1	4	13	16	25	–	37	26	49	38	61	50
	2	5	14	17	26	–	38	27	50	39	62	–
	3	6	15	18	27	–	39	28	51	40	63	–
	4	7	16	19	28	–	40	29	52	41	64	–
	5	8	17	20	29	–	41	30	53	42	65	–
	6	9	18	21	30	–	42	31	54	43	66	–
	7	10	19	22	31	–	43	32	55	44	67	–
	8	11	20	23	32	–	44	33	56	45	68	–
	9	12	21	24	33	–	45	34	57	46	69	–
	10	13	22	25	34	–	46	35	58	47	70	–
	11	14	23	–	35	–	47	36	59	48	71	2
	12	15	24	–	36	1	48	37	60	49	72	3
KMP1-02-II-14-...												
	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number
	1	4	13	16	25	28	37	34	49	46	61	58
	2	5	14	17	26	29	38	35	50	47	62	59
	3	6	15	18	27	30	39	36	51	48	63	60
	4	7	16	19	28	31	40	37	52	49	64	61
	5	8	17	20	29	32	41	38	53	50	65	62
	6	9	18	21	30	33	42	39	54	51	66	63
	7	10	19	22	31	–	43	40	55	52	67	64
	8	11	20	23	32	–	44	41	56	53	68	65
	9	12	21	24	33	–	45	42	57	54	69	–
	10	13	22	25	34	–	46	43	58	55	70	–
	11	14	23	26	35	–	47	44	59	56	71	2
	12	15	24	27	36	1	48	45	60	57	72	3
KMP1-02-II-16-...												
	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number	Pin	Wire number
	1	4	13	16	25	28	37	38	49	50	61	62
	2	5	14	17	26	29	38	39	50	51	62	63
	3	6	15	18	27	30	39	40	51	52	63	64
	4	7	16	19	28	31	40	41	52	53	64	65
	5	8	17	20	29	32	41	42	53	54	65	66
	6	9	18	21	30	33	42	43	54	55	66	67
	7	10	19	22	31	34	43	44	55	56	67	68
	8	11	20	23	32	35	44	45	56	57	68	69
	9	12	21	24	33	36	45	46	57	58	69	70
	10	13	22	25	34	37	46	47	58	59	70	71
	11	14	23	26	35	38	47	48	59	60	71	2
	12	15	24	27	36	1	48	49	60	61	72	3

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP2-03-...

- Plug socket with cable for multi-pin connection of 24 inputs/outputs or 24 solenoid coils/valves
- Pre-assembled
- Cable lengths of 10 m or by customer request



Note


The only difference between KMP2-03-E-... (variant for inputs/outputs) and KMP2-03-V-... (variant for valves) lies in the different reverse polarity protection in the plug.



Accessories for valve terminals
Electrical connector systems

5.1

General technical data	
Type	KMP2-03-...
Type of mounting	Knurled ring
Mounting position	Any
Operating voltage range	[V] Max. 250 AC
	[V] Max. 300 DC
Current-carrying capacity	[A] 7.5
Cable composition	[mm ²] 26x0.75
Cable colour code	Black wires with continuous white numbering (1 ... 26)
Cable diameter	[mm] 15
Protection class to EN 60 529	IP65 (assembled)
Material of housing	Nickel-plated copper base alloy
Material of seal	Neoprene, light and oil resistant
Material of contacts	Gold-plated copper base alloy
Material of cable sheath	Polyvinyl chloride
Ambient temperature	[°C] –20 ... +80
Ambient temperature of flexible cable installation	[°C] –5 ... +80


Ordering data						
View	Electrical connection	Product weight		Cable length [m]	Type	Part No.
		Cable [g/m]	Total [g]			
	26-pin plug socket		3600	10	KMP2-03-E-10-26	175 665
	26-pin plug socket	Approx. 350	Acc. to length	Any	KMP2-03-E-X-26	18 683
	26-pin plug socket		3637	10	KMP2-03-V-10-26	175 667
	26-pin plug socket	Approx. 350	Acc. to length	Any	KMP2-03-V-X-26	18 681

Electrical connection technology, for multi-pin plug connection

Technical data – KMP2-03-...




Dimensions
KMP2-03-...




1 Cable length of 5 m or 10 m


Download CAD data → www.festo.com/en/engineering

Plug socket, N-coded
(KMP2-03-V-...)



Plug socket, Y-coded
(KMP2-03-E-...)




Wiring allocation (soldering side view)						
KMP2-03-...						
	Pin	Wire number	Pin	Wire number	Pin	Wire number
	1	1	10	10	19	19
	2	2	11	11	20	20
	3	3	12	12	21	21
	4	4	13	13	22	22
	5	5	14	14	23	23
	6	6	15	15	24	24
	7	7	16	16	25	25
	8	8	17	17	26	26
	9	9	18	18	–	–

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP3-...

- Plug socket with cable for multi-pin connection
- Pre-assembled
- Cable lengths of 5 m or 10 m
- 9-pin or 25-pin
- Sub-D



Accessories for valve terminals
Electrical connector systems

5.1

General technical data			
Type	KMP3-9P-...		KMP3-25P-...
Type of mounting	2 M3x16 screws		
Mounting position	Any		
Electrical connection	9-pin Sub-D socket		25-pin Sub-D socket
Operating voltage range	[V DC]	24	
Current-carrying capacity	[A]	3	
Cable diameter	[mm]	9.5	12
Protection class to EN 60 529	IP65 (assembled)		
Material of housing	Polyamide (Schulamid, 6GB30)		
Material of contacts	Gold-plated copper base alloy		
Material of cable sheath	Polyvinyl chloride		
Material of seal	Nitrile rubber (NBR)		
Ambient temperature	[°C]	–30 ... +80	
Ambient temperature of flexible cable installation	[°C]	–5 ... +80	

Ordering data						
	Cable composition [mm ²]	Product weight		Cable length [m]	Type	Part No.
		Cable [g/m]	Total [g]			
	10x0.34		425	5	KMP3-9P-08-5	18 698
	10x0.34		814	10	KMP3-9P-08-10	18 579
	10x0.34	Approx. 117	Acc. to length	Any	KMP3-9P-08-X	18 697
	18x0.34		672	5	KMP3-25P-16-5	18 624
	18x0.34		1,303	10	KMP3-25P-16-10	18 625
	18x0.34	Approx. 180	Acc. to length	Any	KMP3-25P-16-X	18 699
	24x0.25	Approx. 178	Acc. to length	Any	KMP3-25P-22-X	163 971

Electrical connection technology, for multi-pin plug connection

FESTO



Technical data – KMP3-...

Dimensions

KMP3-...

Download CAD data → www.festo.com/en/engineering

Type	1	B1	B2	D1	H1	H2	H3	L1	L2	L3
KMP3-09P-...	9-pin Sub-D socket	30	23	8.3	43	37	35	50	43	Length according to type (5 m, 10 m or any)
KMP3-25P-...	25-pin Sub-D socket	30	23	11.2	47	37	35	70	63	


Wiring allocation (socket view)								
KMP3-9P-...								
	Pin	Core colour	Pin	Core colour				
	1	White	6	Blue				
	2	Green	7	Red				
	3	Yellow	8	Purple				
	4	Grey	9	Black				
	5	Pink	–	Brown				
	KMP3-25P-16-...		KMP3-25P-22-...					
	Pin	Core colour	Pin	Core colour	Pin	Core colour	Pin	Core colour
	1	White	14	Yellow-brown	1	White	14	Yellow-brown
	2	Green	15	White-grey	2	Green	15	White-grey
	3	Yellow	16	Grey-brown	3	Yellow	16	Grey-brown
	4	Grey	17	–	4	Grey	17	White-pink
	5	Pink	18	–	5	Pink	18	Pink-brown
	6	Blue	19	–	6	Blue	19	White-blue
	7	Red	20	–	7	Red	20	Brown-blue
	8	Purple	21	–	8	Purple	21	White-red
	9	Grey-pink	22	–	9	Grey-pink	22	Brown-red
	10	Red-blue	23	–	10	Red-blue	23	–
	11	White-green	24	Brown	11	White-green	24	Brown
12	Brown-green	25	Black	12	Brown-green	25	Black	
13	White-yellow	–	–	13	White-yellow	–	–	

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP4-...

- Plug socket with cable for multi-pin connection
- Pre-assembled
- Cable lengths of 5 m or 10 m
- 9-pin or 25-pin
- Sub-D
- Suitable for chain link trunking



Accessories for valve terminals
Electrical connector systems

5.1

General technical data		
Type	KMP4-9P-...	KMP4-25P-...
Type of mounting	2 M3x16 screws	
Mounting position	Any	
Electrical connection	9-pin Sub-D socket	25-pin Sub-D socket
Operating voltage range [V DC]	24	
Current-carrying capacity [A]	3	
Cable composition [mm ²]	10x0.25	25x0.25
Cable diameter [mm]	8.3	11.2
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Polyamide (Schulamid, 6GB30)	
Material of contacts	Gold-plated copper base alloy	
Material of seal	Nitrile rubber (NBR)	
Ambient temperature [°C]	-40 ... +70	
Ambient temperature of flexible cable installation [°C]	-5 ... +70	

Ordering data					
	Material of cable sheath	Product weight [g]	Cable length [m]	Type	Part No.
	Polyurethane	330	5	KMP4-9P-5-PUR	193 014
	Polyvinyl chloride	426	5	KMP4-9P-5-PVC	193 012
	Polyurethane	675	10	KMP4-9P-10-PUR	193 015
	Polyvinyl chloride	792	10	KMP4-9P-10-PVC	193 013
	Polyurethane	732	5	KMP4-25P-5-PUR	193 018
	Polyvinyl chloride	854	5	KMP4-25P-5-PVC	193 016
	Polyurethane	1411	10	KMP4-25P-10-PUR	193 019
	Polyvinyl chloride	1617	10	KMP4-25P-10-PVC	193 017

Electrical connection technology, for multi-pin plug connection

Technical data – KMP4-...



Dimensions

Download CAD data → www.festo.com/en/engineering

KMP4-...

Type	1	B1	B2	D1	H1	H2	H3	L1	L2	L3
KMP4-09P-...	9-pin Sub-D socket	30	23	8.3	43	37	35	50	43	Length according to type (5 m or 10 m)
KMP4-25P-...	25-pin Sub-D socket	30	23	11.2	47	37	35	70	63	

Wiring allocation (socket view)

KMP4-25P-...

Pin	Core colour	Pin	Core colour
1	White	14	Yellow-brown
2	Green	15	White-grey
3	Yellow	16	Grey-brown
4	Grey	17	White-pink
5	Pink	18	Pink-brown
6	Blue	19	White-blue
7	Red	20	Brown-blue
8	Purple	21	White-red
9	Grey-pink	22	Brown-red
10	Red-blue	23	White-black
11	White-green	24	Brown
12	Brown-green	25	Black
13	White-yellow		

KMP4-9P-...

Pin	Core colour	Pin	Core colour
1	White	6	Blue
2	Green	7	Red
3	Yellow	8	Purple
4	Grey	9	Black
5	Pink	–	Brown

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP6-...

- Plug socket with cable for multi-pin connection
- Pre-assembled
- Cable lengths 2.5 m, 5 m or 10 m
- 9-pin, 15-pin, 25-pin or 26-pin
- Sub-D
- Suitable for chain link trunking



Accessories for valve terminals
Electrical connector systems

5.1

General technical data					
Type	KMP6-9P-...	KMP6-15P-...	KMP6-25P-12-...	KMP6-25P-20-...	KMP6-26P-...
Type of mounting	2 M4x6.3 screws				
Mounting position	Any				
Operating voltage range	[V]	24 DC			
Current-carrying capacity	[A]	2.8			
Cable diameter	[mm]	7.6	8.5	8.5	10.3
Protection class to EN 60 529	IP40 (assembled)				
Material of housing	Polyester, fibreglass reinforced				
Material of contacts	Gold-plated copper base alloy				
Material of cable sheath	Polyvinyl chloride				
Ambient temperature	[°C]	-30 ... +80			
Ambient temperature of flexible cable installation	[°C]	-5 ... +80			


Ordering data						
	Electrical connection	Cable composition [mm ²]	Product weight [g]	Cable length [m]	Type	Part No.
	9-pin Sub-D socket	8x0.34 + 1x0.5	248	2.5	KMP6-09P-08-2,5	531 184
		8x0.34 + 1x0.5	454	5	KMP6-09P-08-5	531 185
		8x0.34 + 1x0.5	864	10	KMP6-09P-08-10	531 186
	15-pin Sub-D socket	15x0.34	293	2.5	KMP6-15P-12-2,5	527 543
		15x0.34	585	5	KMP6-15P-12-5	527 544
		15x0.34	1,134	10	KMP6-15P-12-10	527 545
	25-pin Sub-D socket	15x0.34	329	2.5	KMP6-25P-12-2,5	530 049
		15x0.34	590	5	KMP6-25P-12-5	530 050
		15x0.34	1140	10	KMP6-25P-12-10	530 051
	25-pin Sub-D socket	20x0.25 + 5x0.34	432	2.5	KMP6-25P-20-2,5	530 046
		20x0.25 + 5x0.34	814	5	KMP6-25P-20-5	530 047
		20x0.25 + 5x0.34	1600	10	KMP6-25P-20-10	530 048
	26-pin Sub-D socket	20x0.25	Approx. 280	2.5	KMP6-26P-16-2,5	527 546
		20x0.25	Approx. 570	5	KMP6-26P-16-5	527 547
		20x0.25	1145	10	KMP6-26P-16-10	527 548

Electrical connection technology, for multi-pin plug connection



Technical data – KMP6-...

Dimensions Download CAD data → www.festo.com/en/engineering





Type	1	B1	D1	H1	L1	L2
KMP6-09P-...	9-pin Sub-D socket	16	7.6	31.2	34.5	Length according to type (2.5 m, 5 m or 10 m)
KMP6-15P-...	15-pin Sub-D socket	16	8.5	40	34.5	
KMP6-25P-12-...	25-pin Sub-D socket	16	8.5	53.4	37.7	
KMP6-25P-20-...	25-pin Sub-D socket	16	10.3	53.4	37.7	
KMP6-26P-...	26-pin Sub-D socket	16	8.6	40	34.5	

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMP6-...



Wiring allocation (socket view)				
KMP6-9P-...				
	Pin	Core colour	Pin	Core colour
	1	White	6	Pink
	2	Brown	7	Blue
	3	Green	8	Red
	4	Yellow	9	Black ¹⁾
	5	Grey		
KMP6-15P-...				
	Pin	Core colour	Pin	Core colour
	1	White	9	Black
	2	Brown	10	Purple
	3	Green	11	Grey-pink
	4	Yellow	12	Red-blue
	5	Grey	13	White-green
	6	Pink	14	Brown-green
	7	Blue	15	White-yellow
	8	Red		

1) Wire cross section 0.5 mm²

Electrical connection technology, for multi-pin plug connection

Technical data – KMP6-...

FESTO

Wiring allocation (socket view)								
	KMP6-25P-12-...				KMP6-25P-20-...			
	Pin	Core colour	Pin	Core colour	Pin	Core colour	Pin	Core colour
	1	White	14	–	1	White	14	Brown-green
	2	Brown	15	–	2	Brown	15	White-yellow
	3	Green	16	–	3	Green	16	Yellow-brown
	4	Yellow	17	–	4	Yellow	17	White-grey
	5	Grey	18	–	5	Grey	18	Grey-brown
	6	Pink	19	–	6	Pink	19	White-pink
	7	Blue	20	–	7	Blue	20	Pink-brown
	8	Red	21	–	8	Red	21	White-blue ¹⁾
	9	Black	22	–	9	Black	22	Brown-blue ¹⁾
	10	Purple	23	White-green	10	Purple	23	White-red ¹⁾
	11	Grey-pink	24	Brown-green	11	Grey-pink	24	Brown-red ¹⁾
	12	Red-blue	25	White-yellow	12	Red-blue	25	White-black ¹⁾
	13	–			13	White-green		
KMP6-26P-...								
	Pin	Core colour	Pin	Core colour				
	1	White	14	Brown-green				
	2	Brown	15	White-yellow				
	3	Green	16	Yellow-brown				
	4	Yellow	17	–				
	5	Grey	18	–				
	6	Pink	19	–				
	7	Blue	20	–				
	8	Red	21	–				
	9	Black	22	–				
	10	Purple	23	White-grey				
	11	Grey-pink	24	Grey-brown				
	12	Red-blue	25	White-pink				
	13	White-green	26	Pink-brown				


1) Wire cross section 0.34 mm²

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KEA-1-25P-...

- Plug socket with cable for multi-pin connection
- Pre-assembled
- Cable lengths of 5 m, 10 m or by customer request
- 25-pin
- Sub-D



Accessories for valve terminals
Electrical connector systems

5.1

General technical data		
Type	KEA-1-25P-...	
Type of mounting	2 M3x16 screws	
Mounting position	Any	
Electrical connection	25-pin Sub-D socket	
Operating voltage range	[V]	250 AC
	[V]	250 DC
Current-carrying capacity	[A]	4
Cable diameter	[mm]	12
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Polyamide (Schulamid, 6GB30)	
Material of contacts	Gold-plated copper base alloy	
Material of cable sheath	Polyvinyl chloride	
Ambient temperature	[°C]	–20 ... +80
Ambient temperature of flexible cable installation	[°C]	–5 ... +70


Ordering data						
	Cable composition [mm ²]	Product weight		Cable length [m]	Type	Part No.
		Cable [g/m]	Total [g]			
	25x0.34		1092	5	KEA-1-25P-5	177 413
	25x0.34		2040	10	KEA-1-25P-10	177 414
	25x0.34	Approx. 190	Acc. to length	Any	KEA-1-25P-X	177 415

Electrical connection technology, for multi-pin plug connection

Technical data – KEA-1-25P-...



Dimensions Download CAD data → www.festo.com/en/engineering



Type	1	B1	B2	D1	H1	H2	H3	L1	L2	L
KEA-1-25P-...	25-pin Sub-D socket	30	23	12	47	37	35	70	63	Length according to type (5 m or 10 m)

Wiring allocation (socket view)

KEA-1-25P-...	Pin	Core colour
	1	White
	2	Green
	3	Yellow
	4	Grey
	5	Pink
	6	Blue
	7	Red
	8	Purple
	9	Grey-pink
	10	Red-blue
	11	White-green
	12	Brown-green
	13	White-yellow
	14	Yellow-brown
	15	White-grey
	16	Grey-brown
	17	White-pink
	18	Pink-brown
	19	White-blue
	20	Brown-blue
	21	White-red
	22	Brown-red
	23	White-black
	24	Brown
	25	Black

Electrical connection technology, for multi-pin plug connection

FESTO

Technical data – KMPV-...


- Plug socket with cable for multi-pin connection (to multi-pin plug distributor MPV-...)
- Pre-assembled
- Cable lengths of 5 m or 10 m
- 15-pin
- Sub-D



Accessories for valve terminals
Electrical connector systems

5.1

General technical data	
Type	KMPV-...
Type of mounting	2 M4x16 screws
Mounting position	Any
Electrical connection	15-pin Sub-D socket
Operating voltage range [V]	30 DC
Current-carrying capacity [A]	2.8
Cable diameter [mm]	8.2
Protection class to EN 60 529	IP65 (assembled)
Material of housing	Polyester, fibreglass reinforced
Material of contacts	Gold-plated copper base alloy
Material of cable sheath	Polyurethane
Ambient temperature [°C]	–20 ... +80

Ordering data					
	Cable composition [mm ²]	Product weight [g]	Cable length [m]	Type	Part No.
	15x0.25	300	5	KMPV-SUB-D-15-5	177 673
	15x0.25	400	10	KMPV-SUB-D-15-10	177 674

Electrical connection technology, for multi-pin plug connection

Technical data – KMPV-...

FESTO

Dimensions

KMPV-...

- 1 Sub-D plug, 15-pin
- 2 Cable gland fitting PG9
- 3 Cable length of 5 m or 10 m

Download CAD data → www.festo.com/en/engineering

Wiring allocation (socket view)

KMPV-...

Pin	Core colour	Pin	Core colour
1	White	9	Black
2	Brown	10	Purple
3	Green	11	Grey-pink
4	Yellow	12	Red-blue
5	Grey	13	White-green
6	Pink	14	Brown-green
7	Blue	15	White-yellow
8	Red		

Electrical connection technology, for multi-pin plug connection

Technical data – SD-SUB-BU...

FESTO


- Plug socket for multi-pin connection
- Can be fabricated with any cable lengths
- 9-pin or 25-pin
- Sub-D



Accessories for valve terminals
Electrical connector systems

5.1

General technical data		
Type	SD-SUB-BU...	
Type of mounting	2 M3x16 screws	
Mounting position	Any	
Operating voltage range	[V]	250 AC
	[V]	250 DC
Current-carrying capacity	[A]	5
Protection class to EN 60 529	IP65 (assembled)	
Material of housing	Polyamide (Schulamid, 6GB30)	
Material of contacts	Gold-plated copper base alloy	
Material of seal	Nitrile rubber (NBR)	
Ambient temperature	[°C]	–55 ... +125

Ordering data						
	Electrical connection	Cable gland connection	Perm. cable diameter [mm]	Product weight [g]	Type	Part No.
	9-pin Sub-D socket	PG9	6 ... 9	38	SD-SUB-D-BU9	18 708
	25-pin Sub-D socket	PG11	7 ... 12	53	SD-SUB-D-BU25	18 709

Electrical connection technology, for multi-pin plug connection


Technical data – SD-SUB-BU-...

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering

SD-SUB-BU-...



Type	1	B1	B2	H1	H2	H3	L1	L2
SD-SUB-D-BU9	9-pin Sub-D socket	30	23	43	37	35	50	43
SD-SUB-D-BU25	25-pin Sub-D socket	30	23	47	37	35	70	63