


Spojni vod NEBB-M12W5-P-5-LE4

Broj artikla: 8066683

FESTO



Tehnički podaci

| Svojstvo | Vrednost |
|--|--|
| Odgovara standardu | Core colours and connection numbers to EN 60947-5-2 EN 61076-2-101 |
| Cable identification | With inscription label holder |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | okruglo |
| Electrical connection 1, connection type | Utičnica |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 5 |
| Electrical connection 1, occupied pins/wires | 4 |
| Electrical connection 1, type of mounting | Screw lock with A/F13 |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | Kabl |
| Electrical connection 2, connection technology | otvoreni kraj |
| Electrical connection 2, number of pins/wires | 4 |
| Electrical connection 2, occupied pins/wires | 4 |
| Područje pogonskog napona DC | 0 ... 250 V |
| Područje pogonskog napona AC | 0 ... 250 V |
| Strujna opteretivost kod 40°C | 4 A |
| Čvrstoća na udarno naprezanje | 2,5 kV |
| Dužina kabla | 5 m |
| Svojstvo kabla | Za statičke namene |
| Uslovi ispitivanja kabla | Uslovi ispitivanja na zahtev |
| Bending radius, fixed cable installation | ≥ 14 mm |
| Prečnik kabla | 4,5 mm |
| Struktura kabla | 4x0,25 |
| Nazivni presek provodnika | 0,25 mm ² |
| Krajevi žica | Sheath removed Cut off bluntly |
| Mehanička zaštita | IP65 IP68 IP69K |
| Note on degree of protection | u montiranom stanju |
| Temperatura okoline | -25 ... 70 °C |
| CE znak (vidi izjavu o usklađenosti) | prema EU-niski napon-smernica in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | ISO class 4 |
| Materijal - napomena | RoHS komformnost |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 2 - Moderate corrosion stress |
| Material cable sheath | PVC |
| Boja izolacije | sivo |
| Material housing | TPE-U(PU) |

| Svojstvo | Vrednost |
|-----------------------------|--------------------------|
| Boja kućišta | crno |
| Material screw-type lock | Nickel-plated brass |
| Material seals | NBR |
| Material electrical contact | Gold-plated copper alloy |
| Material insulation | PVC |