


Senzor interface CASB-MT-D3-R7

Broj artikla: 8071781

FESTO



Tehnički podaci

Svojstvo	Vrednost
Uputstva za korišćenje	The product is suitable for industrial purposes only. Measures for interference suppression may be required in residential areas.
Funkcija dijagnostike	Prikaz preko LED-a
Položaj ugradnje	proizvoljno
Zaštita od zamene polova	Da
Output frequency	TTL signal: max. 7200 Hz HTL signal: max. 450 Hz
Područje pogonskog napona DC	20,4 ... 30 V
Trajanje uključenosti	100 %
Maks. električna primljena snaga	6 W
Nazivni pogonski napon DC	24 V
Preostala talasnost	5 %
Potrošnja struje kod neopterećenih izlaza	50 mA
Strujna opteretivost po izlazu	50 mA
Dozvola	RCM Mark
KC mark	KC-EMV
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Otpornost na vibracije	Ispitivanje transporta sa stepenom težine 2 prema FN 942017-4 i EN 60068-2-6
Udarna čvrstoća	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Klasa korozione otpornosti KBK	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Zaštita od direktnog i indirektnog dodira	Protective extra-low voltage with safe disconnection (PELV)
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-5 ... 50 °C
Težina proizvoda	350 g
Signalno područje	HTL signal: high: min. 18 V; low: max. 2 V TTL signal: high: min. 2.4 v; low: max. 0.4 V
Electrical connection, output, function	TTL
Electrical connection, output, connection type	Utikači
Electrical connection, output, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection, output, number of pins/wires	8
Electrical connection for output 2, function	HTL
Electrical connection for output 2, connection type	Utikači
Electrical connection for output 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for output 2, number of pins/wires	5
Electrical connection for valve, connection type	Utikači
Electrical connection for valve, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for valve, number of pins/wires	8
Electrical connection for sensor, connection type	2 x utičnica
Electrical connection for sensor, connection technology	M12x1, A-coded in accordance with EN 61076-2-101

Svojstvo	Vrednost
Electrical connection for sensor, number of pins/wires	8
Vrsta pričvrščenja	With through-hole for M4 screw
Materijal - napomena	RoHS komfornost
Material seals	FPM NBR
Material housing	Anodised wrought aluminium alloy