


Spojni vod NEBC-M12W8-E-15-N-M12G8

Broj artikla: 8080789

FESTO



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-101
Dozvola	c UL us - Listed (OL)
Mesto izdavanja sertifikata	UL E474609
Cable identification	Without inscription label holder
Težina proizvoda	736 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Electrical connection 2, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	0,8 kV
Shielding	ne
Dužina kabla	15 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 30 mm
Bending radius, flexible cable installation	≥ 30 mm
Prečnik kabla	6 mm
Odstupanje prečnika kabla	± 0,2 mm
Struktura kabla	8x0,25
Nazivni presek provodnika	0,25 mm ²
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 90 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress

Svojstvo	Vrednost
Material cable sheath	TPE-U(PUR)
Boja izolacije	Silver-grey
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Mesing
Material insulation	PP