

Cylinder, Type DSNU - Basic Version

Accessory Dimensions

Rod clevis type SG-...

SG-...



Includes:

- 1 rod clevis
- 1 hinged spring pin
- 1 hex nut

The rod clevis is fitted to the piston rod thread and permits swivelling movement of the cylinder in one plane.

Materials:

- Rod clevis: Galvanized steel
- Nut: Galvanized steel



Type	Size [in.]	B2	B3	CE ±0.4	CK ∅ H9	CM
SG-6-32	5/16, 3/8	0.43	0.31	0.62	0.16	0.16
SG-10-32	1/2, 5/8	0.43	0.31	0.62	0.16	0.16
SG-5/16-24	3/4	0.85	0.63	1.26	0.31	0.31
SG-3/8-24	1	1.02	0.79	1.57	0.39	0.39

Type	Size [in.]	CV	D1 ∅	KK	LE ±0.5	Weight [lb]
SG-6-32	5/16, 3/8	0.20	0.31	6-32 UNC-2B	0.31	0.022
SG-10-32	1/2, 5/8	0.20	0.31	10-32 UNF-2B	0.31	0.022
SG-5/16-24	3/4	0.39	0.55	5/16-24 UNF-2B	0.63	0.110
SG-3/8-24	1	0.47	0.71	3/8-24 UNF-2B	0.79	0.220

Rod eye type SGS-...

SGS-...


Includes:

- 1 rod eye
- 1 hex nut

The rod eyes are maintenance-free due to the combination of steel/PTFE-bronze material in the swivel bearing.

Materials:

- Rod eye: Galvanized steel
- Bearing cup: SnBz8 (PTFE-bronze material)
- Nut: Galvanized steel



Type	Size [in.]	AV	CE	CN ∅ H7	D1 ∅	EF
SGS-6-32	5/16, 3/8	0.39	1.06	0.20	0.43	0.35
SGS-10-32	1/2, 5/8	0.39	1.06	0.20	0.43	0.35
SGS-5/16-24	3/4	0.65	1.42	0.31	0.63	0.47
SGS-3/8-24	1	0.79	1.69	0.39	0.75	0.55

Type	Size [in.]	EN	EU	KK	Z	≈ 2 [in.]	Weight [lb]
SGS-6-32	5/16, 3/8	0.31	0.24	6-32 UNC-2B	13	0.354	0.037
SGS-10-32	1/2, 5/8	0.31	0.24	10-32 UNF-2B	13	0.433	0.055
SGS-5/16-24	3/4	0.47	0.35	5/16-24 UNF-2B	13	0.551	0.099
SGS-3/8-24	1	0.55	0.41	3/8-24 UNF-2B	13	0.669	0.154