
FESTO



Accessories, MS series Product range overview



Туре		Accessories for size			
		MS4	MS6	MS9	MS12
Mounting attachment	s for individual dev	rices	•		•
Mounting bracket MS-WB	\$	■ → 4	■ → 4	-	-
Mounting bracket MS-WBM		■ → 4	-	-	-
Mounting bracket MS-WR	8	■ → 5	■ → 5	-	-
Hex nut MS-WRS		■ → 5	■ → 5	-	-
Mounting attachments	s for individual dev	vices/combinations			
Mounting bracket MS-WP	Da	■ → 7	■ → 7	■ → 13	■ → 15
Mounting bracket MS-WPB	57	■ → 8	■ → 8	■ → 13	-
Mounting bracket MS-WPM	j	■ → 9	■ → 9	■ → 14	-
Mounting bracket MS-WPE	Tron	■ → 10	■ → 10	-	-
Connectors	•				
Module connector MS-MV		■ → 10	■ → 10	■ → 14	■ → 15
Module connector MS-MVM	17	■ → 10	■ → 10	-	-
Module connector MS-RMV		→ 16	■ → 16	■ → 19	-
Module connector MS-AMV		→ 16	■ → 16	-	-
Module connector MS-ARMV		-	■ → 19	→ 19, 21	■ → 21

Accessories, MS series Product range overview



Туре		Accessories for size			
		MS4	MS6	MS9	MS12
Adapters for mounting o	on profiles				
Power supply modules MS-E-IPM-40-80		■ → 24	■ → 24	-	-
Power supply modules MS-E-IPM-80-80		■ → 24	■ → 24	-	-
Branching modules MS-A-IPM-80		■ → 24	■ → 24	-	-
Branching modules MS-A-RMV-IPM-80		■ → 24	■ → 24	-	-
Sealing rings MS-NNR	0	■ → 24	→ 24	-	-
Cover plates	· ·	1	<u>'</u>		
Connecting plate MS-AG	800	■ → 30	■ → 30	→ 32	■ → 33
Cover plate MS-END		■ → 31	■ → 31	-	-
Mounting plate MS-AEND	0	■ → 31	■ → 31	-	-
Security components		1		·	
Padlock LRVS-D	3	■ → 34	→ 34	→ 34	■ → 34

FESTO


Mounting bracket MS4/6-WB

(order code: WB)

• For wall mounting

Material: Steel





Dimensions ar	nd ordering	data									
Size	B1	B2	В3	B4	L1	L2	L3	L4	Weight [g]	Part No.	Туре
MS4	56.2	41.2	4	44.2	104.6	46.6	5.6	46.5	46	532185	MS4-WB
MS6	79.4	61.9	4.5	55	157.6	71	6.6	71	121	532196	MS6-WB


Mounting bracket MS4-WBM

(order code: WBM)

• For wall mounting

Material: Steel





Dimensions ar	nd ordering d	ata								
Size	B1	B2	В3	В4	L1	L2	L3	Weight [g]	Part No.	Туре
MS4	66.5	44	10	44	41.3	35	6.5	48	526062	MS4-WBM

FESTO

Mounting bracket MS4/6-WR

(order code: WR)

- For wall mounting
- For filter regulator, pressure regulator


Material:

Steel



The hex nut for attaching components to this bracket must be ordered separately.





Dimensions ar	nd ordering d	ata								
Size	B1	B2	В3	B4	L1	L2		Weight [g]	Part No.	Туре
MS4	68	44	8	41	52	44	7	49	526064	MS4-WR
MS6	70	42	8.2	40	67	57	7.1	90	526075	MS6-WR


Hex nut MS4/6-WRS

- For front panel mounting
- For attaching the mounting bracket MS...-WR

Material:

Aluminium





Dimensions a	nd ordering data				
Size	L1	= © 1	Weight	Part No.	Туре
			[g]		
MS4	6	36	6.9	532187	MS4-WRS
MS6	7	55	20.9	532188	MS6-WRS

FESTO

Mounting attachments MS4/MS6

Mounting bracket MS4/6-WP...


Clearances for mounting service unit combinations

Size MS4

- 1 service unit with MS4-WP...: 40.2 mm (20.1 mm)¹⁾
- 2 service units with MS4-WP...: 80.4 mm (40.2 mm)¹⁾

Size MS6

- 1 service unit with
 - MS6-WP/WPB/WPE: 62 mm (31 mm)¹⁾
 - MS6-WPM-D: 69 mm (38 mm)¹⁾
- 2 service units with
 - MS6-WP/WPB/WPE: 124 mm (62 mm)¹⁾
 - MS6-WPM-2D: 138 mm (76 mm)¹⁾




1) With distributor block MS-FRM-FRZ

Mounting dimensions



The distributor block MS4/6-FRM-FRZ has a dimension of half grid width.



	2 service with dimer	grid	with dimens 1 dist blo	ice unit grid ion and ributor ock RM-FRZ	2 distr blo MS-FR	cks			with	e unit grid nsion	block A	ibutor MS-FRM- RZ				
Туре	B1	B2	B1	B2	B1	B2	В3	B4	B5 ¹⁾	В6	B5 ¹⁾	В6	L1	L2	L3	L4
MS4-WP				4				44					106	46.5		46.7
MS4-WPB/WPE	95.4	80.4	75.3	60.3	55.2	40.2	4	66	41.9	40.2	21.8	20.1			5.6	
MS4-WPMD								44					92.8	34.8		45.2
MS6-WP	141	124	110	93	79	62	4.5	54.1	64.5	62	33.5	31	158	71		71
MS6-WPB/WPE	141	124	110	93	79	02	4.5	90.5	04.5	02	22.5	51	138	/1	6.6	/1
MS6-WPMD	168	138	137	107	106	76	17.5	54.1	68	69	37	38	98.6	41.3		41.3

¹⁾ With accessory cover plate MS-END

FESTO

Mounting bracket MS4/6-WP


(order code: WP)

- For connecting modules via wall mounting
- In combination with a connecting plate MS4/6-AG... for individual wall mounting
- In combination with mounting plate MS4/6-AEND for individual wall mounting via direct thread
- For pressure regulator LRB with angled outlet block B... at rear

Material: Die-cast aluminium

Note on materials: Free of copper and PTFE





Dimensions	and orderii	ng data											
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No.	Туре
MS4	55.2	40.2	4	44	83.4	106	46.5	5.6	46.7	2	39	532184	MS4-WP
MS6	79	62	4.5	54.1	115	158	71	6.6	71	2	76	532195	MS6-WP
For use in ex	plosive are	as in zone	es 2 and 2	22									
MS4	55.2	40.2	4	44	83.4	106	46.5	5.6	46.7	2	39	541554	MS4-WP-EX
MS6	79	62	4.5	54.1	115	158	71	6.6	71	2	76	541544	MS6-WP-EX

 $^{1) \}quad \hbox{Corrosion resistance class 2 as per Festo standard 940 070}\\$ Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

FESTO

Mounting bracket MS4/6-WPB

(order code: WPB)


- For connecting modules via wall mounting
- In combination with a connecting plate MS4/6-AG... for individual wall mounting
- In combination with mounting plate MS4/6-AEND for individual wall mounting via direct thread
- Provides large wall gap for pressure regulator

Material:

Die-cast aluminium

Note on materials: Free of copper and PTFE





Dimensions a	ınd orderii	ng data											
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No.	Туре
MS4	55.2	40.2	4	66	83.4	106	46.5	5.6	46.7	2	55	526063	MS4-WPB
MS6	79	62	4.5	90.5	115	158	71	6.6	71	2	115	526074	MS6-WPB
For use in exp	losive are	as in zone	es 2 and 2	22									
MS4	55.2	40.2	4	66	83.4	106	46.5	5.6	46.7	2	55	541552	MS4-WPB-EX
MS6	79	62	4.5	90.5	115	158	71	6.6	71	2	115	541542	MS6-WPB-EX

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

FESTO

Mounting bracket MS4/6-WPM

(order code: WPM)


- For connecting modules via wall mounting
- In combination with a connecting plate MS4/6-AG... for individual wall mounting
- Speedy attachment and detachment
- For installation of modules with regulating knob pointing downwards

The distance piece D or 2D (designated in the type code) is included in the scope of delivery and ensures the correct clearance


Material:

Die-cast aluminium









Dimensions ar	nd orderin	g data											
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4	Clearance	Weight [g]	Part No.	Туре
MS4	55.2	40.2	4	44	83.4	92.8	34.8	5.6	45.2	40.2	45	526060	MS4-WPM-D
	95.4	80.4	4	44	123.4	92.0	34.6	5.6	45.2	80.4	55	526061	MS4-WPM-2D
MS6	99	69	17.5	54.1	129	98.6	41.3	6.6	41.3	69	144	526073	MS6-WPM-D
	168	138	17.5	J4.1	198	70.0	41.7	0.0	41.7	138	154	532186	MS6-WPM-2D



Mounting attachments MS4/MS6


FESTO

Mounting bracket MS4/6-WPE

• Inexpensive alternative to mounting bracket MS4/6-WPB

Note on materials: RoHS-compliant





Dimensions ar	nd ordering	g data											
Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	CRC ¹⁾	Part No.	Туре	
MS4	55.2	40.2	4.2	66	83.4	106	46.6	5.7	46.6	2	558869	MS4-WPE	-⊙- New
MS6	79	62	4.3	90.5	115	158	71	6.5	71	2	1025936	MS6-WPE	-⊙- New

1) Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Module connector MS4/6-MV

For connecting modules

Material:

Stainless steel/polyacetal

Note on materials:

Free of copper and PTFE $\,$



Ordering data				
Size	CRC ¹⁾	Weight	Part No.	Туре
		[g]		
MS4	2	36	532798	MS4-MV
MS6	2	54	532799	MS6-MV
For use in explosive areas in zones 2 and 22				
MS4	2	36	541553	MS4-MV-EX
MS6	2	54	541543	MS6-MV-EX

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

FESTO

Module connector MS4/6-MVM

• For installation of modules with regulating knob pointing downwards

Material:

Die-cast aluminium





Ordering data		
Size	Part No.	Туре
MS4	532800	MS4-MVM
MS6	532801	MS6-MVM




FESTO

Mounting bracket MS9-WP...


Clearances for mounting service unit combinations

1 service unit: 90 mm

2 service units: 180 mm



Mounting dimensions



Туре	B1	B2	В3	В4	B5	В6	L1	L2	L3	L4
MS9-WP				75						
MS9-WPB	205	180	8.5	99	97	90	162	72.75	8.3	72.25
MS9-WPM				90.5	1					



Mounting attachments MS9

FESTO

Mounting bracket MS9-WP

(order code: WP)

• For connecting modules via wall mounting

 In combination with a connecting plate MS9-AG... for individual wall mounting


Material:

Module connector, bracket, hollow bolt: Die-cast aluminium Screws: Steel Seals: Nitrile rubber RoHS-compliant Free of copper and PTFE

Temperature of medium:

−10 ... +60 °C





Dimensions ar	Dimensions and ordering data												
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4		Weight [g]	Part No.	Туре
MS9	115	90	8.5	25	75	162	81.25	8.3	145	2	180	552947	MS9-WP

1) Corrosion resistance class 2 as per Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Mounting bracket MS9-WPB

(order code: WPB)

- For connecting modules via wall mounting
- In combination with a connecting plate MS9-AG... for individual wall mounting
- Same wall gap for combination with MS12 series using the mounting bracket MS12-WP


Material:

Module connector, bracket, hollow bolt: Die-cast aluminium

Screws: Steel Seals: Nitrile rubber RoHS-compliant Free of copper and PTFE

Temperature of medium:





Dimensions a	Dimensions and ordering data												
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No.	Туре
MS9	115	90	8.5	25	99	162	81.25	8.3	145	2	210	552949	MS9-WPB

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



Mounting attachments MS9

FESTO

Mounting bracket MS9-WPM

(order code: WPM)

- For connecting modules via wall mounting
- In combination with a connecting plate MS9-AG... for individual wall mounting

• Speedy attachment and detachment

• Same wall gap for combination with MS6 series using the mounting bracket MS6-WPB

The distance pieces included in the scope of delivery ensure the correct clearance.

Material:


Module connector, bracket, hollow

bolt: Die-cast aluminium Screws: Steel Seals: Nitrile rubber RoHS-compliant Free of copper and PTFE

Temperature of medium:

−10 ... +60 °C





Dimensions and ordering data													
Size	B1	B2	В3	B4	B5	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No.	Туре
MS9	115	90	8.5	25	90.5	162	81.25	8.3	145	2	220	552948	MS9-WPM

1) Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Module connector MS9-MV

· For connecting modules

Material:

Module connector, hollow bolt:

Die-cast aluminium

Screws: Steel

Seals: Nitrile rubber

RoHS-compliant

Free of copper and PTFE

Temperature of medium:



Ordering data		
Size	CRC ¹⁾ Weight Part No. Type	
	[g]	
MS9	2 110 552950 MS9-MV	

Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

FESTO

Mounting bracket MS12-WP


(order code: WP)

- For connecting modules via wall mounting
- In combination with a connecting plate for individual wall mounting

Material:

Die-cast aluminium Free of copper and PTFE





Dimensions and	Dimensions and ordering data											
Size	B1	B2	B3	B4	L1	L2	L3		Weight [g]	Part No.	Туре	
MS12	162	124	12	99	230	100	11	100	700	537133	MS12-WP	

Module connector MS12-MV

• For connecting modules

Material:

Die-cast aluminium


Free of copper and PTFE




Ordering data			
Size	Weight	Part No.	Туре
	[g]		
MS12	500	537134	MS12-MV







Mount	ting attachments	
		→ Page/Internet
1	Module connector MS4/6-RMV	17
2	Module connector MS4-6-AMV	18





FESTO

Module connector MS4/6-RMV


• For connecting service units at right angles to the axis of connection

Material:

Connecting plate, module connector: Die-cast aluminium Sealing ring: Nitrile rubber RoHS-compliant

Temperature of medium:





Dimensions ar	Dimensions and ordering data											
Size	B1	В2	CRC ¹⁾	Weight [g]	Part No.	Туре						
MS4	40.2	8.5	2	42	543490	MS4-RMV						
MS6	62	11	2	112	543491	MS6-RMV						
For use in expl	osive areas in zones 2 and 22											
MS4	40.2	8.5	2	42	563393	MS4-RMV-EX						
MS6	62	11	2	112	563394	MS6-RMV-EX						

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



FESTO

Module connector MS4-6-AMV


• For connecting MS4 and MS6 service units into one unit

Material:

Connecting plate, module connector: Die-cast aluminium Sealing ring: Nitrile rubber RoHS-compliant

Temperature of medium: −10 ... +60 °C






Dimensions ar	limensions and ordering data											
Size	B1	B2	В3	CRC ¹⁾	Weight [g]	Part No.	Туре					
MS4/6	40.2	10	62	2	77	543489	MS4-6-AMV					
For use in explosive areas in zones 2 and 22												
MS4/6	40.2	10	62	2	77	563392	MS4-6-AMV-EX					

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or



FESTO



Mount	ing attachments	
		→ Page/Internet
1	Module connector	17
	MS6-RMV	
2	Module connector	20
	MS6-9-ARMV	
3	Mounting bracket	8
	MS6-WPB	
4	Mounting bracket	14
	MS9-WPM	

Accessories, MS series Module connector MS6/MS9

FESTO

Module connector MS6-9-ARMV

- For connecting MS6 and MS9 service units into one unit
- · Rotation of service unit at right angles to the axis of connection possible

Material:

Connecting plate, module connector:

Die-cast aluminium

Screws: Steel

Seals: Nitrile rubber

RoHS-compliant

Free of copper and PTFE

Temperature of medium:


-10 ... +60 °C



Note

The larger mounting bracket must always be used on the module connector. The mounting bracket must be ordered separately.






Dimensions and ordering data											
Size	B1	B2	В3	B4	B5	CRC ¹⁾	Weight [g]	Part No.	Туре		
MS6/9	43	55	62	90	90.5	2	350	552951	MS6-9-ARMV		

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



FESTO



Mount	ing attachments	
		→ Page/Internet
1	Module connector	22
	MS9-RMV	
2	Module connector	23
	MS9-12-ARMV	
3	Mounting bracket	13
	MS9-WPB	
4	Mounting bracket	15
	MS12-WP	



FESTO

Module connector MS9-RMV

• For connecting service units at right angles to the axis of connection

Material:

Connecting plate, module connector:

Die-cast aluminium

Screws: Steel


Seals: Nitrile rubber

RoHS-compliant

Free of copper and PTFE

Temperature of medium:





Dimensions and ordering data											
Size	B1	B2	В3	B4	CRC ¹⁾	Weight [g]	Part No.	Туре			
MS9	55	55	90	90	2	920	552952	MS9-RMV			

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



Mounting attachments MS9/MS12

FESTO

Module connector MS9-12-ARMV


- For connecting MS9 and MS12 service units into one unit
- Rotation of service unit at right angles to the axis of connection possible

Material:


Connecting plate, module connector:
Die-cast aluminium
Screws: Steel
Seals: Nitrile rubber
ROHS-compliant
Free of copper and PTFE

 $\label{temperature} \mbox{Temperature of medium:}$

−10 ... +60 °C








Dimensions ar	Dimensions and ordering data											
Size	B1	B2	В3	B4	B5	CRC ¹⁾	Weight [g]	Part No.	Туре			
MS9/12	55	77	90	124	99	2	990	552953	MS9-12-ARMV			

1) Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



pries, MS series FESTO



Mour	nting attachments	
		→ Page/Internet
1	Power supply module	25
	MS4/6-E-IPM-40-80	
2	Power supply module	26
	MS4/6-E-IPM-80-80	
3	Branching module	27
	MS4/6-A-IPM-80	
4	Branching module	28
	MS4/6-A-RMV-IPM-80	
5	Sealing ring	29
	MS4/6-NNR	
6	Profile 40x80/80x80, cover plate, supply plate, drilling jig	On request



Further mounting attachments are required for mounting a service unit combination → 6



Mounting attachments MS4/MS6

FESTO

Power supply module MS4/6-E-IPM-40-80


- For mounting a service unit to the front of a profile of size 40x80
- Module connector can be repositioned by 90° for horizontal mounting of a service unit


Material

Connecting plate, hollow bolt, module connector: Die-cast aluminium

Screws: Steel Seals: Nitrile rubber RoHS-compliant

Temperature of medium:





Dimensions ar	Dimensions and ordering data											
Size	B1	B2		Weight [g]	Part No.	Туре						
MS4	40.2	16	2	109	543494	MS4-E-IPM-40-80						
MS6	62	16	2	141	543496	MS6-E-IPM-40-80						

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



Mounting attachments MS4/MS6

FESTO

Power supply module MS4/6-E-IPM-80-80

- For mounting a service unit to the front of a profile of size 80x80
- Module connector can be repositioned by 90° for horizontal mounting of a service unit


Material:

Connecting plate, hollow bolt, module connector: Die-cast aluminium

Screws: Steel Seals: Nitrile rubber RoHS-compliant

Temperature of medium:





Dimensions ar	Dimensions and ordering data											
Size	B1	B2	CRC ¹⁾	Weight [g]	Part No.	Туре						
MS4	40.2	18	2	186	543495	MS4-E-IPM-80-80						
MS6	62	18	2	218	543497	MS6-E-IPM-80-80						

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



FESTO

Branching module MS4/6-A-IPM-80


- For mounting a service unit on the long side of a profile
- Module connector can be repositioned by 90° for horizontal mounting of a service unit

Material:

Connecting plate, hollow bolt, module connector: Die-cast aluminium Screws: Steel Seals: Nitrile rubber RoHS-compliant

Temperature of medium:





Dimensions ar	Dimensions and ordering data											
Size	B1	В2	CRC ¹⁾	Weight [g]	Part No.	Туре						
MS4	40.2	16	2	124	543498	MS4-A-IPM-80						
MS6	62	16	2	156	543499	MS6-A-IPM-80						

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Mounting attachments MS4/MS6

FESTO

Branching module MS4/6-A-RMV-IPM-80

- For mounting a service unit on the long side of a profile
- Suitable for manifold mounting (the fittings on the module connector can be accessed from above for fast replacement of an individual component)
- Module connector can be repositioned by 90° for horizontal mounting of a service unit

Material:

Connecting plate, hollow bolt,

 $module\ connector:$

Die-cast aluminium


Screws: Steel

Seals: Nitrile rubber

RoHS-compliant

Temperature of medium:





Dimensions ar	Dimensions and ordering data											
Size	B1	B2	L1	CRC ¹⁾	Weight [g]	Part No.	Туре					
MS4	40.2	24.5	55	2	150	543500	MS4-A-RMV-IPM-80					
MS6	62	27	77	2	236	543501	MS6-A-RMV-IPM-80					

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.




FESTO

Sealing ring MS4/6-NNR

• For sealing a branching module MS-A-IPM when used as a power supply module

Material: Nitrile rubber RoHS-compliant

Temperature of medium:



Dimensions and ordering data			
Size	CRC ¹⁾	Part No.	Туре
MS4	2	543492	MS4-NNR
MS6	2	543493	MS6-NNR

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Accessories, MS series Connecting plates MS4/MS6

FESTO

Connecting plate MS4/6-AG...


(order code: AG...)

- Adapter for pneumatic connection
- MS6-AGE for implementing threaded connection G3/4

Material: Aluminium

Note on materials: Free of copper and PTFE





Dimensions	and orderi	ng data											
Size	B1	B2	В3	B4	B5	D1	D2	L1	L2	CRC ¹⁾	Weight	Part No.	Туре
											[g]		
MS4						G1/8				2	128	526068	MS4-AGA
	83.5	21.5	-	21	-	G1/4	16.8	42	-	2	128	526069	MS4-AGB
						G3/8				2	128	526070	MS4-AGC
MS6						G1/4				2	300	526080	MS6-AGB
	115	26.5	_	31	_	G3/8	24	62	_	2	300	526081	MS6-AGC
	113	20.5)1	_	G1/2	24	02		2	300	526082	MS6-AGD
						G3/4				2	300	526083	MS6-AGE
For use in ex	plosive are	as in zone	es 2 and 2	22									
MS4						G1/8				2	128	541549	MS4-AGA-EX
	83.5	21.5	12.5	21	72.5	G1/4	16.8	42	14.5	2	128	541550	MS4-AGB-EX
						G3/8				2	128	541551	MS4-AGC-EX
MS6						G1/4				2	300	541538	MS6-AGB-EX
	115	26.5	20.5	31	98.3	G3/8	24	62	15.5	2	300	541539	MS6-AGC-EX
	115	20.5	20.5)1	70.3	G1/2	24	02	15.5	2	300	541540	MS6-AGD-EX
						G3/4				2	300	541541	MS6-AGE-EX

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or

 $^{||\}cdot||$ Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Accessories, MS series Connecting plates MS4/MS6


FESTO

Cover plate MS4/6-END

• Can be used to cover the body sides of the first and last module if connecting plates are not used

Material: Reinforced polyamide Free of copper and PTFE





Dimensions ar	Dimensions and ordering data											
Size	B1	B2	В4	L1	Part No.	Туре						
MS4	43.6	6	21	42	538779	MS4-END						
MS6	67	8	31	62	538780	MS6-END						


Mounting plate MS4/6-AEND

(order code: WBE; scope of delivery includes wall mounting plate MS6-WPB)

• In combination with mounting bracket MS-WP or MS-WPB for individual wall mounting via direct thread

Material: Reinforced polyamide RoHS-compliant Free of copper and PTFE





Dimensions and ordering data																
Size	B1	B2	В3	В	4	B5	D1	L1	L2	L3	L4	L5	CRC ¹⁾	Weight	Part No.	Туре
				WP	WPB		Ø							[g]		
MS4	55.2	40.2	4	44	66	30.4	20.3	106	46.5	5.6	46.7	42	2	4	542966	MS4-AEND
MS6	79	62	4.5	54	90.5	48.4	32	158	71	6.6	71	62	2	17	535408	MS6-AEND

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



Accessories, MS series Connecting plates MS9

FESTO

Connecting plate MS9-AG...


(order code: AG...)

• Adapter for pneumatic connection

Material: Connecting plate, hollow bolt: Die-cast aluminium Seals: Nitrile rubber RoHS-compliant Free of copper and PTFE

Temperature of medium:





Dimensions and ordering data												
Size	B1	B2	D1	*	KBK1)	Weight [g]	Part No.	Туре				
MS9	132	112	G½	30	2	300	552954	MS9-AGD				
	132	112	G3/4	36	2	300	552955	MS9-AGE				
	142	112	G1	41	2	300	552956	MS9-AGF				
	162	112	G11⁄4	50	2	400	552957	MS9-AGG				
	176	112	G1½	55	2	400	552958	MS9-AGH				

¹⁾ Corrosion resistance class 2 as per Festo standard 940 070 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or

 $^{\|\}cdot\|$ Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Accessories, MS series Connecting plates MS12

FESTO

Connecting plate MS12-AG...


(order code: AG...)

• Adapter for pneumatic connection

Material: Die-cast aluminium

Free of copper and PTFE





Dimensions and ordering data													
Size	B1	B2	В3	B4	B5	D1	L1	L2	L3	L4	Weight	Part No.	Туре
											[g]		
MS12			12	99	184	G1	230			100	1,300	537135	MS12-AGF
	162	124			184	G11/4		100	11			537136	MS12-AGG
	102				184	G1½		100	11			537137	MS12-AGH
					196	G2						537138	MS12-AGI

 $[\]parallel$. Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Accessories, MS series Security components MS4/MS6/MS9/MS12

FESTO

Padlock LRVS-D

Material: Housing: Brass

Ambient temperature: −20 ... +60 °C



Ordering data									
Size	Weight	Part No.	Туре						
	[g]								
MS4/MS6/	120	193786	LRVS-D						
MS9/MS12									