

Proximity sensors SIE..., inductive

Product overview

FESTO



- Designs for DC and AC
- Switch output PNP, NPN or analogue
- Ø 3 mm ... M30 and special designs
- Corrosion-resistant and welding field immune versions
- Versions with increased switching distance
- Free of copper and PTFE

Detailed product information

➔ www.festo.com/catalogue/sie

Product overview						
Variant	Type	Operating voltage	Switch output / analogue output	Type of mounting	Size	➔ Page/ Internet
Reduction factor, material-specific						
Standard operating distance	SIEN Basic version	10 ... 30 V DC 15 ... 34 V DC	PNP NPN	Flush fitting Non-flush	Ø 4 mm, M5, Ø 6.5 mm, M8, M12, M18, M30	3
	SIED Basic version	20 ... 320 V DC 20 ... 265 V AC	2-wire, contactless	Flush fitting Non-flush	M12, M18, M30	6
	SIES Special design	10 ... 30 V DC	PNP NPN	Flush fitting	5x5x25 mm ... 40x40x120 mm	7
	SIEN-...-PA Polyamide housing	10 ... 30 V DC	PNP NPN	Flush fitting Non-flush	M12, M18, M30	8
	SIED-...-PA Polyamide housing	10 ... 300 V DC 20 ... 250 V AC	2-wire, contactless	Flush fitting Non-flush	M12, M18, M30	9
Increased operating distance	SIEH Basic version	10 ... 30 V DC 15 ... 34 V DC	PNP NPN	Flush fitting	Ø 3 mm, M12, M18	10
	SIEH-...-CR Stainless steel housing	10 ... 30 V DC	PNP NPN	Flush fitting	M12, M18	10
Analogue output	SIEA	15 ... 30 V DC	0 ... 10 V and 4 ... 20 mA	Flush fitting	M8, M12, M18, M30	12
Reduction factor 1 for all metals, welding field immune						
Increased operating distance	SIEF Basic version	10 ... 30 V DC	PNP NPN	Non-flush Partially flush	M8, M12, M18, M30	13
	SIEF-...-WA Housing resistant to welding spatter	10 ... 30 V DC	PNP NPN	Flush fitting Partially flush	M12, M18, M30, 40x40 mm	13

Proximity sensors SIE..., inductive

Type codes

FESTO

SIE	N	-	M	30	NB	-	P	S	-	K	-	L	-	
Type														
SIE	Proximity sensor, inductive													
Design														
A	With analogue output													
D	For DC and AC													
F	With reduction factor 1 for all metals, welding field immune													
H	With increased operating distance													
N	With standard operating distance													
S	Special design													
Constructional design														
-	Round													
M	Metric parallel thread													
Q	Block-shaped													
V3	Block-shaped													
Size														
Type of mounting														
B	Flush													
NB	Non-flush													
S	Partially flush													
Electrical output														
P	Switch output PNP													
N	Switch output NPN													
Z	2-wire output													
PU	Analogue output 0 ... 10 V													
UI	Analogue output 0 ... 10 V and 4 ... 20 mA													
Switching element function														
S	Normally open													
O	Normally closed													
A	Antivalent													
Electrical connection														
K	Cable													
S	Plug													
X	Screw terminals													
Indication														
-	Without indication													
L	Switching status													
2L	Switching status and ready status													
Variant														
-	Standard													
CR	Stainless steel housing													
PA	Polyamide housing													
WA	Housing resistant to welding spatter													

Proximity sensors SIEN, inductive

FESTO

Technical data – Standard operating distance, basic version

General technical data								
Size	Ø 4 mm	M5	Ø 6.5 mm	M8x1	M12x1	M18x1	M30x1.5	
Type of mounting	Flush				Flush or non-flush			
Rated operating distance S_n	Flush [mm]	0.8	0.8	1.5	1.5	2.0	5.0	10.0
	Non-flush [mm]	–	–	–	2.5	4.0	8.0	15.0
Repetition accuracy	Flush [mm]	0.04	0.04	0.075	0.075	0.1	0.15	0.3
	Non-flush [mm]	–	–	–	0.125	0.2	0.2	0.4

Electrical data								
Size	Ø 4 mm	M5	Ø 6.5 mm	M8x1	M12x1	M18x1	M30x1.5	
Electrical connection	Cable	3-wire						
	Plug	M8x1, 3-pin				M12x1, 3-pin		
Operating voltage range	[V DC]	10 ... 30		15 ... 34				
Max. output current as a function of temperature	[mA]	200 at $\leq 70^\circ\text{C}$		150 at $\leq 85^\circ\text{C}$				
	[mA]			200 at $\leq 50^\circ\text{C}$				
Max. switching frequency	Flush [Hz]	3,000	3,000	1,500	1,500	1,200	800	350
	Non-flush [Hz]	–	–	–	900	800	300	300
Protection against short circuit	Pulsed							
Protection against polarity reversal	For all electrical connections							
Protection class	IP67							

Operating and environmental conditions													
Size	Ø 4 mm	M5	Ø 6.5 mm	M8x1	M12x1	M18x1	M30x1.5						
Ambient temperature	[°C]	–25 ... +70		–25 ... +85									
Ambient temperature with flexible cable installation	[°C]	–25 ... +70		–25 ... +85									
CE mark (see declaration of conformity)	In accordance with EU EMC directive												
Certification	C-Tick												


Materials							
Size	Ø 4 mm	M5	Ø 6.5 mm	M8x1	M12x1	M18x1	M30x1.5
Housing	High-alloy stainless steel						
Cable sheath	Polyurethane						

Ordering data														
Size	S_n ¹⁾ [mm]	Type of mounting	Switch output	Switching element function	Electrical connection									
					Cable	Plug	Part No.							
\varnothing 4 mm														
	0.8			PNP	Normally open	150 362	SIEN-4B-PS-K-L							
					Normally closed	150 366	SIEN-4B-PO-K-L							
	NPN				Normally open	150 360	SIEN-4B-NS-K-L							
					Normally closed	150 364	SIEN-4B-NO-K-L							
M5														
	0.8			PNP	Normally open	150 370	SIEN-M5B-PS-K-L							
					Normally closed	150 374	SIEN-M5B-PO-K-L							
	NPN				Normally open	150 368	SIEN-M5B-NS-K-L							
					Normally closed	150 372	SIEN-M5B-NO-K-L							
M12x1														
M18x1														
M30x1.5														

1) S_n Rated operating distance [mm]

Proximity sensors SIEN, inductive

Technical data – Standard operating distance, basic version

Ordering data													
Size [mm]	S _n ¹⁾	Type of mounting	Switch out- put	Switching element function	Electrical connection								
					Cable		Plug						
					Part No.	Type	Part No.	Type					
Ø 6.5 mm													
 1.5													
Flush	PNP	Normally open	150 378	SIEN-6,5B-PS-K-L	150 379	SIEN-6,5B-PS-S-L	150 383	SIEN-6,5B-PO-S-L					
			150 382	SIEN-6,5B-PO-K-L	150 383	SIEN-6,5B-PO-S-L							
		NPN	150 376	SIEN-6,5B-NS-K-L	150 377	SIEN-6,5B-NS-S-L							
			150 380	SIEN-6,5B-NO-K-L	150 381	SIEN-6,5B-NO-S-L							
M8													
 1.5													
Flush	PNP	Normally open	150 386	SIEN-M8B-PS-K-L	150 387	SIEN-M8B-PS-S-L	150 389	SIEN-M8B-PO-S-L					
			150 390	SIEN-M8B-PO-K-L	150 391	SIEN-M8B-PO-S-L							
		NPN	150 384	SIEN-M8B-NS-K-L	150 385	SIEN-M8B-NS-S-L							
			150 388	SIEN-M8B-NO-K-L	150 389	SIEN-M8B-NO-S-L							
 2.5													
Non-flush	PNP	Normally open	150 394	SIEN-M8NB-PS-K-L	150 395	SIEN-M8NB-PS-S-L	150 399	SIEN-M8NB-PO-S-L					
			150 398	SIEN-M8NB-PO-K-L	150 399	SIEN-M8NB-PO-S-L							
		NPN	150 392	SIEN-M8NB-NS-K-L	150 393	SIEN-M8NB-NS-S-L							
			150 396	SIEN-M8NB-NO-K-L	150 397	SIEN-M8NB-NO-S-L							
M12													
 2.0													
Flush	PNP	Normally open	150 402	SIEN-M12B-PS-K-L	150 403	SIEN-M12B-PS-S-L	150 407	SIEN-M12B-PO-S-L					
			150 406	SIEN-M12B-PO-K-L	150 407	SIEN-M12B-PO-S-L							
		NPN	150 400	SIEN-M12B-NS-K-L	150 401	SIEN-M12B-NS-S-L							
			150 404	SIEN-M12B-NO-K-L	150 405	SIEN-M12B-NO-S-L							
 4.0													
Non-flush	PNP	Normally open	150 410	SIEN-M12NB-PS-K-L	150 411	SIEN-M12NB-PS-S-L	150 415	SIEN-M12NB-PO-S-L					
			150 414	SIEN-M12NB-PO-K-L	150 415	SIEN-M12NB-PO-S-L							
		NPN	150 408	SIEN-M12NB-NS-K-L	150 409	SIEN-M12NB-NS-S-L							
			150 412	SIEN-M12NB-NO-K-L	150 413	SIEN-M12NB-NO-S-L							
M18													
 5.0													
Flush	PNP	Normally open	150 418	SIEN-M18B-PS-K-L	150 419	SIEN-M18B-PS-S-L	150 423	SIEN-M18B-PO-S-L					
			150 422	SIEN-M18B-PO-K-L	150 423	SIEN-M18B-PO-S-L							
		NPN	150 416	SIEN-M18B-NS-K-L	150 417	SIEN-M18B-NS-S-L							
			150 420	SIEN-M18B-NO-K-L	150 421	SIEN-M18B-NO-S-L							
 8.0													
Non-flush	PNP	Normally open	150 426	SIEN-M18NB-PS-K-L	150 427	SIEN-M18NB-PS-S-L	150 431	SIEN-M18NB-PO-S-L					
			150 430	SIEN-M18NB-PO-K-L	150 431	SIEN-M18NB-PO-S-L							
		NPN	150 424	SIEN-M18NB-NS-K-L	150 425	SIEN-M18NB-NS-S-L							
			150 428	SIEN-M18NB-NO-K-L	150 429	SIEN-M18NB-NO-S-L							
M30													
 10.0													
Flush	PNP	Normally open	150 434	SIEN-M30B-PS-K-L	150 435	SIEN-M30B-PS-S-L	150 439	SIEN-M30B-PO-S-L					
			150 438	SIEN-M30B-PO-K-L	150 439	SIEN-M30B-PO-S-L							
		NPN	150 432	SIEN-M30B-NS-K-L	150 433	SIEN-M30B-NS-S-L							
			150 436	SIEN-M30B-NO-K-L	150 437	SIEN-M30B-NO-S-L							
 15.0													
Non-flush	PNP	Normally open	150 442	SIEN-M30NB-PS-K-L	150 443	SIEN-M30NB-PS-S-L	150 447	SIEN-M30NB-PO-S-L					
			150 446	SIEN-M30NB-PO-K-L	150 447	SIEN-M30NB-PO-S-L							
		NPN	150 440	SIEN-M30NB-NS-K-L	150 441	SIEN-M30NB-NS-S-L							
			150 444	SIEN-M30NB-NO-K-L	150 445	SIEN-M30NB-NO-S-L							

1) S_n Rated operating distance [mm]

Proximity sensors SIED, inductive

FESTO

Technical data – Standard operating distance, for DC and AC

General technical data				
Size	M12x1	M18x1	M30x1.5	
Type of mounting	Flush or non-flush			
Rated operating distance S_n	Flush [mm] Non-flush [mm]	2.0 4.0	5.0 8.0	10.0 15.0
Repetition accuracy	Flush [mm] Non-flush [mm]	± 0.1 ± 0.2	± 0.15 ± 0.2	± 0.3 ± 0.4

Electrical data			
Size	M12x1	M18x1	M30x1.5
Electrical connection	Cable, 2-wire Plug M12x1, 2-pin		
Operating voltage range	[V DC] [V AC]	20 ... 320 20 ... 265	
Max. output current	[mA]	200	300
Max. switching frequency DC	Flush [Hz] Non-flush [Hz]	1,200 900	490 340
Max. switching frequency AC	Flush [Hz] Non-flush [Hz]	25	25
Minimum load current	[mA]	5.0	
Protection against short circuit		No	
Protection against polarity reversal		For all electrical connections	
Protection class		IP67	

Operating and environmental conditions	
Ambient temperature	[°C]
Ambient temperature with flexible cable installation	[°C]
CE mark (see declaration of conformity)	In accordance with EU EMC directive In accordance with EU Low Voltage Directive
Certification	C-Tick

Materials	
Housing	Nickel-plated brass; polyamide
Cable sheath	Polyurethane

Proximity sensors SIED, inductive

Technical data – Standard operating distance, for DC and AC

Ordering data										
Size [mm]	S _n ¹⁾	Type of mounting	Switch out- put	Switching element function	Electrical connection					
					Cable					
						Part No. Type				
M12 – For DC and AC										
	2.0	Flush	2-wire, con- tactless	Normally open	538 272	SIED-M12B-ZS-K-L				
				Normally closed	538 274	SIED-M12B-ZO-K-L				
	4.0	Non-flush	2-wire, con- tactless	Normally open	538 268	SIED-M12NB-ZS-K-L				
				Normally closed	538 270	SIED-M12NB-ZO-K-L				
M18 – For DC and AC										
	5.0	Flush	2-wire, con- tactless	Normally open	538 280	SIED-M18B-ZS-K-L				
				Normally closed	538 282	SIED-M18B-ZO-K-L				
	8.0	Non-flush	2-wire, con- tactless	Normally open	538 276	SIED-M18NB-ZS-K-L				
				Normally closed	538 278	SIED-M18NB-ZO-K-L				
M30 – For DC and AC										
	10.0	Flush	2-wire, con- tactless	Normally open	538 288	SIED-M30B-ZS-K-L				
				Normally closed	538 290	SIED-M30B-ZO-K-L				
	15.0	Non-flush	2-wire, con- tactless	Normally open	538 284	SIED-M30NB-ZS-K-L				
				Normally closed	538 286	SIED-M30NB-ZO-K-L				

1) S_n Rated operating distance [mm]

Proximity sensors SIES, inductive

FESTO

Technical data – Standard operating distance, special design

General technical data					
Design	SIES-Q5B-...	SIES-Q8B-...	SIES-V3B-...	SIES-QB-...	SIES-Q40B-...
Type of mounting	Flush				
Rated operating distance S_n [mm]	0.8	1.5	2.0	2.0	15.0
Repetition accuracy [mm]	±0.04	±0.075	±0.1	±0.1	±0.75

Electrical data					
Design	SIES-Q5B-...	SIES-Q8B-...	SIES-V3B-...	SIES-QB-...	SIES-Q40B-...
Electrical connection	Cable, 3-wire	Cable, 3-wire Plug, M8x1, 3-pin	Plug, M8x1, 3-pin	Cable, 3-wire	Screw terminals
Operating voltage range [V DC]	10 ... 30				
Max. output current [mA]	200		–		
Max. output current as a function of temperature [mA]	200 at ≤ 70 °C		150 at ≤ 85 °C		
			200 at ≤ 50 °C		
Max. switching frequency [Hz]	3,000	1,500	1,200	1,200	100
Protection against short circuit	Pulsed				
Protection against polarity reversal	For all electrical connections				
Protection class	IP67				IP65

Operating and environmental conditions					
Design	SIES-Q5B-...	SIES-Q8B-...	SIES-V3B-...	SIES-QB-...	SIES-Q40B-...
Ambient temperature [°C]	–25 ... +70		–25 ... +85		
CE mark (see declaration of conformity)	In accordance with EU EMC directive				
Certification	C-Tick				

Materials					
Design	SIES-Q5B-...	SIES-Q8B-...	SIES-V3B-...	SIES-QB-...	SIES-Q40B-...
Housing	Nickel-plated brass		Die-cast zinc	Polybutylene terephthalate, reinforced	Polyester
Cable sheath	Polyurethane				–

Size	S_n ¹⁾ [mm]	Type of mounting	Switch output	Switching element function	Electrical connection				
					Cable		Plug		
					Part No.	Type	Part No.	Type	
Special design									
	0.8			Normally open	178 291	SIES-Q5B-PS-K-L	–		
				Normally closed	174 549	SIES-Q5B-PO-K-L	–		
	1.5			Normally open	178 290	SIES-Q5B-NS-K-L	–		
				Normally closed	174 548	SIES-Q5B-NO-K-L	–		
	1.5			Normally open	178 294	SIES-Q8B-PS-K-L	178 295	SIES-Q8B-PS-S-L	
				Normally closed	174 552	SIES-Q8B-PO-K-L	174 553	SIES-Q8B-PO-S-L	
	2.0			Normally open	178 292	SIES-Q8B-NS-K-L	178 293	SIES-Q8B-NS-S-L	
				Normally closed	174 550	SIES-Q8B-NO-K-L	174 551	SIES-Q8B-NO-S-L	
	2.0			Normally open	150 488	SIES-QB-PS-K-L	150 491	SIES-V3B-PS-S-L	
				Normally closed	150 489	SIES-QB-PO-K-L	–		
	15.0			Normally open	–		150 490	SIES-V3B-NS-S-L	
				Normally closed	–		–		
									

1) S_n Rated operating distance [mm]

2) Electrical connection with screw terminals

Proximity sensors SIEN-...-PA, inductive

Technical data – Standard operating distance, polyamide housing

General technical data					
Size	M12x1	M18x1	M30x1.5		
Mounting conditions	Flush or non-flush				
Rated operating distance S_n	Flush [mm]	2.0	5.0	10.0	
	Non-flush [mm]	4.0	8.0	15.0	
Repetition accuracy	Flush [mm]	0.04	0.1	0.2	
	Non-flush [mm]	0.08	0.16	0.3	

Electrical data					
Size	M12x1	M18x1	M30x1.5		
Electrical connection	Cable, 3-wire				
Operating voltage range	[V DC] 10 ... 30				
Max. output current	[mA] 200				
Max. switching frequency DC	Flush [Hz]	2,000	1,000	500	
	Non-flush [Hz]	2,000	1,000	500	
Protection against short circuit	Pulsed				
Protection against polarity reversal	For all electrical connections				
Protection class	IP65, IP67				

Operating and environmental conditions					
Ambient temperature	[°C]	–25 ... +70			
Ambient temperature with flexible cable installation	[°C]	0 ... 70			
CE mark (see declaration of conformity)	In accordance with EU EMC directive				
Certification	C-Tick				

Materials					
Housing	Reinforced polyamide				
Cable sheath	Polyvinyl chloride				

Ordering data						
Size	S_n ¹⁾ [mm]	Type of mounting	Switch output	Switching element function	Electrical connection	
					Cable	Part No. Type
M12x1						
	2.0	Flush	PNP	Normally open	538 323	SIEN-M12B-PS-K-L-PA
			NPN		538 324	SIEN-M12B-NS-K-L-PA
	4.0	Non-flush	PNP	Normally open	538 329	SIEN-M12NB-PS-K-L-PA
			NPN		538 330	SIEN-M12NB-NS-K-L-PA
M18x1						
	5.0	Flush	PNP	Normally open	538 325	SIEN-M18B-PS-K-L-PA
			NPN		538 326	SIEN-M18B-NS-K-L-PA
	8.0	Non-flush	PNP	Normally open	538 331	SIEN-M18NB-PS-K-L-PA
			NPN		538 332	SIEN-M18NB-NS-K-L-PA
M30x1.5						
	10.0	Flush	PNP	Normally open	538 327	SIEN-M30B-PS-K-L-PA
			NPN		538 328	SIEN-M30B-NS-K-L-PA
	15.0	Non-flush	PNP	Normally open	538 333	SIEN-M30NB-PS-K-L-PA
			NPN		538 334	SIEN-M30NB-NS-K-L-PA

1) S_n Rated operating distance [mm]

Proximity sensors SIED-...-PA, inductive

FESTO

Technical data – Standard operating distance, polyamide housing, for DC and AC

General technical data						
Size	M12x1	M18x1	M30x1.5			
Mounting conditions	Flush or non-flush					
Rated operating distance S_n	Flush [mm]	2.0	5.0	10.0		
	Non-flush [mm]	4.0	8.0	15.0		
Repetition accuracy	Flush [mm]	0.04	0.1	0.2		
	Non-flush [mm]	0.08	0.16	0.3		

Electrical data						
Size	M12x1	M18x1	M30x1.5			
Electrical connection	Cable, 2-wire					
Operating voltage range	[V DC]	10 ... 300				
	[V AC]	20 ... 250				
Max. output current	[mA]	100	300			
Max. switching frequency DC	Flush [Hz]	60				
	Non-flush [Hz]	60				
Max. switching frequency AC	Flush [Hz]	20				
	Non-flush [Hz]	20				
Minimum load current	[mA]	3.0				
Protection against short circuit	No					
Protection against polarity reversal	For all electrical connections					
Protection class	IP65, IP67					

Operating and environmental conditions						
Ambient temperature	[°C]	-25 ... +70				
Ambient temperature with flexible cable installation	[°C]	0 ... 70				
CE mark (see declaration of conformity)	In accordance with EU EMC directive In accordance with EU Low Voltage Directive					
Certification	C-Tick					

Materials					
Housing	Reinforced polyamide				
Cable sheath	Polyvinyl chloride				

Ordering data					
Size	S_n ¹⁾ [mm]	Type of mounting	Switch output	Switching element function	Electrical connection
					Cable Part No. Type
M12					
	2.0	Flush	2-wire, contactless	Normally open	538 336 SIED-M12B-ZS-K-L-PA
	4.0	Non-flush			538 335 SIED-M12NB-ZS-K-L-PA
M18					
	5.0	Flush	2-wire, contactless	Normally open	538 338 SIED-M18B-ZS-K-L-PA
	8.0	Non-flush			538 337 SIED-M18NB-ZS-K-L-PA
M30					
	10.0	Flush	2-wire, contactless	Normally open	538 340 SIED-M30B-ZS-K-L-PA
	15.0	Non-flush			538 339 SIED-M30NB-ZS-K-L-PA

1) S_n Rated operating distance [mm]

Proximity sensors SIEH, inductive

Technical data – Increased operating distance

FESTO

General technical data					
Size	Basic version			Stainless steel housing	
	Ø 3 mm	M12x1	M18x1	M12x1	M18x1
Type of mounting	Flush				
Rated operating distance S_n [mm]	1.0	4.0	7.0	6.0	10.0
Repetition accuracy [mm]	0.02	0.2	0.2	0.3	0.5

Electrical data					
Size	Basic version			Stainless steel housing	
	Ø 3 mm	M12x1	M18x1	M12x1	M18x1
Electrical connection	Cable	3-wire			
	Plug	M8x1, 3-pin	M12x1, 3-pin	M12x1, 3-pin	
Operating voltage range	[V DC]	10 ... 30	15 ... 34	10 ... 30	
Max. output current as a function of temperature	[mA]	100	150 at $\leq 85^{\circ}\text{C}$ 200 at $\leq 50^{\circ}\text{C}$	200	
Max. switching frequency	[Hz]	3,000	400	250	600
Protection against short circuit		Pulsed			
Protection against polarity reversal		For all electrical connections			
Protection class		IP67			


Operating and environmental conditions					
Size	Basic version			Stainless steel housing	
	Ø 3 mm	M12x1	M18x1	M12x1	M18x1
Ambient temperature	[°C]	-25 ... +70	-25 ... +85	-25 ... +70	
Ambient temperature with flexible cable installation	[°C]	-5 ... +70	-5 ... +85	-5 ... +70	
CE mark (see declaration of conformity)		In accordance with EU EMC directive			
Certification		C-Tick			

Materials					
Size	Basic version			Stainless steel housing	
	Ø 3 mm	M12x1	M18x1	M12x1	M18x1
Housing	High-alloy stainless steel	Nickel-plated brass		High-alloy steel	
Cable sheath	Polyurethane				

Proximity sensors SIEH, inductive

FESTO

Technical data – Increased operating distance

Ordering data						
Size [mm]	S _n ¹⁾	Type of mounting	Switch out- put	Switching element function	Electrical connection	
					Cable	Plug
Ø 3 mm						
	1.0	Flush	PNP	Normally open	538 264 SIEH-3B-PS-K-L	538 263 SIEH-3B-PS-S-L
			NPN	Normally open	538 266 SIEH-3B-NS-K-L	538 265 SIEH-3B-NS-S-L
M12x1						
	4.0	Flush	PNP	Normally open	150 450 SIEH-M12B-PS-K-L	150 451 SIEH-M12B-PS-S-L
				Normally closed	150 454 SIEH-M12B-PO-K-L	150 455 SIEH-M12B-PO-S-L
			NPN	Normally open	150 448 SIEH-M12B-NS-K-L	150 449 SIEH-M12B-NS-S-L
				Normally closed	150 452 SIEH-M12B-NO-K-L	150 453 SIEH-M12B-NO-S-L
M18x1						
	7.0	Flush	PNP	Normally open	150 458 SIEH-M18B-PS-K-L	150 459 SIEH-M18B-PS-S-L
				Normally closed	150 462 SIEH-M18B-PO-K-L	150 463 SIEH-M18B-PO-S-L
			NPN	Normally open	150 456 SIEH-M18B-NS-K-L	150 457 SIEH-M18B-NS-S-L
				Normally closed	150 460 SIEH-M18B-NO-K-L	150 461 SIEH-M18B-NO-S-L
M12x1 – Stainless steel housing						
	6.0	Flush	PNP	Normally open	538 252 SIEH-M12B-PS-K-L-CR	538 251 SIEH-M12B-PS-S-L-CR
				Normally open	538 254 SIEH-M12B-NS-K-L-CR	538 253 SIEH-M12B-NS-S-L-CR
M18x1 – Stainless steel housing						
	10.0	Flush	PNP	Normally open	538 256 SIEH-M18B-PS-K-L-CR	538 255 SIEH-M18B-PS-S-L-CR
				Normally open	538 258 SIEH-M18B-NS-K-L-CR	538 257 SIEH-M18B-NS-S-L-CR

1) S_n Rated operating distance [mm]

Proximity sensors SIEA, inductive

Technical data – Analogue output

FESTO

General technical data				
Size	M8x1	M12x1	M18x1	M30x1.5
Type of mounting	Flush			
Distance measuring range [mm]	0 ... 4	0 ... 6	0 ... 10	0 ... 20
Repetition accuracy [mm]	0.3	0.3	0.3	0.3
Repetition accuracy under constant conditions [mm]	±0.01	±0.01	±0.02	±0.05
Displacement resolution [mm]	0.001	0.001	0.002	0.005

Electrical data				
Size	M8x1	M12x1	M18x1	M30x1.5
Electrical connection	Plug	M8x1, 3-pin	M12x1, 4-pin	
Operating voltage range [V DC]	15 ... 30			
Max. switching frequency [Hz]	1,600	1,000	500	200
Protection against short circuit	Pulsed			
Protection against polarity reversal	For operating voltage			
Protection class	IP67			

Operating and environmental conditions				
Size	M8x1	M12x1	M18x1	M30x1.5
Ambient temperature [°C]	-25 ... +70			
CE mark (see declaration of conformity)	In accordance with EU EMC directive			
Certification	C-Tick			

Materials				
Size	M8x1	M12x1	M18x1	M30x1.5
Housing	Brass, chrome-plated			

Ordering data					
Size	S ¹⁾ [mm]	Type of mounting	Analogue output	Electrical connection	
	0 ... 4	Flush	0 ... 10 V	–	538 291 SIEA-M8B-PU-S
	0 ... 6	Flush	0 ... 10 V	4 ... 20 mA	538 292 SIEA-M12B-UI-S
	0 ... 10	Flush	0 ... 10 V	4 ... 20 mA	538 293 SIEA-M18B-UI-S
	0 ... 20	Flush	0 ... 10 V	4 ... 20 mA	538 294 SIEA-M30B-UI-S

1) S Position measuring range [mm]

Proximity sensors SIEF, inductive

FESTO

Technical data – Increased operating distance, reduction factor 1, welding field immune

General technical data					
Size	M8x1	M12x1	M18x1	M30x1.5	40x40 mm
Type of mounting	Non-flush	Flush or partially flush			Partially flush
Rated operating distance S_n	Flush [mm] Partially flush [mm]	– 4.0	3.0 8.0	5.0 12.0	10.0 20.0
Repetition accuracy	Flush [mm] Partially flush [mm]	– 0.08	0.06 0.16	0.1 0.24	0.2 0.4
					0.7

Electrical data					
Size	M8x1	M12x1	M18x1	M30x1.5	40x40 mm
Electrical connection	Cable Plug	3-wire M8x1, 3-pin	M12x1, 3-pin, Fixcon		
Operating voltage range	[V DC]	10 ... 30			10 ... 65
Max. output current	[mA]	150	200		
Max. switching frequency DC	Flush [Hz] Partially flush [Hz]	– 2,000	3,000 2,000	2,500 2,000	2,000 1,500
Protection against short circuit	Pulsed				
Protection against polarity reversal	For all electrical connections				
Protection class	IP67				

Operating and environmental conditions					
Resistance to interference from magnetic fields	Magnetic direct and alternating field				
Ambient temperature	–30 ... +85				
CE mark (see declaration of conformity)	In accordance with EU EMC directive				
Certification	C-Tick				

Materials								
Size	M8x1	M12x1	M18x1	M30x1.5	40x40 mm			
Basic version								
Housing	High-alloy stainless steel; polyamide	Brass, chrome-plated; polybutylene terephthalate			Reinforced polyamide			
Cable sheath	Polyurethane							
Housing resistant to welding spatter								
Housing	–	Brass, PTFE-coated; polybutylene terephthalate	–					

Proximity sensors SIEF, inductive

Technical data – Increased operating distance, reduction factor 1, welding field immune

FESTO


Ordering data													
Size [mm]	S _n ¹⁾	Type of mounting	Switching element function	Electrical connection	Switch output								
					PNP		NPN						
Part No. Type						Part No.	Type	Part No.	Type				
Basic version													
M8x1													
	4.0	Partially flush	Normally open	Cable	538 308	SIEF-M8NB-PS-K-L	538 310	SIEF-M8NB-NS-K-L					
				Plug	538 307	SIEF-M8NB-PS-S-L	538 309	SIEF-M8NB-NS-S-L					
M12x1													
	8.0	Partially flush	Normally open	Cable	538 312	SIEF-M12NB-PS-K-L	538 314	SIEF-M12NB-NS-K-L					
				Plug	538 311	SIEF-M12NB-PS-S-L	538 313	SIEF-M12NB-NS-S-L					
M18x1													
	12.0	Partially flush	Normally open	Cable	538 316	SIEF-M18NB-PS-K-L	538 318	SIEF-M18NB-NS-K-L					
				Plug	538 315	SIEF-M18NB-PS-S-L	538 317	SIEF-M18NB-NS-S-L					
M30x1.5													
	10.0	Partially flush	Normally open	Cable	538 320	SIEF-M30NB-PS-K-L	538 322	SIEF-M30NB-NS-K-L					
				Plug	538 319	SIEF-M30NB-PS-S-L	538 321	SIEF-M30NB-NS-S-L					
40x40 mm													
	35.0	Partially flush	Antivalent	Plug	538 341	SIEF-Q40S-PA-S-2L	538 342	SIEF-Q40S-NA-S-2L					
Housing resistant to welding spatter													
M12x1													
	3.0	Flush	Normally open	Plug	538 297	SIEF-M12B-PS-S-L-WA	538 298	SIEF-M12B-NS-S-L-WA					
		Partially flush			538 295	SIEF-M12NB-PS-S-L-WA	538 296	SIEF-M12NB-NS-S-L-WA					
M18x1													
	5.0	Flush	Normally open	Plug	538 301	SIEF-M18B-PS-S-L-WA	538 302	SIEF-M18B-NS-S-L-WA					
		Partially flush			538 299	SIEF-M18NB-PS-S-L-WA	538 300	SIEF-M18NB-NS-S-L-WA					
M30x1.5													
	10.0	Flush	Normally open	Plug	538 305	SIEF-M30B-PS-S-L-WA	538 306	SIEF-M30B-NS-S-L-WA					
		Partially flush			538 303	SIEF-M30NB-PS-S-L-WA	538 304	SIEF-M30NB-NS-S-L-WA					

1) S_n Rated operating distance [mm]

Proximity sensors SIE..., inductive

Peripherals overview

FESTO



Mounting attachments and accessories

Proximity sensors

- [1] SIE...-...S, with plug
- [2] SIE...-...K, with cable

Connecting cables

- [3] NEBU-M...G..., SIM-M...-...G
- [4] NEBU-M...W..., SIM-M...-...W

Mounting attachments

- [5] SIEZ-...B...
- [6] SIEZ-UV
- [7] SIEZ-UH

Inscription label

- [8] SIEZ-LB

Ordering data – Connecting cables M8x1

Technical data → Internet: nebu

	Number of wires	Cable length [m]	Part No.	Type
Straight plug socket				
	3	2.5	541 333	NEBU-M8G3-K-2.5-LE3
	5		541 334	NEBU-M8G3-K-5-LE3
Angled plug socket				
	3	2.5	541 338	NEBU-M8W3-K-2.5-LE3
	5		541 341	NEBU-M8W3-K-5-LE3
Straight plug socket, straight plug				
	4	2.5	554 037	NEBU-M8G3-K-2.5-M8G4 ¹⁾

1) For connection of proximity sensors SIEA-M8B to the signal converter SVE4-US

Ordering data – Connecting cables M12x1

Technical data → Internet: nebu

	Number of wires	Cable length [m]	Part No.	Type
Straight plug socket				
	3	2.5	541 363	NEBU-M12G5-K-2.5-LE3
	5		541 364	NEBU-M12G5-K-5-LE3
	4	5	541 328	NEBU-M12G5-K-5-LE4
Angled plug socket				
	3	2.5	541 367	NEBU-M12W5-K-2.5-LE3
	5		541 370	NEBU-M12W5-K-5-LE3
	4	5	541 329	NEBU-M12W5-K-5-LE4
Straight plug socket, straight plug				
	4	2.5	554 036	NEBU-M12G5-K-2.5-M8G4 ¹⁾

1) For connection of proximity sensors SIEA-MxxB to the signal converter SVE4

Ordering data – Mounting attachments

For design Part No. Type

With stop for flush mounting

	M8	538 346	SIEZ-B-8
	M12	538 348	SIEZ-B-12
	M18	538 350	SIEZ-B-18
	M30	538 352	SIEZ-B-30

Without stop

	4	538 343	SIEZ-NB-4
	6.5	538 344	SIEZ-NB-6,5
	M8	538 345	SIEZ-NB-8

	M12	538 347	SIEZ-NB-12
	M18	538 349	SIEZ-NB-18
	M30	538 351	SIEZ-NB-30

	M12, M18	538 354	SIEZ-UH
	M12, M18	538 355	SIEZ-UV

Inscription label

	M12 ... M30	538 353	SIEZ-LB
--	-------------	---------	---------