 New

## Position transmitters SMAT-8M, for T-slot

**FESTO**



# Position transmitters SMAT-8M, for T-slot

Key features


## Design

### General

The SMAT-8M is a position transmitter for the contactless sensing of the piston position of drives that can be detected magnetically. It supplies a displacement-proportional analogue

output signal in the position measuring range. It is connected directly to the analogue PLC inputs without any accessories. With its extremely compact design,


the SMAT-8M is the ideal solution for grippers, short-stroke cylinders and all applications in which installation space is restricted.

 **Note**  
It can be used with Festo cylinders with T-slot (profile slot 8) as well as round cylinders and tie-rod cylinders with mounting kits. A selection aid with suitable drives can be found on the following pages.

## Position measuring range

The SMAT-8M supplies a displacement-proportional analogue output signal of 0 ... 10 V in the position measuring range of up to 40 mm (depending on the drive used). In other words, the output voltage increases when the piston moves in the direction of the piston rod. When the piston retracts, the output voltage drops. The installation direction of the SMAT-8M is irrelevant in this case. To achieve the best possible function on the drive in question, the position measuring range must be initialised on the drive during installation.

As a visual aid, the green LED lights up within the position measuring range (B) and the red LED lights up outside of the measuring range (A)/(C) in normal operation.




## Repetition accuracy

The repetition accuracy is  $\pm 0.025$  mm on grippers and  $\pm 0.1$  mm on standard drives.

With standard drives, the repetition accuracy in the centre of the measuring range is lower than at the edge. It is  $\pm 0.06$  mm at a distance of  $\pm 5$  mm from the centre, for example. For critical applications, it is recommended that the SMAT-8M be mounted so as to have the relevant measuring points close to 5.5 V.

Repetition accuracy as a function of position measuring range S



## Position transmitters SMAT-8M, for T-slot

Selection aid

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
<b>Standards-based cylinders</b>		
Standard cylinder DSNU-8	+	19
Standard cylinder DSNU-10	+	22
Standard cylinder DSNU-12	+	21
Standard cylinder DSNU-16	+	21
Standard cylinder DSNU-20	+	20
Standard cylinder DSNU-25	+	28
Round cylinder DSNU-32	+	25
Round cylinder DSNU-40	+	29
Round cylinder DSNU-50	+	31
Round cylinder DSNU-63	+	36
Standard cylinder DNCB-32	+	25
Standard cylinder DNCB-40	+	28
Standard cylinder DNCB-50	+	30
Standard cylinder DNCB-63	+	32
Standard cylinder DNCB-80	+	35
Standard cylinder DNCB-100	+	29
Standard cylinder DNC-32	+	29
Standard cylinder DNC-40	o <sup>1)</sup>	–
Standard cylinder DNC-50	o <sup>1)</sup>	–
Standard cylinder DNC-63	+	34
Standard cylinder DNC-80	+	35
Standard cylinder DNC-100	+	37
Standard cylinder DNC-125	+	38
Standard cylinder DNG-32	+	28
Standard cylinder DNG-40	+	34
Standard cylinder DNG-50	o <sup>1)</sup>	–
Standard cylinder DNG-63	+	32
Standard cylinder DNG-80	+	32
Standard cylinder DNG-100	+	32
Compact cylinder ADN-12	+	22
Compact cylinder ADN-16	+	26
Compact cylinder ADN-20	+	30
Compact cylinder ADN-25	+	27
Compact cylinder ADN-32	+	31
Compact cylinder ADN-40	+	28
Compact cylinder ADN-50	+	25
Compact cylinder ADN-63	+	31
Compact cylinder ADN-80	o <sup>1)</sup>	–
Compact cylinder ADN-100	+	28
Compact cylinder ADN-125	+	37

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
<b>Cylinders with piston rod</b>		
Short-stroke cylinder ADVC/AEVC-32	+	Stroke < position measuring range SMAT-8M
Short-stroke cylinder ADVC/AEVC-40	+	
Short-stroke cylinder ADVC/AEVC-50	+	
Short-stroke cylinder ADVC/AEVC-63	+	
Short-stroke cylinder ADVC/AEVC-80	+	
Short-stroke cylinder ADVC/AEVC-100	+	
Compact cylinder ADVU/AEUV-12	+	23
Compact cylinder ADVU/AEUV-16	+	20
Compact cylinder ADVU/AEUV-20	+	29
Compact cylinder ADVU/AEUV-25	+	25
Compact cylinder ADVU/AEUV-32	+	27
Compact cylinder ADVU/AEUV-40	+	24
Compact cylinder ADVU/AEUV-50	+	22
Compact cylinder ADVU/AEUV-63	+	32
Compact cylinder ADVU/AEUV-80	+	35
Compact cylinder ADVU/AEUV-100	+	33
Compact cylinder ADVU/AEUV-125	+	35
Flat cylinder DZF-12	+	29
Flat cylinder DZF-18	+	26
Flat cylinder DZF-25	+	28
Flat cylinder DZF-32	+	26
Flat cylinder DZF-40	o <sup>1)</sup>	–
Flat cylinder DZF-50	o <sup>1)</sup>	–
Flat cylinder DZF-63	o <sup>1)</sup>	–
<b>Rodless cylinders</b>		
Linear drive DGC-18	+	30
Linear drive DGC-25	o <sup>1)</sup>	–
Linear drive DGC-32	o <sup>1)</sup>	–
Linear drive DGC-40	o <sup>1)</sup>	–
<b>Function-oriented drives</b>		
Linear/swivel clamp CLR-12	+	22
Linear/swivel clamp CLR-16	+	26
Linear/swivel clamp CLR-20	+	30
Linear/swivel clamp CLR-25	+	27
Linear/swivel clamp CLR-32	+	31
Linear/swivel clamp CLR-40	+	28
Linear/swivel clamp CLR-50	+	25
Linear/swivel clamp CLR-63	+	31

+ Unrestricted use

o On request

1) Different from technical data. Usability on request.

## Position transmitters SMAT-8M, for T-slot

Selection aid

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Drives with linear guides		
Guided drive DFM-12	+	21
Guided drive DFM-16	+	15
Guided drive DFM-20	+	24
Guided drive DFM-25	+	26
Guided drive DFM-32	+	25
Guided drive DFM-40	o <sup>1)</sup>	–
Guided drive DFM-50	+	21
Guided drive DFM-63	+	31
Guided drive DFM-80	+	30
Guided drive DFM-100	+	25
Guided drive DFM-12-B	+	16
Guided drive DFM-16-B	+	20
Guided drive DFM-20-B	+	26
Guided drive DFM-25-B	+	24
Guided drive DFM-32-B	+	29
Guided drive DFM-40-B	+	30
Guided drive DFM-50-B	+	31
Guided drive DFM-63-B	+	33
Linear unit SLE-10	+	22
Linear unit SLE-16	+	21
Linear unit SLE-20	+	20
Linear unit SLE-25	+	28
Linear unit SLE-32	+	25
Linear unit SLE-40	+	29
Linear unit SLE-50	+	31

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Handling units		
Linear module HMPL-12	+	Stroke < position measuring range SMAT-8M
Linear module HMPL-16	+	
Linear module HMPL-20	+	
Three-point gripper HGD-32	+	
Three-point gripper HGD-50	+	
Parallel gripper HGP-10	+	
Parallel gripper HGP-16	+	
Parallel gripper HGP-20	+	
Parallel gripper HGP-25	+	
Parallel gripper HGP-35	+	
Angle gripper HGW-16	+	
Angle gripper HGW-25	+	
Angle gripper HGW-32	+	
Angle gripper HGW-40	+	
Radial gripper HGR-16	+	
Radial gripper HGR-25	+	
Radial gripper HGR-32	+	
Radial gripper HGR-40	+	

+ Unrestricted use


o On request

1) Different from technical data. Usability on request.

# Position transmitters SMAT-8M, for T-slot

Peripherals overview

**FESTO**




Accessories	→ Page/Internet
1 Connecting cable NEBU-M8G4	9
2 Connecting cable NEBU-M8W4	9
3 Inscription label ASLR	9
4 Mounting kit SMBR-8-8/100-S6, heat-resistant	9
5 Mounting kit SMBR	9
6 Mounting SMBZ-8	9
7 Connecting cable NEBU-M8G4	9
8 Parallel gripper HGP	hgp
Three-point gripper HGD	hgd
Angle gripper HGW	hgw
Radial gripper HGR	hgr

Accessories	→ Page/Internet
9 Standard cylinder DNCB	dncb
Standard cylinder DNC	dnc
Compact cylinder ADN	adn
Short-stroke cylinder ADVC/AEVC	advc
Compact cylinder ADVU/AEJU	advu
Flat cylinder DZF	dzf
Linear drive DGC	dgc
Linear/swivel clamp CLR	clr
Guided drive DFM	dfm
Linear module HMPL	hmpl
10 Standard cylinder/round cylinder DSNU	dsnu
Linear unit SLE	sle
11 Standard cylinder DNG	dng
12 Signal converter SVE4	sve4

## Position transmitters SMAT-8M, for T-slot

Type codes




# Position transmitters SMAT-8M, for T-slot

Technical data

FESTO

Function

Normal operation



Technical data		
General		
Design		For T-slot
Certification		C-tick
CE marking (see declaration of conformity)		To EU EMC Directive
Input signal/measuring element		
Measuring principle		Magnetic
Position measuring range	[mm]	$\leq 40^{1)}$
Signal processing		
Max. speed of travel	[m/s]	3
Output, general		
Displacement resolution	[mm]	$\leq 0.05^{1)}$
Repetition accuracy	[mm]	$\pm 0.1^{1)}$ on cylinders $\pm 0.025^{1)}$ on grippers
Analogue output		
Typical linearity error	[mm]	$\pm 1^{1)}$ on cylinders $\pm 0.2^{1)}$ on grippers
Electrical outputs		
Analogue output	[V]	0 ... 10
Protection against short circuit		Yes
Protection against overloading		Yes
Output signal		Analogue
Electronics		
Operating voltage range	[V DC]	15 ... 30
Typical scanning interval	[ms]	3.4
Protection against polarity reversal		For all electrical connections
Electromechanics		
Electrical connection		Cable with plug, M8x1, knurled ring, 4-pin
Ambient temperature with flexible cable installation	[°C]	-5 ... +70
Cable length	[m]	0.3
Cable characteristics		Energy chain + robots
Cable test conditions		Energy chain: 5 million cycles, bending radius 28 mm Torsional strength: >300,000 cycles, $\pm 270^\circ/0.1$ m Resistance to bending: to Festo standard; test conditions on request
Information on materials for cable sheath		Thermoplastic polyurethane elastomer, halogen-free, oil-resistant

1) Depending on drive/gripper used.

# Position transmitters SMAT-8M, for T-slot


Technical data

Technical data	
<b>Mechanical components</b>	
Type of mounting	Secured with screw, insertable in the slot from above
Product weight [g]	10
Information on housing materials	Reinforced polyamide
Note on materials	RoHS-compliant
<b>Display/operation</b>	
Status display	LED red, green
<b>Immissions/emissions</b>	
Ambient temperature [°C]	-25 ... +75
Protection class	IP65, IP68
Corrosion resistance class CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

## Pin allocation




## Wire colours


BN = brown                      BU = blue  
 BK = black                      WH = white

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



B1	D1	D2	D3	H1	L1	L2	L3	L4	L5	⌀
5	M8x1	9.6	2.9	4.6	300	34.8	31.8	41.1	23	1.5




Ordering data					
Size	Analogue output [V]	Electrical connection	Cable length [m]	Part No.	Type
	0 ... 10	M8 plug, 4-pin, rotatable thread	0.3	553744	SMAT-8M-U-E-0,3-M8D







## Position transmitters SMAT-8M, for T-slot

Accessories

**FESTO**

Ordering data – Mounting attachments			
	For piston diameter	Part No.	Type
<b>Mounting kit SMBR-8-8/100-S6, heat-resistant</b>			
	8 ... 100	538937	SMBR-8-8/100-S6
<b>Mounting kit SMBR</b>			
	8	175091	SMBR-8-8
	10	175092	SMBR-8-10
	12	175093	SMBR-8-12
	16	175094	SMBR-8-16
	20	175095	SMBR-8-20
	25	175096	SMBR-8-25
	32	175097	SMBR-8-32
	40	175098	SMBR-8-40
	50	175099	SMBR-8-50
63	175100	SMBR-8-63	
<b>Mounting SMBZ</b>			
	32 ... 100	537806	SMBZ-8-32/100
	125 ... 320	537808	SMBZ-8-125/320

Ordering data – Connecting cable NEBU-M8				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541343	NEBU-M8G4-K-2.5-LE4
			5	541343	NEBU-M8G4-K-5-LE4
	Straight socket, M8x1, 4-pin	Straight socket, M8x1, 4-pin	2.5	554035	NEBU-M8G4-K-2.5-M8G4
	Angled socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541344	NEBU-M8W4-K-2.5-LE4
			5	541344	NEBU-M8W4-K-2.5-LE4

Ordering data – Inscription label ASLR				
	Size	Part No.	Type	PU <sup>1)</sup>
	23x4 mm	541598	ASLR-L-423	34

1) Packaging unit in quantity per frame