





Ball valve actuators VZPR



Ball valve actuators VZPR

Key features and product range overview


General	Construction	Characteristics	
<ul style="list-style-type: none"> -  - Connecting thread Rp$\frac{1}{4}$... Rp$2\frac{1}{2}$ -  - Flow rate Kv 5.9 ... 535 m³/h 	<ul style="list-style-type: none"> • Brass design VZPR ... • Stainless steel design VZPR ...-R • Port pattern to Namur VDI/VDE 3845 	<ul style="list-style-type: none"> • Combination of a pneumatic quarter-turn actuator and a ball valve • Flow is fully opened or closed in both directions • 5/2-way valve with Namur port pattern can be mounted directly on the drive unit • Limit switch attachments for end-position sensing can be mounted directly on the drive unit 	<p>Valves with Namur port pattern → Internet: namur</p> <p>Limit switch attachments with Namur mounting-hole pattern → Internet: dapz</p>

Version	Type	Connecting thread ¹⁾	Nominal diameter [mm]	Nominal operating pressure [bar]	→ Page/Internet
Brass					
	VZPR-BPD-...	Rp $\frac{1}{4}$	15	40	5
		Rp $\frac{3}{8}$	15	40	
		Rp $\frac{1}{2}$	15	40	
		Rp $\frac{3}{4}$	20	40	
		Rp1	25	40	
		Rp $1\frac{1}{4}$	32	40	
		Rp $1\frac{1}{2}$	40	25	
		Rp2	50	25	
		Rp $2\frac{1}{2}$	63	25	
Stainless steel					
	VZPR-BPD-...-R	Rp $\frac{1}{4}$	10	63	9
		Rp $\frac{3}{8}$	12		
		Rp $\frac{1}{2}$	16		
		Rp $\frac{3}{4}$	20		
		Rp1	25		
		Rp $1\frac{1}{4}$	32		
		Rp $1\frac{1}{2}$	40		
		Rp2	50		
		Rp $2\frac{1}{2}$	65		

1) Cylindrical barrel with female thread to DIN ISO 228-1

Ball valve actuators VZPR

Peripherals overview



Mounting attachments and accessories		
	Brief description	→ Page/Internet
1	Limit switch attachment QH-DR-E Square design Pneumatic, electrical or inductive sensing	qh-dr-e
2	Limit switch attachment DAPZ Square design Electrical, electrically explosion-proof or inductive sensing	dapz
3	Limit switch attachment DAPZ Round design, variant AR Electrical, inductive or inductively explosion-proof sensing	dapz
4	Limit switch attachment DAPZ Round design, variant RO	dapz
5	Solenoid valve MFH Basic valve with pilot control valve for F solenoid coil	8
	Solenoid valve MN1H Basic valve with pilot control valve for N1 solenoid coil	8
	Solenoid valve MGTBH Basic valve with pilot control valve, solenoid coil and socket	8
6	Solenoid valve NVF3 For F solenoid coil and explosion-proof F solenoid coil	8
7	Ball valve actuator VZPR Combination of quarter-turn actuator and ball valve Variants: Brass or stainless steel	8

Ball valve actuators VZPR

Type codes





		VZPR	-	B	P	D	H	-	22	-	R	38	R
Type													
VZPR	Ball valve actuator												
Valve													
B	Ball valve												
Drive													
P	Quarter-turn actuator DAPS												
Mode of operation													
D	Double-acting												
Torque													
H	With high torque												
Valve function													
22	2/2-way valve												
Closing direction													
R	Closes to right												
Connecting thread													
14	Rp1/4												
38	Rp3/8												
12	Rp1/2												
34	Rp3/4												
1	Rp1												
114	Rp1 1/4												
112	Rp1 1/2												
2	Rp2												
212	Rp2 1/2												
Variant													
R	Stainless steel version												

Ball valve actuators VZPR-BPD



Technical data

Function



-  Swivel angle
0 ... 90°
-  Flow rate Kv
5.9 ... 535 m³/h



-  Connecting thread
Rp1/4 ... Rp2 1/2
-  Torque
15 ... 180 Nm

General technical data									
Connecting thread	Rp1/4	Rp3/8	Rp1/2	Rp3/4	Rp1	Rp1 1/4	Rp1 1/2	Rp2	Rp2 1/2
Quarter-turn actuator									
Pneumatic connection	G1/8								
Constructional design	Scotch yoke mechanism, double-acting								
Type of mounting	Via female threads								
Mounting position	Any								
Swivel angle [°]	90								
Closing direction	Closes to right								
Torque at 5.6 bar and 0° swivel angle [Nm]	15	15	15	30	30	60	60	106	180
Ball valve									
Valve function	2/2								
Constructional design	2-way ball valve								
Sealing principle	Soft								
Actuation type	Pneumatic								
Direction of flow	Reversible								
Nominal diameter [mm]	15	15	15	20	25	32	40	50	63
Flow rate Kv [m ³ /h]	5.9	9.4	17	41	70	121	200	292	535

Operating and environmental conditions									
Connecting thread	Rp1/4	Rp3/8	Rp1/2	Rp3/4	Rp1	Rp1 1/4	Rp1 1/2	Rp2	Rp2 1/2
Ambient temperature [°C]	-20 ... +80								
Temperature of medium [°C]	-20 ... +150								
Corrosion resistance class CRC ²⁾	1								
Food industry approval	No								
Quarter-turn actuator									
Operating pressure ¹⁾ [bar]	1 ... 8.4								
Operating medium	Dried air, lubricated or unlubricated								
Ball valve									
Nominal operating pressure [bar]	40	40	40	40	40	40	25	25	25
Operating medium	Compressed air, water, neutral gasses, neutral fluids, vacuum								

1) Minimum operating pressures vary for single-acting quarter-turn actuators depending upon spring quantity.

2) Corrosion resistance class 1 to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Ball valve actuators VZPR-BPD


Technical data

FESTO

Materials		
Housing		Brass
Ball		Brass
Seals	Housing	Polytetrafluoroethylene, fibre glass reinforced
	Shaft	Fluoro elastomer

Weight [g]			
Connecting thread		Connecting thread	
Rp1/4	1300	Rp1 1/4	3200
Rp3/8	1300	Rp1 1/2	3800
Rp1/2	1200	Rp2	5400
Rp3/4	1500	Rp2 1/2	7300
Rp1	1800		

Operating pressure p2 as a function of nominal operating pressure p1




Ball valve actuators VZPR-BPD

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com




Connecting thread D1	B1	B2	B3	D2 Ø max.	D6 Ø	D7 Ø	H1	H2	H3
Rp1/4	52.2	24.2	28	35	9.2	13	72.2	28	20
Rp3/8									
Rp1/2									
Rp3/4	59.2	27.7	31.5	45	10.9	13	79.2	31.5	20
Rp1				55					
Rp1 1/4	70.4	32.7	37.7	65	14.5	13	90.4	37.7	20
Rp1 1/2				75					
Rp2	83.3	38.5	44.8	90	16.2	17	103.3	44.8	20
Rp2 1/2	107.5	51	56.5	110	20.2	22	137.5	56.5	30



Connecting thread D1	H4	H5	H6	L1	L2	L3	T3	⊥1	⊥2
Rp1/4	92.5	0.8	3.2	159	15	75	10	26	8
Rp3/8									
Rp1/2									
Rp3/4	104.2	-	4	174	16	80	10	32	9
Rp1					19			41	
Rp1 1/4	130.2	-	4	198	21	110	13	50	10
Rp1 1/2	135.4				55				
Rp2	158.3	-	4	236.5	25	140	13	70	12
Rp2 1/2	192.5			289.9	24	143	16	83	15

Ball valve actuators VZPR-BPD

Technical data

FESTO

Ordering data – Ball valve actuators		Part No.	Type
	Connecting thread		
	Rp1/4	540 510	VZPR-BPD-22-R14
	Rp3/8	540 511	VZPR-BPD-22-R38
	Rp1/2	540 512	VZPR-BPD-22-R12
	Rp3/4	540 513	VZPR-BPD-22-R34
	Rp1	540 514	VZPR-BPD-22-R1
	Rp1 1/4	540 515	VZPR-BPD-22-R114
	Rp1 1/2	540 516	VZPR-BPD-22-R112
	Rp2	540 517	VZPR-BPD-22-R2
Rp2 1/2	540 874	VZPR-BPD-22-R212	

Ordering data – Limit switch attachments (Namura)		Technical data → Internet: dapz, qh-dr	
Sensing principle	Explosion-proof	Part No.	Type
Square design			
	Electrical	–	534 468 DAPZ-SB-M-250AC-DSM-RO
	Electrical	■	534 470 DAPZ-SB-M-250AC-EXS-RO
	Inductive	–	534 473 DAPZ-SB-I-30DC-DSAM-RO
	Pneumatic	–	164 855 QH-DR-E-S3-PK-3-B-B
	Electrical	–	164 854 QH-DR-E-S3-E-SW-B
	Inductive	–	164 853 QH-DR-E-SIEN-M12-NB-B
Round design			
	Electrical	–	534 469 DAPZ-SB-M-250AC-DR-RO
	Inductive	–	534 471 DAPZ-SB-I-30DC-DR-RO
	Inductive	■	534 472 DAPZ-SB-I-25DC-R-RO
	Electrical	–	534 474 DAPZ-SB-M-250AC-DR-AR
	Inductive	–	534 475 DAPZ-SB-I-30DC-DR-AR
	Inductive	■	534 476 DAPZ-SB-I-25DC-EXDR-AR


Ordering data – Solenoid valves (Namura)		Technical data → Internet: solenoid valves	
Standard nominal flow rate	For coil type	Part No.	Type
900	F solenoid coil	535 987	NVF3-MOH-5/2-K-1/4-EX
	V solenoid coil	535 988	NVF3-MOH-5/2-K-1/4-1A-EX
1000	F solenoid coil	183 973	MFH-5/2K-FR-NA
	N1 solenoid coil	183 974	MN1H-5/2K-FR-NA
	1)	184 105	MGTBH-3/2-1,2-24DC
	1)	185 246	MGTBH-3/2-1,2-110AC
	1)	185 248	MGTBH-3/2-1,2-230AC

1) Solenoid coil included in scope of delivery

Ball valve actuators VZPR-BPD, stainless steel


Technical data


Function



-  - Connecting thread
Rp1/4 ... Rp2 1/2

-  - Torque
30 ... 240 Nm

-  - Swivel angle
0 ... 90°

-  - Flow rate Kv
16 ... 507 m³/h



General technical data									
Connecting thread	Rp1/4	Rp3/8	Rp1/2	Rp3/4	Rp1	Rp1 1/4	Rp1 1/2	Rp2	Rp2 1/2
Drive									
Pneumatic connection	G1/8								
Constructional design	Scotch yoke mechanism, double-acting								
Type of mounting	Via female threads								
Mounting position	Any								
Swivel angle [°]	90								
Closing direction	Closes to right								
Torque at 5.6 bar and 0° swivel angle [Nm]	30	30	30	30/60 ¹⁾	60	60/106 ¹⁾	106/180 ¹⁾	180	240
Ball valve									
Valve function	2/2								
Constructional design	2-way ball valve								
Sealing principle	Soft								
Actuation type	Pneumatic								
Direction of flow	Reversible								
Nominal diameter [mm]	10	12	16	20	25	32	40	50	65
Flow rate Kv [m ³ /h]	16	21	35	46	72	105	170	275	507

1) With this connecting thread there are two ball valve actuators with different torques available for selection.

Operating and environmental conditions	
Ambient temperature [°C]	-20 ... +80
Temperature of medium [°C]	-20 ... +150
Corrosion resistance class CRC ¹⁾	3
Food industry approval	No
Quarter-turn actuator	
Operating pressure ²⁾ [bar]	1 ... 8.4
Operating medium	Dried air, lubricated or unlubricated
Ball valve	
Nominal operating pressure [bar]	63
Operating medium	Compressed air, water, neutral gasses, neutral fluids, vacuum

- 1) Corrosion resistance class 3 to Festo standard 940 070
Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.
- 2) Minimum operating pressures vary for single-acting quarter-turn actuators depending upon spring quantity.

Materials	
Housing	High-alloy stainless steel
Ball	High-alloy stainless steel
Seals	Housing Polytetrafluoroethylene, fibre glass reinforced
	Shaft Fluoro elastomer

Ball valve actuators VZPR-BPD, stainless steel



Technical data

FESTO



Weight [g]		Connecting thread	
Connecting thread		Connecting thread	
Rp1/4	1200	Rp1/4, torque: 60 Nm	3800
Rp3/8	1200	Rp1/4, torque: 100 Nm	4200
Rp1/2	1700	Rp1/2, torque: 100 Nm	5100
Rp3/4, torque: 30 Nm	1800	Rp1/2, torque: 180 Nm	7000
Rp3/4, torque: 60 Nm	2700	Rp2	8700
Rp1	3100	Rp2 1/2	14400

Operating pressure p2 as a function of nominal operating pressure p1

Standard torque




High torque



Dimensions

Download CAD data → www.festo.com



Ball valve actuators VZPR-BPD, stainless steel

Technical data


Connecting thread D1	Torque [Nm]	B1	B2	B3	B4 max.	D6 ∅	D7 ∅	H1	H2	H3
Rp1/4	30	59.2	27.7	31.5	50	10.9	13	79.2	31.5	20
Rp3/8	30									
Rp1/2	30									
Rp3/4	30									
Rp3/4	60	70.4	32.7	37.7	55	14.5	13	90.4	37.7	20
Rp1	60				65					
Rp1 1/4	60				75					
Rp1 1/4	106				75					
Rp1 1/2	106	83.3	38.5	44.8	85	16.2	17	103.3	44.8	20
Rp1 1/2	180				85					
Rp2	180				100					
Rp2 1/2	240				170					
Rp2 1/2	240	111.1	51	60.1	170	22.5	22	141.1	60.1	30



Connecting thread D1	Torque [Nm]	H4 ±2	H5	H6	L1	L2	L3 ±2	T3	≈C1	≈C2
Rp1/4	30	101.2	0.8	4	174.3	14	65	10	19	9
Rp3/8	30								24	
Rp1/2	30								29	
Rp3/4	30								35	
Rp3/4	60	115.4	-	-	198.1	19	80	13	35	10
Rp1	60	122.4							41	
Rp1 1/4	60	128.4							50	
Rp1 1/4	106	141.3							50	
Rp1 1/2	106	151.3	-	-	237.1	23	110	13	58	12
Rp1 1/2	180	175.5							58	
Rp2	180	185.5							73	
Rp2 1/2	240	210.1							90	
Rp2 1/2	240	210.1	-	-	313.6	38	185	17	90	19


Ball valve actuators VZPR-BPD, stainless steel

FESTO

Technical data

Ordering data		Connecting thread	Part No.	Type
		Rp1/4	540 526	VZPR-BPD-22-R14R
		Rp3/8	540 527	VZPR-BPD-22-R38R
		Rp1/2	540 528	VZPR-BPD-22-R12R
		Rp3/4, torque: 30 Nm/operating pressure: 5.6 bar	540 529	VZPR-BPD-22-R34R
		Rp3/4, torque: 60 Nm/operating pressure: 5.6 bar	540 875	VZPR-BPDH-22-R34R
		Rp1	540 530	VZPR-BPD-22-R1R
		Rp1 1/4, torque: 60 Nm/operating pressure: 5.6 bar	540 531	VZPR-BPD-22-R114R
		Rp1 1/4, torque: 100 Nm/operating pressure: 5.6 bar	540 876	VZPR-BPDH-22-R114R
		Rp1 1/2, torque: 100 Nm/operating pressure: 5.6 bar	540 532	VZPR-BPD-22-R112R
		Rp1 1/2, torque: 180 Nm/operating pressure: 5.6 bar	540 877	VZPR-BPDH-22-R112R
		Rp2	540 533	VZPR-BPD-22-R2R
		Rp2 1/2	540 878	VZPR-BPD-22-R212R

Ordering data – Limit switch attachments (Namura)			Technical data → Internet: dapz, qh-dr	
	Sensing principle	Explosion-proof	Part No.	Type
Square design				
	Electrical	–	534 468	DAPZ-SB-M-250AC-DSM-RO
	Electrical	■	534 470	DAPZ-SB-M-250AC-EXS-RO
	Inductive	–	534 473	DAPZ-SB-I-30DC-DSAM-RO
	Pneumatic	–	164 855	QH-DR-E-S3-PK-3-B-B
	Electrical	–	164 854	QH-DR-E-S3-E-SW-B
	Inductive	–	164 853	QH-DR-E-SIEN-M12-NB-B
Round design				
	Electrical	–	534 469	DAPZ-SB-M-250AC-DR-RO
	Inductive	–	534 471	DAPZ-SB-I-30DC-DR-RO
	Inductive	■	534 472	DAPZ-SB-I-25DC-R-RO
	Electrical	–	534 474	DAPZ-SB-M-250AC-DR-AR
	Inductive	–	534 475	DAPZ-SB-I-30DC-DR-AR
	Inductive	■	534 476	DAPZ-SB-I-25DC-EXDR-AR

Ordering data – Solenoid valves (Namura)		Technical data → Internet: solenoid valves		
	Standard nominal flow rate	For coil type	Part No.	Type
	900	F solenoid coil	535 987	NVF3-MOH-5/2-K-1/4-EX
		V solenoid coil	535 988	NVF3-MOH-5/2-K-1/4-IA-EX
	1000	F solenoid coil	183 973	MFH-5/2K-FR-NA
		N1 solenoid coil	183 974	MN1H-5/2K-FR-NA
		¹⁾	184 105	MGTBH-3/2-1,2-24DC
		¹⁾	185 246	MGTBH-3/2-1,2-110AC
		¹⁾	185 248	MGTBH-3/2-1,2-230AC
		¹⁾		

1) Solenoid coil included in scope of delivery