

Limit switch attachments DAPZ

FESTO



Limit switch attachments DAPZ

FESTO


Type codes

		DAPZ	–	SB	–	M	–	250AC	–	EXS	–	RO
Type												
DAPZ	Limit switch attachment											
Specification												
SB	Sensor box											
Measuring principle												
I	Inductive											
M	Electrical, micro switch											
Operating voltage												
25DC	25 V DC											
30DC	30 V DC											
250AC	250 V AC											
Design												
EX	Explosion-proof											
D	Display											
S	Square design											
R	Round design											
A	AS-interface connection											
M	Solenoid plug											
Variant												
RO	Foot height fixed											
AR	Foot height adjustable											

Limit switch attachments DAPZ, square design

Technical data

- Drive interface to Namur VDI/VDE 3845
- Simple and quick assembly and connection
- Integrated solenoid valve actuation
- DAPZ-SB-I-... with AS-interface



General technical data			
Sensing type	Mechanical		Contactless
Variant	Basic version	Explosion-proof	Basic version
Measuring principle	Electrical	Electrical	Inductive
Operating voltage range	[V AC]	0 ... 250	–
	[V DC]	–	10 ... 30
Max. switching capacity	16 A, 250 V AC	4 A, 250 V AC	–
Switching element function	Changeover switch	Changeover switch	Normally closed contact
Electrical connection	M20x1.5	M20x1.5	AS-interface flat cable plug
Display	Yes	No	Yes
Ambient temperature [°C]	–25 ... +85	–25 ... +85	–25 ... +85
Protection class	Housing IP65	Housing IP65	Housing IP65
ATEX category gas	–	II 2G	–
Explosion ignition protection type gas	–	Ex ed IIC T6	–
Explosion-proof ambient temperature	–	–20°C ≤ Ta ≤ +60°C	–
CE marking symbol (see conformity declaration)	As per EU low voltage directive	As per EU explosion protection directive (ATEX)	–
Certificate issuing office	–	PTB 05 ATEX 1087	–
Corrosion resistance class CRC ¹⁾	2	3	2

- 1) Corrosion resistance class 2 according to Festo standard 940 070
 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents
 Corrosion resistance class 3 according to Festo standard 940 070
 Components with heavy corrosion exposure. Externally visible components in direct contact with normal industrial atmosphere or media such as solvents and cleaning agents, where the surface requirement is predominantly functional

Materials			
Sensing type	Mechanical		Contactless
Variant	Basic version	Explosion-proof	Basic version
Housing socket	Polyamide, black	Polyamide, black	Polyamide, black
Housing cover	Polycarbonate, transparent	Polyamide, black	Polycarbonate, transparent
Seal	Silicone, ethylene propylene rubber or nitrile rubber	Ethylene propylene rubber	Silicone, ethylene propylene rubber or nitrile rubber


Limit switch attachments DAPZ, square design

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



- 1 Connection for AS-interface flat cable
- 2 Cable conduit fitting M12x1.5
- 3 Solenoid plug

	B1	B2	H1	H2	L1	L2	L3
Feet mounted inwards							
Foot 20	30	64	20	80	80	145	300
Foot 30	30	64	30	80	80	145	300
Foot 50 (order accessories separately)	30	64	50	80	80	145	300
Feet mounted outwards							
Foot 20	30	64	20	80	130	145	300
Foot 30	30	64	30	80	130	145	300
Foot 50 (order accessories separately)	30	64	50	80	130	145	300
Mounting with adapter (order accessories separately) → 9							
DAPZ-SBZ-K0-RO	25	64	20	80	50	145	300
DAPZ-SBZ-K3-RO	30	64	30	80	150	145	300

Ordering data					
Sensing type	Variant	Measuring principle	Operating voltage	Part No.	Type
Mechanical	Basic version	Electrical	250 V AC	534 468	DAPZ-SB-M-250AC-DSM-RO
Mechanical	Explosion-proof	Electrical	250 V AC	534 470	DAPZ-SB-M-250AC-EXS-RO
Contactless	Basic version	Inductive	30 V DC	534 473	DAPZ-SB-I-30DC-DSAM-RO

Limit switch attachments DAPZ, round design, variant RO

FESTO

Technical data

- Drive interface to Namur
VDI/VDE 3845
- Simple and quick assembly
and connection
- Integrated solenoid valve actuation



General technical data			
Sensing type	Mechanical	Contactless	
Variant	Basic version	Basic version	Explosion-proof
Measuring principle	Electrical	Inductive	Inductive
Operating voltage range	[V AC]	0 ... 250	–
	[V DC]	–	10 ... 30
Max. switching capacity	16 A, 250 V AC	–	–
Switching element function	Changeover switch	NO contact, PNP	NC contact, Namur
Electrical connection	M20x1.5	M20x1.5	M20x1.5
Display	Yes	Yes	No
Ambient temperature [°C]	–25 ... +100	–25 ... +70	–25 ... +70
Protection class	Housing IP65	Housing IP65	Housing IP65
ATEX category gas	–	–	II 2G
Explosion ignition protection type gas	–	–	EEx ia IIC T6
Explosion-proof ambient temperature	–	–	–25°C ≤ Ta ≤ +70°C
CE marking symbol (see conformity declaration)	As per EU low voltage directive	–	As per EU explosion protection directive (ATEX)
Certificate issuing office	–	–	TÜV 99 ATEX 1479 X
Corrosion resistance class CRC ¹⁾	2	2	2

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Materials			
Sensing type	Mechanical	Contactless	
Variant	Basic version	Basic version	Explosion-proof
Housing socket	Polyamide, black	Polyamide, black	Polyamide, black
Housing cover	Polycarbonate, transparent	Polycarbonate, transparent	Polyamide, black
Seal	Silicone, ethylene propylene rubber or nitrile rubber	Silicone, ethylene propylene rubber or nitrile rubber	Silicone, ethylene propylene rubber or nitrile rubber

Limit switch attachments DAPZ, round design, variant RO

FESTO

Technical data

Dimensions

Basic version

2 Cable conduit fitting M20x1.5

Download CAD data → www.festo.com

Explosion-proof

2 Cable conduit fitting M20x1.5

	B1	B2	H1	H2	H3	L1	L2
Feet mounted inwards							
Foot 20	30	80	20	97	75	80	122
Foot 30	30	80	30	97	75	80	122
Foot 50 (order accessories separately)	30	80	50	97	75	80	122
Feet mounted outwards							
Foot 20	30	80	20	97	75	130	122
Foot 30	30	80	30	97	75	130	122
Foot 50 (order accessories separately)	30	80	50	97	75	130	122
Mounting with adapter (order accessories separately)							→ 9
DAPZ-SBZ-K0-RO	25	80	20	97	75	50	122
DAPZ-SBZ-K3-RO	30	80	30	97	75	150	122

Ordering data					
Sensing type	Variant	Measuring principle	Operating voltage	Part No.	Type
Mechanical	Basic version	Electrical	250 V AC	534 469	DAPZ-SB-M-250AC-DR-RO
Contactless	Basic version	Inductive	30 V DC	534 471	DAPZ-SB-I-30DC-DR-RO
Contactless	Explosion-proof	Inductive	25 V DC	534 472	DAPZ-SB-I-25DC-R-RO

Limit switch attachments DAPZ, round design, variant AR

FESTO

Technical data

- Drive interface to Namur
VDI/VDE 3845
- Simple and quick assembly
and connection
- Integrated solenoid valve actuation



General technical data			
Sensing type	Mechanical	Contactless	
Version	Basic version	Basic version	Explosion-proof
Sensing principle	Electrical	Inductive	Inductive
Operating voltage range	[V AC]	4 ... 250	–
	[V DC]	4 ... 250	10 ... 30
Nominal operating voltage	[V DC]	–	8
Insulation voltage	[V]	250	50
Surge strength	[kV]	2.5	0.5
Protection against short circuit	None	Pulsed	None
Intrinsic current consumption at operating voltage	1 mA ... 5 A	0 ... 100 mA	–
Switching current	attenuated [mA]	–	≤ 1
	non-attenuated [mA]	–	≥ 3
Switching element function	Changeover switch	NO contact, PNP	NC contact, Namur
Electrical connection	M20x1.5	M20x1.5	M20x1.5
Display	Yes	Yes	Yes
Ambient temperature	[°C]	–20 ... +70	–20 ... +70
Design	Round	Round	Round
Mounting position	Any	Any	Any
Type of mounting	Via through-holes	Via through-holes	Via through-holes
Connectable nominal conductor cross section	[mm²]	< 2.5	< 2.5
Cable diameter	[mm]	7 ... 13	7 ... 13
Protection class	IP67	IP67	IP67
Degree of contamination	3	3	3
ATEX symbol	–	–	II 2 G EEx ia IIB T6
ATEX ambient temperature	–	–	–20°C ≤ Ta ≤ +70°C
CE mark (see declaration of conformity)	In accordance with EU Low Voltage Directive	–	In accordance with EU explosion protection directive (ATEX)
Corrosion resistance class CRC ¹⁾	2	2	2
Protection against polarity reversal	–	For all electrical connections	–
Based on standard	EN 60947-5-1	EN 60947-5-2	EN 60947-5-2, EN 60947-5-6

1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Materials			
Sensing type	Mechanical	Contactless	
Variant	Basic version	Basic version	Explosion-proof
Housing socket	Acrylic butadiene styrene	Acrylic butadiene styrene	Acrylic butadiene styrene
Housing cover	Polycarbonate, transparent	Polycarbonate, transparent	Polycarbonate, transparent
Seal	Nitrile rubber	Nitrile rubber	Nitrile rubber


Limit switch attachments DAPZ, round design, variant AR

FESTO

Technical data

Dimensions

Download CAD data → www.festo.com



2 Cable conduit fitting M20x1.5




	B1	B2	B3	H1	H2	L1	L2	L3
Feet mounted inwards								
Foot height adjustable	30	62	52.5	20, 30, 50	100	80	144	130
Feet mounted outwards								
Foot height adjustable	30	62	52.5	20, 30, 50	100	130	144	130

Ordering data					
Sensing type	Variant	Measuring principle	Operating voltage	Part No.	Type
Mechanical	Basic version	Electrical	250 V AC	534 474	DAPZ-SB-M-250AC-DR-AR
Contactless	Basic version	Inductive	30 V DC	534 475	DAPZ-SB-I-30DC-DR-AR
Contactless	Explosion-proof	Inductive	25 V DC	534 476	DAPZ-SB-I-25DC-EXDR-AR

Limit switch attachments DAPZ

Accessories

FESTO

Ordering data		
	Brief description	Part No. Type
Foot		
	Kit for limit switch attachment DAPZ-...-RO Shaft height 50 mm, port pattern 130 x 30 mm	534 477 DAPZ-SBZ-F50-RO
Adapter for foot mounting		
	Kit for limit switch attachment DAPZ-...-RO on the quarter turn actuator DRD/DRE sizes 1 and 2 Foot connection L50 x B25 x H20 mm	534 478 DAPZ-SBZ-K0-RO
	Kit for limit switch attachment DAPZ-...-RO on the quarter turn actuator DRD/DRE sizes 375 ... 880 Foot connection L150 x B30 x H30 mm	534 479 DAPZ-SBZ-K3-RO
Bus connection		
	Flat cable for AS-interface components, yellow, 100 m	18 940 KASI-1,5-Y-100
	Cable distributor for flat cable, cable parallel, rotatable	18 786 ASI-KVT-FK
	Cable distributor for flat cables, cables symmetrical	18 797 ASI-KVT-FK-S
	Cable cap for flat cable (50 included in scope of delivery)	18 787 ASI-KK-FK
	Cable sleeve (20 included in scope of delivery)	165 593 ASI-KT-FK
Other		
	Combi power pack for AS-interface	191 082 ASI-CNT-115/230-VAC-B
	Addressing device for AS-interface stations	18 959 ASI-PRG-ADR
	Addressing cable for addressing device	18 960 KASI-ADR

Limit switch attachments QH-DR-E

FESTO

Technical data

Limit switch attachment with choice of
3 sensing methods:

- Pneumatic
with micro stem actuated valve
S-3-PK-3-B
- Electrical
with micro switch with roller lever,
IP 67 (splash-proof) S-3-E-SW-B
- Inductive
with proximity sensor
SIEN-M12-NB-B



Technical data	
Pneumatic sensing	
Medium	Filtered compressed air, lubricated or unlubricated
Function	3/2-way valve, directly actuated, normally closed
Pneumatic connection	Barbed fitting for 3 mm plastic tubing
Nominal size	1.8 mm
Operating pressure range	-1 ... +8 bar
Connection	Pg13.5
Temperature range	-10 ... +60 °C
Electrical sensing	
Utilisation category	AC 15/AC 12; DC 13/DC 12
Operating voltage range	0 ... 250 V AC; 0 ... 250 V DC
Rated operating current at rated operating voltage	Ohmic load (AC 12 / DC 12): 230 V DC: 0.3 A, 230 V AC: 10 A Inductive load (AC 12 / DC 12): 230 V DC: 0.2 A, 230 V AC: 4 A
Rated surge voltage	2.5 kV
Cross-section of connectable cables	0.2 ... 2.5 mm ²
Electrical connection	Cable gland connector Pg13.5
Temperature range	-25 ... +80 °C
Protection class	Housing IP65
CE symbol	Yes, to EN 60 947-5-1: 1991
Inductive sensing	
Operating voltage range	10 ... 30 V DC
Rated operating current	200 mA
Idle current	≤1 mA
Output	Short circuit proof, reverse polarity protected Voltage drop: ≤ 3.2 V, residual current: ≤ 0.01 mA
Cross-section of connectable cables	0.2 ... 2.5 mm ²
Electrical connection	Cable gland connector Pg13.5
Temperature range	-25 ... +85 °C
Display	Yellow LED
Protection class	Housing IP65
CE symbol	Yes, to EN 50 947-5-2:1995

Materials	
Housing base	Polymer
Cover	Transparent polymer
Seal	Ethylene propylene rubber


Limit switch attachments QH-DR-E

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



1 Cable gland connector Pg13.5

	B1	B2	D1 Ø	H1	H2	L1	L2
QH-DR-E- ...	64	30	5.5	102	28.5	146	80

Ordering data

Sensing principle	Part No.	Type
Pneumatic with S3-PK-3-B	164 855	QH-DR-E-S3-PK-3-B-B
Electrical with S3-E-SW-B	164 854	QH-DR-E-S3-E-SW-B
Inductive with SIE-M12-NB-B	164 853	QH-DR-E-SIEN-M12-NB-B