


pressure vacuum generator PGVA-2-P1V1-Q4-A

Broj artikla: 8163214
Novo

FESTO



Tehnički podaci

Svojstvo	Vrednost
Položaj ugradnje	proizvoljno
Finoća filtera	0,01 µm
Podrška konfiguracije	Phyton scripts
Prikaz	LED
Output pressure 1 (MPa)	-0,062 MPa
Output pressure 2	0,08 MPa
Standard flow rate	< 1,2 l/min
Dimenzije Š x D x V	169 mm x 208 mm x 55 mm
Područje pogonskog napona DC	21,6 ... 26,4 V
Električna primljena snaga	11 W
Nazivni pogonski napon DC	24 V
Dozvoljena kolebanja napona	+/- 10 %
Power supply, function	Load and functional earth
Power supply, type of connection	Utičnica
Power supply, connection technology	Terminal strip
Power supply, number of pins/wires	5
Dozvola	RCM Mark
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Otpornost na vibracije	Ispitivanje transporta sa stepenom težine 2 prema FN 942017-4 i EN 60068-2-6
Udarna čvrstoća	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Temperatura ležaja	-20 ... 70 °C
Relativna vlažnost vazduha	0 - 85 %
Sound power level	55 dB(A)
Mehanička zaštita	IP20
Temperatura okoline	0 ... 40 °C
Težina proizvoda	1,8 kg
Električno aktiviranje	integrirani kontroler
Vrsta pričvršćenja	With female thread M4
Pneumatski priključak 1	QS-4
Pneumatski priključak 2	QS-4
Pneumatic connection, number	2
Boja kućišta	sivo
Materijal - napomena	RoHS komformnost
Material housing	Aluminium, powder-coated