

Proportional pressure regulators VPPE/VPPE with display



FESTO



Proportional pressure regulators VPPE/VPPE with display

FESTO


Product range overview

Function	Version	Pneumatic connection 1	Nominal size for air supply/exhaust [mm]	Pressure regulation range [bar]	Setpoint input		→ Page/Internet
					Voltage type 0 ... 10 V	Current type 4 ... 20 mA	
Pressure regulators		G1/8	5/2.5	0.15 ... 6	■	—	5
		G1/8	5/2.5	0.02 ... 2	■	■	8
				0.06 ... 6			
				0.1 ... 10			

Proportional pressure regulators VPPE/VPPE with display

Peripherals overview

FESTO



Accessories			
	Type	Brief description	→ Page/Internet
1	Proportional pressure regulator	VPPE	5
2	Proportional pressure regulator with display	VPPE...E1	8
3	Setpoint module	MPZ	For generating 6+1 analogue voltage signals
4	Digital input/output	–	For actuating the setpoint module
5	Plug socket with cable	SIM-M12-5GD-...-PU	With straight plug socket for actuating the VPPE...E1
6	Plug socket with cable	SIM-M12-4GD-5PU	With straight plug socket for actuating the VPPE
7	Plug socket with cable	SIM-M12-4WD-5PU	With angled plug socket for actuating the VPPE
8	Plug socket	SIE-GD	Straight plug socket for actuating the VPPE
9	Plug socket	SIE-WD-TR	Angled plug socket for actuating the VPPE
10	Push-in fitting	QS	For compressed air tubing with standard O.D.
11	Silencer	U	For fitting in exhaust ports

Proportional pressure regulators VPPE

Type codes

FESTO

VPPE		3	1/8	6	010
Type					
VPPE	Proportional pressure regulator with switching valve head				
Valve function					
3	3-way pressure regulator				
Pneumatic connection					
1/8	Female thread G1/8				
Pressure regulation range					
6	0.15 ... 6 bar				
Analogue setpoint input					
010	0 ... 10 V				

Proportional pressure regulators VPPE

FESTO

Technical data

-  - Flow rate
1,000 l/min

-  - Voltage
21.6 ... 26.4 V DC

-  - Pressure regulation range
0.15 ... 6 bar


Variants

- Setpoint input as analogue voltage signal 0 ... 10 V



General technical data			
Pneumatic connection 1 and 2			G1/8
Design			Pilot actuated 3-way proportional pressure regulator
Sealing principle			Soft
Actuation type			Electrical
Type of control			Pilot actuated via 2/2-way valves
Type of mounting			Via through-hole
Mounting position			Any, preferably vertical
Nominal size	Air supply	[mm]	5
	Exhaust	[mm]	2.5
Standard nominal flow rate		[l/min]	→ Graph
Product weight		[g]	445

Flow rate qn as a function of output pressure p2



Electrical data	
Electrical connection	Plug, round design, 4-pin, M12x1
Operating voltage range	[V DC] 24 ±10% = 21.6 ... 26.4
Power supply indicator	LED
Residual ripple	10%
Max. electrical power consumption	[W] 3.6
Setpoint input signal	[V DC] 0 ... 10
Protection against short circuit	For all electrical connections
Reverse polarity protection	For all electrical connections
Protection class	IP65
CE mark (see declaration of conformity)	To EU EMC Directive

-  - Note
Output pressure is maintained unregulated if the power supply cable is interrupted.

Proportional pressure regulators VPPE

Technical data

FESTO

Operating and environmental conditions		
Operating medium		Filtered, unlubricated compressed air, grade of filtration 40 µm Neutral gases
Supply pressure 1	[bar]	7 ... 8
Pressure regulation range	[bar]	0.15 ... 6
Max. pressure hysteresis	[bar]	0.15
Ambient temperature	[°C]	10 ... 50
Temperature of medium	[°C]	10 ... 50
Corrosion resistance class CRC		2 ¹⁾

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Information on materials	
Housing	Wrought aluminium alloy
Seals	NBR

Dimensions

1 Earthing hole

[Download CAD data → www.festo.com](http://www.festo.com)

Type												
VPPE-3-1/8-6-010	B1	B2	∅ D1	D2	EE	H1	H2	H3	H4	H5	H6	
	50	32	4.5	M12x1	G1/8	114	102	23	13	28	8	

M12x1 – Pin allocation for VPPE

- 1 Power supply
21.6 ... 26.4 V DC
- 2 Setpoint (-)
- 3 GND (-)
- 4 Setpoint (+) 0 ... 10 V DC

Ordering data		
Pneumatic connection	Pressure regulation range [bar]	Part No. Type
G1/8	0 ... 6	539639 VPPE-3-1/8-6-010

Proportional pressure regulators VPPE with display

FESTO

Type codes

		VPPE	–	3	–	1/8	–	6	–	010	–	E1	T
Type													
VPPE	Proportional pressure regulator with switching valve head												
Valve function													
3	3-way pressure regulator												
Pneumatic connection													
1/8	Female thread G1/8												
Pressure regulation range													
2	0.02 ... 2 bar												
6	0.06 ... 6 bar												
10	0.1 ... 10 bar												
Analogue setpoint input													
010	0 ... 10 V												
420	4 ... 20 mA												
Operator unit													
E1	Segmented LED display												
Operator unit													
–	In-line valve												
T	Common supply manifold assembly												

Proportional pressure regulators VPPE with display

FESTO

Technical data

-  Flow rate
310 ... 1,250 l/min
-  Voltage
21.6 ... 26.4 V DC
-  Pressure regulation range
0.02 ... 2 bar
0.06 ... 6 bar
0.1 ... 10 bar

Variants

- Setpoint input as analogue voltage signal 0 ... 10 V
- Setpoint input as analogue current signal 4 ... 20 mA
- Assembly as in-line valve or on common supply manifold (manifold on request)
- 3-digit LED display





General technical data			
Pneumatic connection 1 and 2			G1/8
Design and valve function			Pilot actuated 3-way proportional pressure regulator
Sealing principle			Soft
Actuation type			Electrical
Reset method			Mechanical spring
Type of control			Pilot actuated via 2/2-way valves
Type of mounting			Via through-hole
Mounting position			Any
Nominal size	Air supply	[mm]	5
	Exhaust	[mm]	2.5
Standard nominal flow rate			→ Graphs
Product weight			390

Flow rate q_n as a function of output pressure p_2



VPPE-3-1-1/8-2- ... $q_n 1 \rightarrow 2$

$q_n 2 \rightarrow 3$





VPPE-3-1-1/8-6- ... $q_n 1 \rightarrow 2$

$q_n 2 \rightarrow 3$



VPPE-3-1-1/8-10- ... $q_n 1 \rightarrow 2$

$q_n 2 \rightarrow 3$



Proportional pressure regulators VPPE with display

FESTO

Technical data

Electrical data			
Electrical connection		Plug, round design, 5-pin, M12x1	
Operating voltage range		[V DC]	24 ±10% = 21.6 ... 26.4
Power supply indicator		LED	
Residual ripple		10%	
Max. electrical power consumption		[W]	4.2
Setpoint input and analogue output signal	Voltage	[V DC]	0 ... 10
	Current	[mA]	4 ... 20
Protection against short circuit		For all electrical connections	
Switching output		PNP	
Reverse polarity protection		For all electrical connections	
Protection class		IP65	
CE mark (see declaration of conformity)		To EU EMC Directive	

Operating and environmental conditions				
Pressure regulation range	[bar]	0.02 ... 2	0.06 ... 6	0.1 ... 10
Operating medium		Filtered, unlubricated compressed air, grade of filtration 40 µm Neutral gases		
Supply pressure 1	[bar]	3 ... 4	6 ²⁾ ... 8	6 ²⁾ ... 11
Max. pressure hysteresis	[mbar]	20	30	50
FS (full scale) linearity error	[%]	± 1		
FS (full scale) repetition accuracy	[%]	0.5		
Temperature coefficient	[%/K]	0.04/1		
Duty cycle	[%]	100		
Ambient temperature	[°C]	0 ... 60		
Temperature of medium	[°C]	10 ... 50		
Corrosion resistance class	[CRC]	2 ¹⁾		

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents
- 2) Supply pressure 1 should always be 1 bar greater than the maximum regulated output pressure

 Note

Output pressure is maintained unregulated if the power supply cable is interrupted.

Information on materials	
Housing	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant


Proportional pressure regulators VPPE with display

Technical data

FESTO


Dimensions

Download CAD data → www.festo.com



Type												
VPPE-3-1/8-... E1 ...	B1	B2	B3	∅ D1	D2	EE	H1	H2	H3	H4	H5	H6
	50	32	3.05	4.5	M12x1	G1/8	117.2	105.8	27.5	73.8	63.8	17.5
	H7	H8	H9									
	32.5	22.5	7									

M12x1 – Pin allocation for VPPE with display



- 1 Power supply
21.6 ... 26.4 V DC
- 2 Setpoint (-)
- 3 GND (-)
- 4 Setpoint (+) 0 ... 10 V DC/
4 ... 20 mA
- 5 Actual value output or switching output (can be chosen via the control panel)

Ordering data			
Pneumatic connection	Pressure regulation range [bar]	Voltage type 0 ... 10 V Part No. Type	Current type 4 ... 20 mA Part No. Type
G1/8	0.02 ... 2	557771 VPPE-3-1-1/8-2-010-E1	557774 VPPE-3-1-1/8-2-420-E1
		557777 VPPE-3-1-1/8-2-010-E1T	557779 VPPE-3-1-1/8-2-420-E1T
	0.06 ... 6	557772 VPPE-3-1-1/8-6-010-E1	557775 VPPE-3-1-1/8-6-420-E1
		567539 VPPE-3-1-1/8-6-010-E1T	567540 VPPE-3-1-1/8-6-420-E1T
	0.1 ... 10	557773 VPPE-3-1-1/8-10-010-E1	557776 VPPE-3-1-1/8-10-420-E1
		557778 VPPE-3-1-1/8-10-010-E1T	557780 VPPE-3-1-1/8-10-420-E1T

Proportional pressure regulators VPPE/VPPE with display

FESTO

Accessories

Ordering data				
	Description	Cable length [m]	Part No.	Type
Plug socket with cable for VPPE with display		Technical data → Internet: sim-m12-5gd		
	Straight, 5-pin, M12x1	2.5	175715	SIM-M12-5GD-2,5-PU
		5	175716	SIM-M12-5GD-5-PU
Plug socket with cable		Technical data → Internet: sim-m12-4gd		
	Straight, 4-pin, M12x1	5	164259	SIM-M12-4GD-5-PU
Plug socket with cable		Technical data → Internet: sim-m12-4wd		
	Angled, 4-pin, M12x1	5	164258	SIM-M12-4WD-5-PU
Plug socket		Technical data → Internet: sie-gd		
	Straight, 4-pin, M12x1	–	18494	SIE-GD
Plug socket		Technical data → Internet: sie-wd		
	Angled, 4-pin, M12x1	–	12956	SIE-WD-TR
Setpoint module		Technical data → Internet: mpz		
	Setpoint module for generating 6 + 1 analogue voltage signals	–	546224	MPZ-1-24DC-SGH-6-SW