


Wide range of configuration options

→ www.festo.com/en/engineering



- Three sizes:
MS4 – grid
dimension 40 mm
MS6 – grid
dimension 62 mm
MS12 – grid
dimension 124 mm
- Modular
- Easy to assemble
- Broad range of functions
- Compact with high flow rates
- Modern design
- Wide choice of variants
- Integrated safety functions



Specified types in accordance with
ATEX directive for potentially
explosive atmospheres

→ www.festo.com/en/ex

MS series service units

Product range overview

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [µm]			
				0.05 ... 0.7	0.05 ... 2.5	0.1 ... 4	0.3 ... 7	0.1 ... 12	0.5 ... 16	0.01	1	5	40
Code			AG...	D2	D4	D5	D6	D7	D8	A	B	C	E
Service units													
MSB-FRC 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
	12	–											
Service unit combinations (further variants can be ordered using the configurator → www.festo.com/en/engineering)													
MSB 	4	G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
	6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
	12	–											
Individual devices													
Filter regulators MS-LFR 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	■	■
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	■	■	■	–	–	■	■
Filters MS-LF 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	■	■
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	■	■
Fine and micro filters MS-LFM 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	■	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	■	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	■	■	–	–
Activated carbon filters MS-LFX 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	–	–
Pressure regulators MS-LR 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	■	■	■	–	–	–	–
Pressure regulators MS-LRB 	4	G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–	–
	6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–	–
	12	–											
Precision pressure regulators MS-LRP 	4	–											
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–	–
	12	–											
Precision pressure regulators MS-LRPB 	4	–											
	6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–	–
	12	–											

MS series service units

Product range overview


FESTO

Type	Size	Bowl guard		Condensate drains				Pressure indicator					Actuator lock		Options		→ Page
		Plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully-automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter for EN pressure gauge G1/8	Adapter for EN pressure gauge G1/4	Pressure sensor with display	Rotary knob, lockable	Rotary knob, long	Silencer	Flow direction from right to left	
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	LD	S	Z	
Service units																	
MSB-FRC	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	2-2
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Service unit combinations																	
MSB	4	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	2-2
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Individual devices																	
Filter regulators MS-LFR	4	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	3-2
	6	■	■	■	■	■	■	■	■	–	■	■	■	■	–	■	
	12	–	■	■	–	■	■	■	■	–	■	–	■	■	–	■	3-18
Filters MS-LF	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	4-2, 4-4
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	4-26, 4-28
Fine and micro filters MS-LFM	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	4-2, 4-12
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	4-26, 4-33
Activated carbon filters MS-LFX	4	■	■	■	–	–	–	–	–	–	–	–	–	–	–	■	4-2, 4-20
	6	■	■	■	–	–	–	–	–	–	–	–	–	–	–	■	
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	■	4-26, 4-40
Pressure regulators MS-LR	4	–	–	–	–	–	–	■	■	■	■	■	■	■	–	■	5-2, 5-7
	6	–	–	–	–	–	–	■	■	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	■	■	–	■	–	■	■	–	■	5-58
Pressure regulators MS-LRB	4	–	–	–	–	–	–	■	■	■	■	■	■	■	–	■	5-2, 5-16
	6	–	–	–	–	–	–	■	■	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRP	4	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	5-24, 5-29
	6	–	–	–	–	–	–	■	–	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRPB	4	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	5-24, 5-38
	6	–	–	–	–	–	–	■	–	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	

MS series service units

Product range overview

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]				Supply voltage			
				0.3 ... 4	0.3 ... 7	0.5 ... 12	0.5 ... 16	24 V DC (connection pattern to EN 175301)	24 V DC (connection pattern M12 to DESINA)	110 V AC (connection pattern to EN 175301)	230 V AC (connection pattern to EN 175301)
Code			AG...	D5	D6	D7	D8	V24	V24P	V110	V230
Individual devices											
Electrical pressure regulators MS-LRE		4	–					–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	■	–	–	–
		12	–								
Lubricators MS-LOE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
On-off valves MS-EM(1)		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
On-off valves MS-EE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	■	–	■
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	■	■	■
Soft-start valves MS-DL		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
Soft-start valves MS-DE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	■	–	■
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	■	■	■
Membrane air dryers MS-LDM1		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–								
Branching modules MS-FRM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
Flow sensors MS-SFE		4	–								
		6	G1/2	G1/2	–	–	–	–	–	–	–
		12	–								

MS series service units


Product range overview

FESTO

Type	Size	Bowl guard		Pressure indicator					Switch output		Options		→ Page
		Plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter for EN pressure gauge G1/8	Adapter for EN pressure gauge G1/4	Pressure sensor with display	2x PNP	2x NPN	Silencer	Flow direction from right to left	
Individual devices													
Electrical pressure regulators MS-LRE	4	-											5-46
	6	-	-	■	■	-	■	-	-	-	-	■	
	12	-											
Lubricators MS-LOE	4	■	■	-	-	-	-	-	-	-	-	■	6-2
	6	■	■	-	-	-	-	-	-	-	-	■	
	12	-	■	-	-	-	-	-	-	-	-	-	■
On-off valves MS-EM(1)	4	-	-	■	■	■	■	■	-	-	■	■	7-2, 7-5
	6	-	-	■	■	-	■	■	-	-	■	■	
	12	-	-	■	■	-	■	-	-	-	■	■	7-30, 7-33
On-off valves MS-EE	4	-	-	■	■	■	■	■	-	-	■	■	7-2, 7-10
	6	-	-	■	■	-	■	■	-	-	■	■	
	12	-	-	■	■	-	■	-	-	-	■	■	7-30, 7-37
Soft-start valves MS-DL	4	-	-	■	■	■	■	■	-	-	-	■	7-2, 7-18
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	■	-	■	-	-	-	-	■	7-30, 7-41
Soft-start valves MS-DE	4	-	-	■	■	■	■	■	-	-	-	■	7-2, 7-23
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	■	-	■	-	-	-	-	■	7-30, 7-45
Membrane air dryers MS-LDM1	4	-	■	-	-	-	-	-	-	-	-	■	8-2
	6	-	■	-	-	-	-	-	-	-	-	■	
	12	-											
Branching modules MS-FRM	4	-	-	■	■	■	■	■	-	-	-	■	9-2
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	-	-	-	-	-	-	-	-	9-14
Flow sensors MS-SFE	4	-											10-2
	6	-	-	-	-	-	-	-	■	■	-	■ ¹⁾	
	12	-											

1) To be ordered via configurator software only → www.festo.com/en/engineering

Wide range of configuration options
→ www.festo.com/en/engineering



- MS4 – grid
dimension 40 mm
MS6 – grid
dimension 62 mm
- Modular
- Easy to assemble
- Broad range of functions
- Compact with high flow rates
- Modern design
- Wide choice of variants
- Integrated safety functions


Specified types in accordance with
ATEX directive for potentially
explosive atmospheres
→ www.festo.com/en/ex



Service unit combinations MSB4/MSB6, MS series

Peripherals overview

FESTO



Note

The choice of accessories depends on the selected service unit combination.

Range of accessories

➔ Peripherals pages of the individual devices

Mounting attachments and accessories		➔ Page
1	Cover cap MS4/6-END	11-3
2	Connecting plate MS4/6-AG...	11-2
3	Module connector MS4/6-MV	11-7
4	Silencer U	11-10
5	Angled socket PEV-1/4-WD-LED	11-9
6	Plug socket MSSD-C-4P	11-9
7	Plug socket with cable KMEB	11-9
8	Plug socket MSSD-EB	11-9
9	Illuminating seal MEB-LD	11-9
10	Padlock LRVS-D	11-10
-	Mounting bracket (for service unit MSB-FRC) MS4/6-WP/WPB/WPM	11-5, 11-6

Service unit combinations MSB4/MSB6, MS series

Type codes

FESTO

		MSB	6	-	1/2	:	H7	N3	M2	-	WP
--	--	-----	---	---	-----	---	----	----	----	---	----

Series	
MSB	Service unit combination

Size	
4	Grid dimension 40 mm
6	Grid dimension 62 mm

Pneumatic connection	
1/4	Thread G1/4
1/2	Thread G1/2

Service unit combination	
On-off valve	→ 7-4
C3	MS...-EM1
Filters → 4-3	
H1	MS...-LF-ERV
H2	MS...-LF-ERM
H3	MS...-LF-CRM
H4	MS...-LF-CRV
H7	MS...-LF-EUV
H8	MS...-LF-EUM
Filter regulator → 3-3	
J1	MS...-LFR-D7-ERM-AS
J2	MS...-LFR-D7-ERV-AS
J3	MS...-LFR-D7-CRM-AS
J4	MS...-LFR-D7-CRV-AS
Pressure regulator → 5-6	
N2	MS...-LR-D6-AS
N3	MS...-LR-D7-AS
Soft-start valve → 7-4	
A1	MS...-DL
Lubricator → 6-3	
M1	MS...-LOE-R
M2	MS...-LOE-U
On-off valve → 7-4	
D1	MS...-EE-V24
D7	MS...-EE-10V24
Branching module → 9-4	
F3	MS...-FRM-Y

Type of mounting	
WP	Mounting bracket

Further variants can be ordered using the modular system

Service unit combinations → www.festo.com/en/engineering

- Connection size
- Connecting plates
- Service unit equipment
- Alternative flow direction


Service unit combinations MSB4/MSB6, MS series

Technical data


FESTO

Function

With condensate drain
manual rotary



With condensate drain
fully automatic



-  Flow rate
900 ... 3,300 l/min
-  Temperature range
-10 ... +60 °C
-  Pressure regulation
range
1 ... 12 bar



- On-off valve MS...-EM1
manually actuated
- Filter regulator MS...-LFR-D7
- Branching module MS...-FRM-Y
with pressure switch without display
- Lubricator MS...-LOE-R
- Mounting bracket MS...-WP

- For filtered and lubricated compressed air
- Supply pressure can be opened and closed
- Output pressure is infinitely adjustable within the pressure regulation range
- The unit is vented when switched off
- Electrical pressure monitoring with adjustable switching pressure
- Removal of filtered and unlubricated compressed air at the branching module connections

General technical data		
Size	MSB4	MSB6
Pneumatic connection 1, 2, 3	G1/4	G1/2
Regulating function	With primary pressure compensation	
	With return flow function	
	With secondary venting	
	Output pressure constant	
Type of mounting	Via accessories	
Assembly position	Vertical ±5°	
Grade of filtration [µm]	5 (air purity class at the output 3.7.- to DIN ISO 8573-1)	
	40 (air purity class at the output 5.7.- to DIN ISO 8573-1)	
Bowl guard	Plastic bowl guard	
Condensate drain	Manual rotary	
	Fully automatic	
Actuator lock	Rotary knob with detent	
	Lockable with accessories	
Pressure regulation range [bar]	1 ... 12	
Pressure indicator	With pressure gauge	

Standard nominal flow rate qnN [l/min]			
Size	MSB4	MSB6	
Grade of filtration	5 µm	900	3,200
	40 µm	950	3,300

Service unit combinations MSB4/MSB6, MS series

FESTO

Technical data

Operating and environmental conditions				
Condensate drain	Manual rotary		Fully automatic	
Size	MSB4	MSB6	MSB4	MSB6
Supply pressure [bar]	1.5 ... 14	1.5 ... 18	1.5 ... 12	1.5 ... 12
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm			
Ambient temperature [°C]	-10 ... +60		+5 ... +60	
Temperature of medium [°C]	-10 ... +60		+5 ... +60	
Storage temperature [°C]	-10 ... +60		-10 ... +60	
Corrosion resistance	CRC ¹⁾		2	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]		
Size	MSB4	MSB6
Service unit combination	1,700	2,550
Mounting bracket	40	76

MS series service units
Service units

2

 Note

Materials → Technical data of the individual devices



Standard flow rate q_n as a function of output pressure p_2

Pressure regulation range 1 ... 12 bar
MSB4-1/4

Grade of filtration 5 µm



Grade of filtration 40 µm

Primary pressure $p_1 = 10$ bar



MSB6-1/2


Primary pressure $p_1 = 10$ bar



Service unit combinations MSB4/MSB6, MS series

Technical data

FESTO



Type	B1	B2	B3	B4	B5	B6	D1	L1	L2
MSB4	160.8	40.2	80.4	4	44	80	G $\frac{1}{4}$	201	87
MSB6	248	62	124	4.5	54	100	G $\frac{1}{2}$	285	134.5

Type	L3 Condensate drain		L4	L5	L6	L7	L8	L9	L10
	manual rotary	fully auto- matic							
MSB4	17.7	20.4	25	53	46.5	93.2	106	5.6	80
MSB6	15.8	18.5	68	66	71	142	158	6.6	130

Ordering data

Pressure regulation range 1... 12 bar

Size	Condensate drain	Connection	Grade of filtration 5 μm		Grade of filtration 40 μm	
			Part No.	Type	Part No.	Type
Plastic bowl guard						
MSB4	manual rotary	G¼	542 307	MSB4-¼:C3J3F3M1-WP	542 295	MSB4-¼:C3J1F3M1-WP
	fully automatic	G¼	542 313	MSB4-¼:C3J4F3M1-WP	542 301	MSB4-¼:C3J2F3M1-WP
MSB6	manual rotary	G½	542 283	MSB6-½:C3J3F3M1-WP	542 271	MSB6-½:C3J1F3M1-WP
	fully automatic	G½	542 289	MSB6-½:C3J4F3M1-WP	542 277	MSB6-½:C3J2F3M1-WP



MS series service units

Accessories


FESTO

Connecting plate MS4/6-AG...

(order code: AG...)

- Adapter for pneumatic connection
- MS6-AGE for implementing threaded connection G $\frac{3}{4}$

Material:
Aluminium




Dimensions and ordering data									
Size	B1	B2	B4	D1	D2	L1	Weight [g]	Part No.	Type
MS4	83.5	21.5	21	G $\frac{1}{8}$	16.8	42	128	526 068	MS4-AGA
				G $\frac{1}{4}$				526 069	MS4-AGB
				G $\frac{3}{8}$				526 070	MS4-AGC
MS6	115	26.5	31	G $\frac{1}{4}$	24	62	300	526 080	MS6-AGB
				G $\frac{3}{8}$				526 081	MS6-AGC
				G $\frac{1}{2}$				526 082	MS6-AGD
				G $\frac{3}{4}$				526 083	MS6-AGE

Connecting plate MS12-AG...

(order code: AG...)

- Adapter for pneumatic connection

Material:
Die-cast aluminium
Free of copper and PTFE



Dimensions and ordering data												
Size	B1	B2	B3	B4	B5	D1	L1	L2	L3	L4	Weight [g]	Part No. Type
MS12	162	124	12	99	184	G1	230	100	11	100	1,300	537 135 MS12-AGF
					184	G1 $\frac{1}{4}$						537 136 MS12-AGG
					184	G1 $\frac{1}{2}$						537 137 MS12-AGH
					196	G2						537 138 MS12-AGI

MS series service units

Accessories

FESTO


Cover cap MS4/6-END

- Can be used to cover the body sides of the first and last module if connecting plates are not used.

Material:

Reinforced polyamide

Free of copper and PTFE



Dimensions and ordering data						
Size	B1	B2	B4	L1	Part No.	Type
MS4	43.6	6	21	42	538 779	MS4-END
MS6	67	8	31	62	538 780	MS6-END

Mounting plate MS6-AEND


(order code: WBE; scope of delivery includes wall mounting plate MS6-WPB)

- In combination with wall mounting plate MS6-WP or MS6-WPB for mounting an individual unit on a wall with direct thread

Material:

Reinforced polyamide

Free of copper and PTFE



Dimensions and ordering data											
Size	B1	B2	B3	B4	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No. Type
MS6	79	62	4.5	90.5	158	71	6.6	71	2	17	535 408 MS6-AEND  New

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

MS series service units

Accessories

FESTO

Mounting bracket MS4/6-WP...

Clearances for mounting service unit combinations

1 unit

MS4-...: 40 mm

MS6-...: 62 mm

2 units

MS4-...: 80 mm

MS6-...: 124 mm with WP, WPB


138 mm with WPM-2D

1 Mounting bracket WP, WPB or WPM-D


2 Mounting bracket WP, WPB or WPM-2D

Number of units

1 2 3 4 5 6 7 8 9 10



Mounting dimensions



Type	B1	B2	B3	B4	B5	B6	L1	L2	L3	L4
MS4-WP	95.2	80	4	44	41.9	40	106	46.5	5.6	46.7
MS4-WPB				66						
MS4-WPM-...D				44			92.8	34.8		40
MS6-WP	141	124	4.5	54	64.5	62	158	71	6.6	71
MS6-WPB				90.5						
MS6-WPM-...D				54			98.6	41.3		41.3

MS series service units

Accessories

FESTO


Mounting bracket MS4/6-WP

(order code: WP)

- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- In combination with mounting plate MS6-AEND or for mounting an individual unit with direct thread on a wall
- For pressure regulator LRB with angled outlet block B... at rear

Material:

Die-cast aluminium



Dimensions and ordering data												
Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS4	55.2	40.2	4	44	83.4	106	46.5	5.6	46.7	39	532 184	MS4-WP
MS6	79	62	4.5	54	115	158	71	6.6	71	76	532 195	MS6-WP


Mounting bracket MS4/6-WPB

(order code: WPB)

- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- In combination with mounting plate MS6-AEND or for mounting an individual unit with direct thread on a wall
- Provides large wall gap for pressure regulator

Material:

Die-cast aluminium



Dimensions and ordering data												
Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS4	55.2	40.2	4	66	83.4	106	46.5	5.6	46.7	55	526 063	MS4-WPB
MS6	79	62	4.5	90.5	115	158	71	6.6	71	115	526 074	MS6-WPB

MS series service units

Accessories

FESTO

Mounting bracket MS4/6-WPM

(order code: WPM)



- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- Speedy attachment and detachment
- For installation of modules with regulating knob pointing downwards

The distance piece D or 2D (designated in the type code) is included in the scope of delivery and ensures the correct clearance


Material:
Die-cast aluminium



MS4-WPM-D



MS6-WPM-D



Dimensions and ordering data													
Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Clearance	Weight [g]	Part No.	Type
MS4	55.2	40	4	44	83.4	92.8	34.8	5.6	45.2	40	45	526 060	MS4-WPM-D
	95.2	80			123.4					80	55	526 061	MS4-WPM-2D
MS6	99	69	17.5	54	129	98.6	41.3	6.6	41.3	62	144	526 073	MS6-WPM-D
	168	138			198					124	154	532 186	MS6-WPM-2D

MS series service units

Accessories

FESTO

Wall mounting plate MS12-WP


(order code: WP)

- For connecting the modules for wall mounting
- In combination with a connecting plate for mounting an individual unit on a wall

Material:

Die-cast aluminium

Free of copper and PTFE



Dimensions and ordering data

Size	B1	B2	B3	B4	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS12	162	124	12	99	230	100	11	100	700	537 133	MS12-WP

Module connector MS...-MV

- For connecting modules

Material:

MS4/6: Stainless steel/polyacetate

MS12: Die-cast aluminium,
free of copper and PTFE



MS4/6



MS12

Ordering data


Size	Weight [g]	Part No.	Type
MS4	36	532 798	MS4-MV
MS6	54	532 799	MS6-MV
MS12	500	537 134	MS12-MV

Module connector MS4/6-MVM

- For installation of modules with regulating knob pointing downwards

Material:

Die-cast aluminium



MS4



MS6

Ordering data

Size	Part No.	Type
MS4	532 800	MS4-MVM
MS6	532 801	MS6-MVM

MS series service units

Accessories

FESTO

Filter cartridge MS4/6-LF...



MS...-LFM



MS...-LFP



MS...-LFX

Ordering data				
Size		Grade of filtration [μm]	Part No.	Type
MS4	Micro-filter cartridge	0.01	162 674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162 677	MS4/D-MINI-LFM-B
	Filter cartridge	5	534 501	MS4-LFP-C
	Filter cartridge	40	534 502	MS4-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	532 912	MS4/D-MINI-LFX
MS6	Micro-filter cartridge	0.01	532 909	MS6-LFM-A
	Fine-filter cartridge	1	532 910	MS6-LFM-B
	Filter cartridge	5	534 499	MS6-LFP-C
	Filter cartridge	40	534 500	MS6-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	532 911	MS6-LFX


Filter cartridge MS12-LF...



MS12-LFM-B



MS12-LFM-A



MS12-LFX

Ordering data				
Size		Grade of filtration [μm]	Part No.	Type
MS12	Micro-filter cartridge	0.01	537 146	MS12-LFM-A
	Fine-filter cartridge	1	537 145	MS12-LFM-B
	Filter cartridge	5	537 143	MS12-LFP-C
	Filter cartridge	40	537 144	MS12-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	537 147	MS12-LFX


MS series service units

Accessories

FESTO

Ordering data – Angled socket PEV					Technical data → www.festo.com	
	Description	Operating voltage range	Electrical connection	Switching status display	Part No.	Type
	for PEV-1/4-...-OD	15 ... 30 V DC	4-pin	Yellow LED	164 274	PEV-1/4-WD-LED-24
		≤ 230 V AC	4-pin	Yellow LED	164 275	PEV-1/4-WD-LED-230
		≤ 180 V DC				

Ordering data – Plug socket MSSD					Technical data → www.festo.com	
	Description	Operating voltage range	Electrical connection	Type of mounting cable connection	Part No.	Type
	for PEV-1/4-...-OD	≤ 250 V AC/DC	3-pin	Clamping screws	171 157	MSSD-C-4P
	for MS4/6-EE/DE	≤ 250 V AC/DC	3-pin	Clamping screws	151 687	MSSD-EB
			4-pin	Insulation displacement technology	192 745	MSSD-EB-S-M14
	for MS12-EE/DE	≤ 250 V AC/DC	3-pin	Clamping screws	34 583	MSSD-C
			4-pin	Insulation displacement technology	192 748	MSSD-C-S-M16

Ordering data – Plug socket with cable KMEB/KMC					Technical data → www.festo.com	
	Description	Operating voltage range	Switching status display	Cable length [m]	Part No.	Type
	for MS4/6-EE/DE	24 V DC	LED	2.5	151 688	KMEB-1-24-2,5-LED
		24 V DC	LED	5	151 689	KMEB-1-24-5-LED
		24 V DC	LED	10	193 457	KMEB-1-24-10-LED
		230 V AC	–	2.5	151 690	KMEB-1-230AC-2,5
		230 V AC	–	5	151 691	KMEB-1-230AC-5
		230 V AC	–	10	193 459	KMEB-1-230AC-10
	for MS12-EE/DE	24 V DC	LED	2.5	30 931	KMC-1-24DC-2,5-LED
		24 V DC	LED	5	30 933	KMC-1-24DC-5-LED
		24 V DC	LED	10	193 459	KMC-1-24-10-LED
		230 V AC	–	2.5	30 932	KMC-1-230AC-2,5
		230 V AC	–	5	30 934	KMC-1-230AC-5

Ordering data – Illuminating seal MEB-LD/MC-LD				Technical data → www.festo.com	
	Description	Operating voltage range	Part No.	Type	
	for plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC	151 717	MEB-LD-12-24DC	
		230 V DC/AC ±10%	151 718	MEB-LD-230AC	
	for plug socket with cable KMC and plug socket MSSD-C	12 ... 24 V DC	19 145	MC-LD-12-24DC	
		230 V DC/AC ±10%	19 146	MC-LD-230AC	

Ordering data – Locking clip CPV18-HV				Technical data → www.festo.com	
	Description	Part No.	Type	PU ¹⁾	
	for MS4/6-EE/DE-...-V24				
	Cover for manual override, the clip prevents actuation	530 056	CPV18-HV		10

1) Packaging unit quantity

MS series service units


Accessories

FESTO

Ordering data – Silencer U			Technical data → www.festo.com	
	Description	Pneumatic connection	Part No.	Type
	for MS4-EM1/EE	G1/4	6 842	U-1/4-B
	for MS6-EM1/EE	G1/2	6 844	U-1/2-B
	for MS12-EM/EE	G1	151 990	U-1-B

Ordering data – Double nipple ESK				
	Description	Pneumatic connection		Part No. Type
	Adjustable for angular compensation • For retro-fitting pressure switch PEV or pressure sensor SDE1 to branching module MS-FRM	R1/8	R1/4	534 151 ESK-1/8-1/4
		R1/4	R1/4	151 521 ESK-1/4-1/4
			R1/2	534 153 ESK-1/4-1/2

Ordering data – Padlock LRV5-D				
	Description	Weight [g]	Part No.	Type
	for filter or pressure regulators	120	193 786	LRV5-D

Ordering data – Special oil OFSW				
	Description	Scope of delivery	Part No.	Type
	for lubricators	1 litre	152 811	OFSW-32