

Motor units MTR-DCI, intelligent servo motors

FESTO



Motor units MTR-DCI, intelligent servo motors

Key features

FESTO

General information

The motor unit MTR-DCI is an innovative motor with integrated power electronics for positioning tasks.

Four components in one housing

Integrated in the MTR-DCI are the motor, gear unit, controller and power electronics. This means that there is no need for a control cabinet or extensive cabling.

Reliable

The integrated power electronics and controller removes the need for motor cables and improves the electromagnetic compatibility. Additional monitoring functions are integrated.

Uncomplicated

The complete commissioning process can be performed directly on the MTR-DCI via the optional LCD display or on a PC via the user-friendly menus in the FCT (Festo Configuration Tool). No matter which approach is used, all parameters are continuously controlled.

At a glance

- Compact design
- Smooth profile prevents the ingress of dirt
- DC motor with planetary gear unit and encoder
- Gear unit ratio: 7:1; 14:1, 22:1
- Protection class IP54

Positioning functionality

- 16 traversing records (including homing)
- Constant acceleration and braking
- Positioning control

Protective functions

- Temperature monitoring
- Current monitoring
- Voltage failure detection
- Following error monitoring
- Software end-position detection

Easy actuation via

- I/O interface
- Profibus
- CANopen
- DeviceNet





- 1 Control panel with integrated display (optional)
- 2 Input for reference limit switches
- 3 RS232 interface
- 4 Operator interface: I/O interface
- 5 Power supply
- 6 Gear unit



Typical applications

Adjusting sorting conveyors


Programming formats for paper or foil cutting machines



Motor units MTR-DCI, intelligent servo motors

FESTO

Type codes



Motor units MTR-DCI, intelligent servo motors

FESTO

Technical data

Size
32 ... 62 mm

Voltage
24, 48 V DC

Fieldbus interfaces



CANopen

DeviceNet



General technical data				
Size	32	42	52	62
Rotary position generator	Optical encoder			
No. of increments/revolution	300 (1,200) ¹⁾	500 (2,000) ¹⁾		
Controller operating mode	PWM MOSFET power amplifier			
Display resolution	128 x 64 pixels			
Type of mounting	Can be bolted on or clamped to gearing unit flange			
Gearing unit type	Planetary gearing			
Gear unit ratio	G7	6.75 (7:1); 1-stage		
	G14	13.73 (14:1); 2-stage		
	G22	–		
				22.21 (22:1); 2-stage

1) Internal 4-fold evaluation

Electrical data – Motor					
Size		32	42	52	62
Nominal voltage	[V DC]	24 ±10%			48 –10%/+5%
Nominal current (motor)	[A]	0.73	2	5	6.19
Peak current	[A]	2.1	3.8	7.7	20
Motor constant	[Ncm/A]	4.5	6.1	6.4	12.1
Nominal power (motor)	[W]	17	48	122	316
Max. current (digital logic outputs)	[mA]	200		60	
Parameterisation interface		RS232; 9,600 baud			

Mechanical data – Motor									
Size	32		42		52		62		
Gear unit ratio	G7	G14	G7	G14	G7	G14	G7	G14	G22
Gearing unit output speed [rpm]	481	237	444	218	444	218	504	248	153
Gearing unit torsional backlash [°]	≤ 1.9	≤ 1.55	≤ 1.3	≤ 0.95	≤ 1.1	≤ 0.75	≤ 1	≤ 1.5	≤ 1.5
Gearing unit output torque [Nm]	0.15	0.29	0.59	1.13	1.62	3.08	3.78	7.2	11.66
Gearing unit efficiency	0.75	0.7	0.8	0.75	0.8	0.75	0.8	0.75	0.75
Mass moment of inertia (rotor) [kg cm ²]	0.024		0.323		1.209		3.3		
Mass moment of inertia (gearing unit) [kg cm ²]	0.00089	0.00149	0.00235	0.00441	0.01132	0.01711	0.017	0.035	0.022
Radial shaft load [N]	40	70	160	230	200	320	240	360	360
Axial shaft load [N]	10	20	50	80	60	100	50	70	70
Product weight [kg]	0.72	0.74	1.72	1.83	3.1	3.3	7.6	8.0	8.0

Motor units MTR-DCI, intelligent servo motors

FESTO

Technical data

Operating and environmental conditions				
Size	32	42	52	62
Digital logic outputs	Not electrically isolated		Electrically isolated	
Insulation protection class to VDE 60034	F			
Protection class	IP54			
Protective functions	I ² T monitoring			
	Following error monitoring			
	Software end position detection			
	Voltage failure detection			
	Current monitoring			
	Temperature monitoring: Silicon absolute temperature sensor, switches off at temperatures >70 °C			
Ambient temperature [°C]	0 ... +50			
Storage temperature [°C]	−25 ... +60			
Relative air humidity [%]	0 ... 95 (non-condensing)			
CE mark (see declaration of conformity)	In accordance with EU EMC directive			
Certification	C-Tick			
Note on materials	Contains paint wetting impairment substances			

Materials	
Motor unit housing	Anodised aluminium
Motor unit cover	Aluminium, precision casting, coated (size 62 milled)

Technical data – I/O/fieldbus interface				
Type	MTR-DCI-...-IO	MTR-DCI-...-CO	MTR-DCI-...-PB	MTR-DCI-...-DN
Interface	I/O interface for 15 traversing records and homing	CANopen	Profibus DP	DeviceNet
Number of digital logic inputs	6	–	–	–
Number of digital logic outputs	2	–	–	–
Max. current of digital logic outputs (size)	32/42	200	–	–
	52/62	60	–	–
Bus terminating resistor ¹⁾	–	Not integrated in the device	Not integrated in the device	Not integrated in the device
Communication profile	–	DS301 / FHPP	DP-V0/V1 / FHPP	FHPP
	–	DS301; DSP402	Step7 functional modules	Device type 0C _h
Max. fieldbus baud rate [kbps]	–	1,000	12,000	500

1) Details of bus terminating resistor → 10


Motor units MTR-DCI, intelligent servo motors

Technical data


FESTO

Torque M as a function of rotational speed n


Size 32




Size 42



Size 52



Size 62



Gear unit ratio 7:1

- 1 Torque, nom.
- 2 Torque, max.

Gear unit ratio 14:1

- 3 Torque, nom.
- 4 Torque, max.

Gear unit ratio 22:1


- 5 Torque, nom.
- 6 Torque, max.

Motor units MTR-DCI, intelligent servo motors

Technical data

FESTO

Pin allocation



1 Reference switch, 3-pin M8 socket

Pin	Function
1	24 V
4	Reference input
3	0 V
–	

2 RS 232 interface, 4-pin M8 socket

Pin	Function
1	0 V
2	Transmitted data (TxD)
3	Received data (RxD)
4	–

3 I/O interface, 9-pin Sub-D plug

Pin	Function
1	Traversing record coding, bit 0
2	Traversing record coding, bit 1
3	Traversing record coding, bit 2
4	Traversing record coding, bit 3
5	Start bit
6	Enable bit
7	Ready signal output
8	MC signal output
9	0 V

3 CANopen interface, 9-pin Sub-D plug

Pin	Function
1	–
2	CAN_L
3	CAN_GND
4	–
5	CAN_SHLD
6	CAN_V–
7	CAN_H
8	–
9	CAN_V+

3 Profibus interface, 9-pin Sub-D socket

Pin	Function
1	–
2	Logic_GND
3	RxD/TxD-P
4	CNTR-P
5	DGND
6	VP
7	Logic_V (24 V DC)
8	RxD/TxD-N
9	–

3 DeviceNet interface, 9-pin Sub-D plug

Pin	Function
1	–
2	CAN_L
3	CAN_GND
4	–
5	CAN_SHLD
6	CAN_V–
7	CAN_H
8	–
9	CAN_V+

4 Power supply, 2-pin plug

Pin	Function
1	24 V DC (for MTR-DCI-32/42/52), 48 V DC (for MTR-DCI-62)
2	0 V
–	
–	
–	
–	
–	
–	
–	

Motor units MTR-DCI, intelligent servo motors


Technical data

FESTO


Dimensions

Download CAD Data → www.festo.com/us/cad


Size 42




Size 32



Size 52



Size 62



- 1 M8x1, 4-pin
- 2 M8x1, 3-pin
- 3 Sub-D, 9-pin
- 4 Sub-D, 2-pin

Type	D1 Ø g10	D2 Ø ±0.1	D3 Ø h8	D4 Ø h7	D5 Ø	H1	L1 ±1	L2 ±1	L3	L4	L5	L6	T1	T2 +2
MTR-DCI-32S-...-G7	–	–	21.5	6	–	13±0.2	175.5	–	18.7±0.6	2.5±0.3	–	–	6	–
MTR-DCI-32S-...-G14	–	–	21.5	6	–	13±0.2	175.5	–	18.7±0.6	2.5±0.3	–	–	6	–
MTR-DCI-42S-...-G7	42	42	25	8	–	11	176	33.3	25±1	2±0.1	25	–	7±2	10
MTR-DCI-42S-...-G14	42	42	25	8	–	11	176	46.3	25±1	2±0.1	25	–	7±2	10
MTR-DCI-52S-...-G7	52	52	32	12	–	17.3	194	39	33±1	3±0.3	31	–	10	–
MTR-DCI-52S-...-G14	52	52	32	12	–	17.3	194	53	33±1	3±0.3	31	–	10	–
MTR-DCI-62S-...-G7	62	62	40	14	15	61.3	270	47	39±1	5±0.3	31.3	9	10	–
MTR-DCI-62S-...-G14	62	62	40	14	15	61.3	270	47	39±1	5±0.3	31.3	9	10	–
MTR-DCI-62S-...-G22	62	62	40	14	15	61.3	270	47	39±1	5±0.3	31.3	9	10	–

Motor units MTR-DCI, intelligent servo motors

FESTO

Ordering data – Modular products

M Mandatory data											
Module No.	Motor unit		Flange/size		Nominal voltage		Measuring system		Parameterisation interface		
533 736 533 742 533 748 533 754 Order example	Motor type		Torque class		Plug design		Gearing unit		Electrical connection technology		
	MTR	DCI	32	S	VC	SC	E	G7	R2	IO	
			42		VD			G14	H2	CO	
			52					G22		PB	
			62							DN	
533 742	MTR	- DCI	- 42	S	- VC	SC	- E	G7	- R2	IO	

Ordering table								
Size	32	42	52	62	Condition s	Code		Enter code
M Module No.	533 736	533 742	533 748	533 754				
Motor unit	Motor unit					MTR		MTR
Motor type	DC servo motor with integrated position controller					-DCI		-DCI
Flange/size	32	42	52	62		-...		
Torque class	Standard torque class					S		S
Nominal voltage	[V] 24 DC					-VC		
	[V] -			48 DC		-VD		
Plug design	Straight plug					SC		SC
Measuring system	Encoder					-E		-E
Gearing unit	Integrated planetary gearing i = 6.75					G7		
	Integrated planetary gearing i = 13.73					G14		
			Integrated planetary gearing i = 22.21			G22		
Parameterisation interface	RS232 interface					-R2		
	RS232 interface + control panel					-H2		
Electrical connection technology	I/O interface					IO		
	CANopen					CO		
	Profibus DP					PB		
	DeviceNet					DN		



Transfer order code



	MTR	-	DCI		S		SC	-	E		-		-	
--	-----	---	-----	--	---	--	----	---	---	--	---	--	---	--

Motor units MTR-DCI, intelligent servo motors

Accessories

FESTO

Ordering data – Cables				
	Brief description	Cable length	Part No.	Type
	Supply cable Allocation → 7	2.5 m	537 931	KPWR-MC-1-SUB-9HC-2,5
		5 m	537 932	KPWR-MC-1-SUB-9HC-5
		10 m	537 933	KPWR-MC-1-SUB-9HC-10
	Control cable for I/O connection to any PLC controller Allocation → 7	2.5 m	537 923	KES-MC-1-SUB-9-2,5
		5 m	537 924	KES-MC-1-SUB-9-5
		10 m	537 925	KES-MC-1-SUB-9-10
	Programming cable For parameterisation and commissioning via the RS232 interface using FCT software Allocation → 7	2.5 m	537 926	KDI-MC-M8-SUB-9-2,5

Ordering data – Plugs			
	Brief description	Part No.	Type
Fieldbus adapter for Profibus			
	– 9-pin Sub-D plug to 5-pin round M12 plug/socket, plus round M12 plug for logic voltage supply – Bus terminating resistor must be connected externally	537 934	FBA-PB-SUB-9-3XM12
Fieldbus adapter for CANopen and DeviceNet			
	– 9-pin Sub-D plug to 5-pin round M12 plug – Bus terminating resistor must be connected externally	540 324	FBA-CO-SUB-9-M12

Motor units MTR-DCI, intelligent servo motors

Accessories

FESTO

Ordering data – Software			
	Brief description	Part No.	Type
	Operator package contains: – CD-ROM – with user documentation for MTR-DCI, in the languages de, en, es, fr, it, sv – with FCT (Festo Configuration Tool) configuration software – Brief description This package is included in the scope of delivery.	550 905	P.BP-MTR-DCI

Ordering data – Documentation ¹⁾					
	Language	Part No.	Type	Part No.	Type
		For I/O interface		For Profibus interface	
	DE	539 615	P.BE-MTR-DCI-IO-DE	539 623	P.BE-MTR-DCI-PB-DE
	EN	539 616	P.BE-MTR-DCI-IO-EN	539 624	P.BE-MTR-DCI-PB-EN
	ES	539 617	P.BE-MTR-DCI-IO-ES	539 625	P.BE-MTR-DCI-PB-ES
	FR	539 618	P.BE-MTR-DCI-IO-FR	539 626	P.BE-MTR-DCI-PB-FR
	IT	539 619	P.BE-MTR-DCI-IO-IT	539 627	P.BE-MTR-DCI-PB-IT
	SV	539 620	P.BE-MTR-DCI-IO-SV	539 628	P.BE-MTR-DCI-PB-SV
		For CANopen interface		For DeviceNet interface	
	DE	539 629	P.BE-MTR-DCI-CO-DE	553 530	P.BE-MTR-DCI-DN-DE
	EN	539 630	P.BE-MTR-DCI-CO-EN	553 531	P.BE-MTR-DCI-DN-EN
	ES	539 631	P.BE-MTR-DCI-CO-ES	553 532	P.BE-MTR-DCI-DN-ES
	FR	539 632	P.BE-MTR-DCI-CO-FR	553 533	P.BE-MTR-DCI-DN-FR
	IT	539 633	P.BE-MTR-DCI-CO-IT	553 534	P.BE-MTR-DCI-DN-IT
	SV	539 634	P.BE-MTR-DCI-CO-SV	553 535	P.BE-MTR-DCI-DN-SV

1) User documentation in paper form is not included in the scope of delivery

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com