

Branching modules FRM/Distributor blocks FRZ, D series






FESTO



Branching modules FRM/Distributor blocks FRZ, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Pneumatic connection										Pressure regulation range [bar]			Grade of filtration [μm]									
		M5	M7	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$	G1	QS4	QS6	0.5	0.5	2.5	...	12	12	0.01	1	5	40			
Service units																								
FRC/FRCS		Micro	■	■	■	—	—	—	—	■	■	■	—	—	—	—	—	—	■	—	—	—		
		Mini	—	—	■	■	■	—	—	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	—	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	■	■	■	■	—	—	■	■	—	—	■	■	—	—	■	■	
Service unit combinations																								
FRC-K		Micro	—																			—	■	—
		Mini	—	—	■	■	■	—	—	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	—	—	■	■	—	—	■	■	—	—	■	■	
LFR-K LFRS-K		Micro	—																			—	■	—
		Mini	—	—	■	■	■	—	—	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	—	—	■	■	—	—	■	■	—	—	■	■	
Individual devices																								
Filter regulators LFR/LFRS		Micro	■	■	■	—	—	—	—	—	■	■	■	—	—	—	—	—	■	—	—	—	—	
		Mini	—	—	■	■	■	■	—	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	■	■	
Filters LF		Micro	■	■	■	—	—	—	—	—	■	■	■	—	—	—	—	—	■	—	—	—	—	
		Mini	—	—	■	■	■	■	—	—	—	—	—	—	—	—	—	—	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	■	■	
Fine and micro filters LFMA/LFMB		Micro	—																			—	■	—
		Mini	—	—	■	■	■	■	—	—	—	—	—	—	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	■	■	
Active carbon filters LFX		Micro	—																			—	—	—
		Mini	—	—	■	■	■	■	—	—	—	—	—	—	—	—	—	■	■	—	—	—	—	
		Midi	—	—	—	■	■	■	■	—	—	—	■	■	—	—	—	■	■	—	—	—	—	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	—	—	
Filter combinations LFMBA		Micro	—																			—	■	—
		Mini	—	—	■	■	■	■	■	—	—	—	—	—	—	—	—	■	■	—	—	■	■	
		Midi	—	—	—	■	■	■	■	■	—	—	—	■	■	—	—	■	■	—	—	■	■	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	■	■	
Pressure regulators LR/LRS		Micro	■	■	■	—	—	—	—	—	■	■	■	—	—	—	—	—	■	—	—	—	—	
		Mini	—	—	■	■	■	■	■	—	—	—	—	—	—	—	—	■	■	—	—	—	—	
		Midi	—	—	—	■	■	■	■	■	—	—	—	■	■	—	—	■	■	—	—	—	—	
		Maxi	—	—	—	—	—	—	■	■	■	■	—	■	■	—	—	■	■	—	—	—	—	

Branching modules FRM/Distributor blocks FRZ, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Bowl guard		Condensate drain		Pressure indication		Actuator lock	Supply voltage		Options		➔ Page/ Internet		
		Metal bowl guard	Plastic bowl	Manual rotary	Semi-automatic	Fully automatic	With pressure gauge		24 V DC	110 V AC	230 V AC	Directly actuated pressure regulator with integrated return flow function	Pilot actuated pressure regulator with integrated return flow function		
Service units															
FRC/FRCS	Micro	-	■	■	■	■	-	■	■	■	-	-	-	-	frc
	Mini	■	-	■	-	■	■	■	■	■	-	-	-	-	
	Midi	■	-	■	-	■	■	■	■	■	-	-	-	-	
	Maxi	■	-	■	-	■	■	■	■	■	-	-	■	■	
Service unit combinations															lfr
FRC-K	Micro	-													
	Mini	■	-	■	-	■	■	-	■	-	■	-	-	-	
	Midi	■	-	■	-	■	■	-	■	-	■	-	-	-	
	Maxi	■	-	■	-	■	■	-	■	-	■	-	■	■	
LFR-K LFRS-K	Micro	-													lfr
	Mini	■	-	■	-	■	■	-	■	■	■	-	-	-	
	Midi	■	-	■	-	■	■	-	■	■	■	-	-	-	
	Maxi	■	-	■	-	■	■	-	■	■	■	-	■	■	
Individual devices															lf
Filter regulators LFR/LFRS	Micro	-	■	■	■	■	-	■	■	■	-	-	-	-	
	Mini	■	-	■	-	■	■	■	■	■	-	-	-	-	
	Midi	■	-	■	-	■	■	■	■	■	-	-	-	-	
	Maxi	■	-	■	-	■	■	■	■	■	-	-	■	■	
Filters LF	Micro	-	■	■	■	■	-	-	-	-	-	-	-	-	lf
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	-	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	-	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	-	
Fine and micro filters LFMA/LFMB	Micro	-													lfma, lfmb
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	-	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	-	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	-	
Active carbon filters LFX	Micro	-													lfx
	Mini	■	-	-	-	-	-	-	-	-	-	-	-	-	
	Midi	■	-	-	-	-	-	-	-	-	-	-	-	-	
	Maxi	■	-	-	-	-	-	-	-	-	-	-	-	-	
Filter combinations LFMBA	Micro	-													lfmba
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	■	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	■	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	■	
Pressure regulators LR/LRS	Micro	-	-	-	-	-	■	■	■	■	-	-	-	-	lr
	Mini	-	-	-	-	-	■	■	■	■	-	-	■	-	
	Midi	-	-	-	-	-	■	■	■	■	-	-	■	-	
	Maxi	-	-	-	-	-	■	■	■	■	-	-	■	-	

Branching modules FRM/Distributor blocks FRZ, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Pneumatic connection										Pressure regulation range [bar]	
		M5	M7	G ¹ / ₈	G ¹ / ₄	G ³ / ₈	G ¹ / ₂	G ³ / ₄	G1	QS4	QS6	0.5	0.5
												7	12
Individual devices													
Pressure regulators LRB/LRBS		Micro	—										
		Mini	—	—	—	■	—	—	—	—	—	■	■
		Midi	—	—	—	—	■	—	—	—	—	■	■
		Maxi	—										
Pressure regulator combinations LRB-K		Micro	—										
		Mini	—	—	—	■	■	—	—	—	—	■	■
		Midi	—	—	—	—	■	■	—	—	—	■	■
		Maxi	—										
Lubricators LOE		Micro	■	■	■	—	—	—	—	■	■	—	—
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—
On-off valves HE		Micro	—										
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—
On-off valves, electrical HEE		Micro	—										
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—
On-off valves, pneumatic HEP		Micro	—										
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	■	—	—
Soft-start valves HEL		Micro	—										
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	■	—	—
Membrane air dryers LDM1		Micro	—										
		Mini	—										
		Midi	—										
		Maxi	—	—	—	—	—	■	■	■	■	—	—
Branching modules FRM		Micro	—										
		Mini	—	—	■	■	■	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	■	—	—
Distributor block FRZ		Micro	—	—	—	—	—	—	—	—	—	—	—
		Mini	—	—	—	—	—	—	—	—	—	—	—
		Midi	—	—	—	—	—	—	—	—	—	—	—
		Maxi	—	—	—	—	—	—	—	—	—	—	—

Branching modules FRM/Distributor blocks FRZ, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Bowl guard		Pressure indication		Actuator lock		Supply voltage			Options		➔ Page/ Internet
		Metal bowl guard	Plastic bowl	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Non-return function	Pressure switch	
Individual devices													
Pressure regulators	Micro	–											
LRB/LRBS	Mini	–	–	–	■	■	■	–	–	–	–	–	lrb
	Midi	–	–	–	■	■	■	–	–	–	–	–	
	Maxi	–	–										
Pressure regulator combinations	Micro	–											
LRB-K	Mini	–	–	–	■	■	–	–	–	–	–	–	lrb
	Midi	–	–	–	■	■	–	–	–	–	–	–	
	Maxi	–	–										
Lubricators	Micro	–	■	–	■	–	–	–	–	–	–	–	loe
LOE	Mini	■	–	–	■	–	–	–	–	–	–	–	
	Midi	■	–	–	■	–	–	–	–	–	–	–	
	Maxi	■	–	–	■	–	–	–	–	–	–	–	
On-off valves	Micro	–											he
HE	Mini	–	–	–	■	■	–	–	–	–	–	–	
	Midi	–	–	–	■	■	–	–	–	–	–	–	
	Maxi	–	–	–	■	■	–	–	–	–	–	–	
On-off valves, electrical	Micro	–											hee
HEE	Mini	–	–	–	■	–	–	■	■	■	–	–	
	Midi	–	–	–	■	–	–	■	■	■	–	–	
	Maxi	–	–	–	■	–	–	■	■	■	–	–	
On-off valves, pneumatic	Micro	–											hep
HEP	Mini	–	–	–	■	–	–	–	–	–	–	–	
	Midi	–	–	–	■	–	–	–	–	–	–	–	
	Maxi	–	–	–	■	–	–	–	–	–	–	–	
Soft-start valves	Micro	–											hel
HEL	Mini	–	–	–	■	–	–	–	–	–	–	–	
	Midi	–	–	–	■	–	–	–	–	–	–	–	
	Maxi	–	–	–	■	–	–	–	–	–	–	–	
Membrane air dryers	Micro	–											ldm1
LDM1	Mini	–											
	Midi	–											
	Maxi	■	–	–	■	–	–	–	–	–	–	–	
Branching modules	Micro	–											
FRM	Mini	–	–	–	■	–	–	–	–	–	■	■	6
	Midi	–	–	–	■	–	–	–	–	–	■	■	
	Maxi	–	–	–	■	–	–	–	–	–	■	■	
Distributor block	Micro	–	–	–	■	–	–	–	–	–	–	–	
FRZ	Mini	–	–	–	■	–	–	–	–	–	–	–	12
	Midi	–	–	–	■	–	–	–	–	–	–	–	
	Maxi	–	–	–	■	–	–	–	–	–	–	–	

Branching modules FRM, D series, metal design


Peripherals overview

FESTO

Mini/Midi/Maxi

Individual unit with connection plates

Individual unit without connection plates, for service unit combination



Mounting attachments and accessories

	Individual unit		Combination		→ Page/ Internet
	with connection plates	without connection plates	with connection plates	without connection plates	
[1] Mounting bracket HFOE	■	–	■	–	hfoe-d
[2] Threaded pin (included in scope of delivery) FRB	–	–	■	■	frb-d
[3] Double nipple ESK	■	■	■	■	14
[4] Pressure switches PEV	■	■	■	■	14
[5] Plug socket MSSD-C	■	■	■	■	14
[6] Angled plug socket PEV-....-WD-LED	■	■	■	■	14

Branching modules FRM, D series, metal design

FESTO

Type codes

FRM - H - 1/4 - D - MIDI

Basic function

FRM	Branching module
-----	------------------

Non-return function/pressure switch

	Standard
H	With integrated non-return function
Y	With pressure switch

Pneumatic connection

	Without connection plates
1/8	Thread G1/8
1/4	Thread G1/4
3/8	Thread G3/8
1/2	Thread G1/2
3/4	Thread G3/4
1	Thread G1

Series

D	Series
---	--------

Size

MINI	Grid dimension 40 mm (without connection plates)
MIDI	Grid dimension 55 mm (without connection plates)
MAXI	Grid dimension 66 mm (without connection plates)

Branching modules FRM, D series, metal design


Technical data

FESTO

Function


- - Flow rate
1,300 ... 20,000 l/min

Standard



- - Temperature range
-10 ... +60 °C
- - Operating pressure
0 ... 16 bar

With non-return function



- An integrated non-return valve prevents return flow of lubricated compressed air
- Branching module for compressed air distribution for attachment of additional modules (pressure regulator, pressure switch, etc.)
- Several additional air connections for greater flexibility
- Can be used as an intermediate distributor for varying air qualities

General technical data

Size	Mini			Midi				Maxi		
Pneumatic connection 1 ¹⁾	G1/8	G1/4	G3/8	G1/4	G3/8	G1/2	G3/4	G1/2	G3/4	G1
Pneumatic connection 2 ¹⁾	G1/8	G1/4	G3/8	G1/4	G3/8	G1/2	G3/4	G1/2	G3/4	G1
Pneumatic connection 3	G1/4			G1/2				G3/4		
Pneumatic connection 4	G1/4									
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]									
Design	Branching module									
Type of mounting	Via accessories In-line installation									
Assembly position	Any									
Operating pressure [bar]										
Standard	0 ... 16									
With non-return function	0.15 ... 16			0.2 ... 16				0.25 ... 16		
With pressure switch	0 ... 12									

1) with connection plates

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Branching modules FRM, D series, metal design

FESTO

Technical data

Standard nominal flow rate¹⁾ qnN [l/min]

Port		Without connection plates	With connection plates					
			G ¹ / ₈	G ¹ / ₄	G ³ / ₈	G ¹ / ₂	G ³ / ₄	G1
Standard								
In main flow direction	Mini	3,300	1,500	3,300	3,300	-	-	-
1 → 2	Midi	8,200	-	3,500	7,000	8,200	8,800	-
	Maxi	20,000	-	-	-	11,700	20,000	17,400
With non-return function								
In main flow direction	Mini	2,000	1,300	2,000	2,100	-	-	-
1 → 2	Midi	5,600	-	3,400	5,500	5,600	5,500	-
	Maxi	15,000	-	-	-	9,600	15,000	13,400
With pressure switch								
In main flow direction	Mini	3,300	-					
1 → 2	Midi	8,200	-					
	Maxi	20,000	-					

1) Measured at p₁ = 6 bar and Δp = 1 bar.

Ambient conditions

Size	Mini	Midi	Maxi
Ambient temperature [°C]	-10 ... +60		
Temperature of medium [°C]	-10 ... +60		
Storage temperature [°C]	-10 ... +60		
Corrosion resistance class CRC ¹⁾	2		

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]

Port		Without connection plates	With connection plates					
			G ¹ / ₈	G ¹ / ₄	G ³ / ₈	G ¹ / ₂	G ³ / ₄	G1
Mini								
Without pressure switch	210	290	280	290	-	-	-	-
With pressure switch	590	-						
Midi								
Without pressure switch	520	-	770	760	740	710	-	
With pressure switch	900	-						
Maxi								
Without pressure switch	900	-	-	-	1,160	1,120	1,230	
With pressure switch	1,280	-						

Materials

Sectional view



Branching module

[1] Housing	Die-cast zinc
[2] Connection plates	Die-cast zinc
[3] Cover plate	Galvanised steel
- Seals	Nitrile rubber, polyvinyl chloride
Note on materials	Free of copper, PTFE and silicone

Branching modules FRM, D series, metal design


Technical data

FESTO

Dimensions


Mini/Midi/Maxi

With connection plates



4 Threaded pin (exchangeable)

Without connection plates




→ Flow direction

Type	B1	B2	B3	B4	B5	D1	D2	D3	D6	H1	H2	L1	L2	T1	T2
Mini															
FRM-1/8-D-MINI	64	52	40	30	-	G1/8	-	M4	G1/4	20	11	42	7	7	-
FRM-1/4-D-MINI						G3/4									
FRM-3/8-D-MINI	70					G3/8									
FRM-D-MINI	-	-				5.8	-	11		-	-			-	10
Midi															
FRM-1/4-D-MIDI						G1/4	-	M5	G1/2	32	22	59	8	8	-
FRM-3/8-D-MIDI		85	70	55	43	G3/8									
FRM-1/2-D-MIDI						G1/2									
FRM-3/4-D-MIDI						G3/4									
FRM-D-MIDI	-	-				6.8	-	24		-	-			-	11
Maxi															
FRM-1/2-D-MAXI		96	80			G1/2	-	M5	G3/4	32	22	70	8	8	-
FRM-3/4-D-MAXI				66	46	G3/4									
FRM-1-D-MAXI	116	91				G1									
FRM-D-MAXI	-	-				6.8	-	30		-	-			-	11

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions – Pressure switch PEV

Mini/Midi/Maxi



Download CAD data → www.festo.com

Technical data → Internet: pev-1/4

Pressure switch PEV-1/4-B-OD with adjustable pressure switching point, plug, square design to DIN EN 175 301, type A

Type	B6	B7	L3
FRM-Y-D-MINI	20	62	92.3
FRM-Y-D-MIDI	27.5	69.5	92.3
FRM-Y-D-MAXI	33	75	92.3

Branching modules FRM, D series, metal design

FESTO

Technical data

Ordering data – Without connection plates

Size	Standard		With integrated non-return function		With pressure switch PEV-1/4-B-OD	
	Part No.	Type	Part No.	Type	Part No.	Type
Mini	170684	FRM-D-MINI	170687	FRM-H-D-MINI	542184	FRM-Y-D-MINI
Midi	170685	FRM-D-MIDI	170688	FRM-H-D-MIDI	542185	FRM-Y-D-MIDI
Maxi	170686	FRM-D-MAXI	170689	FRM-H-D-MAXI	542186	FRM-Y-D-MAXI

Ordering data – With connection plates

Size	Port	Standard		With integrated non-return function	
		Part No.	Type	Part No.	Type
Mini	G1/8	164949	FRM-1/8-D-MINI	162788	FRM-H-1/8-D-MINI
	G1/4	164950	FRM-1/4-D-MINI	162789	FRM-H-1/4-D-MINI
	G3/8	164951	FRM-3/8-D-MINI	162790	FRM-H-3/8-D-MINI
Midi	G1/4	186523	FRM-1/4-D-MIDI	186525	FRM-H-1/4-D-MIDI
	Gy	164952	FRM-3/8-D-MIDI	162791	FRM-H-3/8-D-MIDI
	G1/2	164953	FRM-1/2-D-MIDI	162792	FRM-H-1/2-D-MIDI
	G3/4	164954	FRM-3/4-D-MIDI	162793	FRM-H-3/4-D-MIDI
Maxi	G1/2	186524	FRM-1/2-D-MAXI	186526	FRM-H-1/2-D-MAXI
	G3/4	164955	FRM-3/4-D-MAXI	162794	FRM-H-3/4-D-MAXI
	G1	164956	FRM-1-D-MAXI	162795	FRM-H-1-D-MAXI

Distributor blocks FRZ, D series, metal design

Type codes

FESTO


FRZ	-	D	-	MIDI
Basic function				
FRZ	Distributor block			
Series				
D	Series			
Size				
MICRO	Grid dimension 25 mm (without connecting plates)			
MINI	Grid dimension 40 mm (without connecting plates)			
MIDI	Grid dimension 55 mm (without connecting plates)			
MAXI	Grid dimension 66 mm (without connecting plates)			

Distributor blocks FRZ, D series, metal design

FESTO


Technical data

FRZ-D-MICRO




Additional air connections can be used to branch off filtered, unlubricated compressed air, e.g. to supply air barriers, sensors and control systems, or for especially clean air in combination with micro filter LFM.

FRZ-D-MINI/MIDI/MAXI





Materials:
Housing: Aluminium
Cover plate: Galvanised steel




Dimensions

Micro



4 Threaded pin (exchangeable)

Mini/Midi/Maxi



⇒ Flow direction

Download CAD data → www.festo.com

Type	B1	B2	B3	B4	B5	D1 ∅	D2	D3	D4	T2
Mini										
FRZ-D-MINI	30	20	40	30	6	12	G ¹ / ₄	M4	G ¹ / ₄	12
Midi										
FRZ-D-MIDI	35	32	55	43	7	16	G ¹ / ₄	M5	G ¹ / ₂	8
Maxi										
FRZ-D-MAXI	40	32	65	46	7	22	G ¹ / ₄	M5	G ³ / ₄	10

 Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Distributor block

Distributor Block		
Size	Part No.	Type
Without threaded connecting plates		
Micro	526815	FRZ-D-MICRO
Mini	162786	FRZ-D-MINI
Midi	159592	FRZ-D-MIDI
Maxi	162787	FRZ-D-MAXI

Branching modules FRM/Distributor blocks FRZ, D series

Accessories

FESTO

Ordering data – Pressure switch PEV				Technical data → Internet: pev-1/4	
	Pneumatic connection	Pressure switching point	Electrical connection	Part No.	Type
	G1/4	Adjustable with visual scale	Plug, square design to DIN EN 175 301, type A	161760	PEV-1/4-SC-OD
	G1/4	Adjustable	Plug, square design to DIN EN 175 301, type A	175250	PEV-1/4-B-OD
	G1/4	Adjustable	Plug socket MSSD-C-4P	10773	PEV-1/4-B

Ordering data – Angled socket PEV					Technical data → Internet: pev-1/4	
	Description	Operating voltage range	Electrical connection	Switching status display	Part No.	Type
	for PEV-1/4-...-OD	15 ... 30 V DC	4-pin	Yellow LED	164274	PEV-1/4-WD-LED-24
		≤ 230 V AC ≤ 180 V DC	4-pin	Yellow LED	164275	PEV-1/4-WD-LED-230

Ordering data – Plug socket MSSD-C-4P					Technical data → Internet: mssd-c-4p	
	Description	Operating voltage range	Electrical connection	Type of mounting cable connection	Part No.	Type
	for PEV-1/4-...-OD	≤ 250 V AC/DC	3-pin	Clamping screws	171157	MSSD-C-4P

Ordering data – Double nipple ESK			Technical data → Internet: esk-1/4-1/4		
	Description	Pneumatic connection	Part No.	Type	
	Adjustable for angular compensation • For retro-fitting pressure switch PEV to branching module FRM	R1/4	R1/4	151521	ESK-1/4-1/4