


Sensor boxes SRAP, analogue

FESTO



Sensor boxes SRAP, analogue

Key features

FESTO


General information

- Analogue sensor box for greater functionality. The analogue sensor box monitors the position of semi-rotary actuators and reports this back to the controller via an analogue 4 ... 20 mA output signal.

Advantages


- Simple mounting and commissioning: can be mounted directly on the semi-rotary actuator DFPB without the need for mounting accessories, with teach-in function for flexible adjustment of the zero point within a range from 0 – 270°
- Everything in view, including from a distance: colour-based indication of the current position of the semi-rotary actuator
- Innovative and intelligent: homing to the actual swivel angle makes optimum use of the initial range
- Sturdy and explosion-proof: a match for even harsh, corrosive and potentially explosive environments thanks to corrosion-resistant and waterproof metal housing
- Insensitive to vibration. Always supplies a stable signal as there is no contact between the shaft and sensor
- Quick and easy integration in existing systems thanks to the industrial analogue output signal
- Cost and time savings thanks to the common power supply for the sensor box and solenoid valve
- Cost-efficient regulation in combination with 5/3-way valve compared with positioner solution
- Festo know-how in automation: concept and solution from a single source
- You can find information on the media resistance of the product at → www.festo.com

1 cable connector



- Power supply for sensor box only

2 cable connectors




- Common power supply for sensor box and solenoid valve

Sensor boxes SRAP, analogue

Peripherals overview

FESTO



Mounting attachments and accessories		
	Brief description	→ Page/Internet
1	Adapter kit DASB-P1-HA-SB ¹⁾	Hole pattern 30x80 mm, height 20 mm dasb
2	Adapter kit DASB-P1-HL-SB	Hole pattern 30x130 mm, height 50 mm dasb
3	Adapter kit DASB-P1-HB-SB	Hole pattern 30x80 mm, height 30 mm dasb
4	Adapter kit DASB-P1-HC-SB	Hole pattern 30x130 mm, height 30 mm dasb
5	Coupling DARQ-C-S9	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S11	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S14	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S17	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S22	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S27	For direct mounting on semi-rotary actuators DFPB darq

1) The adapter kit DASB-P1-HA-SB can optionally be used for all DFPB actuators.

Sensor boxes SRAP, analogue

Type codes

FESTO


		SRAP	-	M	-	CA1	-	BB270	-	1	-	A	-	T2P20	-		-	EX2
Function																		
SRAP	Analogue sensor box																	
Product version																		
M	Primarily metal																	
Design																		
C	Sensor box																	
Mechanical interface																		
A1	Direct mounting, hole pattern 30x80 mm																	
Indicator type																		
	No indicator																	
BB	Blue/black position indicator																	
GR	Green/red position indicator																	
YB	Yellow/black position indicator																	
Measuring range																		
270	0 ... 270°																	
Nominal operating voltage																		
1	24 V DC																	
Electrical output																		
A	4 ... 20 mA																	
Electrical connection																		
T	Terminal box																	
Valve connection																		
	None																	
2	With valve connection																	
Cable connector																		
M20	M20x1.5, metal																	
P20	M20x1.5, polymer																	
Temperature range																		
	Standard -20 ... +80 °C																	
EU certification																		
	None																	
EX2	II 3GD																	

Sensor boxes SRAP, analogue

Technical data

FESTO

- The analogue sensor box not only reports the open/closed position of the semi-rotary actuator, but also detects the entire swivel range and reports this back to the controller via an analogue signal
- The integrated sensors are based on proven 2D Hall technology



General technical data			
Adjustment range for angle detection	[°]	0 ... 270	
Based on standard		VDI/VDE 3845 (NAMUR)	
Design		Angular	
Mounting position		Any	
Measured variable		Swivel angle	
Measuring principle		Magnetic Hall	
Adjustment options		Teach-in	
		Teach-in via electrical connection	
Idle current	[mA]	12 ... 20	
Analogue output	[mA]	4 ... 20	
Repetition accuracy of analogue output		+/- 1 deg	
Operating voltage range	Direct voltage DC	[V]	15 ... 30
Insulation voltage		[V]	50
Surge capacity		[kV]	0.8
Protection against short circuit		Yes	
Protection against overloading		Yes	
Reverse polarity protection		For all electrical connections	
Electrical connection		9-pin	
		Screw terminal	
		Plug-in	
Cable connector		M20x1.5	
Max. cable length	[m]	30	
Permissible cable diameter	[mm]	5 ... 13	
Connectable nominal conductor cross section	[mm ²]	2.5	
Product weight	[g]	1,000	
Housing material		Wrought aluminium alloy	
Note on materials		RoHS-compliant	

Sensor boxes SRAP, analogue

Technical data

FESTO

Operating and environmental conditions	
Certification	C-Tick c UL us - Recognized (OL)
Ambient temperature [°C]	-20 ... +80 °C
Protection class	IP65
CE mark (see declaration of conformity)	To EU EMC Directive
Electrical protection class	III
Degree of contamination	3
Corrosion resistance class CRC ¹⁾	3

- 1) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Operating and environmental conditions with explosion protection	
Certification	C-Tick c UL us - Recognized (OL)
Ambient temperature [°C]	-20 ... +80 °C
Protection class	IP65
CE mark (see declaration of conformity)	To EU EMC Directive To EU Explosion Protection Directive (ATEX)
ATEX category for gas	II 3G
Explosion ignition protection type for gas	Ex nA II T5 X
ATEX category for dust	II 3D
Explosion ignition protection type for dust	Ex tD A22 IP65 T90°C X
Explosion-proof ambient temperature	-20 °C ≤ Ta ≤ +80 °C
Explosion protection certification outside the EU	EPL Dc (RU) EPL Gc (RU)
Electrical protection class	III
Degree of contamination	3
Corrosion resistance class CRC ¹⁾	3

- 1) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.


Sensor boxes SRAP, analogue

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	B1	B2 ±1	B3	B4	D1	H1	H2	H3	H4	L1	L2 ±1	L3	☞						
SRAP-M-CA1-BB270-1-A-TP20	94	82	30	-	M5	112.7	80	74.5	7.8	148	120	80	24						
SRAP-M-CA1-BB270-1-A-TP20-Ex2										147			22						
SRAP-M-CA1-GR270-1-A-TM20										148			24						
SRAP-M-CA1-GR270-1-A-TP20										147			22						
SRAP-M-CA1-GR270-1-A-TP20-Ex2										148			24						
SRAP-M-CA1-YB270-1-A-TM-20																			
SRAP-M-CA1-YB270-1-A-TP-20																			
SRAP-M-CA1-YB270-1-A-TP-20-Ex2																			
SRAP-M-CA1-GR270-1-A-T2P20																			
SRAP-M-CA1-GR270-1-A-T2P20-Ex2				27															
SRAP-M-CA1-270-1-A-T2P20																			
SRAP-M-CA1-270-1-A-T2P20-Ex2																			

Sensor boxes SRAP, analogue

Technical data

FESTO





Ordering data – Sensor boxes SRAP, analogue without explosion protection			
	Position indicator	Part No.	Type
	Blue/black	568236	SRAP-M-CA1-BB270-1-A-TP20
	Red/green	568238	SRAP-M-CA1-GR270-1-A-TM20
	Red/green	568239	SRAP-M-CA1-GR270-1-A-TP20
	Yellow/black	568242	SRAP-M-CA1-YB270-1-A-TM20
	Yellow/black	568243	SRAP-M-CA1-YB270-1-A-TP20
	Red/green	568246	SRAP-M-CA1-GR270-1-A-T2P20
	No indicator	570527	SRAP-M-CA1-270-1-A-T2P20

Ordering data – Sensor boxes SRAP, analogue with explosion protection			
	Position indicator	Part No.	Type
	Blue/black	568237	SRAP-M-CA1-BB270-1-A-TP20-Ex2
	Red/green	568241	SRAP-M-CA1-GR270-1-A-TP20-Ex2
	Yellow/black	568245	SRAP-M-CA1-YB270-1-A-TP20-Ex2
	Red/green	568247	SRAP-M-CA1-GR270-1-A-T2P20-Ex2
	No indicator	570528	SRAP-M-CA1-270-1-A-T2P20-Ex2

Sensor boxes SRAP, analogue

Accessories

FESTO

Dimensions and ordering data			
	Brief description	Part No.	Type
Adapter kit			
	Adapter kit for DRD/DRE, DAPS and DFPB, shaft height 20 mm, hole patterns 80x30 mm	568275	DASB-P1-HA-SB
	Adapter kit for third-party drives, shaft height 50 mm, hole patterns 130x30 mm	568276	DASB-P1-HL-SB
	Adapter kit for DRD/DRE and DAPS, shaft height 30 mm, hole patterns 80x30 mm	572418	DASB-P1-HB-SB
	Adapter kit for DRD/DRE and DAPS, shaft height 30 mm, hole patterns 130x30 mm	572419	DASB-P1-HC-SB
Couplings			
	Couplings for direct mounting of sensor boxes SRBP/SRAP on quarter turn actuators DFPB. Technical data ➔ Internet: dfpb	568674	DARQ-C-S9
		568675	DARQ-C-S11
		568676	DARQ-C-S14
		568677	DARQ-C-S17
		568678	DARQ-C-S22
		568679	DARQ-C-S27
Cable connector			
	Polymer cable connector M20x1.5	568278	NETC-P-M20-P4
	Metal cable connector M20x1.5	568279	NETC-M-M20-P4