

# Local controllers DLP-VSE



# Local controllers DLP-VSE

Technical data



This local controller is a convenient manual unit for controlling process actuators. Using a local controller, a pneumatic drive can assume the functionality of an electrical drive.

- Can be mounted directly on the actuator or on a wall
- Emergency compressed air connection
- Safe thanks to its key-operated switch with removable key
- Large, long-life fluorescent display for the open/closed position of the process valve
- Operated on site or remote-controlled



General technical data					
Type	DLP-VSE-2-5/2-C	DLP-VSE-2-5/2-O	DLP-VSE-3-5/3-G	DLP-VSE-3-5/3-G-ASI	DLP-VSE-3-5/3-G-DP
Type of mounting	Via through-holes Via accessories				
Operating pressure [bar]	3 ... 8				
Nominal operating pressure [bar]	6				
Voltage supply [V DC]	20.4 ... 28.8			–	20.4 ... 28.8
Voltage supply with AS-interface [V DC]	–			26.5 ... 31.6	–
Auxiliary voltage supply with AS-interface [V DC]	–			20.4 ... 28.8	–
Max. current consumption [mA]	120			180	
Duty cycle of solenoid coils [%]	100				
Product weight [g]	1,600			1,700	
Protection class	IP65 Plug connector when fully pushed in, or fitted with protective cover				

Operating and environmental conditions	
Operating medium	Filtered compressed air, unlubricated, grade of filtration 50 µm Filtered compressed air, lubricated, grade of filtration 50 µm
Ambient temperature [°C]	–5 ... +50 based on EN 60654-1 class C1 (use in weather-protected areas)
Optional ambient temperature [°C]	–25 ... +55 to EN 60654-1 class C2 (use in weather-protected areas)
Relative air humidity [%]	5 ... 100 condensing
Corrosion resistance class CRC <sup>1)</sup>	3
CE mark (see declaration of conformity)	In accordance with EU EMC directive

1) Corrosion resistance class 3 to Festo standard 940 070  
Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface


Materials	
Housing	Wrought aluminium alloy
Cap	Wrought aluminium alloy, anodised
External screws	Galvanised steel
Seals	Nitrile rubber

# Local controllers DLP-VSE

Technical data

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Size	B1	B2	B3	B4	B5	B6	D1	D2	H1	H2	H3	L1	L2	L3
DLP-VSE...	156	54.3	61	36.9	217	12.5	G $\frac{1}{8}$	M5	196.5	117.2	29	222	80	44

		Fieldbus connection	
		AS-interface	Profibus DP
1	Power supply	■	■
2	PLC connection or external controller	■	■
3	Limit switch inputs	■	■
4	Cable socket for AS-interface Sub-D plug	-	■
5	Mounting kit DLP-VSE-BP for wall mounting	Accessories → 5	Accessories → 5
6	Sub-base DLP-VSE-OBEN for wall mounting	Accessories → 5	Accessories → 5
7	Sub-base DLP-VSE-OBEN-NAMUR for mounting on the linear actuator DLP	Accessories → 5	Accessories → 5
8	Voltage supply with AS-interface	-	■
9	AS-interface bus connection	-	■
10	Switch cover for Profibus addressing	-	■

## Local controllers DLP-VSE

FESTO












Technical data

Ordering data		
Brief description	Part No.	Type
Integrated 5/2-way valve, converted mechanically into a 3/2-way valve, normally closed, by sealing working port 2	188 463	DLP-VSE-2-5/2-C
Integrated 5/2-way valve, converted mechanically into a 3/2-way valve, normally open, by sealing working port 4	188 466	DLP-VSE-2-5/2-O
Integrated 5/3-way valve, normally closed	188 472	DLP-VSE-3-5/3-G
Integrated 5/3-way valve, normally closed, with AS-interface fieldbus connection	188 473	DLP-VSE-3-5/3-G-ASI
Integrated 5/3-way valve, normally closed, with Profibus DP fieldbus connection	188 474	DLP-VSE-3-5/3-G-DP

# Local controllers DLP-VSE

Accessories

**FESTO**

Ordering data				
	Brief description	Part No.	Type	PU <sup>1)</sup>
<b>Mounting</b>				
	Mounting kit for wall mounting in conjunction with the sub-base DLP-VSE-OBEN	192 062	DLP-VSE-BP	1
	Sub-base in conjunction with mounting kit DLP-VSE-BP for tubing connection in the direction of the drive	192 061	DLP-VSE-OBEN	1
	Sub-base for mounting on the linear valve actuator DLP	192 060	DLP-VSE-OBEN-NAMUR	1
<b>Fieldbus connection</b> <span style="float: right;">Technical data → Internet: asi, fbs</span>				
	Cable socket for AS-interface	18 785	ASI-SD-FK	1
	Cable socket for AS-interface	196 089	ASI-SD-FK180	1
	Sub-D plug for Profibus DP	532 216	FBS-SUB-9-GS-DP-B	1
<b>Fittings</b> <span style="float: right;">Technical data → Internet: fittings</span>				
	Push-in fitting, male thread with internal hex	153 015	QS-1/8-8-1	1
	Barbed fitting, high-alloy stainless steel with sealing ring	13 967	CRCN-M5-PK-3	1
	Barbed fitting, high-alloy stainless steel with sealing ring	13 970	CRCN-1/8-PK-4	1
	Quick connector, aluminium design with sealing ring for plastic tubing PL, PP, PU	3 561	CK-M5-PK-3	10
	Quick connector, plastic design with moulded-on sealing ring for plastic tubing PL, PP, PU	2 028	CK-1/8-PK-6	10
<b>Silencer</b> <span style="float: right;">Technical data → Internet: u</span>				
	Sintered bronze	4 645	U-M5	10
	Polymer	2 307	U-1/8	1

1) Packaging unit quantity

# Product Range and Company Overview

## A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

## The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

## Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

## Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

---

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

---

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

---

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



---

## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)