



- Low-cost drive solutions
- Simple commissioning
- Coordinated motor/controller combinations

Stepper motors MTRE-ST

Key features and type codes

Key features

Motors MTRE-ST

→ 3

- System product for positioning technology
- Stepper motor with integrated controller
- With/without brake
- Controlled operation
- Step-accurate positioning through pre-specified number of control pulses



Motor flange MTR-FL

→ 5

- The right motor flange for every motor/axis combination



Motor cable KMTRE-ST

→ 5

- Screened cable
- Can be used at -40 ... +125 °C
- Suitable for use with energy chains
- Protection class IP67



Type codes

MTRE – ST – 42 – 48S – AB

Type	
MTRE	Motor with integrated controller

Type of motor	
ST	Stepper motor

Flange dimensions	
42	42 mm

Nominal voltage/connection type	
48	24 ... 48 V DC
S	Plug connection

Additional function	
A	No additional function
B	Brake

Stepper motors MTRE-ST

Technical data

FESTO




General technical data		MTRE-ST-42-48S-AA	MTRE-ST-42-48S-AB
Nominal voltage	[V]	48	
Nominal motor current	[A]	1.2	
Motor holding torque	[Nm]	0.34	
Stepper angle (full step)	[°]	1.8 ±5%	
Drive mass moment of inertia	[kg cm ²]	0.068	0.07
Brake voltage	[V]	–	24
Brake power	[W]	–	6
Brake holding torque	[Nm]	–	0.4
Radial shaft load	[N]	18	18
Axial shaft load	[N]	7	7
Product weight	[kg]	0.45	0.55


Operating and environmental conditions	
Insulation protection class to VDE 60034	B
Protection class with/without gear unit	IP54
Ambient temperature	[°C] 0 ... +50
CE mark (see declaration of conformity)	To EU EMC Directive
Storage temperature	[°C] –25 ... +60
Relative air humidity (non-condensing)	[%] 45 ... 80

Torque M as a function of rotational speed n

at nominal voltage 24 V



at nominal voltage 48 V



— Full step
 - - - Half step

Stepper motors MTRE-ST


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Motor




Type	B1	B2	D1 ∅	D2 ∅	D5	L1	L3	L4	L5
MTRE-ST-42-48S-AA	42	31	5	22	M3	111	24	2	-
MTRE-ST-42-48S-AA						136			

Motor flange


EAMF-A-28A-42A

EAMF-A-30A-42A




Type	B1	B2	B3	B4	D1 ∅	D2 ∅	D3 ∅	D4 ∅	D5 ∅	D7	D8	L1	T1	T2	W1
EAMF-A-28A-42A	42	31.5	33.5	31	22 G7	28 H7	16	30	21	M3	M3	16.5	1.8	2.5	45°
EAMF-A-30A-42A	42	-	-	31	22	30	16	-	26.2	M3	M3	18	4.6	2.5	30°

Ordering data

	Part No.	Type
	530 059	MTRE-ST-42-48S-AA
	530 060	MTRE-ST-42-48S-AB

Stepper motors MTRE-ST

Accessories

Ordering data for cable KMTRE-ST...						
	Protection class of motor plug	Ambient temperature	Suitable for energy chains	Cable length	Part No.	Type
	IP67	-40 ... +125 °C	Yes	5 m	530 074	KMTRE-ST42-5
				10 m	530 075	KMTRE-ST42-10
				X length (max. 25 m)	530 076	KMTRE-ST42-X

Ordering data for motor flange MTR-FL...			
	Brief description	Part No.	Type
	For connection to a toothed belt axis DGE-8-...-ZR	530 080	EAMF-A-28A-42A
	For connection to a spindle axis DGE-18-...-SP		
	For connection to a toothed belt axis DGE-12-...-ZR	530 079	EAMF-A-30A-42A

Product Range and Company Overview

A Complete Suite of Automation Services


Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com