




- High-precision guidance
- Able to absorb high torques
- Saves space in comparison with standard cylinders
- For contactless position sensing

Guided cylinders DFP

Features

FESTO



Brief description

- Double-acting
- High-precision guidance thanks to recirculating ball bearing guide
- Able to absorb high torques
- Saves space in comparison with standard cylinders with external guide unit
- Flexible cushioning rings/plates at both ends for $\varnothing 10 \dots 16 \text{ mm}$
- Pneumatic cushioning adjustable at both ends for $\varnothing 25 \dots 80 \text{ mm}$
- For contactless position sensing

Guided cylinders DFP

Features

FESTO




Less installation space required

Standard cylinder with guide unit

Guided cylinder
DFP





High precision

Grooved piston rod with recirculating ball bearing guide






Mounting options

Via female thread




Via through-holes



Guided cylinders DFP

Peripherals overview

FESTO



Accessories				
	Brief description	Piston Ø [mm]		→ Page/Internet
		10 ... 16	25 ... 32	
1	Push-on flange FFP	For piston Ø 25 ... 32 mm	–	16
2	Push-on flange FFP	For piston Ø 10 ... 16 mm	–	16
3	Slot cover ABP-5-S	To protect the sensor cable and keep dirt out of the sensor slots	–	18
4	Proximity sensors SME/SMT-8	Can be integrated in the cylinder profile barrel	–	18
5	Connecting cable, straight NEBU	–	–	18
6	Connecting cable, angled NEBU	–	–	18
7	Proximity sensors SME/SMT-10	Can be integrated in the cylinder profile barrel	–	17
8	Proximity sensors SME/SMT-10F	Can be integrated in the cylinder profile barrel	–	17
–	Centring pins/sleeves ZBH	–	–	17

Guided cylinders DFP

Type codes

FESTO


		DFP	–	50	–	80	–	PPV	–	A		S2
Type												
Double-acting												
DFP	Guided cylinder											
Piston Ø [mm]												
Stroke [mm]												
Cushioning												
P	Flexible cushioning rings/plates at both ends											
PPV	Pneumatic cushioning adjustable at both ends											
Sensing												
A	For proximity sensing											
Variant												
S2	Through piston rod											

Guided cylinders DFP

Technical data

FESTO

Function



- Ø - Diameter
10 ... 16 mm
- I - Stroke length
25 ... 100 mm

- T - www.festo.com

Variant




S2



DFP-...-P-A

Function




- Ø - Diameter
25 ... 80 mm
- I - Stroke length
25 ... 500 mm

- T - www.festo.com

Variant



S2



DFP-...-PPV-A

General technical data						
Piston Ø	10	16	25	32	50	80
Pneumatic connection	M3	M5	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$
Operating medium	Filtered compressed air, lubricated or unlubricated					
Guide	Via ball bearings					
Cushioning	Flexible cushioning rings/plates at both ends			Adjustable at both ends		
Cushioning length [mm]	–	–	17	20	22	32
Position sensing	For proximity sensing					
Type of mounting	Via female threads					
	Using through holes					
Mounting position	Any					

Operating and environmental conditions	
Operating pressure [bar]	0.5 ... 10
Ambient temperature ¹⁾ [°C]	–10 ... +60

1) Note operating range of proximity sensors

Forces [N] and impact energy [Nm]						
Piston Ø	10	16	25	32	50	80
Theoretical force at 6 bar, advancing ¹⁾	47	121	295	483	1,178	3,016
Theoretical force at 6 bar, retracting	31	91	217	364	884	2,262
Max. impact energy at the end positions	0.05	0.07	0.2	0.35	0.6	1.6

1) The force in the advance stroke is the same as the force in the return stroke with the variant S2.

Guided cylinders DFP

Technical data

FESTO

Speed [m/s]							
Piston Ø	10	16	25	32	50	80	
Maximum speed advancing v_{maxA}	0.8	0.8	1.5	1.5	1	0.9	
Maximum speed retracting v_{maxL}	0.8	0.8	1.5	1.5	1	0.7	


Max. torque ¹⁾ [Nm]							
Piston Ø	10	16	25	32	50	80	
	dynamic	0.2	0.4	1.1	5.8	19	75
	static	0.4	0.6	2.7	8.5	25	100

1) Torque at piston rod

Weights [g]													
Stroke [mm]	Piston Ø												
	10		16		25		32		50		80		
	Basic version	S2	Basic version	S2	Basic version	S2	Basic version	S2	Basic version	S2	Basic version	S2	
25	118	124	180	195	590	652	–	–	–	–	–	–	–
50	147	156	218	238	660	737	1,180	1,297	2,960	3,351	8,077	8,814	
80	173	185	263	290	740	836	1,295	1,439	3,150	3,570	8,561	9,414	
100	198	212	293	325	794	902	1,357	1,519	3,340	3,855	8,856	9,787	
160	–	–	–	–	957	1,102	1,590	1,805	3,804	4,468	9,786	10,949	
200					–	–	1,732	1,983	4,100	4,863	10,460	11,778	
250							1,914	2,210	4,490	5,377	11,289	12,801	
320							–	–	5,030	6,091	12,436	14,220	
400									5,610	6,869	13,750	15,844	
500									–	–	15,442	17,924	

Materials

Sectional view




Guided cylinder	
1 Piston rod	Tempered steel
2 Bearing end cap	Aluminium
3 Cylinder barrel	Anodised aluminium
4 End cap	Aluminium
– Seals	Polyurethane, polyacetal, nitrile rubber
Note on material	Free of copper, PTFE and silicone

Guided cylinders DFP

Technical data

FESTO

Max. permissible dynamic lateral force F_q at the piston rod



Calculation of the max. permissible dynamic lateral force F_q

$$F_q = \frac{A}{(B + X_s + H) \times K + 1 + C \times L}$$

F_q = Permissible lateral force [N]
 A = Equivalent bearing load [N]
 B = Constant [mm]
 C = Constant [1/mm]
 H = Stroke [mm]
 L = Lever arm [mm]
 K = Constant [1/mm]
 X_s = Distance from centre of mass [mm]


Calculation parameters

	Piston Ø [mm]					
	10	16	25	32	50	80
A	220	274	725	1,460	2,430	5,620
B	37.5	37.5	48	57	75.5	96
C	0.84	0.51	0.4	0.22	0.14	0.09
K	0.47	0.47	0.3	0.19	0.13	0.088


Max. permissible dynamic lateral force F_q at the piston rod as a function of the lever arm L

Distance from the centre of mass $X_s = 0$ mm


F_q with 25 mm stroke




F_q with 50 mm stroke



F_q with 80 mm stroke



F_q with 100 mm stroke



Guided cylinders DFP


Technical data

FESTO


Max. permissible dynamic lateral force F_q at the piston rod as a function of the lever arm L

Distance from the centre of mass $X_s = 0$ mm


F_q with 160 mm stroke




F_q with 200 mm stroke




F_q with 250 mm stroke




F_q with 320 mm stroke



F_q with 400 mm stroke



F_q with 500 mm stroke




Guided cylinders DFP


Technical data

FESTO


Deflection f at the piston rod as a function of the lateral force F_q




DFP-10




DFP-16




DFP-25




DFP-32



DFP-50



DFP-80



- 1 25 mm stroke
- 2 50 mm stroke
- 3 80 mm stroke

- 4 100 mm stroke
- 5 160 mm stroke
- 6 200 mm stroke

- 7 250 mm stroke
- 8 320 mm stroke


- 9 400 mm stroke
- 10 500 mm stroke

Guided cylinders DFP


Technical data

FESTO


Torsion angle α of the piston rod as a function of the torque M




DFP-10




DFP-16




DFP-25




DFP-32




DFP-50



DFP-80



Technical data

Download CAD data → www.festo.comPiston $\varnothing$ 10...16 mm

+ = plus stroke length

Technical drawing of a cylinder with dimensions and stroke length indicators. The drawing shows a side view of the cylinder with a piston rod extending from the right. Dimensions are labeled as follows:

- ZM++**: Total length of the cylinder plus two times the stroke length.
- AM**: Distance from the center of the cylinder to the end of the piston rod.
- WH+**: Distance from the center of the cylinder to the end of the piston rod, plus the stroke length.
- VD**: Distance from the center of the cylinder to the end of the piston rod.
- G**: Distance from the center of the cylinder to the end of the piston rod.
- MM**: Distance from the center of the cylinder to the end of the piston rod.
- KK**: Distance from the center of the cylinder to the end of the piston rod.
- B**: Diameter of the cylinder.
- h1**: Distance from the center of the cylinder to the end of the piston rod.

Legend:

- +** = plus stroke length
- ++** = plus 2x stroke length

+ = plus stroke length

++ = plus 2x stroke length

Ø	G	H1	H2	KF	KK	L1	L2	L3	L4	L5 ¹⁾	L6	L7	L8	L9	L10
[mm]						min.									
10	6	14.3	4.5	M4	M4	25	38.5	12.5	25	50	33	9	5.5	5.5	28.5
16	8	17.5	5.5	M4	M6	25	40.5	13	20	44	27.5	11	20	8	30

1) With stroke > 80 mm

Guided cylinders DFP


Technical data

FESTO


Dimensions

Piston Ø 25 ... 80 mm

Download CAD data → www.festo.com



Variant S2



Ø	AF	AM	B	B1	B2	BG	D1	D2	D3	I	EE	F	G	J1	J2
[mm]			Ø d11	±0.02			Ø h7	Ø H7	Ø						
25	12.5	22	25	31	31	14	13	5	4.5	38	G1/8	2.5	22	3.6	7
32	16	22	30	40	40	16	16	5	5.3	45	G1/8	2.5	25.1	4.5	8
50	20	32	40	52	52	17	25	9	6.6	64	G1/4	2.5	29.6	7.5	14
80	24	40	45	75	75	17	40	9	8.4	93	G3/8	2.5	35.9	7	20

Ø	J3	J4	KF	KK	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11
[mm]															
25	3.1	6	M6	M10x1.25	30	58	6.5	11.8	4.1	22.5	31	38	29	2.3	12.8
32	5.2	6	M8	M10x1.25	32	74.5	7	14	3.3	29	40	49	36	1	20
50	8.5	10.4	M10	M16x1.5	40	107.5	10	18	5.1	44	52	70	54	4.2	29
80	8	12.5	M12	M20x1.5	41	143	14	23	10.5	58.5	75	96	72.5	5	39.5

Ø	MM	PL	RT	T1	T2	T3	TG	UG	VA	VD	WH	ZJ	ZM	≈G1	≈G2
[mm]	Ø f8														
25	10	8.5	M5	1	11	21	27	40	2	17.5	29.4	119.5	179	9	5
32	12	15.6	M6	1	14	22	32.5	50	4	18	26	150.4	210	10	6
50	20	14	M8	2.1	16	32	46.5	66	4	28	37	194	273	17	8
80	25	16.4	M10	2.1	20	40	72	96	4	34.7	46	249	338	22	6

Guided cylinders DFP

Technical data

FESTO

Ordering data – Basic version					
Design	Stroke [mm]	Part No.	Type ¹⁾	Stroke [mm]	Part No. Type ¹⁾
	Piston Ø 10 mm			Piston Ø 16 mm	
	25	186 729	DFP-10-25-P-A	25	186 733 DFP-16-25-P-A
	50	186 730	DFP-10-50-P-A	50	186 734 DFP-16-50-P-A
	80	186 731	DFP-10-80-P-A	80	186 735 DFP-16-80-P-A
	100	186 732	DFP-10-100-P-A	100	186 736 DFP-16-100-P-A
	Piston Ø 25 mm			Piston Ø 32 mm	
	25	186 737	DFP-25-25-PPV-A	25	– –
	50	186 738	DFP-25-50-PPV-A	50	186 742 DFP-32-50-PPV-A
	80	186 739	DFP-25-80-PPV-A	80	186 743 DFP-32-80-PPV-A
	100	186 740	DFP-25-100-PPV-A	100	186 744 DFP-32-100-PPV-A
	160	186 741	DFP-25-160-PPV-A	160	186 745 DFP-32-160-PPV-A
	200	–	–	200	186 746 DFP-32-200-PPV-A
	250			250	186 747 DFP-32-250-PPV-A
	Piston Ø 50 mm			Piston Ø 80 mm	
	50	186 748	DFP-50-50-PPV-A	50	186 756 DFP-80-50-PPV-A
	80	186 749	DFP-50-80-PPV-A	80	186 757 DFP-80-80-PPV-A
	100	186 750	DFP-50-100-PPV-A	100	186 758 DFP-80-100-PPV-A
	160	186 751	DFP-50-160-PPV-A	160	186 759 DFP-80-160-PPV-A
	200	186 752	DFP-50-200-PPV-A	200	186 760 DFP-80-200-PPV-A
	250	186 753	DFP-50-250-PPV-A	250	186 761 DFP-80-250-PPV-A
	320	186 754	DFP-50-320-PPV-A	320	186 762 DFP-80-320-PPV-A
	400	186 755	DFP-50-400-PPV-A	400	186 763 DFP-80-400-PPV-A
	500	–	–	500	186 764 DFP-80-500-PPV-A

1) In each case the scope of delivery includes 2 of the centring sleeves listed as accessories. Centring sleeves are supplied to repeat order in packs of 10. Proximity sensors and mounting screws are not included in the scope of delivery for guided cylinders.

Guided cylinders DFP

Technical data

FESTO

Ordering data – Variants					
Design	Stroke [mm]	Part No.	Type ¹⁾²⁾	Stroke [mm]	Part No. Type ¹⁾²⁾
S2 – Through piston rod					
	Piston Ø 10 mm			Piston Ø 16 mm	
	25	186 765	DFP-10-25-P-A-S2	25	186 769 DFP-16-25-P-A-S2
	50	186 766	DFP-10-50-P-A-S2	50	186 770 DFP-16-50-P-A-S2
	80	186 767	DFP-10-80-P-A-S2	80	186 771 DFP-16-80-P-A-S2
	100	186 768	DFP-10-100-P-A-S2	100	186 772 DFP-16-100-P-A-S2
	Piston Ø 25 mm			Piston Ø 32 mm	
	25	186 773	DFP-25-25-PPV-A-S2	25	– –
	50	186 774	DFP-25-50-PPV-A-S2	50	186 778 DFP-32-50-PPV-A-S2
	80	186 775	DFP-25-80-PPV-A-S2	80	186 779 DFP-32-80-PPV-A-S2
	100	186 776	DFP-25-100-PPV-A-S2	100	186 780 DFP-32-100-PPV-A-S2
	160	186 777	DFP-25-160-PPV-A-S2	160	186 781 DFP-32-160-PPV-A-S2
	200	–	–	200	186 782 DFP-32-200-PPV-A-S2
	250	–	–	250	186 783 DFP-32-250-PPV-A-S2
	Piston Ø 50 mm			Piston Ø 80 mm	
	50	186 784	DFP-50-50-PPV-A-S2	50	186 792 DFP-80-50-PPV-A-S2
	80	186 785	DFP-50-80-PPV-A-S2	80	186 793 DFP-80-80-PPV-A-S2
	100	186 786	DFP-50-100-PPV-A-S2	100	186 794 DFP-80-100-PPV-A-S2
	160	186 787	DFP-50-160-PPV-A-S2	160	186 795 DFP-80-160-PPV-A-S2
	200	186 788	DFP-50-200-PPV-A-S2	200	186 796 DFP-80-200-PPV-A-S2
	250	186 789	DFP-50-250-PPV-A-S2	250	186 797 DFP-80-250-PPV-A-S2
	320	186 790	DFP-50-320-PPV-A-S2	320	186 798 DFP-80-320-PPV-A-S2
	400	186 791	DFP-50-400-PPV-A-S2	400	186 799 DFP-80-400-PPV-A-S2
	500	–	–	500	186 800 DFP-80-500-PPV-A-S2

- 1) In each case the scope of delivery includes 2 of the centring sleeves listed as accessories. Centring sleeves are supplied to repeat order in packs of 10. Proximity sensors and mounting screws are not included in the scope of delivery for guided cylinders.
- 2) The scope of delivery also includes a hex nut for the piston rod thread.

Guided cylinders DFP

Accessories

FESTO


Push-on flange FFP

for piston $\varnothing$ 10 ... 16 mm

Material:

Wrought aluminium alloy

Free of copper, PTFE and silicone



Dimensions and ordering data

For $\varnothing$	B1	B2	B4	B5	D1	D2	D3	D4	L1	L2	L3	L4	T1	CRC ¹⁾	Part No.	Type
[mm]		± 0.02				$\varnothing$ H7							$+0.2$			
10	15	9	26	20	M4	2	M4	M3	15	8.5	9	31.5	2.5	2	186 801	FFP-10
16	19	12	33	26	M4	5	M4	M4	17	10.5	11	31.5	1	2	186 802	FFP-16

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents


Push-on flange FFP

for piston $\varnothing$ 25 ... 80 mm

Material:

Wrought aluminium alloy

Free of copper, PTFE and silicone



Dimensions and ordering data

For $\varnothing$	B1	B2	B3	D1	D2	D3	L1	L2	L3	L4	T1	CRC ¹⁾	Part No.	Type
[mm]		± 0.02			$\varnothing$ H7						$+0.2$			
25	38	30	22	M6	7	M5	27	18	19	39	1.6	2	186 803	FFP-25
32	49	40	25	M8	7	M5	27	18	19	41	1.6	2	186 804	FFP-32
50	64	50	36	M10	9	M6	35	23	25	52	2.1	2	186 805	FFP-50
80	94	70	54	M12	12	M8	40	25	27	56	2.6	2	186 806	FFP-80

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Guided cylinders DFP

Accessories


FESTO

Centring sleeves ZBH

Material:

Steel, corrosion resistant

Free of copper, PTFE and silicone



Dimensions and ordering data							
D1	B1	D2	CRC ¹⁾	Weight	Part No.	Type	PU ²⁾
Ø		Ø		[g]			
h7	-0.2						
5	2.4	3.2	2	1	189 652	ZBH-5	10
7	3	5.3	2	1	186 717	ZBH-7	10
9	4	6.4	2	1	150 927	ZBH-9	10

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

2) Packaging unit quantity

Ordering data – Proximity sensors for C-slot, magneto-resistive						Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire, in-line	2.5	525 915	SMT-10F-PS-24V-K2,5L-OE	
			Plug M8x1, 3-pin, in-line	0.3	525 916	SMT-10F-PS-24V-K0,3L-M8D	
			Plug M8x1, 3-pin, lateral	0.3	526 675	SMT-10F-PS-24V-K0,3Q-M8D	
	Insertable in the slot lengthwise	PNP	Plug M8x1, 3-pin, in-line	0.3	173 220	SMT-10-PS-SL-LED-24	
			Cable, 3-wire, in-line	2.5	173 218	SMT-10-PS-KL-LED-24	


Ordering data – Proximity sensors for C-slot, magnetic reed						Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot from above, flush with cylinder profile	Contacting	Plug M8x1, 3-pin, in-line	0.3	525 914	SME-10F-DS-24V-K0,3L-M8D	
			Cable, 3-wire, in-line	2.5	525 913	SME-10F-DS-24V-K2,5L-OE	
			Cable, 2-wire, in-line	2.5	526 672	SME-10F-ZS-24V-K2,5L-OE	
	Insertable in the slot lengthwise	Contacting	Plug M8x1, 3-pin, in-line	0.3	173 212	SME-10-SL-LED-24	
			Cable, 3-wire, in-line	2.5	173 210	SME-10-KL-LED-24	

Guided cylinders DFP

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 3-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables					Technical data → Internet: nebu
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2,5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2,5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2,5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2,5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Ordering data – Slot cover for T-slot				
	Mounting	Length	Part No.	Type
	Insertable from above	2x 0.5 m	151 680	ABP-5-S