

End-position controllers CPX-CMPX



End-position controllers CPX-CMPX

Overview


Servo-pneumatic drive technology

Positioning and Soft Stop applications as an integral component of the valve terminal CPX – the modular peripheral system for decentralised automation tasks.

The modular design means that valves, digital inputs and outputs, positioning modules and end-position controllers, as appropriate to the application, can be combined in almost any way on the CPX terminal.

Advantages:

- Pneumatics and electrics – control and positioning on one platform
- Innovative positioning technology – piston rod drives, rodless drives, rotary drives
- Actuation via fieldbus
- Remote maintenance, remote diagnostics, web server, SMS and e-mail alert are all possible via TCP/IP
- Modules can be quickly exchanged and expanded without altering the wiring



End-position controllers CPX-CMPX

Key features

Axis controller CPX-CMAX



Free choice:
Position and force control, directly actuated or selected from one of 64 configurable position sets.
Looking for something more:
The configurable function for switching to the next set enables simple functional sequences to be realised in the axis controller CPX-CMAX. Everything is recognisable:
The auto-identification function identifies each station with its device data on the controller CPX-CMAX.

Also included:
The functional scope of the controller CPX-CMAX includes actuation of a brake or clamping unit via the proportional directional control valve VPWP.
Up to 7 modules (max. 7 axes) can be operated in parallel and independently of each other.
Commissioning via FCT (Festo configuration software) or via fieldbus: no programming, only configuring.

Technical data → Internet: [cpx-cmax](#)

Advantages:

- Greater flexibility
- OEM friendly – commissioning also via fieldbus
- Clear installation and fast commissioning
- Cost effective
- You program the system in your PLC environment

End-position controller CPX-CMPX



Fast travel between the mechanical end stops of the cylinder, stopping gently and without impact in the end position.
Fast commissioning via control panel, fieldbus or handheld unit.
Improved downtime regulation.
Actuation of a brake or clamping unit via the proportional directional control valve VPWP is an integral component of the controller CMPX.

Depending on the fieldbus chosen, up to 9 end-position controllers can be actuated on the CPX terminal. All system data can be read and written via the fieldbus, for example the mid positions also.

Technical data → 7

Advantages:

- Greater flexibility
- OEM friendly – commissioning also via fieldbus
- Clear installation and fast commissioning
- Cost-effective
 - Up to 30% faster cycle rates
 - Significantly reduced system vibration
- Improved work ergonomics thanks to significantly reduced noise level
- The extended diagnostics help to reduce the service time of the machine

Proportional directional control valve VPWP



The 5/3-way proportional directional control valve for applications with Soft Stop and pneumatic positioning.
Fully digitalised – with integrated pressure sensors, with new diagnostic functions.
In sizes 4, 6 and 8.
Flow rate from 350, 700 and 1,400 l/min.

With switching output for actuating a brake.
Coloured supply ports.
Pre-assembled cables guarantee faultless and fast connection with the controllers CPX-CMPX and CPX-CMAX.

Technical data → Internet: [vpwp](#)

Advantages:

- Clear installation and fast commissioning
- Reduction of system downtimes thanks to the new diagnostic options
- With switching output for actuating a brake/clamping unit


End-position controllers CPX-CMPX

Drive options

FESTO

System with linear drive DGCI

Technical data → Internet: dgci



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Linear drive DGCI with displacement encoder
- 6 Connecting cable KVI-CP-3-...


- Pneumatic rodless linear drive with displacement encoder and recirculating ball bearing guide
- Displacement encoder with absolute and contactless measuring
- Identically constructed with pneumatic linear drive DGC
- Diameter: 18 ... 40 and 63 mm
- Stroke: 100 ... 2,000 mm in fixed lengths
- Range of application: Soft Stop and pneumatic positioning of loads from 1 ... 180 kg
- No sensor interface required

Advantages:

- Finished drive unit, precision guide
- Excellent running characteristics
- For fast and accurate positioning down to ± 0.2 mm (only with axis controller CPX-CMAX)

System with standard cylinder DNCI

Technical data → Internet: dnci



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Standard cylinder DNCI with displacement encoder
- 5 Sensor interface CASM-S-D3-R7
- 6 Connecting cable KVI-CP-3-...

- Standard cylinder with integrated displacement encoder, conforms to DIN ISO 6432, VDMA 24 562, NF E 49 003.1 and Uni 10 290
- Displacement encoder with contactless and incremental measuring
- Diameter: 32 ... 63 mm
- Stroke: (10) 100 ... 500 (2,000) mm
- Range of application: Soft Stop and pneumatic positioning: loads from 3 ... 180 kg and the matching sensor interface CASM-S-D3-R7
- Pre-assembled cables guarantee faultless and fast electrical connection

Advantages:


- Compact drive unit
- Universal applications
- Also with guide unit
- For fast and accurate positioning down to ± 0.3 mm (only with axis controller CPX-CMAX)

End-position controllers CPX-CMPX

Drive options

System with swivel module DSMI

Technical data → Internet: [dsmi](#)



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Swivel module DSMI with displacement encoder
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5


- Swivel module DSMI with integrated displacement encoder
- Identically constructed with pneumatic swivel module DSM
- Absolute displacement encoder on basis of potentiometer
- Swivel range from 0 ... 270°
- Size: 25 and 40
- Max. torque: 5 or 20 Nm
- Range of application: Soft Stop and pneumatic positioning: mass moments of inertia from 15 ... 1,200 kgcm² and the matching sensor interface CASM-S-D2-R3
- Pre-assembled cables guarantee faultless and fast connection with the proportional directional control valve VPWP

Advantages:

- Finished drive unit, compact, can be used immediately
- High angular acceleration
- With adjustable fixed stops
- For fast and accurate positioning down to ±0.2° (only with axis controller CPX-CMAX)

System with potentiometer

Technical data → Internet: [casm](#)



- 2 Proportional directional control valve VPWP
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5
- 8 Connecting cable NEBC-A1W3-K-0,4-N-M12G5

- Attachable potentiometers with absolute measurement, with high degree of protection
- With connecting rod or moment compensator
- Measuring range: 100 ... 2,000 mm
- Pre-assembled cables guarantee faultless and fast connection with the sensor interface CASM
- Range of application: Soft Stop and pneumatic positioning with cylinder Ø 18 ... 80 mm, loads from 1 ... 300 kg

Advantages:

- Clear installation and fast commissioning
- Cost effective
- Can also be used in harsh environmental conditions
- Variety in the drives: CPX-CMPX and CPX-CMAX also support cylinders with external displacement encoder

End-position controllers CPX-CMPX


Drive options

System components for Soft Stop systems with end-position controller CPX-CMPX							
		Linear drive DGCI	Standard cylinder DNCI	Swivel module DSMI	Potentiometer LWG	Potentiometer TLF	→ Page/Internet
1	End-position controller CPX-CMPX	■	■	■	■	■	7
2	Proportional directional control valve VPWP	■	■	■	■	■	vpwp
4	Sensor interface CASM-S-D2-R3	-	-	■	■	■	casm
5	Sensor interface CASM-S-D3-R7	-	■	-	-	-	casm
6	Connecting cable KVI-CP-3-...	■	■	■	■	■	10
7	Connecting cable NEBC-P1W4-...	-	-	■	■	-	nebc
8	Connecting cable NEBC-A1W3-...	-	-	-	-	■	nebc


End-position controllers CPX-CMPX

Type codes and peripherals overview

Type codes



Peripherals overview



Accessories		
Type	Brief description	→ Page/Internet
1	End-position controller CPX-CMPX Integrated in the CPX terminal. Screws for mounting on the plastic interlinking block are included in the scope of delivery.	8
6	Connecting cable KVI-CP-3 For connecting end-position controller CPX-CMPX and proportional directional control valve VPWP.	10
9	Operator unit CPX-MMI-1 Commissioning and servicing unit for the CPX terminal. It provides data requisition, configuration and diagnostics functions for CPX terminals.	11
10	Connecting cable KV-M12 For connecting the operator unit CPX-MMI-1 and CPX terminal.	10
11	Inscription label IBS For labelling the modules.	10
12	Interlinking block CPX-GE Connects the individual modules. Two versions are available: plastic or metal interlinking block.	11
-	Screws CPX-M-M3 For mounting on the metal interlinking block.	10

End-position controllers CPX-CMPX

Technical data

The end-position controller CPX-CMPX is intended exclusively for use in valve terminals CPX.



General technical data		
Operating voltage range	[V DC]	18 ... 30
Nominal operating voltage	[V DC]	24
Current consumption at nominal operating voltage	[mA]	80
Load voltage range	[V DC]	20 ... 30
Nominal load voltage	[V DC]	24
Perm. load current	[A]	2.5
Power supply requirement		PELV (Protected Extra-Low Voltage)
Number of axes per module		1
Length of connecting cable to axis	[m]	≤ 30
Max. no. of modules		9
Display		7-segment display
Control elements		3 keys
Assigned addresses	Outputs	bit 6x8
	Inputs	bit 6x8
Diagnostics		
LED indicators	Red	Module status
	Yellow	Load voltage
7-segment display		3-digit, for parameter and status
Device-specific diagnostics via fieldbus		Parameter and status
Device-specific diagnostics via operator unit CPX-MMI		Parameter and status
Control interface		
Data		CAN bus with Festo protocol
		Digital
		Integrated terminating resistor
Electrical connection		5-pin
		M9
		Socket
Materials		
Housing		Polyamide
Product weight	[g]	140
Dimensions	Length	[mm] 107
	Width	[mm] 50
	Height	[mm] 55


Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +50
Relative air humidity	[%]	5 ... 95, non-condensing
Protection class to IEC 60529		IP65
CE mark (see declaration of conformity)		To EU EMC Directive
Vibration resistance to DIN/IEC 68, Part 2-6		With wall mounting: tested to severity level 2
		With H-rail mounting: tested to severity level 1
Continuous shock resistance to DIN/IEC 68, Part 2-27		With wall mounting: tested to severity level 2
		With H-rail mounting: tested to severity level 1

End-position controllers CPX-CMPX

Technical data

Performance data		
	Value	Comment
Motion characteristics	Stop-to-stop positioning	–
Operating pressure [bar]	4 ... 8	Range recommended
Stroke [mm]	100 ... 2,000	Dependent on drive
Load [kg]	1 ... 300	Dependent on drive
Cycle time [s]	0.45 ... 2.50	Dependent on stroke and load
Number of intermediate positions	2	–
Stop accuracy [mm]	< 0.05	Determined by the fixed stop
Intermediate position accuracy [mm]	±2	–

Connection and display components



Pin allocation – plug 2

	Pin	Signal	Designation
	1	+24 V	Nominal operating voltage
	2	+24 V	Load voltage
	3	0 V	Ground
	4	CAN_H	CAN high
	5	CAN_L	CAN low
	Housing	Screened	Cable screening


Permitted bus nodes/FEC



Bus node/FEC	Protocol	Max. perm. number of modules	Remarks
CPX-FEC	–	9	Revision 14 (R14) and above
CPX-FB6	Interbus	2	On request
CPX-FB11	DeviceNet	9	Revision 20 (R20) and above
CPX-FB13	Profibus DP	9	Revision 22 (R22) and above
CPX-FB14	CANopen	3	On request
CPX-FB23	CC-Link	9	On request
CPX-FB32	Ethernet/IP	9	On request
CPX-FB33	Profinet, M12	9	On request
CPX-FB34	Profinet, RJ45	9	On request
CPX-FB38	EtherCat	9	On request


End-position controllers CPX-CMPX


Accessories


FESTO

Ordering data – End-position controllers		Part No.	Type
	Order code in the CPX configurator: T20	548931	CPX-CMPX-C-1-H1

Ordering data – Connecting cables			
	Brief description	Cable length [m]	Part No. Type
	Connecting cable with angled plug and angled socket	0.25	540327 KVI-CP-3-WS-WD-0,25
		0.5	540328 KVI-CP-3-WS-WD-0,5
		2	540329 KVI-CP-3-WS-WD-2
		5	540330 KVI-CP-3-WS-WD-5
		8	540331 KVI-CP-3-WS-WD-8
		Connecting cable with straight plug and straight socket	2
5	540333 KVI-CP-3-GS-GD-5		
8	540334 KVI-CP-3-GS-GD-8		
	Connector for control cabinet through-feed	–	543252 KVI-CP-3-SSD

Ordering data – Screws			
	Brief description	Part No.	Type
	For mounting on the metal interlinking block	550216	CPX-M-M3X22-4X

Ordering data – Inscription labels			
	Brief description	Quantity	Part No. Type
	Inscription labels 6x10, in frames	64	18576 IBS-6X10


Documentation ¹⁾			
	Language	Part No.	Type
	DE	555479	P.BE-CPX-CMPX-SYS-DE
	EN	555480	P.BE-CPX-CMPX-SYS-EN
	ES	555481	P.BE-CPX-CMPX-SYS-ES
	FR	555482	P.BE-CPX-CMPX-SYS-FR
	IT	555483	P.BE-CPX-CMPX-SYS-IT
	SV	555484	P.BE-CPX-CMPX-SYS-SV


1) Manual in paper form is not included in the scope of delivery


End-position controllers CPX-CMPX


Accessories

FESTO

Ordering data – Operator units				
	Brief description	Part No.	Type	
	Commissioning and servicing unit for the CPX terminal	529043	CPX-MMI-1	

Ordering data – Connecting cables				
	Brief description	Cable length [m]	Part No.	Type
	Connecting cable with straight plug and straight socket, for operator unit CPX-MMI-1	1.5	529044	KV-M12-M12-1,5
		3.5	530901	KV-M12-M12-3,5

Ordering data – Interlinking block, plastic, as expansion block					
	Brief description	Connection	Part No.	Type	
	Without power supply	–	195742	CPX-GE-EV	
	With additional power supply for outputs	M18	195744	CPX-GE-EV-Z	
		7/8" – 5-pin	541248	CPX-GE-EV-Z-7/8-5POL	
		7/8" – 4-pin	541250	CPX-GE-EV-Z-7/8-4POL	
	With additional power supply for valves	M18	533577	CPX-GE-EV-V	
		7/8" – 4-pin	541252	CPX-GE-EV-V-7/8-4POL	

Ordering data – Tie rods				
	Brief description	Extension	Part No.	Type
	For extension using an interlinking block	1-fold	525418	CPX-ZA-1-E