

## Soft-start and exhaust valves MS-SV, MS series








**FESTO**



# Soft-start and exhaust valves MS-SV, MS series

FESTO

Product range overview – MS series service units

Type	Size			Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [µm]					
						0.05 ...	0.05 ...	0.1 ...	0.3 ...	0.1 ...	0.5 ...						
Code						0.7	2.5	4	7	12	16	0.01	1	5	40		
					AG...	D2	D4	D5	D6	D7	D8	A	B	C	E		
Service units																	
MSB-FRC		4	G1/8, G1/4	G1/8, G1/4, G3/8		–	–	–	■	■	–	–	–	■	■		
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	■	■	–	–	–	■	■		
		9	–														
		12	–														
Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9)																	
MSB		4	G1/4	G1/8, G1/4, G3/8		–	–	–	■	■	–	–	–	■	■		
		6	G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	■	■	–	–	–	■	■		
		9	–														
		12	–														
Individual devices																	
Filter regulators MS-LFR		4	G1/8, G1/4	G1/8, G1/4, G3/8		–	–	■	■	■	–	–	–	■	■		
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	■	■	■	■	–	–	■	■		
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2		–	–	■	■	■	■	–	–	■	■		
		12	–	G1, G1 1/4, G1 1/2, G2		–	–	–	■	■	■	–	–	■	■		
Filters MS-LF		4	G1/8, G1/4	G1/8, G1/4, G3/8		–	–	–	–	–	–	–	–	■	■		
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	–	–	–	–	–	■	■		
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2		–	–	–	–	–	–	–	–	■	■		
		12	–	G1, G1 1/4, G1 1/2, G2		–	–	–	–	–	–	–	–	■	■		
Fine and micro filters MS-LFM		4	G1/8, G1/4	G1/8, G1/4, G3/8		–	–	–	–	–	–	■	■	–	–		
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	–	–	–	■	■	–	–		
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2		–	–	–	–	–	–	■	■	–	–		
		12	–	G1, G1 1/4, G1 1/2, G2		–	–	–	–	–	–	■	■	–	–		
Activated carbon filters MS-LFX		4	G1/8, G1/4	G1/8, G1/4, G3/8		–	–	–	–	–	–	–	–	–	–		
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	–	–	–	–	–	–	–		
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2		–	–	–	–	–	–	–	–	–	–		
		12	–	G1, G1 1/4, G1 1/2, G2		–	–	–	–	–	–	–	–	–	–		
Water separators MS-LWS																	
		4	–														
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4		–	–	–	–	–	–	–	–	–	–		
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2		–	–	–	–	–	–	–	–	–	–		
		12	–	G1, G1 1/4, G1 1/2, G2		–	–	–	–	–	–	–	–	–	–		

# Soft-start and exhaust valves MS-SV, MS series

FESTO











Product range overview – MS series service units

Type	Size	Bowl guard		Condensate drains				Pressure indicator					Security		Options		→ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	E11	S	Z	
<b>Service units</b>																	
<b>MSB-FRC</b>	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6
	9	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
<b>Service unit combinations</b>																	
<b>MSB</b>	4	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6
	9	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
<b>Individual devices</b>																	
<b>Filter regulators MS-LFR</b>	4	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	ms4-lfr
	6	■	■	■	■	■	■	■	■	–	■	■	■	■	–	■	ms6-lfr
	9	–	■	■	■	■	■	■	■	–	■	■	■	■	–	■	ms9-lfr
	12	–	■	■	–	■	■	■	■	–	■	–	■	■	–	■	ms12-lfr
<b>Filters MS-LF</b>	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	ms4-lf
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms6-lf
	9	–	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms9-lf
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lf
<b>Fine and micro filters MS-LFM</b>	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	ms4-lfm
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms6-lfm
	9	–	■	■	■	■	■	–	–	–	–	–	–	–	–	■	ms9-lfm
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lfm
<b>Activated carbon filters MS-LFX</b>	4	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms4-lfx
	6	■	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms6-lfx
	9	–	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms9-lfx
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	■	ms12-lfx
<b>Water separators MS-LWS</b>	4	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	■	–	–	■	■	–	–	–	–	–	–	–	–	■	ms6-lws
	9	–	■	–	–	■	■	–	–	–	–	–	–	–	–	■	ms9-lws
	12	–	■	–	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lws

# Soft-start and exhaust valves MS-SV, MS series

FESTO

Product range overview – MS series service units

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Supply voltage			
				0.05 ... 0.7	0.05 ... 2.5	0.1 ... 4	0.3 ... 7	0.1 ... 12	0.5 ... 16	24 V DC, connection pattern to EN 175301	24 V DC, connection M12 to IEC 61076-2-101	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301
Code			AG...	D2	D4	D5	D6	D7	D8	V24	V24P	V110	V230
<b>Individual devices</b>													
Pressure regulators <b>MS-LR</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	■	■	■	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	■	■	–	–	–	–
Pressure regulators <b>MS-LRB</b>		4	G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators <b>MS-LRP</b>		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators <b>MS-LRPB</b>		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Electrical pressure regulators <b>MS-LRE</b>		4	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–
Lubricators <b>MS-LOE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	–
On-off valves, manually actuated <b>MS-EM(1)</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	–
On-off valves, electrically actuated <b>MS-EE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	■	–	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	■	–	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	–	–	–	■	■	■	■
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	■	■	■	■
Soft-start valves, pneumatically actuated <b>MS-DL</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	–
Soft-start valves, electrically actuated <b>MS-DE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	■	–	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	■	–	■	■
		9	–	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	■	■	■	■

# Soft-start and exhaust valves MS-SV, MS series

FESTO







Product range overview – MS series service units

Type	Size	Bowl guard		Pressure indicator					Security		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	AS	E11	S	Z	
<b>Individual devices</b>													
Pressure regulators <b>MS-LR</b>	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lr
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lr
	9	–	–	■	■	–	■	■	■	■	–	■	ms9-lr
	12	–	–	■	■	–	■	–	■	■	–	■	ms12-lr
Pressure regulators <b>MS-LRB</b>	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lrb
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lrb
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators <b>MS-LRP</b>	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrp
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators <b>MS-LRPB</b>	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrpb
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Electrical pressure regulators <b>MS-LRE</b>	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	■	–	■	–	–	–	–	■	ms6-lre
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Lubricators <b>MS-LOE</b>	4	■	■	–	–	–	–	–	–	–	–	■	ms4-loe
	6	■	■	–	–	–	–	–	–	–	–	■	ms6-loe
	9	–	■	–	–	–	–	–	–	–	–	■	ms9-loe
	12	–	■	–	–	–	–	–	–	–	–	■	ms12-loe
On-off valves, manually actuated <b>MS-EM(1)</b>	4	–	–	■	■	■	■	■	–	–	■	■	ms4-em1
	6	–	–	■	■	–	■	■	–	–	■	■	ms6-em1
	9	–	–	■	■	–	■	–	–	–	■	■	ms9-em
	12	–	–	■	■	–	■	–	–	–	■	■	ms12-em
On-off valves, electrically actuated <b>MS-EE</b>	4	–	–	■	■	■	■	■	–	–	■	■	ms4-ee
	6	–	–	■	■	–	■	■	–	–	■	■	ms6-ee
	9	–	–	■	■	–	■	–	–	–	■	■	ms9-ee
	12	–	–	■	■	–	■	–	–	–	■	■	ms12-ee
Soft-start valves, pneumatically actuated <b>MS-DL</b>	4	–	–	■	■	■	■	■	–	–	–	■	ms4-dl
	6	–	–	■	■	–	■	■	–	–	–	■	ms6-dl
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-dl
Soft-start valves, electrically actuated <b>MS-DE</b>	4	–	–	■	■	■	■	■	–	–	–	■	ms4-de
	6	–	–	■	■	–	■	■	–	–	–	■	ms6-de
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-de

## Soft-start and exhaust valves MS-SV, MS series

**FESTO**

Product range overview – MS series service units

Type	Size	Pneumatic connection in housing	Connecting plate	Performance Level		Supply voltage			
				Category 1, 1-channel	Category 4, 2-channel with self-monitoring	24 V DC, connection pattern to EN 175301	24 V DC, connection M12 to IEC 61076-2-101/ to EN 60947-5-2	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301
Code			AG...	C	E	V24	V24P	V110	V230
<b>Individual devices</b>									
Soft start and exhaust valves <b>MS-SV-C</b>		4	–		–	■	■	■	■
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	–	–	–
		12	–						
Soft start and exhaust valves <b>MS-SV-E</b>		4	–						
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	■	■	–	–
		9	–						
		12	–						
Membrane air dryers <b>MS-LDM1</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–
		9	–						
		12	–						
Branching modules <b>MS-FRM</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–
Distributor blocks <b>MS-FRM-FRZ</b>		4	G1/4	–	–	–	–	–	–
		6	G1/2	–	–	–	–	–	–
		9	–						
		12	–						
Flow sensors <b>SFAM</b>		4	–						
		6	G1/2	G1/2	–	–	–	–	–
		9	–	G1, G1 1/2	–	–	–	–	–
		12	–						

# Soft-start and exhaust valves MS-SV, MS series

FESTO

Product range overview – MS series service units


Type	Size	Bowl guard		Pressure indicator					Switch output		Options		→ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	2x PNP or NPN, 1 analogue output 4 ... 20 mA	2x PNP or NPN, 1 analogue output 0 ... 10 V	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	2SA	2SV	S	Z/R	
<b>Individual devices</b>													
Soft start and exhaust valves <b>MS-SV-C</b>	4	–											–
	6	–	–	■	■	–	■	■	–	–	■	■	8
	9	–	–	■	■	–	■	■	–	–	■	■	32
	12	–											–
Soft start and exhaust valves <b>MS-SV-E</b>	4	–											–
	6	–	–	■	■	–	■	■	–	–	■	■	18
	9	–											–
	12	–											–
Membrane air dryers <b>MS-LDM1</b>	4	–	■	–	–	–	–	–	–	–	–	■	ms4-ldm1
	6	–	■	–	–	–	–	–	–	–	–	■	ms6-ldm1
	9	–											–
	12	–											–
Branching modules <b>MS-FRM</b>	4	–	–	■	■	■	■	■	–	–	–	■	ms4-frm
	6	–	–	■	■	–	■	■	–	–	–	■	ms6-frm
	9	–	–	■	■	–	■	■	–	–	–	■	ms9-frm
	12	–	–	■	–	–	–	–	–	–	–	–	ms12-frm
Distributor blocks <b>MS-FRM-FRZ</b>	4	–	–	–	–	–	–	–	–	–	–	■	ms4-frm
	6	–	–	–	–	–	–	–	–	–	–	■	ms6-frm
	9	–											–
	12	–											–
Flow sensors <b>SFAM</b>	4	–											–
	6	–	–	–	–	–	–	–	■	■	–	■	sfam-62
	9	–	–	–	–	–	–	–	■	■	–	■	sfam-90
	12	–											–

## Soft-start and quick exhaust valves MS6-SV-C, MS series

Peripherals overview

**FESTO**

### Soft-start and quick exhaust valve MS6-SV-C



#### Note


Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Supply voltage  
V24/10V24/V110/V230

Supply voltage  
10V24P

Supply voltage  
V24P



## Soft-start and quick exhaust valves MS6-SV-C, MS series

Peripherals overview

Mounting attachments and accessories						
		Individual device		Combination		➔ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
1	Cover cap MS6-END	–	–	■	–	ms6-end
2	Mounting plate MS6-AEND	■ <sup>1)</sup>	–	■ <sup>1)</sup>	–	ms6-aend
3	Connecting plate MS6-AG...	–	■ <sup>1)</sup>	–	■ <sup>1)</sup>	ms6-ag
4	Mounting bracket MS6-WB	■	■	–	–	ms6-wb
5	Module connector MS6-MV	–	■	■	■	ms6-mv
6	Mounting bracket MS6-WP	■	■	■	■	ms6-wp
	Mounting bracket (not shown) MS6-WPB/WPE/WPM	■	■	■	■	ms6-wp
7	Silencer U-¾-B	■	■	■	■	45
8	MS pressure gauge AG/RG	■	■	■	■	16
9	Adapter plate for EN pressure gauge ¼ A4	■	■	■	■	16
10	Pressure gauge MA	■	■	■	■	46
11	Pressure sensor with operational status indicator AD7 ... AD10	■	■	■	■	16
12	Connecting cable NEBU-M8...-LE3	■	■	■	■	46
13	Pressure sensor with LCD display AD1 ... AD4	■	■	■	■	16
14	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	46
15	Cover MS6-SV-C-MK	■	■	■	■	44
16	Illuminating seal MEB-LD	■	■	■	■	45
17	Plug socket with cable KMEB	■	■	■	■	45
18	Plug socket MSSD-EB	■	■	■	■	45
19	Locking clip CPV18-HV	■	■	■	■	46
20	Connecting cable NEBU-M12G5	■	■	■	■	46
21	Connecting cable NEBU-M12W5	■	■	■	■	46

1) Module connector MS6-MV [5] or mounting bracket MS6-WP/WPB/WPE/WPM [6] is required for mounting.

## Soft-start and quick exhaust valves MS6-SV-C, MS series

**FESTO**

Type codes

		MS	6	-	SV	-	1/2	-	C	-	10V24	-	S
Series													
MS	Standard service unit												
Size													
6	Grid dimension 62 mm												
Service function													
SV	Soft-start and quick exhaust valve												
Pneumatic connection													
1/2	Female thread G1/2												
Performance level													
C	Category 1, to EN ISO 13849-1												
Supply voltage													
10V24	Supply voltage 24 V DC												
Silencer													
S	Silencer												


Additional variants can be ordered using the modular product system → 16

- Connecting plates
- Supply voltage
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Tamper protection
- Flow direction

# Soft-start and quick exhaust valves MS6-SV-C, MS series

Technical data

## Function



## Flow rate

5,700 l/min

## Temperature range

0 ... +60 °C

## Pressure

3 ... 18 bar

[www.festo.com/en/](http://www.festo.com/en/)

Spare\_parts\_service



Electro-pneumatic soft-start and quick exhaust valve for gradual pressurisation and quick exhausting of system components (single channel).

The main flow control valve in the cover permits a gradual build-up of output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is present at the output.

- Suitable for applications with high flow rates and restricted space with medium safety requirements up to controller category 1, performance level "c"
- High volumetric flow rate for pressurisation and venting
- The filling flow rate can be set via a flow control valve for gradual pressure build-up
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional cover for the control sections as tamper protection

## Safety characteristics

Conforms to standard	EN ISO 13849-1
Safety function	Venting
Performance level (PL)	Venting: up to category 1, PL c
Proven component	Yes
Shock resistance	Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 according to FN 942017-4 and EN 60068-2-6

## General technical data

Pneumatic connection 1, 2	G½ (female thread)	G¼ ... G¾ (with connecting plate AG...)
Pneumatic connection 3	G¾	
Actuation type	Electric	
Design	Piston spool valve	
Type of mounting	Via accessories	
	In-line installation	
Mounting position	Any	
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output	
	Via pressure sensor for displaying output pressure via operational status indicator and electrical output	
	Via pressure gauge for displaying output pressure	
	Via pressure gauge with red/green scale for displaying output pressure	
	G¼ prepared	
Valve function	3/2-way valve, closed, single solenoid	
	Soft-start function, adjustable	
Non-overlapping	Yes	
Exhaust function	No flow control	
Reset method	Mechanical spring	
Type of control	Piloted	
Pilot air supply	Internal	
Sealing principle	Soft	

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS6-SV-C, MS series

Technical data

**FESTO**

Flow rate characteristics	
Pneumatic connection	Female thread G1/2
Standard nominal flow rate $q_{nN}^{1)}$ [l/min]	
In main flow direction 1 → 2	5,700
In venting direction 2 → 3	7,600 <sup>2)</sup>
C value [l/s*min]	
In main flow direction 1 → 2	23.2
In venting direction 2 → 3	25.6
b value	
In main flow direction 1 → 2	0.4
In venting direction 2 → 3	0.4

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with respect to atmosphere with silencer S

Electrical data		
Coil characteristics	V24, V24P	24 V DC: 1.5 W; permissible voltage fluctuations $\pm 10\%$
	10V24, 10V24P	24 V DC: 2.5 W; permissible voltage fluctuations $\pm 10\%$
	V110	110 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations $\pm 10\%$
	V230	230 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations $-14\%/+10\%$
Electrical connection	V24, 10V24	Plug, 2-pin, to EN 175301-803, type C
	V110, V230	Plug, 3-pin, to EN 175301-803, type C
	10V24P	M12x1, 2-pin, to IEC 61076-2-101
	V24P	M12x1, 2-pin, to EN 60947-5-2
Protection class	IP65 with plug socket	
Duty cycle	[%]	100
Switching time off	[ms]	65
Switching time on	[ms]	370

Operating and environmental conditions			
Variant	Coil characteristic V24, V24P	Coil characteristic 10V24, 10V24P	Coil characteristic V110, V230
Operating pressure [bar]	3 ... 18 (3 ... 10) <sup>2)</sup>	3 ... 10	3 ... 18 (3 ... 10) <sup>2)</sup>
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]		
Note on operating/ pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Ambient temperature [°C]	0 ... +60 (0 ... +50) <sup>2)</sup>		
Temperature of medium [°C]	0 ... +60 (0 ... +50) <sup>2)</sup>		
Storage temperature [°C]	-10 ... +60 (0 ... +50) <sup>2)</sup>		
Corrosion resistance class CRC <sup>1)</sup>	2		
CE marking (see declaration of conformity)	–	–	To EU Low Voltage Directive
Fire classification to UL 94	V0-V2		
Certification	C-Tick		

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

2) With pressure sensor AD...

Weight [g]	
Soft-start and quick exhaust valve	886
Soft-start and quick exhaust valve with silencer S	1,006


# Soft-start and quick exhaust valves MS6-SV-C, MS series

**FESTO**

Technical data

Materials	
Housing	Die-cast aluminium
Piston spool	High-alloy stainless steel
Seals	Nitrile rubber
Note on materials	RoHS-compliant

## Adjusting elements



- 1 Screw for adjusting the pressure switchover point
- 2 Flow control screw for adjusting the filling time
- 3 Manual override at the soft-start and quick exhaust valve:
  - Detenting/self-resetting as

soon as the solenoid coil or manual override at the pilot solenoid valve is actuated.

- 4 Manual override at the pilot solenoid valve:
  - Non-detenting, actuation from above (with 10V24)


- Non-detenting/detenting, actuation from above (with 10V24P)
- Non-detenting/detenting, actuation from the front (with V24/V24P/V110/V230)

## Dimensions – Basic design


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

With female thread 1/2, with cover plate


Supply voltage  
V24/10V24/V110/V230




Supply voltage  
10V24P



Supply voltage  
V24P




With silencer S



- 1 Plug connection to EN 175301-803
- 2 Electrical connection to IEC 61076-2-101, plug M12x1, 2-pin for NEBU-M12
- 3 Electrical connection to EN 60947-5-2, plug M12x1, 2-pin for NEBU-M12

→ Flow direction


Supply voltage V24/V24P/V110/V230



### Note

For detenting manual override, remove the grey cover 6 and push the slide 5 downwards.

Supply voltage 10V24/10V24P



- 4 Non-detenting manual override (as supplied) at the pilot solenoid valve
- 5 Slide
- 6 Cover
- 7 Non-detenting and detenting manual override (variant 10V24 non-detenting only) at the pilot solenoid valve

Type	B1	B4	B5	D1	D2	D5	L1	L2	L4
MS6-SV-C	62	31	76	G3/2	M12x1	G3/4	144	71	130

Type	L8				L9		
	V24/V110/V230	10V24	10V24P	V24P	V24/V110/V230	10V24	10V24P
MS6-SV-C	36.6	32.6	36.55	48	26	24	26

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS6-SV-C, MS series

**FESTO**


Technical data

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated MS pressure gauge with standard scale AG or red/green scale RG, display unit [bar]

Adapter plate A4 for EN pressure gauge  $\frac{1}{4}$ , without pressure gauge



Type	B4	B5	D4
MS6-SV-...-AG	31	77	–
MS6-SV-...-RG	31	78.5	–
MS6-SV-...-A4	31	78.5	G $\frac{1}{4}$

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS6-SV-C, MS series


Technical data

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: [sde1](#)



Variant AD1:  
SDE1-D10-G2-MS-L-P1-M8 with  
3-pin plug M8x1, 1 switching  
output PNP


Variant AD2:  
SDE1-D10-G2-MS-L-N1-M8 with  
3-pin plug M8x1, 1 switching  
output NPN

Variant AD3:  
SDE1-D10-G2-MS-L-PI-M12 with  
4-pin plug M12x1, 1 switching  
output PNP and 4 ... 20 mA  
analogue

Variant AD4:  
SDE1-D10-G2-MS-L-NI-M12 with  
4-pin plug M12x1, 1 switching  
output NPN and 4 ... 20 mA  
analogue

Pressure sensor with operational status indicator AD7 ... AD10

Technical data → Internet: [sde5](#)



Variant AD7:  
SDE5-D10-O-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/O contact

Variant AD8:  
SDE5-D10-C-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/C contact

Variant AD9:  
SDE5-D10-O3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/O contact

Variant AD10:  
SDE5-D10-C3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/C contact

Type	B4	B5	B6	D6	L5	L6
MS6-SV-...-AD1/AD2	31	102	32.3	M8x1	35.1	46.7
MS6-SV-...-AD3/AD4				M12x1		55.8
MS6-SV-...-AD7/AD8/AD9/AD10	31	79	–	M8x1	–	–

### Ordering data

Ordering data			
Size	Connection	With silencer	
		Part No.	Type
Cover plate			
MS6	G1½	8001469	MS6-SV-1½-C-10V24-S

## Soft-start and quick exhaust valves MS6-SV-C, MS series

**FESTO**

Ordering data – Modular products

M Mandatory data →						
Module No.	Series	Size	Function	Pneumatic connection	Performance level	Supply voltage
548713	MS	6	SV	1/2, AGB, AGC, AGD, AGE	C	V24, V24P, 10V24, 10V24P, V110, V230
Ordering example						
548713	MS	6	SV	AGB	C	10V24

Ordering table					
Grid dimension	[mm]	62	Condition s	Code	Enter code
M Module No.	548713				
Series	Standard			MS	MS
Size	6			6	6
Function	Soft-start and quick exhaust valve			-SV	-SV
Pneumatic connection	Female thread G1/2			-1/2	
	Connecting plate G1/4			-AGB	
	Connecting plate G3/8			-AGC	
	Connecting plate G1/2			-AGD	
	Connecting plate G3/4			-AGE	
Performance level	Category 1, 1-channel, to EN ISO 13849-1			-C	-C
Supply voltage	24 V DC (pin allocation to EN 175301), 3 ... 18 bar			-V24	
	24 V DC with M12 plug socket adapter (pin allocation to EN 60947-5-2), 3 ... 18 bar			-V24P	
	24 V DC (pin allocation to EN 175301), 3 ... 10 bar			-10V24	
	24 V DC, M12 to IEC 61076-2-101, 3 ... 10 bar			-10V24P	
	110 V AC (pin allocation to EN 175301), 3 ... 18 bar			-V110	
	230 V AC (pin allocation to EN 175301), 3 ... 18 bar			-V230	

Transfer order code

548713	MS	6	SV		C	
--------	----	---	----	--	---	--

# Soft-start and quick exhaust valves MS6-SV-C, MS series

Ordering data – Modular products

Options					
Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Tamper protection	Flow direction
S	AG, A4, RG, AD1, AD2, AD3, AD4, AD7, AD8, AD9, AD10	PSI, MPA	WP, WPM, WB	MK	Z
- S	- AG	-	- WP	-	-

Ordering table					
Grid dimension	[mm]	62	Condition s	Code	Enter code
0 Silencer	Pressure gauge/pressure gauge alternatives	Silencer		-S	
		MS pressure gauge		-AG	
		Adapter plate for EN pressure gauge 1/4, without pressure gauge		-A4	
		Integrated pressure gauge, red/green scale		-RG	
		Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	1	-AD1	
		Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	1	-AD2	
		Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	1	-AD3	
		Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	1	-AD4	
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact	1	-AD7	
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact	1	-AD8	
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact	1	-AD9	
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	1	-AD10	
	Alternative pressure gauge scale	psi	2	-PSI	
		MPa	2	-MPA	
	Type of mounting	Mounting bracket, connecting kit	3	-WP	
		Mounting bracket, connecting kit	3	-WPM	
		Mounting bracket, housing		-WB	
	Tamper protection	Complete (manual override at soft-start/quick exhaust valve locked, adjusting screw locked, manual override at pilot solenoid valve locked (only with supply voltage 10V24, 10V24P))		-MK	
	Flow direction	Flow direction from right to left		-Z	

1 AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

2 PSI, MPA Only in combination with pressure gauge AG or RG

3 WP, WPM Only with connecting plate AGB, AGC, AGD or AGE

Transfer order code


-  -  -  -  -  -

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Peripherals overview

**FESTO**

### Soft-start and quick exhaust valve MS6-SV-E



#### Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Peripherals overview

Mounting attachments and accessories						
		Individual device		Combination		➔ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
1	Cover cap MS6-END	–	–	■	–	ms6-end
2	Mounting plate MS6-AEND	■ <sup>1)</sup>	–	■ <sup>1)</sup>	–	ms6-aend
3	Connecting plate MS6-AG...	–	■ <sup>1)</sup>	–	■ <sup>1)</sup>	ms6-ag
4	Module connector MS6-MV	–	–	■	■	ms6-mv
5	Mounting bracket MS6-WPB	■	■	■	■	ms6-wpb
6	Mounting bracket MS6-WPE	■	■	■	■	ms6-wpe
7	MS pressure gauge AG	■	■	■	■	30
8	Adapter plate for EN pressure gauge ¼ A4	■	■	■	■	30
9	Pressure gauge MA	■	■	■	■	46
10	Pressure sensor with LCD display AD1 ... AD4	■	■	■	■	30
11	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	46
12	Multi-pin plug socket NECA	■	■	■	■	42
13	AS-i configuration plug CACC	■	■	■	■	44
14	Addressing cable KASI-ADR	■	■	■	■	kasi-asi
15	Addressing device ASI-PRG-ADR	■	■	■	■	asi-prg-adr
16	Silencer UOS-1	■	■	■	■	43
17	Silencer UOS-1-LF	■	■	■	■	43

1) Module connector MS6-MV or mounting bracket MS6-WPB/WPE is required for mounting.

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**

Type codes

		MS	6	-	SV	-	1/2	-	E	-	10V24	-	SO	-	AG
<b>Series</b>															
MS	Standard service unit														
<b>Size</b>															
6	Grid dimension 62 mm														
<b>Service function</b>															
SV	Soft-start and quick exhaust valve														
<b>Pneumatic connection</b>															
1/2	Female thread G1/2														
<b>Performance level</b>															
E	Category 4, 2-channel with self-monitoring, to EN ISO 13849-1														
<b>Supply voltage</b>															
10V24	24 V DC														
ASIS	22 ... 31.6 V DC, AS-i Safety at Work, SPEC3.0 Profile 7.5.5														
<b>Silencer</b>															
	Without silencer														
SO	Open silencer														
<b>Pressure gauge/pressure gauge alternatives</b>															
AG	MS pressure gauge														
AD1	Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin (only with supply voltage 10V24)														


### Additional variants can be ordered using the modular product system → 30

- Connecting plates
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Multi-pin plug socket
- Type of mounting
- UL certification
- Flow direction

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Technical data

### Function



### Flow rate

4,300 l/min

### Temperature range

-10 ... +50 °C

### Pressure

3.5 ... 10 bar

[www.festo.com/en/](http://www.festo.com/en/)

Spare\_parts\_service



The electro-pneumatic soft-start and quick exhaust valve is used to reduce pressure quickly and reliably and to build up pressure gradually in industrial pneumatic systems and terminals.

The device is a self-testing, redundant mechatronic system conforming to the

requirements of EN ISO 13849-1. The safety-related pneumatic protection objective of safe venting is also guaranteed in the event of faults inside the valve (e.g. due to wear, contamination, electronic faults). Thanks to the 2-channel design and its monitoring, the device fulfils

controller category 3 and 4 requirements. This enables a performance level of max. "e" to be attained.

The device receives the secure enable signals (EN1/EN2) via the electrical connection (multi-pin plug socket NECA Sub-D, 9-pin or AS-i connecting

cable). The signals in question come from commercially available electronic or electromechanical safety switching devices which monitor the protective equipment of the machine (e.g. emergency stop, light curtain, electrical door switch of a protective enclosure, etc.).

### Note

The MS6-SV-...-E-10V24 should only be used in combination with the multi-pin plug socket NECA approved for it. The multi-pin plug socket can be ordered via the modular product system (MP... → 30) or as an accessory (NECA → 42).

### Note

To avoid back pressures, it is recommended that the device be operated together with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → 30) or as an accessory (UOS-1 → 43).

### Note

Only devices that do not impair the pneumatic protective measure – safe venting – may be placed downstream of the MS6-SV-...-E. The MS6-SV-...-E is not permitted for use as a press safety valve.

- Performance level "e"/category 4 according to EN ISO 13849-1
- Conforms to standard IEC 61508
- Switching time delay adjustable via a flow control valve for gradual pressure build-up
- Optional pressure sensor

Safety characteristics		
Type	MS6-SV-...-E-10V24	MS6-SV-...-E-ASIS
Conforms to standard	EN ISO 13849-1	
Safety function	Venting	
Performance level (PL)	Venting: category 4, PL e	
Safety integrity level (SIL)	Venting: SIL 3	
Proven component	Yes	
Note on forced dynamisation	Switching frequency min. 1/month	
Certificate issuing authority	BGIA 0904020	–
CE marking (see declaration of conformity)	To EU Machinery Directive	
	To EU EMC Directive	
Shock resistance	Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 2 according to FN 942017-4 and EN 60068-2-6	

### -H- Note on forced dynamisation: switching frequency min. 1/month

The mechanical system is not tested in the controlled (i.e. pressurised)

state. If the process-related switching frequency (safe venting) is less than

once a month, the machine operator must carry out a forced switch-off.

### Additional functions of MS6-SV-...-E-ASIS:

- Integrated pressure sensors via AS-i protocol
- Pressure monitoring (under/overshooting)

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Technical data

**FESTO**

### MS6-SV-...-E-ASIS in the actuator-sensor interface (AS-i)


The actuator-sensor interface (AS-i) is a system for networking sensors and actuators on the lowest level of the automation hierarchy. It is a non-proprietary, open bus system and enables transfer of data and energy on just one line. This simple method permits an efficient configuration with simultaneously reliable performance. The network topology of the AS-i system can be expanded as desired without any difficulty. An AS-i network consists of a control unit, a so-called master and the

associated sensor and actuator components, namely the slaves. The master cyclically polls all configured slaves and exchanges input and output data with them. A telegram consists of 4 bits of user data. The master communicates with the slaves via a serial transmission protocol. AS-i Safety at Work is a certified standard that enables safety-related components to be used in the AS-i system. The safe AS-i system is designed for safety applications up to category 4 according to

EN ISO 13849-1 PL "e". Mixed operation of standard components and safety-oriented components is possible. The AS-interface master considers the safety-oriented slaves just like all other slaves and incorporates them into the network. The transmission protocol and the cables in the AS-i system are laid out so that they are also capable of transmitting safety-oriented telegrams. The AS-i safety monitor is the central safe component and monitors the

safety-oriented slaves assigned to it within an AS-i system. The safety function is ensured via additional signal transmission between the safety-oriented slaves and the AS-i safety monitor. This transmission takes place with a special safety protocol.






In the case of a stop request or defect, the AS-i safety monitor in protection mode reliably switches the system off with a maximum reaction time of 40 ms.



## Soft-start and quick exhaust valves MS6-SV-E, MS series

Technical data

**FESTO**

MS6-SV-...-E-10V24 with multi-pin plug socket NECA			
Description		Enable signals (EN1/EN2)	Example of connection
NECA-...-MP1	<ul style="list-style-type: none"><li>Static enable signals (EN1 = 24 V, EN2 = 24 V).</li></ul>		
	<ul style="list-style-type: none"><li>Clocked enable signals (EN1 = 0 ... 24 V, EN2 = 0 ... 24 V) for cross-circuit detection. Cross-circuit detection with clock signals is in principle carried out by the safety switching device/safety PLC used.</li></ul>	 <p><b>Note</b></p> <p>Given the fact that clock outputs from different controller manufacturers are not standardised, their usability must be checked in each case. If the clock pulse is outside of the described limits, this is recognised by the MS6-SV-...-E-10V24 as an error and a safe switch-off is performed.</p>	
NECA-...-MP3	<ul style="list-style-type: none"><li>Static enable signals (EN1 = 0 V, EN2 = 24 V).</li><li>Static cross-circuit monitoring possible. A cross circuit in lines EN1 and EN2 does not lead to inadvertent start-up of the valve.</li></ul>		

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Technical data

**FESTO**

General technical data		
Pneumatic connection 1, 2	G½ (female thread)	G¼ ... G¾ (with connecting plate AG...)
Pneumatic connection 3	G1	
Actuation type	Electric	
Design	Piston seat	
Type of mounting	Via accessories	
	In-line installation	
Mounting position	Any	
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output	
	Via pressure gauge for displaying output pressure	
	G¼ prepared	
Position sensing principle	Solenoid piston principle	
Valve function	3/2-way valve, closed, single solenoid	
	Soft-start function, adjustable	
Non-overlapping	No	
Exhaust function	No flow control	
Manual override	None	
Reset method	Mechanical spring	
Switching position display	LED and floating contact	
Type of control	Piloted	
Pilot air supply	Internal	
Sealing principle	Soft	

Note: This product conforms to ISO 1179-1 and ISO 228-1

Flow rate characteristics		
Pneumatic connection	Female thread G1½	
Standard nominal flow rate qnN <sup>1)</sup> [l/min]		
In main flow direction 1 → 2	4,300	
In venting direction 2 → 3	9,000 <sup>2)</sup>	
C value [l/s*min]		
In main flow direction 1 → 2	19.3	
In venting direction 2 → 3	24.6	
b value		
In main flow direction 1 → 2	0.21	
In venting direction 2 → 3	0.4	

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with respect to atmosphere with silencer UOS-1

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**

Technical data

Electrical data		
Type	MS6-SV-...-E-10V24	MS6-SV-...-E-ASIS
Electrical connection	Sub-D, 9-pin	2x M12
Nominal operating voltage [V DC]	24	–
Permissible voltage fluctuations [%]	±10	–
Operating voltage range for AS-interface [V DC]	–	22 ... 31.6
Duty cycle [%]	100	
Max. switching frequency [Hz]	1	
Switching time off [ms]	40	
Switching time on [ms]	130	
Switching position display	LED and floating contact	LED and via AS-i
Protection class	IP65 with plug socket	

AS-i Safety-specific data	
Type	MS6-SV-...-E-ASIS
Fieldbus interface	Socket M12 (AS-i Out) and plug M12 (AS-i In)
LED displays	AS-i and status
Device-specific diagnostics	Inputs for cyclical digital data (exhausted, pressurised, fault) Cyclical analogue values (supply pressure p1, output pressure p2) Acyclical values (counter, pressure monitoring, fault, switching frequency exceeded, status)
Product identification	IO code: 0x7 Profile: 7.5.5 ID code: 0x5 ID1: 0xF ID2: 0x5
Vendor ID AS-interface	0x014D
Device ID AS-interface	0x03A6
Addressing range	Standard slave: 1 ... 31

Operating and environmental conditions		
Type	MS6-SV-...-E-10V24	MS6-SV-...-E-ASIS
Operating pressure [bar]	3.5 ... 10	3.5 ... 10
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	–10 ... +50 (0 ... +50) <sup>2)</sup>	0 ... +50
Temperature of medium [°C]	–10 ... +50 (0 ... +50) <sup>2)</sup>	0 ... +50
Storage temperature [°C]	–10 ... +50 (0 ... +50) <sup>2)</sup>	0 ... +50
Corrosion resistance class CRC <sup>1)</sup>	2	
Noise level [dB(A)]	75 (with silencer UOS-1)	
CE marking (see declaration of conformity)	To EU EMC Directive	
	To EU Machinery Directive	
Fire classification to UL 94	V0-V2	
Certification	cULus recognized (OL)	
	C-Tick	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

2) With pressure sensor AD...

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**


Technical data

Weight [g]	
Soft-start and quick exhaust valve	2,000
Soft-start and quick exhaust valve with silencer UOS-1	2,200

Materials	
Housing	Die-cast aluminium
Piston spool	High-alloy stainless steel
Seals	Nitrile rubber
Note on materials	RoHS-compliant

### Switching point

Pressure p as a function of time t



**Note**

The +20%/–10% switching point tolerance refers to the operating pressure p1.  
Example: A switching point from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**


Technical data

### Dimensions – Basic design

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

With supply voltage 10V24,  
with female thread 1/2, with cover plate

With supply voltage ASIS,  
with female thread 1/2, with cover plate



Type	B1	B2	B3	B4	D1	D5	D6	L1	L2	L3	L4
MS6-SV-1/2-E-10V24	62	58.8	104	22.5	G1/2	G1	55	228	81	61	145.1
MS6-SV-1/2-E-ASIS				26.1						28.3	

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Technical data


**FESTO**

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated MS pressure gauge AG, display unit [bar]

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



Type	B2	B3	D4
MS6-SV-...-E-...-AG	58.8	104.8	–
MS6-SV-...-E-...-A4		106.3	G1/4


Note: This product conforms to ISO 1179-1 and ISO 228-1

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: sde1



Variant AD1:  
SDE1-D10-G2-MS-L-P1-M8 with  
3-pin plug M8x1, 1 switching  
output PNP

Variant AD2:  
SDE1-D10-G2-MS-L-N1-M8 with  
3-pin plug M8x1, 1 switching  
output NPN

Variant AD3:  
SDE1-D10-G2-MS-L-PI-M12 with  
4-pin plug M12x1, 1 switching  
output PNP and 4 ... 20 mA  
analogue

Variant AD4:  
SDE1-D10-G2-MS-L-NI-M12 with  
4-pin plug M12x1, 1 switching  
output NPN and 4 ... 20 mA  
analogue

Type	B2	B3	D6	L5	L6
MS6-SV-...-E-...-AD1/AD2	58.8	130.8	M8x1	31.2	46.7
MS6-SV-...-E-...-AD3/AD4			M12x1		55.8

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**

Technical data

Ordering data – Supply voltage 10V24					
Size	Connection	Without silencer		With silencer	
		Part No.	Type	Part No.	Type
MS pressure gauge, display unit [bar]					
MS6	G1/2	548715	MS6-SV-1/2-E-10V24-AG	548717	MS6-SV-1/2-E-10V24-SO-AG
Pressure sensor with LCD display, plug M8, PNP, 3-pin					
MS6	G1/2	562580	MS6-SV-1/2-E-10V24-AD1		–

Ordering data – Supply voltage ASIS					
Size	Connection	Without silencer		With silencer	
		Part No.	Type	Part No.	Type
MS pressure gauge, display unit [bar]					
MS6	G1½	8001480	MS6-SV-1½-E-ASIS-AG	8001481	MS6-SV-1½-E-ASIS-SO-AG

## Soft-start and quick exhaust valves MS6-SV-E, MS series

**FESTO**

Ordering data – Modular products

M Mandatory data →						
Module No.	Series	Size	Function	Pneumatic connection	Performance level	Supply voltage
548713	MS	6	SV	1/2, AGB, AGC, AGD, AGE	E	10V24, ASIS
Ordering example						
548713	MS	6	- SV	- AGB	- E	- 10V24 -

Ordering table					
Grid dimension	[mm]	62	Condition s	Code	Enter code
M Module No.	548713				
Series	Standard			MS	MS
Size	6			6	6
Function	Soft-start and quick exhaust valve			-SV	-SV
Pneumatic connection	Female thread G1/2			-1/2	
	Connecting plate G1/4			-AGB	
	Connecting plate G3/8			-AGC	
	Connecting plate G1/2			-AGD	
	Connecting plate G3/4			-AGE	
Performance level	Category 4, 2-channel with self-monitoring, to EN ISO 13849-1			-E	-E
Supply voltage	24 V DC (pin allocation to EN 175301)			-10V24	
	22 ... 31.6 V DC, AS-i Safety at Work, SPEC3.0 Profile 7.5.5			-ASIS	

Transfer order code

548713	MS	6	- SV	-	E	-
--------	----	---	------	---	---	---

## Soft-start and quick exhaust valves MS6-SV-E, MS series

Ordering data – Modular products

0 Options						
Silencer	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Multi-pin plug socket	Type of mounting	UL certification	Flow direction
SO	AG, A4, AD1, AD2, AD3, AD4	PSI, MPA	MP1, MP3	WPB	UL1	Z
- SO	- AG	-	- MP1	- WPB	-	-

Ordering table						
Grid dimension	[mm]	62	Condition s	Code		Enter code
0 Silencer		Open silencer		-SO		
Pressure gauge/pressure gauge alternatives		MS pressure gauge		-AG		
		Adapter plate for EN pressure gauge 1/4, without pressure gauge		-A4		
		Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	1	-AD1		
		Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	1	-AD2		
		Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	1	-AD3		
		Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	1	-AD4		
Alternative pressure gauge scale		psi	2	-PSI		
		MPa	2	-MPA		
Multi-pin plug socket		Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	1	-MP1		
		Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), short-circuit detection possible	1	-MP3		
Type of mounting		Mounting bracket, large clearance		-WPB		
UL certification		cULus, ordinary location for Canada and USA	1	-UL1		
Flow direction		Flow direction from right to left		-Z		

1 AD1, AD2, AD3, AD4, MP1, MP2, UL1

Now with supply voltage ASIS.

2 PSI, MPA Not with pressure gauge/pressure gauge alternatives A4, AD1, AD2, AD3, AD4

Transfer order code


-  -  -  -  -  -  -

## Soft-start and quick exhaust valves MS9-SV-C, MS series

Peripherals overview

**FESTO**

### Soft-start and quick exhaust valve MS9-SV-C



#### Note


Additional accessories:

- Module connector for combination with size MS6, MS9 or MS12

➔ Internet: rmv, armv

Supply voltage  
V24/V110/V230

Supply voltage  
10V24P



## Soft-start and quick exhaust valves MS9-SV-C, MS series

Peripherals overview

Mounting attachments and accessories					
		Individual device		Combination	➔ Page/ Internet
		With female thread ¾ or 1	With connecting plate AG...	Module without connecting thread, without connecting plate G	
1	Connecting plate MS9-AG...	–	■	■	ms9-ag
2	Module connector MS9-MV	–	–	■	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	■	ms9-wp
6	Silencer U-1-B	■	■	■	45
7	Cover plate VS	■	■	■	40
8	MS pressure gauge AG/RG	■	■	■	40
9	Pressure sensor with operational status indicator AD7 ... AD10	■	■	■	40
10	Connecting cable NEBU-M8...-LE3	■	■	■	46
11	Adapter plate for EN pressure gauge ¼ A4	■	■	■	40
12	Pressure gauge MA	■	■	■	46
13	Cover MS9-SV-MH/MK	■	■	■	44
14	Illuminating seal MC-LD	■	■	■	45
15	Plug socket with cable KMC	■	■	■	45
16	Plug socket MSSD-C	■	■	■	45
17	Connecting cable NEBU-M12G5	■	■	■	46
18	Connecting cable NEBU-M12W5	■	■	■	46
19	Sensor socket SIE-GD	■	■	■	46
20	Angled socket SIE-WD	■	■	■	46

## Soft-start and quick exhaust valves MS9-SV-C, MS series

**FESTO**

Type codes

		MS	9	-	SV	-	G	-	C	-	V24	-	S	-	VS
<b>Series</b>															
MS	Standard service unit														
<b>Size</b>															
9	Grid dimension 90 mm														
<b>Service function</b>															
SV	Soft-start and quick exhaust valve														
<b>Pneumatic connection</b>															
G	Module without connecting thread, without connecting plate														
<b>Performance level</b>															
C	Category 1, to EN ISO 13849-1														
<b>Supply voltage</b>															
V24	Supply voltage 24 V DC														
<b>Silencer</b>															
S	Silencer														
<b>Pressure gauge/pressure gauge alternatives</b>															
VS	Cover plate														


Additional variants can be ordered using the modular product system → 40

- Connecting plates
- Supply voltage
- Pressure gauge/pressure gauge alternatives
- Alternative pressure gauge scale
- Type of mounting
- Tamper protection
- UL certification
- Flow direction

## Soft-start and quick exhaust valves MS9-SV-C, MS series

Technical data

### Function



### Flow rate

8,300 ... 16,550 l/min

### Temperature range

0 ... +60 °C

### Pressure

3.5 ... 16 bar

[www.festo.com/en/](http://www.festo.com/en/)

Spare\_parts\_service



Electro-pneumatic soft-start and quick exhaust valve for gradual pressurisation and quick exhausting of system components (single channel).

The main flow control valve in the end cap permits a gradual build-up of output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is present at the output.

- Suitable for applications with high flow rates and restricted space with medium safety requirements up to controller category 1, performance level "c"
- High volumetric flow rate for pressurisation and venting
- The filling flow rate can be set via a flow control valve for gradual pressure build-up
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional cover for the control sections as tamper protection

### Safety characteristics

Conforms to standard	EN ISO 13849-1
Safety function	Venting
Performance level (PL)	Venting: up to category 1, PL c
Shock resistance	Shock test with severity level 1 according to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

### General technical data

Pneumatic connection 1, 2	G3/4 (female thread)	G1 (female thread)	G1/2 ... G1 1/2 (with connecting plate AG...)	– (module without connecting thread, without connecting plate G)
Pneumatic connection 3	G1			
Actuation type	Electric			
Design	Piston spool valve			
Type of mounting	Via accessories In-line installation			
Mounting position	Any			
Pressure indicator	Via pressure sensor for displaying output pressure via operational status indicator and electrical output			
	Via pressure gauge for displaying output pressure			
	Via pressure gauge with red/green scale for displaying output pressure			
	G1/4 prepared			
Valve function	3/2-way valve, closed, single solenoid			
	Soft-start function, adjustable			
Exhaust function	No flow control			
Reset method	Mechanical spring			
Type of control	Piloted			
Sealing principle	Soft			

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Soft-start and quick exhaust valves MS9-SV-C, MS series

Technical data

**FESTO**

Electrical data		
Coil characteristics	V24	24 V DC: 8.4 W; permissible voltage fluctuations $\pm 10\%$
	10V24P	24 V DC: 2.7 W; permissible voltage fluctuations $\pm 10\%$
	V110	110 V AC: 50/60 Hz; pick-up power 14.5/12 VA; holding power 10.5/7.6 VA; permissible voltage fluctuations $\pm 10\%$
	V230	230 V AC: 50/60 Hz; pick-up power 14.5/12 VA; holding power 10.5/7.6 VA; permissible voltage fluctuations $\pm 10\%$
Electrical connection	V24, V110, V230	Plug, square design to EN 175301-803, type A
	10V24P	M12x1, 4-pin, to IEC 61076-2-101, to DESINA
Protection class	IP65 with plug socket	
Duty cycle	[%]	100

Flow rate characteristics							
Pneumatic connection	Female thread		Connecting plate				
	3/4	1	AGD	AGE	AGF	AGG	AGH
Standard nominal flow rate $q_{nN}^{1)}$ [l/min]							
In main flow direction 1 $\rightarrow$ 2	14,150	16,460	8,300	13,250	16,340	16,550	15,910
In venting direction 2 $\rightarrow$ 3	14,790	14,140	16,500	14,400	13,800	13,200	13,200
C value [l/s*min]							
In main flow direction 1 $\rightarrow$ 2	57.61	69.59	31.43	54.24	68.24	68.45	66.07
In venting direction 2 $\rightarrow$ 3	55.52	54.01	56.22	54.07	52.73	51.06	51.36
b value							
In main flow direction 1 $\rightarrow$ 2	0.37	0.32	0.47	0.37	0.34	0.35	0.35
In venting direction 2 $\rightarrow$ 3	0.49	0.46	0.60	0.49	0.47	0.45	0.44

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

Operating and environmental conditions			
Variant	Coil characteristic V24	Coil characteristic 10V24P	Coil characteristic V110, V230
Operating pressure [bar]	3.5 ... 16 (3.5 ... 10) <sup>2)</sup>	3.5 ... 10	3.5 ... 16 (3.5 ... 10) <sup>2)</sup>
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Ambient temperature [°C]	0 ... +60 (0 ... +50) <sup>2)</sup>		
Temperature of medium [°C]	0 ... +60 (0 ... +50) <sup>2)</sup>		
Storage temperature [°C]	0 ... +60 (0 ... +50) <sup>2)</sup>		
Corrosion resistance class CRC <sup>1)</sup>	2		
Noise level <sup>3)</sup> [dB(A)]	93 (with silencer S)		
CE marking (see declaration of conformity)	–	–	To EU Low Voltage Directive
Certification (variant UL1)	cULus recognized (OL)		

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

2) With pressure sensor AD...

3) Venting at 10 bar at a distance of 1 m

Weight [g]	
Soft-start/quick exhaust valve	2,970
Soft-start/quick exhaust valve with silencer S	3,200


# Soft-start and quick exhaust valves MS9-SV-C, MS series

**FESTO**

Technical data

## Materials


Sectional view



### Soft-start and quick exhaust valve

1	Housing	Die-cast aluminium
2	Piston spool	Brass
-	Seals	Nitrile rubber
Note on materials		RoHS-compliant

## Adjusting elements



- 1 Screw for adjusting the pressure switchover point
- 2 Flow control screw for adjusting the filling time
- 3 Manual override at the soft-start and quick exhaust valve:
  - Detenting/self-resetting as soon as the solenoid coil or manual override at the pilot solenoid valve is actuated.
- 4 Manual override at the pilot solenoid valve:
  - Non-detenting, actuation from above


## Dimensions – Basic design

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Module without connecting thread, without connecting plate G, with cover plate VS

Supply voltage V24/V110/V230

Supply voltage 10V24P



Type	B1	B2	B3	D2	D5	L1	L2	L3	L4	L5	L6
MS9-SV-G-...-V24/V110/V230	90	45	109	-	G1	200	83	23	36.4	12	189
MS9-SV-G-...-10V24P				M12x1					39.2	10	

## Soft-start and quick exhaust valves MS9-SV-C, MS series

**FESTO**


Technical data

### Dimensions – Connecting thread/connecting plate

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

With female thread 3/4 or 1

With connecting plate AG...



1 Mounting screw M6xmin.90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

→ Flow direction

Type	B4	B5	B6	B7	B8	D1	D6	D7	L6	T1	≡C
MS9-SV-3/4	90	104	91.5	-	-	G3/4	11	6.5	66	6	-
MS9-SV-1						G1					
MS9-SV-AGD	-	-	-	112	132	G1/2	-	-	-	-	30
MS9-SV-AGE					132	G3/4					36
MS9-SV-AGF					142	G1					41
MS9-SV-AGG					162	G1 1/4					50
MS9-SV-AGH					176	G1 1/2					55


Note: This product conforms to ISO 1179-1 and ISO 228-1

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



Type	B2	B3	B9	D3
MS9-SV-...-AG/RG	45	109	-	-
MS9-SV-...-A4		-	110	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Soft-start and quick exhaust valves MS9-SV-C, MS series


Technical data

## Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Pressure sensor with operational status indicator AD7 ... AD10

Technical data → Internet: sde5



→ Flow direction

Variant AD7:  
SDE5-D10-O-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/O contact

Variant AD9:  
SDE5-D10-O3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/O contact

Variant AD8:  
SDE5-D10-C-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/C contact

Variant AD10:  
SDE5-D10-C3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/C contact

Type	B2	B11	D3
MS9-SV-...-AD7/AD8/AD9/AD10	45	112	M8

## Ordering data

Size	Connection	With silencer	
		Part No.	Type
Cover plate			
MS9	—	570737	MS9-SV-G-C-V24-S-VS

## Soft-start and quick exhaust valves MS9-SV-C, MS series

**FESTO**

Ordering data – Modular products

M Mandatory data						
Module No.	Series	Size	Function	Pneumatic connection	Performance level	Supply voltage
562176	MS	9	SV	3/4, 1, AGD, AGE, AGF, AGG, AGH, G	C	V24, 10V24P, V110, V230
<b>Ordering example</b>						
<b>562176</b>	<b>MS</b>	<b>9</b>	<b>- SV</b>	<b>- 1</b>	<b>- C</b>	<b>- V24</b>

Ordering table						
Grid dimension	[mm]	90	Condition s	Code	Enter code	
M Module No.	<b>562176</b>					
Series	Standard			<b>MS</b>		MS
Size	9			<b>9</b>		9
Function	Soft-start and quick exhaust valve			<b>-SV</b>		-SV
Pneumatic connection	Female thread G3/4			<b>-3/4</b>		
	Female thread G1			<b>-1</b>		
	Connecting plate G1/2			<b>-AGD</b>		
	Connecting plate G3/4			<b>-AGE</b>		
	Connecting plate G1			<b>-AGF</b>		
	Connecting plate G1 1/4			<b>-AGG</b>		
	Connecting plate G1 1/2			<b>-AGH</b>		
	Module without connecting thread, without connecting plate			<b>-G</b>		
Performance level	Category 1, 1-channel, to EN ISO 13849-1			<b>-C</b>		-C
Supply voltage	24 V DC (pin allocation to EN 175301), 16 bar			<b>V24</b>		
	24 V DC, M12 to IEC 61076-2-101, 10 bar			<b>10V24P</b>		
	110 V AC (pin allocation to EN 175301), 16 bar			<b>V110</b>		
	230 V AC (pin allocation to EN 175301), 16 bar			<b>V230</b>		

Transfer order code

<b>562176</b>	<b>MS</b>	<b>9</b>	<b>- SV</b>		<b>- C</b>	
---------------	-----------	----------	-------------	--	------------	--

# Soft-start and quick exhaust valves MS9-SV-C, MS series

Ordering data – Modular products

Mandatory data		Options				
Silencer	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Tamper protection	UL certification	Flow direction
S	AG, VS, A4, RG, AD7, AD8, AD9, AD10	PSI, MPA, BAR	WP, WPM, WPB	MH, MK	UL1	Z
- S	- AG	-	-	-	-	-

Ordering table						
Grid dimension	[mm]	90	Condition s	Code		Enter code
M	Silencer	Silencer		-S		-S
	Pressure gauge/pressure gauge alternatives	MS pressure gauge		-AG		
		Cover plate		-VS		
		Adapter plate for EN pressure gauge 1/4, without pressure gauge		-A4		
		Integrated pressure gauge, red/green scale	1	-RG		
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact	2	-AD7		
		Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact	2	-AD8		
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact	2	-AD9		
		Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/C contact	2	-AD10		
O	Alternative pressure gauge scale	Psi	3	-PSI		
		MPa	3	-MPA		
		Bar	3	-BAR		
	Type of mounting	Mounting bracket	4	-WP		
		Mounting bracket	4	-WPM		
		Mounting bracket for large wall gap	4	-WPB		
	Tamper protection	Without manual override (manual override at soft-start/quick exhaust valve locked, adjusting screws open, manual override at pilot solenoid valve locked)		-MH		
		Complete (manual override at soft-start/quick exhaust valve locked, adjusting screws locked, manual override at pilot solenoid valve locked)		-MK		
	UL certification	cULus, ordinary location for Canada and USA	5	-UL1		
	Flow direction	Flow direction from right to left		-Z		

- |                       |  |                 |   |
|-----------------------|--|-----------------|---|
| 1 RG                  | Not with alternative pressure gauge scale PSI, PSI scale serves only as an auxiliary scale | 3 PSI, MPA, BAR | Not with pressure gauge/pressure gauge alternatives VS, A4, AD7, AD8, AD9, AD10 |
| 2 AD7, AD8, AD9, AD10 | Measuring range max. 10 bar  | 4 WP, WPM, WPB  | Not with module G   |
|                       |  | 5 UL1           | Not with supply voltage V110, V230  |

Transfer order code

- S - - - - -

# Soft-start and quick exhaust valves MS-SV, MS series

FESTO

Accessories

## Multi-pin plug socket NECA

(order code in the modular product system: MP1/MP3)

- For soft-start and quick exhaust valve MS6-SV-E



Technical data		
Type of mounting	Via through-hole	
Electrical connection	Sub-D 9-pin, screw terminal 9-pin	
Operating voltage range	[V DC]	21.6 ... 26.4
Nominal operating voltage	[V DC]	24
Acceptable current load	[A]	1.0
Connection cross section	[mm <sup>2</sup> ]	0.34 ... 1.0 without wire end sleeves
	[mm <sup>2</sup> ]	0.34 ... 0.5 with wire end sleeves
Permissible cable diameter	[mm]	5.0 ... 10.0
Protection class to IEC 60529	IP65	

Operating and environmental conditions		
Relative air humidity	95%, non-condensing	
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC <sup>1)</sup>	2	

- 1) Corrosion resistance class 2 according to Festo standard 940 070  
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Materials	
Housing	PA reinforced
Screws	Steel
Union nut	Brass
Seals	Nitrile rubber

Dimensions		Download CAD Data → <a href="http://www.festo.com/us/cad">www.festo.com/us/cad</a>

Ordering data				
Description	Connection	Weight [g]	Part No.	Type
For MS6-SV-E	Without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	60	548719	NECA-S1G9-P9-MP1
	Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), cross-circuit detection possible	60	552703	NECA-S1G9-P9-MP3

## Soft-start and quick exhaust valves MS-SV, MS series

Accessories

### Silencer UOS-1

(order code in the modular product system: S0)

- For soft-start and quick exhaust valve MS6-SV-E

### Silencer UOS-1-LF

- For soft-start and quick exhaust valve MS6-SV-E

### Note

The space-saving silencer UOS-1-LF may only be used for applications with low exhaust rates. Pneumatic port 2 at the soft-start and quick exhaust valve MS6-SV-E must be reduced to G $\frac{1}{4}$  using a connecting plate MS6-AGB.



UOS-1



UOS-1-LF



Technical data	
Pneumatic connection	G1
Design	Open silencer
Type of mounting	Via male thread
Mounting position	Any
Type of seal on threaded collar	No seal

Operating and environmental conditions	
Operating pressure [bar]	0 ... 10
Operating medium	Compressed air to ISO 8573-1:2010 [-:-:-]
Ambient temperature [°C]	-10 ... +50
Corrosion resistance class CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Materials		
Type	UOS-1	UOS-1-LF
Housing	POM	Wrought aluminium alloy
Sleeve	Wrought aluminium alloy	-
Silencer insert	PE	
Note on materials	RoHS-compliant	
	Free of copper and PTFE	

Dimensions		Download CAD Data → <a href="http://www.festo.com/us/cad">www.festo.com/us/cad</a>		
Type	UOS-1	UOS-1-LF		
				

Type	D1	D2 Ø	L1	L2
UOS-1	G1	55	156.5	11.5
UOS-1-LF			72.2	13

Ordering data		Weight [g]	Part No.	Type
For MS6-SV-E	For high exhaust rate	200	552252	UOS-1
	For low exhaust rate	157.9	1901207	UOS-1-LF

## Soft-start and quick exhaust valves MS-SV, MS series


**FESTO**

Accessories

### AS-i configuration plug CACC

- For soft-start and quick exhaust valve MS6-SV-E-ASIS

Note on materials: RoHS-compliant



1 M12 pin, 4-pin

Dimensions and ordering data					
Description	D1	L1	$\frac{1}{4}$ "	Part No.	Type
For MS6-SV-E-ASIS	14.5	48.3	13	573923	CACC-CP-AS

### Cover MS-SV-MH/MK

(order code in the modular product system: MH/MK)

- For soft-start and quick exhaust valve MS6/9-SV-C

Note on materials: RoHS-compliant






MS6-SV-C-MK



MS9-SV-MK



MS9-SV-MH

Ordering data					
Description		CRC <sup>1)</sup>	Part No.	Type	
For MS6-SV-C	Tamper protection for manual override at the soft-start and quick exhaust valve, flow control screw, adjusting screw for pressure switchover point and manual override at the pilot solenoid valve (MS6-SV-...-C-10V24/10V24P only)	2	8001479	MS6-SV-C-MK	
For MS9-SV-C	Tamper protection for manual override at the soft-start and quick exhaust valve, flow control screw, adjusting screw for pressure switchover point and manual override at the pilot solenoid valve	2	1457669	MS9-SV-MK	
	Tamper protection for manual override at the soft-start and quick exhaust valve and manual override at the pilot solenoid valve	2	1457670	MS9-SV-MH	


1) Corrosion resistance class 2 according to Festo standard 940 070


Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



## Soft-start and quick exhaust valves MS-SV, MS series


**FESTO**

Accessories

Ordering data – Silencer U-...-B				Technical data → Internet: u	
	Description	Pneumatic connection	Order code in the modular product system	Part No.	Type
	For MS6-SV-C	G $\frac{3}{4}$	S	<b>6845</b>	<b>U-<math>\frac{3}{4}</math>-B</b>
	For MS9-SV-C	G1	S	<b>151990</b>	<b>U-1-B</b>

Ordering data – Plug socket MSSD				Technical data → Internet: mssd	
	Description	Electrical connection	Type of mounting for cable connection	Part No.	Type
	For MS6-SV-C	3-pin	Clamping screws	<b>151687</b>	<b>MSSD-EB</b>
		4-pin	Insulation displacement connectors	<b>192745</b>	<b>MSSD-EB-S-M14</b>
		3-pin	Clamping screws	<b>539712</b>	<b>MSSD-EB-M12</b>
	For MS9-SV-C	3-pin	Clamping screws	<b>34583</b>	<b>MSSD-C</b>
		4-pin	Insulation displacement connectors	<b>192748</b>	<b>MSSD-C-S-M16</b>



Ordering data – Plug socket with cable KMEB/KMC						Technical data → Internet: kmeb, kmc	
	Description	Operating voltage	Electrical connection	Switching status display	Cable length [m]	Part No.	Type
	For MS6-SV-C	24 V DC	2-pin	LED	2.5	<b>547268</b>	<b>KMEB-3-24-2,5-LED</b>
					5	<b>547269</b>	<b>KMEB-3-24-5-LED</b>
				–	2.5	<b>547270</b>	<b>KMEB-3-24-2,5</b>
					5	<b>547271</b>	<b>KMEB-3-24-5</b>
			3-pin	LED	2.5	<b>151688</b>	<b>KMEB-1-24-2,5-LED</b>
					5	<b>151689</b>	<b>KMEB-1-24-5-LED</b>
					10	<b>193457</b>	<b>KMEB-1-24-10-LED</b>
		230 V AC	3-pin	–	2.5	<b>151690</b>	<b>KMEB-1-230AC-2,5</b>
					5	<b>151691</b>	<b>KMEB-1-230AC-5</b>
	For MS9-SV-C	24 V DC	3-pin	LED	2.5	<b>30931</b>	<b>KMC-1-24DC-2,5-LED</b>
					5	<b>30933</b>	<b>KMC-1-24DC-5-LED</b>
					10	<b>193459</b>	<b>KMC-1-24-10-LED</b>
		230 V AC	3-pin	–	2.5	<b>30932</b>	<b>KMC-1-230AC-2,5</b>
					5	<b>30934</b>	<b>KMC-1-230AC-5</b>



Ordering data – Illuminating seal MEB-LD/MC-LD			Technical data → Internet: meb, mc	
	Description	Operating voltage range	Part No.	Type
	For plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC	<b>151717</b>	<b>MEB-LD-12-24DC</b>
		230 V DC/AC ±10%	<b>151718</b>	<b>MEB-LD-230AC</b>
	For plug socket with cable KMC and plug socket MSSD-C	12 ... 24 V DC	<b>19145</b>	<b>MC-LD-12-24DC</b>
		230 V DC/AC ±10%	<b>19146</b>	<b>MC-LD-230AC</b>


## Soft-start and quick exhaust valves MS-SV, MS series


**FESTO**


Accessories


Ordering data – Connecting cable NEBU-M8				Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type
	M8x1, straight socket	3	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	M8x1, angled socket	3	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3

Ordering data – Connecting cable NEBU-M12				Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type
	M12x1, straight socket	4	2.5	550326	NEBU-M12G5-K-2.5-LE4
			5	541328	NEBU-M12G5-K-5-LE4
	M12x1, angled socket	4	2.5	550325	NEBU-M12W5-K-2.5-LE4
			5	541329	NEBU-M12W5-K-5-LE4

Ordering data – Sensor socket SIE-GD			Technical data → Internet: sie-gd	
	Electrical connection		Part No.	Type
	M12x1, 4-pin		18494	SIE-GD

Ordering data – Angled socket SIE-WD			Technical data → Internet: sie-wd	
	Electrical connection		Part No.	Type
	M12x1, 4-pin		12956	SIE-WD-TR

Ordering data – Pressure gauge MA						
	Nominal size	Pneumatic connection	Display range		Part No.	Type
			[bar]	[psi]		
	Pressure gauge MA, EN 837-1					Technical data → Internet: ma
	40	R¼	0 ... 16	0 ... 232	187080	MA-40-16-R¼-EN
			0 ... 25	0 ... 360	187081	MA-40-25-R¼-EN
		G¼	0 ... 16	0 ... 232	183901	MA-40-16-G¼-EN
	Pressure gauge MA, EN 837-1, with red/green range					Technical data → Internet: ma
50	R¼	0 ... 16	–	525729	MA-50-16-R¼-E-RG	

Ordering data – Locking clip CPV18-HV				Technical data → Internet: cpv18-hv		
	Description			Part No.	Type	PU <sup>1)</sup>
	For MS6-SV-C-...-V24	Cover for the manual override, the clip prevents actuation		530056	CPV18-HV	10

1) Packaging unit

## Product Range and Company Overview

### A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)