




Measuring modules CPX-CMIX Key features

At a glance				
Movement and measurement in one, as an integral component of the valve terminal CPX – the modular peripheral system for decentralised automation tasks. The modular design means that valves, digital inputs and outputs, positioning modules, end-position controllers and measuring modules, as appropriate to the application, can be combined in almost any way on the CPX terminal. Petracting/advancing Time and space saving		 Advantages: Pneumatics and electrics – movement and measurement on one platform Innovative measurement technol- ogy – piston rod drives, rodless drives, rotary drives 	 Actuation via fieldbus Remote maintenance, remote diagnostics, web server, SMS and e-mail alert are all possible via TCP/IP Modules can be quickly exchanged and expanded without altering the wiring 	
Retracting/advancing and measuring in one work step	Time and space-saving	Process reliability	Reduced system costs	
Fully digital data acquisition and transmission means pneumatic cylinders can now be used as sensors. With very high repetition accuracy and incorporating both analogue and digital measuring sensors.	Electrical peripherals enable the highly efficient measuring module to be seamlessly and compactly inte- grated into existing control environ- ments. The new component is tailored to the proven CPX system and can be commissioned quickly and easily.	All process steps are measured and documented, which significantly im- proves quality. The adjustable contact force (via pressure regulator) also increases the precision of the "displacement sensor".	As with all modules in the electrical terminal CPX, easy functional integra- tion in fieldbus/Ethernet networks is a matter of course.	

Drives to use

Linear drives DGCI



- The measurement signal of the linear drive DGCI supplies a CAN signal, which is read in directly into the CPX-CMIX module
- The measuring system measures absolute values, in other words the actual position is immediately available for the controller after the system is switched on

Technical data

Teenneut dutu			
Linearity	[%]	$\leq \pm 0.01$ full scale (nominal length)	
Repetition accuracy	[mm]	< ±0.01	
Hysteresis	[µm]	< 4	
Shortest measurable speed	[mm/s]	10	

Linear drives DGPI, DGPIL or displacement encode MME

Key features

Drives to use

FESTO

9

- The measurement signal of the linear drive DGPI, DGPIL or displacement decoder MME supplies a CAN signal, which is read in directly into the CPX-CMIX module
- The measuring system measures absolute values, in other words the actual position is immediately available for the controller after the system is switched on

Technical data

reennear aata			
Linearity	[%]	$\leq \pm 0.02$ full scale (nominal length)	
Repetition accuracy	[mm]	<±0.01	
Hysteresis	[µm]	< 4	
Shortest measurable speed	[mm/s]	10	

Linear drives DNCI



- The measuring signal of the linear drive DNCI is an incremental signal, which is converted to a CAN signal in the sensor interface CASM-S-D3-R7. The converted signal is then read into the CPX-CMIX
- The measuring system does not measure absolute values, so must be homed after it is switched on. The actual position is available for the controller once this has been done


Technical data

Linearity	[mm]	≤ ±0.07
Repetition accuracy	[mm]	< ±0.02
Hysteresis	[µm]	< 0.03
Shortest measurable speed	[mm/s]	10

Key features

Drives to use

Swivel modules DSMI, standard cylinders DNCM or potentiometers MLO-POT



- The measuring systems supply an analogue measuring signal, which is converted to a CAN signal in the sensor interface CASM-S-D2-R3. The converted signal is then read into the CPX-CMIX
- Potentiometers measure absolute values, in other words the actual position is immediately available for the controller after the potentiometer is switched on

Other potentiometers can be used, in which case the following must be noted:

- The connection resistance of the potentiometer must be 3 ... 20 $k\Omega$
- Poorer potentiometer values for linearity and temperature coefficient will decrease the accuracy of the measured value
- A special cable must be used for connection to the sensor interface


Technical data								
Measuring length	[mm]	100	150	225	300	360	450	500
Linearity	[% of stroke]	±0.1	±0.09	±0.08	±0.07	±0.06	±0.05	±0.05
Repetition accuracy	[mm]	±0.01	±0.01	±0.01	±0.01	±0.011	±0.014	±0.016
Shortest measurable speed	[mm/s]	3	5	7	9	11	14	15
Temperature coefficient	[ppm/°C]	5						

Measuring length	[mm]	600	750	1,000	1,250	1,500	1,750	2,000
Linearity	[% of stroke]	±0.05	±0.04	±0.04	±0.03	±0.03	±0.03	±0.02
Repetition accuracy	[mm]	±0.019	±0.023	±0.03	±0.038	±0.046	±0.054	±0.062
Shortest measurable speed	[mm/s]	18	23	31	38	46	53	61
Temperature coefficient	[ppm/°C]	5						

Measuring modules CPX-CMIX Type codes and peripherals overview

Type codes								
		СРХ	 CMIX]-	M1	- [1]
Valve term	inal							
CPX	Terminal							
Туре								
CMIX	Measuring module							
Function m	nodule							
M1	Measuring unit					I		
Axes								
1	One axis							-

Peripherals overview



Acces	Accessories						
	Туре	Brief description	→ Page/Internet				
1	Measuring module	Integrated in the CPX terminal.	6				
	CPX-CMIX	Screws for mounting on the plastic interlinking block are included in the scope of delivery					
6	Connecting cable KVI-CP-3	For connecting the measuring module CPX-CMIX and sensor interface CASM	8				
11	Inscription label IBS	For labelling the modules	8				
2	Interlinking block	Connects the individual modules.	9				
	CPX-GE	Two versions are available: plastic or metal interlinking block					
-	Screws CPX-M-M3	For mounting on the metal interlinking block	8				
7	Connecting cable NEBC-P1W4	For connecting the sensor interface CASM and swivel module DSMI or potentiometer LWG	nebc				
8	Connecting cable NEBC-A1W3	For connecting the sensor interface CASM and potentiometer TLF	nebc				
9	Connecting cable NEBP-M16W6	For connecting measuring module CPX-CMIX and linear drive DGPI, DGPIL or displacement encoder MME	8				

FESTO

Measuring modules CPX-CMIX Technical data

The measuring module CPX-CMIX is intended exclusively for use in valve terminals CPX.



General technical data			
Operating voltage			
Operating voltage range		[V DC]	18 30
Nominal operating voltage		[V DC]	24
Current consumption at nomi	nal operating voltage	[mA]	80
Protection against short circu	lit		Yes
Power failure bridging		[ms]	10
No. of axis strings			1
Axes per string			1
Length of connecting cable to	axis	[m]	≤ 30
Max. no. of modules			9
Display			7-segment display
Assigned addresses	Outputs	[bit]	6x8
	Inputs	[bit]	6x8
Diagnostics			Channel and module-oriented
			Via local 7-segment display
			Undervoltage of modules
			Undervoltage of measuring system
Status display			Power Load
			Error
Control interface			
Data			CAN bus with Festo protocol
			Digital
Electrical connection			5-pin
			M9
			Socket
Materiala Hausina			Deinformed a character
Materials: Housing			Reinforced polyamide
Note on materials			RoHS-compliant
Product weight	1 4 -	[g]	140
Dimensions	Length	[mm]	107
	Width	[mm]	50
	Height	[mm]	55

FESTO


Measuring modules CPX-CMIX Technical data

FESTO

Operating and environmental conditions

Ambient temperature	[°C]	-5 +50
Relative air humidity	[%]	5 95, non-condensing
Protection class to IEC 60529		IP65

Connection and display components



1	3-digit display
2	Control interface
3	Status LEDs
4	Inscription labels

Pin allocation – Plug 2

	Pin	Signal	Designation			
3	1	+24 V	Nominal operating voltage			
2 4	2	+24 V	Load voltage			
	3	0 V	Ground			
1-2-5	4	CAN_H	CAN high			
	5	CAN_L	CAN low			
	Housing	Screened	Cable screening			

Permitted bus nodes/FEC				
Bus node/FEC	Protocol	Max. no. of CMIX modules		
CPX-FEC	-	9		
CPX-CEC	-	9		
CPX-CEC-C1	-	9		
CPX-CEC-M1	-	9		
CPX-FB6	INTERBUS	2		
CPX-FB11	DeviceNet ¹⁾	9		
CPX-FB13	PROFIBUS-DP ²⁾	9		
CPX-FB14	CANopen	5		
CPX-M-FB20	INTERBUS	2		
CPX-M-FB21	INTERBUS	2		
CPX-FB23-24	CC-Link	5 (function module F23)		
		9 (function module F24)		
CPX-FB32	EtherNet/IP	9		
CPX-FB33	PROFINET, M12	9		
CPX-M-FB34	PROFINET, RJ45	9		
CPX-M-FB35	PROFINET, SCRJ	9		
CPX-FB36	EtherNet/IP	9		
CPX-FB38	EtherCAT	9		

With Revision 20 (R20)
 With Revision 23 (R23)

PROFIBUS[®], DeviceNet[®], CANopen[®], INTERBUS[®], CC-LINK[®], EtherCAT[®], PROFINET[®], EtherNet/IP[®] is a registered trademark of its respective trademark holder in certain countries.

Ordering data – Measuring module					
	Brief description	Part No.	Туре		
	Order code in the CPX configurator: T23	567417	CPX-CMIX-M1-1		

	Brief description	Cable length [m]	Part No.	Туре
	Connecting cable with angled plug and angled socket	0.25	540327	KVI-CP-3-WS-WD-0,25
		0.5	540328	KVI-CP-3-WS-WD-0,5
		2	540329	KVI-CP-3-WS-WD-2
		5	540330	KVI-CP-3-WS-WD-5
		8	540331	KVI-CP-3-WS-WD-8
	Connecting cable with straight plug and straight socket	2	540332	KVI-CP-3-GS-GD-2
		5	540333	KVI-CP-3-GS-GD-5
		8	540334	KVI-CP-3-GS-GD-8
MAR	Connector for control cabinet through-feed	-	543252	KVI-CP-3-SSD
onnection between line	ear drive DGPI, DGPIL or displacement encoder MME and measurin	g module CPX-CMIX		
Ma D	For linear drive DGPI, DGPIL	2	575898	NEBP-M16W6-K-2-M9W5

Ordering data – Screws			
	Brief description	Part No.	Туре
Contraction of the second s	For mounting on the metal interlinking block	550219	CPX-M-M3X22-4X

Ordering data – Inscription labels					
	Brief description	Number	Part No.	Туре	
	Inscription labels 6x10, in frames	64	18576	IBS-6X10	

Documentation ¹⁾	
-----------------------------	--

Documentation ¹			
	Language	Part No.	Туре
	DE	567053	P.BE-CPX-CMIX-DE
	EN	567054	P.BE-CPX-CMIX-EN
	ES	567055	P.BE-CPX-CMIX-ES
	FR	567056	P.BE-CPX-CMIX-FR
	IT	567057	P.BE-CPX-CMIX-IT
	SV	567058	P.BE-CPX-CMIX-SV

1) Manual in paper form is not included in the scope of delivery

Ordering data – Interlinking block, plastic, as expansion block					
	Brief description	Connection	Part No.	Туре	
	Without power supply	-	195742	CPX-GE-EV	
	a second a second s	M18	195744	CPX-GE-EV-Z	
		7/8" – 5-pin	541248	CPX-GE-EV-Z-7/8-5POL	
		7/8" – 4-pin	541250	CPX-GE-EV-Z-7/8-4POL	
	With additional power supply for valves	M18	533577	CPX-GE-EV-V	
		7/8" – 4-pin	541252	CPX-GE-EV-V-7/8-4POL	

Ordering data – Tie rod				
	Brief description	Expansion	Part No.	Туре
	For expansion using an interlinking block	1-fold	525418	CPX-ZA-1-E