


Position transmitters SMAT-8E, for T-slot

FESTO



Position transmitters SMAT-8E, for T-slot

Key features

FESTO



Design

The SMAT-8E is a sturdy magnetic measuring system with a 50 mm range. It provides a standardised analogue current and voltage signal


via an M8x1 plug connection, regardless of the drive used. The transmitter can thus be connected directly to the analogue input of a

programmable logic controller. The piston position of the pneumatic cylinder is detected by contactless sensing and the travel distance can

be measured between any set switching points with typical repeatability of 0.1 mm.



Analogue output as a function of piston position



Analogue output		Description	Range
[V]	[mA]		
0	0	No valid signal, e.g. no operating voltage	–
1	2	Piston outside of the measuring range after the operating voltage is switched on	A, C
2	4	Piston has left the measuring range in the negative direction	A
10	20	Piston has left the measuring range in the positive direction	C
2 ... 10	4 ... 20	Piston within the measuring range at the relevant position	B

Note

Sensors that detect magnetic fields, such as the position transmitter SMAT, must not be secured onto

the drive using mountings made from ferritic materials, as this can lead to malfunction.

Position transmitters SMAT-8E, for T-slot

Selection aid

Drive	Piston Ø	Suitability
Standards-based cylinders		
Standard cylinders DSNU, ESNU		o
Standard cylinders DSN, ESN		–
Standard cylinders DNCB		++
Standard cylinders DNC		++
Standard cylinders DNG		–
Standard cylinders CDN-...-R with sensor strip		–
Standard cylinders DNU		–
Standard cylinders ADN		++
Cylinders with piston rod		
Compact cylinders ADVU, AEVU		++
Short-stroke cylinders ADVC, AEVC	Ø 6 ... 25	–
	Ø 32 ... 100	++
Flat cylinders EZH-10/40-40-A-B		+
Flat cylinders DZF	Ø 12, 25, 32, 40, 63	+
	Ø 18, 50	++
Flat cylinders DZH	Ø 16 ... 25	+
	Ø 32 ... 63	–
Round cylinders DSNU, ESNU		o
Round cylinders DSEU, ESEU		o
Multimount cylinders DMM, EMM		+
Round cylinders CRDG		o
Round cylinders CRDSW		o
Standard cylinders CRHD		o
Standard cylinders CRDSNU		o
Standard cylinders CRDNG		–
Standard cylinders CRDNGS		–
Rodless cylinders		
Linear drives DGC		–
Linear drives DGP, DGPL		–
Linear drives SLG		–
Linear drives DGO		–
Linear drives SLM	Ø 12, 40	++
	Ø 16 ... 32	o
Semi-rotary drives		
Swivel modules DSM	Ø 6 ... 10	–
Semi-rotary drives DRQ		–
Semi-rotary drives DRQD	Ø 6, 8, 12, 40, 50	–
	Ø 16 ... 32	++
Function-oriented drives		
Stopper cylinders STA, STAF		–
Linear/swivel clamps CLR		o
Swivel/linear units DSL		–


Drive	Piston Ø	Suitability
Drives with linear guide		
Mini slides SLS, SLF, SLT		–
Twin-piston cylinders SPZ	Ø 10, 25	o
	Ø 16	++
	Ø 32	–
Guided drives DFP	Ø 10 ... 16	–
	Ø 25 ... 80	o
Mini guided cylinders DFC		–
Guided drives DFM	Ø 12, 25, 50	++
	Ø 16, 20, 32, 40, 63, 80	+
	Ø 100	–
Guided drives DFM-B	Ø 12, 16, 25, 32	–
	Ø 20	+
	Ø 40, 50	++
	Ø 63	–
Linear units SLE		–
Twin-piston cylinders DPZ		++
Handling units		
Linear modules HMP		–
Linear modules HMPL		–
Handling modules HSP		–
Feed separators HPV		–
Three-point grippers HGD		–
Parallel grippers HGP		–
Parallel grippers HGPP		–
Parallel grippers HGPT		–
Angle grippers HGW		–
Radial grippers HGR		–
Cushioning components		
Stop elements YSRWJ		–
Electrical positioning systems		
Toothed belt axes DGE-ZR		–
Spindle axes DGE-SP		–
System components		
Heavy-duty guides HD		–
Valve actuators		
Copac linear actuators DLP-A		–

- ++ Unrestricted use
- + Sensor function guaranteed without restriction; installation direction and clamping are drive-specific
- o On request
- Not suitable

Position transmitters SMAT-8E, for T-slot

Peripherals overview

FESTO



Accessories	→ Page/Internet
1 Connecting cable NEBU-M8	9
2 Standard cylinder DNCB	dncb
Standard cylinder DNC	dnc
Standard cylinder ADN	adn
Compact cylinder ADVU, AEVU	advu
Short-stroke cylinder ADVC, AEVC	advc
Flat cylinder EZH	ezh

Accessories	→ Page/Internet
2 Flat cylinder DZF	dzf
Flat cylinder DZH	dzh
Multimount cylinder DMM, EMM	dmm
Linear drive SLM	slm
Semi-rotary drive DRQD	drqd
Twin-piston cylinder SPZ	spz
Guided drive DFM, DFM-B	dfm

Position transmitters SMAT-8E, for T-slot

Type codes

FESTO


		SMAT	-	8E	-	S50	-	IU	-	E	-	0,3	-	M8D
Type														
SMAT	Position transmitter, magnetic													
Design														
8E	For T-slot, insertable in slot lengthwise													
Position measuring range														
S50	48 ... 52 mm													
Analogue output														
IU	0 ... 10 V, 0 ... 20 mA													
Cable attribute														
E	Energy chain + robot applications													
Cable length														
0,3	0.3 m													
Electrical connection														
M8	Plug M8, 4-pin, fixed													
M8D	Plug M8, 4-pin, rotatable thread													

Position transmitters SMAT-8E, for T-slot

Technical data

Function

Normal operation



SMAT-8E-...-M8



SMAT-8E-...-M8D

General technical data		
Type	SMAT-8E-...-M8	SMAT-8E-...-E-0,3-M8D
Design	For T-slot	
Certification	cULus listed (OL)	–
	C-Tick	
CE mark (see declaration of conformity)	To EU EMC Directive	
Note on materials	Free of copper and PTFE	
	RoHS-compliant	
	–	Cable free of halogen
	–	Cable resistant to oil

Input signal/measuring element		
Measuring principle	Magnetic	
Position measuring range	[mm]	48 ... 52
Ambient temperature ¹⁾	[°C]	–20 ... +50

1) Extended ambient temperature range on request.

Signal processing		
Typ. sampling interval	[ms]	2.85
Max. travel speed	[m/s]	3

Output, general		
Displacement resolution	[mm]	0.064

Analogue output		
Analogue output	[V]	0 ... 10
	[mA]	0 ... 20
Sensitivity	[V/mm]	0.152
	[mA/mm]	0.305
Typ. linearity error	[mm]	0.25
Repetition accuracy of analogue value ²⁾	[mm]	±0.064
Min. load resistance of voltage output	[kΩ]	2
Max. load resistance of current output	[Ω]	500

2) Use of a non-rotating piston rod or a mechanical structure to protect against rotation is recommended.

Position transmitters SMAT-8E, for T-slot



Technical data

FESTO

Output, additional data		
Protection against short circuit	Yes	
Protection against overloading	Yes	
Electronic components		
Operating voltage range	[V DC]	15 ... 30
Idle current	[mA]	32
Reverse polarity protection	For all electrical connections	
Electromechanical components		
Type	SMAT-8E-...-M8	SMAT-8E-...-E-0,3-M8D
Electrical connection	Plug M8x1, 4-pin	
Connection direction	Lateral	In-line
Cable attribute	–	Energy chain + robot applications
Mechanical components		
Type	SMAT-8E-...-M8	SMAT-8E-...-E-0,3-M8D
Mounting position	Any	
Product weight	[g]	15
Housing materials	PA-reinforced, PC	
Cable sheath materials	–	TPE-U(PU)
Display/operation		
Ready status display	Green LED	
Status display	Red LED = outside measuring range	
Immissions/emissions		
Type	SMAT-8E-...-M8	SMAT-8E-...-E-0,3-M8D
Protection class	IP65, IP67	IP65, IP68
Corrosion resistance class CRC ³⁾	2	

3) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pin allocation		
Normal operation	Plug	
		<ul style="list-style-type: none"> 1 Operating voltage 2 Analogue output 0 ... 20 mA 3 0 V 4 Analogue output 0 ... 10 V

Wire colours		
BN = brown	BU = blue	
BK = black	WH = white	

Position transmitters SMAT-8E, for T-slot


Technical data

FESTO


Dimensions

Download CAD Data → www.festo.com/us/cad

SMAT-8E-...-M8






SMAT-8E-...-M8D



Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	L1	L2	L3	L4
SMAT-8E-...-M8	16.8	6.3	5	5.5	M8x1	26.8	19.1	6.1	3.1	60	30	8	–
SMAT-8E-...-M8D						20.6	–					–	420




Ordering data

	Electrical connection	Cable length [m]	Part No.	Type
	Plug M8x1, 4-pin, fixed	–	540191	SMAT-8E-S50-IU-M8
	Plug M8x1, 4-pin, rotatable thread	0.3	570134	SMAT-8E-S50-IU-E-0,3-M8D 

Position transmitters SMAT-8E, for T-slot

Accessories

FESTO

Ordering data – Connecting cables NEBU-M8				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541342	NEBU-M8G4-K-2.5-LE4
			5	541343	NEBU-M8G4-K-5-LE4
	Straight socket, M8x1, 4-pin	Straight socket, M8x1, 4-pin	2.5	554035	NEBU-M8G4-K-2.5-M8G4
	Angled socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541344	NEBU-M8W4-K-2.5-LE4
			5	541345	NEBU-M8W4-K-5-LE4

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drives



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalnepantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com