

Positioners CMSX

FESTO



Positioners CMSX

Key features

FESTO

Function and application


The positioner CMSX-P-S described here is intended for controlling the position of double-acting pneumatic quarter turn actuators in process automation systems. It is suitable for operation with quarter turn actuators

with a swivel angle of approx. 90° and a mechanical interface in accordance with VDI/VDE Directive 3845. The CMSX enables simple and efficient position control based on the PID control algorithm. Positions are

specified via a setpoint signal. The integrated potentiometer senses the current position of the quarter turn actuator via the shaft and forwards the measured value to the internal regulator. The regulator compares the

setpoint value specified by analogue means to the measured value and actuates the two internal fast-switching valves correspondingly by means of pulse-width modulation (PWM).

System structure



- 1 Higher-level system (PLC/IPC or external setpoint generator)
- 2 Positioner CMSX
- 3 Mechanical coupling
- 4 Mounting adapter
- 5 Quarter turn actuator (example: DFPB)
- 6 Process valve (example: VZBA)
- 7 Air – ports 2 and 4

Variants

CMSX-...-A

On the product variant CMSX-...-A, working port 4 is exhausted and working port 2 is pressurised. The process valve is opened or closed depending on the tubing connections between the CMSX-...-A and the quarter turn actuator.

CMSX-...-C

On the product variant CMSX-...-C, working ports 2 and 4 are pressurised to maintain the current position of the quarter turn actuator.

Safety


Multiple freely programmable safety positions in case of current failure, additional digital error signal for emergency shut-down.
Multiple freely configurable, analogue input signals for each task, for reliable monitoring of the actual position via the analogue feedback signal.

Economic efficiency

By means of integrated, analogue feedback functions and the definable safety positions.

Positioners CMSX

Peripherals overview



Mounting components and accessories		
	Brief description	→ Page/Internet
1	CMSX Positioner For position control of double-acting pneumatic quarter turn actuators in process automation systems	5
2	U-Silencer With polymer male thread	u
3	UC-Silencer For reducing noise at exhaust ports	uc
4	QS Push-in fittings A secure solution for every connection	qs
5	DARQ Mounting adapters For connecting positioners/actuators for process automation	8
6	DFPB Quarter turn actuators Actuators for process automation	dfpb, drd, daps

Positioners CMSX

Type codes

FESTO

		CMSX	-	P	-	S	-	A1	-	C	-	U	-	F1	-	D	-	A
Type																		
CMSX	Positioner for process automation																	
Product version																		
P	Primarily polymers																	
Design																		
S	Positioner, path/angle measurement integrated																	
Mechanical interface																		
A1	Hole pattern 30x80 mm																	
Display type																		
C	LCD, backlit																	
Setpoint value																		
U	Configurable (0 ... 10 V, 0 ... 20 mA, 4 ... 20 mA)																	
Position feedback																		
F1	4 ... 20 mA																	
Function																		
D	Double-acting																	
Safety function																		
A	Open or close in case of breakdown ¹⁾																	
C	Maintain position ²⁾ in case of breakdown ¹⁾																	

1) Failure of the power supply

2) Pressurise quarter turn actuator at both ends

Positioners CMSX


Technical data

Voltage

21.6 ... 26.4 V DC

Temperature range

–5 ... +60 °C



General technical data		
Type	CMSX-P-S-A1-C-U-F1-D-A	CMSX-P-S-A1-C-U-F1-D-C
Pneumatic connection	G1/8	
Conforms to standard	VDI/VDE 3845 (NAMUR)	
Cable connector	M20x1.5	
Type of mounting	On flange to ISO 5211, via accessories	
Protection against short circuit	Yes	
Protection against incorrect polarity	For operating voltage connections For setpoint value	
Type of process valve characteristic curves	Freely adjustable over 21 support points Linear, equal percentage (1:25, 1:33, 1:50)	
Leakproof characteristics	Automatic	
	Adjustable	
Control range adaptation	Adjustable	
Alarm for exceeding limit value	No	
Active direction	Adjustable	
	Rising, falling	
Safety precaution	Adjustable	–
	–	Retaining
	Opening	–
	Closing	–
UV resistance	Yes	
Display type	Backlit LCD	
Setting options	Via display and keys	
Standard nominal flow rate	[l/min]	50
Sensing range in degrees	[deg]	0 ... 100
Size of the dead zone	[%]	0.1 ... 10
Product weight	[g]	970

Positioners CMSX

Technical data

FESTO

Operating and environmental conditions		
	CMSX-P-S-A1-C-U-F1-D-A	CMSX-P-S-A1-C-U-F1-D-C
Operating pressure [bar]	3 ... 8	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation not possible	
Operating voltage range DC [V]	21.6 ... 26.4	
Setpoint value [V]	0 ... 10	
Setpoint value [mA]	0 ... 20	
	4 ... 20	
Ambient temperature [°C]	-5 ... 60	
Temperature of medium [°C]	-5 ... 60	
Storage temperature [°C]	-20 ... 60	
Corrosion resistance class CRC ¹⁾	2	
CE marking (see declaration of conformity)	To EU EMC Directive	
Certification	C-Tick	
Protection class	IP65	

- 1) CRC2: Corrosion resistance class to Festo standard 940 070
Components with medium corrosion exposure. Externally visible components with significant decorative function in direct contact with normal industrial atmosphere or media such as coolants and lubricants.

Materials		
1	Housing	PC
2	Threaded coupling	High-alloy stainless steel
3	Adapter plate	Aluminium
	Plate	Aluminium
-	Seals	NBR
-	Cable connection	PA
-	Note on materials	Contains PWIS (paint-wetting impairment substances), RoHS-compliant


Positioners CMSX

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad




Type	B1	B2	B4	B7	B8	B9	B10	D1	D2	D3	D4	H3	H5
CMSX-P-S-A1-C-U-F1-D-A	105.8	65	30	30	17	8	0.5	18	50	35	5.4	5	85.8
CMSX-P-S-A1-C-U-F1-D-C													

Type	H6	H7	H8	H9	H10	H11	H12	L1	L5	L7	W1	≈ 1
CMSX-P-S-A1-C-U-F1-D-A	19	11	3	40.5	20.5	13.5	5.5	200	4	164	45°	25
CMSX-P-S-A1-C-U-F1-D-C												

Positioner	Mounting adapter	H1	H2	L2	L3	L4
CMSX-P-S-A1-C-U-F1-D-A	DARQ-K-P-A1-F05-20-R1	138.5	45	110	81.6	78.4
	DARQ-K-P-A1-F05-30-R1	148.5	55	110	81.6	78.4
	DARQ-K-P-A2-F05-30-R1	148.5	55	160	131.6	128.4
CMSX-P-S-A1-C-U-F1-D-C	DARQ-K-P-A1-F05-20-R1	138.5	45	110	81.6	78.4
	DARQ-K-P-A1-F05-30-R1	148.5	55	110	81.6	78.4
	DARQ-K-P-A2-F05-30-R1	148.5	55	160	131.6	128.4

Ordering data

Positioner	Brief description	Part No.	Type
	Open or close in case of breakdown	2092434	CMSX-P-S-A1-C-U-F1-D-A
	Maintain position in case of breakdown	2110841	CMSX-P-S-A1-C-U-F1-D-C


Positioners CMSX

Accessories

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Type	B1	B3	D1 Ø	D2 Ø	D3 Ø	D4 Ø	H1	H2	H3	L1	L2	L3	W1
DARQ-K-P-A1-F05-20-R1	65	30	50	35	4.5	5.4	45	5	3	110	81.6	78.4	45°
DARQ-K-P-A1-F05-30-R1							55						
DARQ-K-P-A2-F05-30-R1							55			160	131.6	128.4	

Materials

Mounting adapter	High-alloy steel
Coupling	High-alloy stainless steel
Screws	High-alloy stainless steel
Corrosion resistance class CRC ¹⁾	2
Note on materials	Contains PWIS (paint-wetting impairment substances), RoHS-compliant

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Ordering data

	Brief description	Size	Weight [g]	Part No.	Type
	Mounting adapter	20	350	2197135	DARQ-K-P-A1-F05-20-R1
	Mounting adapter	30	380	2197136	DARQ-K-P-A1-F05-30-R1
	Mounting adapter	30	460	2197137	DARQ-K-P-A2-F05-30-R1

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters**
Festo Inc.
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters**
Festo Corporation
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com

Subject to change

Internet: www.festo.com/us