

Linear actuators DLP, Copac

FESTO



Linear actuators DLP, Copac



Key features and type codes

General			
-N-	Diameter	Festo Copac linear valve actuators are ideally suited for use in water, sewage, industrial process water and sileage technology, as well as the paper and bulk goods industry. A clean solution for shut-off, safety and control slide valves. The Copac linear actuator acts directly upon the slide plate and facilitates accurate advancing to various positions.	• Fast or slow valve actuation • Position sensing • Internal air channels eliminate protruding tubing and attachments, and thus also harmful accumulation of contaminants • Suitable for manual on-site use, as well as automatic operation • Opening and closing actuated via flange-mounted solenoid valve with port pattern to Namur, or via valve terminals with a choice of 30 different fieldbus protocols • Sturdy and reliable, even in aggressive environments
-T-	Stroke length		
Force			
	80 ... 320 mm		
	40 ... 600 mm		
	2,800 ... 48,000 N		
			• Highly corrosion resistant • Mounting port pattern to DIN 3358/ISO 5210 for direct mounting • Port pattern to Namur VDI/VDE 3845 for attaching solenoid valves




		DLP	—	100	—	125	—	A
Type								
DLP	Double-acting linear actuator							
Piston Ø [mm]								
Stroke [mm]								
Position sensing								
A	Via proximity sensor							

Linear actuators DLP, Copac

Peripherals overview

FESTO




Mounting attachments and accessories					
	Brief description	DLP-80/100	DLP-125/160	DLP-200 ... 320	→ Page/Internet
1	Rod clevis SG	■	■	■	9
	Rod clevis, stainless steel CRSG	■	■	–	9
2	Rod eye SGS	■	■	■	9
	Rod eye, stainless steel CRSGS	■	■	–	9
3	Rod clevis SGA	■	■	■	9
4	Self-aligning rod coupler FK	■	■	■	9
5	Proximity sensor SMT-8F-I	■	■	■	10
	Proximity sensor SMT-8	■	■	■	10
	Proximity sensor SME-8	■	■	■	10
6	Slot cover ABP-5-S	■	■	■	11
7	Solenoid valve	■	■	■	solenoid valve
8	Local controller DLP-VSE	■	■	■	dlp-vse
9	Sub-base DLP-VSE-OBEN-NAMUR	■	■	■	dlp-vse
10	Measuring unit ASDLP	■	■	–	asdlp
11	Displacement encoder MLO-POT	■	■	■	mlo-pot

Linear actuators DLP, Copac

FESTO

Technical data

Function



-N- Diameter
80 ... 320 mm

-T- Stroke length
40 ... 600 mm

Force
2,800 ... 48,000 N



General technical data							
Piston Ø	80	100	125	160	200	250	320
Pneumatic connection	G $\frac{1}{4}$						
Based on standard	DIN 3358						
Valve connection conforms to	VDI/VDE 3845 (NAMUR)						
Design	Piston cylinder, double-acting						
Cushioning	None						
Stroke reserve [mm]	2				4		
Assembly position	Any						
Position sensing	Via proximity sensor						
Efficiency actuator [%]	95						

Operating and environmental conditions	
Operating pressure ¹⁾ [bar]	2 ... 10
Nominal operating pressure [bar]	6
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)
Ambient temperature ²⁾³⁾ [°C]	-20 ... +80
Corrosion resistance class CRC ⁴⁾	3
CE marking (see declaration of conformity) → www.festo.com	To EU Explosion Protection Directive (ATEX)
ATEX category gas	II 2G
Ex-ignition protection type gas	c T4
ATEX category dust	II 2D
EX-ignition protection type dust	c 120°C
ATEX ambient temperature ³⁾	-20°C ≤ Ta ≤ +60°C

1) Depending upon the counter force of the valve slide, a higher minimum pressure may be required to actuate the overall system

2) Further temperature ranges upon request

3) Note operating range of proximity sensors

4) Corrosion resistance class 3 according to Festo standard 940 070

Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface

Linear actuators DLP, Copac

Technical data


FESTO

Forces [N] and air consumption [NI]							
Piston Ø	80	100	125	160	200	250	320
Theoretical force at 6 bar, advancing	3,016	4,712	7,363	12,064	18,850	29,452	48,255
Theoretical force at 6 bar, retracting	2,827	4,524	6,881	11,581	18,080	28,698	47,501
Theoretical air consumption at 6 bar and 10 mm stroke, pushing	0.35	0.55	0.86	1.41	2.12	3.44	5.63
Theoretical air consumption at 6 bar and 10 mm stroke, pulling	0.33	0.53	0.80	1.35	2.11	3.35	5.54

Weights [g]							
Piston Ø	80	100	125	160	200	250	320
Basic weight with 0 mm stroke	1,843	2,801	4,855	5,854	12,831	21,117	33,907
Additional weight per 10 mm stroke	68	80	145	159	187	325	399
Moving load with 0 mm stroke	624	997	1,809	2,183	4,691	6,650	11,040
Additional moving load per 10 mm stroke	25	25	63	63	99	99	99

Materials

Sectional view



Linear actuator		
1	Piston rod	High-alloy rolled steel
2	Rod bearing	Smooth composite material
3	Cylinder barrel	Smooth anodised aluminium
	Ø 80 ... 200	
	Ø 250, 320	Stainless steel
4	Cylinder cap	Extruded aluminium
-	Seals	Polyurethane, nitrile rubber

Linear actuators DLP, Copac


Technical data

FESTO


Dimensions

Download CAD Data → www.festo.com/us/cad

Ø 80 ... 160



Ø 200 ... 320



1 Mounting slots for proximity sensor SME/SMT-8

+ = plus stroke length

Linear actuators DLP, Copac

Technical data

FESTO

∅ [mm]	AM -2	D1 ∅	D2 ∅	D3 ∅	D4 ∅	D5 ∅	D6 ∅	D7 ∅	D8 ∅	D9 ∅	E	EE	H1	H2	H3
DLP-80-...-A	32	87	20	M8	-	-	-	70	99	M5	108	G $\frac{1}{4}$	43.5	24	-
DLP-100-...-A	32	108	20	M8	-	-	-	70	119	M5	131	G $\frac{1}{4}$	43.5	24	-
DLP-125-...-A	54	135	32	M10	-	-	-	102	147	M5	163	G $\frac{1}{4}$	43.5	24	-
DLP-160-...-A	54	170	32	M10	-	-	-	102	182	M5	199	G $\frac{1}{4}$	43.5	24	-
DLP-200-...-A	72	216	40	M10	M16	140	210	102	-	M5	271	G $\frac{1}{4}$	43.5	24	4.5
DLP-250-...-A	72	260	40	M10	M16	140	244	102	-	M5	308	G $\frac{1}{4}$	43.5	24	4.5
DLP-320-...-A	72	332	40	M10	M16	140	324	102	-	M5	378	G $\frac{1}{4}$	43.5	24	4.5

∅ [mm]	KK	L1	L3	L4	L5	L6	L7	T1	T2	T3	W1	WH	ZB	≈G1
DLP-80-...-A	M16x1.5	73 +1.4/-0.4	-	-	32	-	-	15	-	8	45°	16 +0.6/-1.8	89 +0.6/-0.8	16
		100 +1.4/-0.4												
DLP-80-...-A	M16x1.5	76 +1.4/-0.4	-	-	32	-	-	15	-	8	45°	16 +0.6/-1.8	116 +0.6/-0.8	16
		100 +1.4/-0.4												
DLP-100-...-A	M16x1.5	104 +1.4/-0.4	-	-	32	-	-	15	-	8	45°	16 +0.6/-1.8	92 +0.6/-0.8	16
													120 +0.6/-0.8	
DLP-125-...-A	M27x2	114 +1.6/-0.6	-	-	32	-	-	18	-	8	45°	24 +0.8/-1.8	138 +0.8/-1.0	27
DLP-160-...-A	M27x2	114 +1.6/-0.6	-	-	32	-	-	18	-	8	45°	24 +1.2/-1.8	138 +1.2/-0.8	27
DLP-200-...-A	M36x2	150 +0.8/-1.0	10	81	32	24.5	12	20	24	8	45°	30 ±1.4	180 ±1	36
DLP-250-...-A	M36x2	152 +0.8/-1.4	25	94	32	24.5	12	20	25	8	45°	30 +1.8/-1.4	182 ±1	36
DLP-320-...-A	M36x2	159 +0.8/-1.4	-	130	32	24.5	12	20	25	8	45°	30 +1.8/-1.6	189 +0.8/-1.2	36

Linear actuators DLP, Copac

Technical data

FESTO

Ordering data				
Version	Piston Ø [mm]	Stroke [mm]	Part No.	Type
With position sensing				
	80	40 ... 500	187 479	DLP-80-...-A
	100	50 ... 500	187 480	DLP-100-...-A
	125	50 ... 500	187 481	DLP-125-...-A
	160	100 ... 500	187 482	DLP-160-...-A
	200	100 ... 600	542 711	DLP-200-...-A
	250	100 ... 600	187 483	DLP-250-...-A
	320	150 ... 600	187 484	DLP-320-...-A

Note

Stroke length of the actuator

Generally, the stroke length of the Copac linear actuator corresponds to the nominal diameter of the process valve. The system tolerances may lead to a greater stroke range than the specified nominal stroke range of

the linear actuator. The zero point is set with an adjustable rod clevis. This ensures that the end position of the valve slide is reached and the zero position of the system is fixed.

Linear actuators DLP, Copac

Accessories

FESTO

Ordering data – Piston rod attachments				Technical data → Internet: piston rod attachment			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye SGS				Rod clevis SG			
	80, 100	9 263	SGS-M16x1,5		80, 100	6 146	SG-M16x1,5
	125, 160	10 774	SGS-M27x2		125, 160	14 987	SG-M27x2-B
	200, 250, 320	10 775	SGS-M36x2		200, 250, 320	9 581	SG-M36x2
Rod clevis SGA				Self-aligning rod coupler FK			
	80, 100	10 768	SGA-M16x1,5		80, 100	6 142	FK-M16x1,5
	125, 160	10 770	SGA-M27x2		125, 160	10 485	FK-M27x2
	200, 250, 320	10 771	SGA-M36x2		200, 250, 320	10 746	FK-M36x2

Ordering data – Piston rod attachments, corrosion-resistant				Technical data → Internet: crsg			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye CRS				Rod clevis CRS			
	80, 100	13 571	CRS-M16x1,5		80, 100	195 584	CRSGS-M16x1,5
	125, 160	185 361	CRS-M27x2		125, 160	195 586	CRSGS-M27x2


Ordering data – Displacement encoders			Technical data → Internet: mlo	
	Stroke [mm]	Part No.	Type	
	100	192 213	MLO-POT-100-LWG	
	150	192 214	MLO-POT-150-LWG	
	225	152 645	MLO-POT-225-LWG	
	300	152 646	MLO-POT-300-LWG	
	360	152 647	MLO-POT-360-LWG	
	450	152 648	MLO-POT-450-LWG	
	600	152 650	MLO-POT-600-LWG	
	750	152 651	MLO-POT-750-LWG	


Ordering data – Plug socket for displacement encoder			Technical data → Internet: sd-4	
	Pin	Pin allocation	Part No.	Type
	1	Power supply	194 332	SD-4-WD-7
	2	Signal		
	3	0 V		
	4	PE (yellow), screened		

Linear actuators DLP, Copac


Accessories

FESTO

Ordering data – Proximity sensor for T-slot, magneto-resistive						Technical data → Internet: smt-8	
	Switching output	Electrical connection		Cable length [m]	Part No.	Type	
		Cable	Plug M8x1				
	N/O contact						
	PNP	3-wire	–	2.5	175 436	SMT-8-PS-K-LED-24-B	
				5.0	175 434	SMT-8-PS-K5-LED-24-B	
		–	3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B	
	NPN	3-wire	–	2.5	171 180	SMT-8-NS-K-LED-24-B	
				–	3-pin	0.3	171 181

Ordering data – Proximity sensor for T-slot					Technical data → Internet: crsmt	
	Switching output	Electrical connection	Cable length [m]	Part No.	Type	
	N/O contact					
	PNP	Cable, 3-wire	2.5	525 563	CRSMT-8-PS-K2,5-LED-24	
			5.0	525 564	CRSMT-8-PS-K5-LED-24	

Ordering data – Proximity sensor for T-slot, magnetic reed				Technical data → Internet: sme	
	Connection technology		Cable length [m]	Part No.	Type
	Cable	Cable with plug M8x1			
	N/O contact				
	Operating voltage range 0 ... 30 V AC/DC				
	3-wire	–	2.5	150 855	SME-8-K-LED-24
			5.0	175 404	SME-8-K5-LED-24
			7.5	530 491	SME-8-K-7,5-LED-24
	–	3-pin	0.3	150 857	SME-8-S-LED-24
	2-wire	–	2.5	171 169	SME-8-ZS-KL-LED-24
	Heat-resistant up to 120 °C				
	2-wire	–	2.5	161 756	SME-8-K-24-S6
	Operating voltage range 3 ... 250 V AC/DC				
	2-wire	–	2.5	152 820	SME-8-K-LED-230
	N/C contact				
	3-wire	–	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Ex proximity sensors for T-slot					Technical data → Internet: smt	
	Switching output	Electrical connection	Cable length [m]	Part No.	Type	
	NAMUR	Cable, 2-wire	5.0	536 956	SMT-8F-I-8,2V-K5,0-OE-EX	

Linear actuators DLP, Copac

Accessories

FESTO

Ordering data – Connecting cable M8x1					Technical data ➔ Internet: nebu	
	Electrical connection, left	Electrical connection, right	Switching output	Cable length [m]	Part No.	Type
Basic version						
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	–	2.5	541 333	NEBU-M8G3-K-2.5-LE3
				5	541 334	NEBU-M8G3-K-5-LE3
				10	541 332	NEBU-M8G3-K-10-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	–	2.5	541 338	NEBU-M8W3-K-2.5-LE3
				5	541 341	NEBU-M8W3-K-5-LE3
				10	541 335	NEBU-M8W3-K-10-LE3
With switching status display						
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	PNP	2.5	541 337	NEBU-M8W5P-K-2.5-LE3
				5	541 340	NEBU-M8W5P-K-5-LE3
			NPN	2.5	541 336	NEBU-M8W5N-K-2.5-LE3
				5	541 339	NEBU-M8W5N-K-5-LE3

Ordering data – Slot cover for T-slot			
	Assembly	Length [m]	Part No. Type
	Insertable from above	2x 0.5	151 680 ABP-5-S

Ordering data – Cable clip SMBK-8		
		Part No. Type
	For fixing the cable in the sensor slot	534 254 SMBK-8

Ordering data – Inscription labels					
	Material	Usage	Dimensions [mm]	Part No. Type	PU ¹⁾
	Polycarbonate	For insertion in the inscription label holder	23x4	541 598 ASLR-L-423	34

1) Packaging unit per frame

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com