

1. Multiple distributors QS, Quick Star

FESTO



- Easy to insert
- Easy to release
- Up to 6 outlets
- 360° rotatable




Multiple distributors QS, Quick Star

Key features

FESTO

Application	Simply "plug and work"	Reliably connected	Captive seal
 Effortless selection of the right fitting. Quick Star offers a secure solution for every connection. The convenient push-in fitting system includes well over 1000 types of standard and function fittings.	 The stainless steel retaining ring within the fitting holds the tubing securely without damaging its surface. Vibration and pressure surges are safely absorbed. The tubing can be detached easily by pressing down the blue release ring. For your convenience, the appropriate outside tubing diameter is marked on the release ring.	 A nitrile rubber sealing ring guarantees a perfect seal between standard OD tubing and the body of the fitting. Standard tubing is suitable for use with compressed air and vacuum.	 All of the brass components included in Festo's push-in fittings are nickel plated and are thus highly resistant to corrosion. The tapered ISO R threads have a self-sealing PTFE coating, which allows the fitting to be re-used up to five times without the need for additional sealing components.

360° rotatable	360° rotatable, with ball bearing
 Alignment is performed during assembly. Tube movement is compensated during use.	 Permits rotating motion of up to 500 rpm during use.

Which fitting fits which thread?		
Metric thread ■ Cylindrical metric thread is comparable with G-thread ■ Sealing is guaranteed by a clip-on O-ring	G thread to DIN ISO 228-1 ■ Shorter thread ■ Constant installation depth ■ Replaceable sealing ring ■ Sealing at front ■ Can be re-used a number of times thanks to replaceable sealing ring	R thread to DIN 2999-1 und ISO 7/1 ■ Self-sealing thread ■ Sealing on the threads ■ No additional sealing surface required ■ Smaller installation dimensions since there is no need for a rebate for the sealing surface ■ Can be re-used up to five times
 Metric male thread Metric female thread	 G male thread G female thread	 R male thread G female thread R female thread


Multiple distributors QS, Quick Star

Technical data

FESTO

Materials

Sectional view



	Standard QS
1 Release ring	Polyacetate
2 Seal	Nitrile rubber
3 Housing	Polybuteneterephthalate Nickel plated brass
4 Tube clamping segment	High alloy stainless steel
5 Threaded coupling	Nickel plated brass PTFE sealing compound
6 Plastic tubing, standard O.D.	PAN PUN PUN-H PUN-E
Note on materials	RoHS-conform

Tubing insertion depth



Tubing O.D. [mm]	4	6	8	10	12
Standard QS	15	17	18	20.5	23.5


Operating and environmental conditions

	Standard QS
Temperature dependent operating pressure [bar]	−0.95 ... +14
Operating temperature [°C]	−10 ... +80
Corrosion resistance CRC ¹⁾	1
Certification	Germanischer Lloyd

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Operating pressure p as a function of temperature t



Multiple distributors QS, Quick Star

Technical data

FESTO

Possible push-in fitting/tubing combinations					
Thread	Tubing O.D. [mm]				
	4	6	8	10	12
R1/8	+	++	+	+	–
R1/4	+	+	++	+	+
R3/8	–	+	+	++	+
R1/2	–	–	–	+	++
G1/8	+	++	+	–	–
G1/4	–	+	++	+	+
G3/8	–	–	+	++	+
G1/2	–	–	–	–	++

+ Possible thread/tubing O.D. combinations

++ Optimum thread/tubing O.D. combinations (with regard to flow)

Multiple distributors QS, Quick Star

Product range overview

FESTO

Shape	Design	Type	Connection D1		Tubing O.D.	Connection D2	Connection D3	→ Page/ Internet
			R thread	G thread		Tubing O.D.	Tubing O.D.	
L-shape	Multiple distributor, rotatable 360° – 2 outlets							
		QSLV2	R1/8	G1/8	–	4, 6, 8	–	3 / 5.8-6
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 3 outlets							
		QSLV3	R1/8	G1/8	–	4, 6, 8	–	3 / 5.8-7
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 4 outlets							
		QSLV4	R1/8	G1/8	–	4, 6, 8	–	3 / 5.8-8
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 6 outlets							
		QSLV6	R1/8	G1/8	–	4, 6, 8	–	3 / 5.8-9
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 4 outlets							
		QSQ	R1/8	G1/8	–	4, 6	–	3 / 5.8-10
			R1/4	G1/4		4, 6		
		QSQ reducing	–	–	6	4	–	3 / 5.8-10
					8	6		
T-shape	Multiple distributor, rotatable 360° – 3 outlets							
		QST3	R1/8	G1/8	–	6	4	3 / 5.8-11
			R1/4	G1/4		8	6	
			R3/8	G3/8		10	8	
		QST3 reducing	–	–	6	6	4	3 / 5.8-11
					8	8	6	
					10	10	8	

Multiple distributors QSLV2, Quick Star

Technical data

FESTO


Multiple distributor QSLV2

2 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data															
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	H4	H5	L1	☞1	☞2	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø									[g]			
R thread															
R1/8	2.5	4	10	43.3	8	16.1	14	39	22.2	14	–	29	153 211	QSLV2-1/8-4	1
	3.4	6	12.5	43.3	8	16.1	14	39	24.2	14	–	31	153 212	QSLV2-1/8-6	1
	4.3	8	14.5	46.3	8	17.6	15	42	28.2	17	–	48	153 214	QSLV2-1/8-8	1
R1/4	3.4	6	12.5	46.3	11	17.1	14	40	24.2	14	–	33	153 213	QSLV2-1/4-6	1
	4.4	8	14.5	49.3	11	18.5	15	43	28.2	17	–	51	153 215	QSLV2-1/4-8	1
	5.2	10	18	57.8	11	22	18	51.5	32.5	22	–	89	153 217	QSLV2-1/4-10	1
R3/8	4.4	8	14.5	50.3	12	19.2	15	43.5	28.2	17	–	56	153 216	QSLV2-3/8-8	1
	5.4	10	18	58.8	12	22.7	18	52	32.5	22	–	95	153 218	QSLV2-3/8-10	1
	6.3	12	21	68.4	12	27.3	21	62.1	38.2	27	–	152	153 219	QSLV2-3/8-12	1
R1/2	6.3	12	21	71.4	15	28.4	21	63	38.2	27	–	159	153 220	QSLV2-1/2-12	1
G thread with sealing ring															
G1/8	2.5	4	10	42.2	5.1	13.9	14	–	22.2	14	14	29	186 223	QSLV2-G1/8-4	1
	3.4	6	12.5	42.2	5.1	13.9	14	–	24.2	14	14	31	186 224	QSLV2-G1/8-6	1
	4.3	8	14.5	45.2	5.1	15.4	15	–	28.2	17	17	47	186 226	QSLV2-G1/8-8	1
G1/4	3.4	6	12.5	43.7	5.6	14.4	14	–	24.2	14	17	39	186 225	QSLV2-G1/4-6	1
	4.4	8	14.5	45.7	5.6	15.4	15	–	28.2	17	17	49	186 227	QSLV2-G1/4-8	1
	5.2	10	18	54.2	5.6	18.9	18	–	32.5	22	22	88	186 229	QSLV2-G1/4-10	1
G3/8	4.4	8	14.5	47.2	6.6	15.9	15	–	28.2	17	19	88	186 228	QSLV2-G3/8-8	1
	5.4	10	18	55.7	6.6	19.4	18	–	32.5	22	22	91	186 230	QSLV2-G3/8-10	1
	6.3	12	21	65.3	6.6	23.9	21	–	38.2	27	27	118	186 231	QSLV2-G3/8-12	1
G1/2	6.3	12	21	66.3	7.6	23.9	21	–	38.2	27	27	152	186 232	QSLV2-G1/2-12	1

* Packaging unit quantity

Multiple distributors QSLV3, Quick Star



Technical data

FESTO

Multiple distributor QSLV3

3 outlets

360° rotatable



Dimensions and ordering data															
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	H4	H5	L1	≧1	≧2	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø									[g]			
R thread															
R1/8	2.4	4	10	57.4	8	16.1	14	53.4	22.2	14	–	38	153 221	QSLV3-1/8-4	1
	3.5	6	12.5	57.4	8	16.1	14	53.4	24.2	14	–	41	153 222	QSLV3-1/8-6	1
	4.3	8	14.5	61.3	8	17.6	15	57.3	28.2	17	–	63	153 224	QSLV3-1/8-8	1
R1/4	3.5	6	12.5	60.4	11	17.1	14	54.4	24.2	14	–	44	153 223	QSLV3-1/4-6	1
	4.4	8	14.5	64.3	11	18.5	15	58.3	28.2	17	–	66	153 225	QSLV3-1/4-8	1
	5.3	10	18	75.8	11	22	18	69.8	32.5	22	–	114	153 227	QSLV3-1/4-10	1
R3/8	4.4	8	14.5	65.3	12	19.2	15	59	28.2	17	–	70	153 226	QSLV3-3/8-8	1
	5.4	10	18	76.8	15	22.7	18	70.5	32.5	22	–	120	153 228	QSLV3-3/8-10	1
	6.2	12	21	89.5	12	27.3	21	83.2	38.2	27	–	188	153 229	QSLV3-3/8-12	1
R1/2	6.3	12	21	92.5	15	28.4	21	84.3	38.2	27	–	196	153 230	QSLV3-1/2-12	1
G thread with sealing ring															
G1/8	2.4	4	10	56.2	5.1	13.9	14	–	22.2	14	14	38	186 233	QSLV3-G1/8-4	1
	3.5	6	12.5	56.2	5.1	13.9	14	–	24.2	14	14	40	186 234	QSLV3-G1/8-6	1
	4.3	8	14.5	59.2	5.1	15.4	15	–	28.2	17	17	62	186 236	QSLV3-G1/8-8	1
G1/4	3.5	6	12.5	57.7	5.6	14.4	14	–	24.2	14	17	49	186 235	QSLV3-G1/4-6	1
	4.4	8	14.5	59.7	5.6	15.4	15	–	28.2	17	17	63	186 237	QSLV3-G1/4-8	1
	5.3	10	18	68.2	5.6	18.9	18	–	32.5	22	22	112	186 239	QSLV3-G1/4-10	1
G3/8	4.4	8	14.5	61.2	6.6	15.9	15	–	28.2	17	19	102	186 238	QSLV3-G3/8-8	1
	5.4	10	18	69.7	6.6	19.4	18	–	32.5	22	22	117	186 240	QSLV3-G3/8-10	1
	6.2	12	21	79.3	6.6	23.9	21	–	38.2	27	27	154	186 241	QSLV3-G3/8-12	1
G1/2	6.3	12	21	80.3	7.6	23.9	21	–	38.2	27	27	188	186 242	QSLV3-G1/2-12	1

* Packaging unit quantity

Multiple distributors QSLV4, Quick Star

Technical data

FESTO


Multiple distributor QSLV4

4 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data																
Connection	Nom- inal size	Tubing O.D.	D5 Ø	H1	H2	H3	H4	H5	L1	B1	1	2	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2											[g]			
R thread																
R $\frac{1}{8}$	2.3	4	10	43.3	8	16.1	14	39.3	22.2	10	14	–	34	153 231	QSLV4- $\frac{1}{8}$ -4	1
	3	6	12.4	43.3	8	16.1	14	39.3	26.2	12	14	–	38	153 232	QSLV4- $\frac{1}{8}$ -6	1
	4	8	14.4	46.3	8	17.6	15	42.3	29.1	14	17	–	57	153 234	QSLV4- $\frac{1}{8}$ -8	1
R $\frac{1}{4}$	3	6	12.4	46.3	11	17.1	14	42	26.2	12	14	–	40	153 233	QSLV4- $\frac{1}{4}$ -6	1
	4.2	8	14.4	49.3	11	18.5	15	43.3	29.1	14	17	–	60	153 235	QSLV4- $\frac{1}{4}$ -8	1
	5.2	10	17.6	57.8	12	22	18	51.8	33.5	17	22	–	102	153 237	QSLV4- $\frac{1}{4}$ -10	1
R $\frac{3}{8}$	4.2	8	14.6	50.3	12	19.2	15	44	29.1	14	17	–	65	153 236	QSLV4- $\frac{3}{8}$ -8	1
	5.2	10	17.6	58.5	12	22.7	18	52.5	33.5	17	22	–	109	153 238	QSLV4- $\frac{3}{8}$ -10	1
	7.5	12	21	68.4	12	27.3	21	62.1	37.4	20	27	–	168	153 239	QSLV4- $\frac{3}{8}$ -12	1
R $\frac{1}{2}$	7.6	12	21	71.4	15	28.4	21	63.2	37.4	20	27	–	176	153 240	QSLV4- $\frac{1}{2}$ -12	1
G thread with sealing ring																
G $\frac{1}{8}$	2.3	4	10	42.2	5.1	13.9	14	–	22.2	10	14	14	34	186 243	QSLV4-G $\frac{1}{8}$ -4	1
	3	6	12.4	42.2	5.1	13.9	14	–	26.2	12	14	14	38	186 244	QSLV4-G $\frac{1}{8}$ -6	1
	4	8	14.4	45.2	5.1	15.4	15	–	29.1	14	17	17	56	186 246	QSLV4-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	3	6	12.4	43.7	5.6	14.4	14	–	26.2	12	14	17	46	186 245	QSLV4-G $\frac{1}{4}$ -6	1
	4.2	8	14.4	45.7	5.6	15.4	15	–	29.1	14	17	17	58	186 247	QSLV4-G $\frac{1}{4}$ -8	1
	5.2	10	17.6	54.2	5.6	18.9	18	–	33.5	17	22	22	101	186 249	QSLV4-G $\frac{1}{4}$ -10	1
G $\frac{3}{8}$	4.2	8	14.4	47.2	6.6	15.9	15	–	29.1	14	17	19	97	186 248	QSLV4-G $\frac{3}{8}$ -8	1
	5.2	10	17.6	55.7	6.6	19.4	18	–	33.5	17	22	22	106	186 250	QSLV4-G $\frac{3}{8}$ -10	1
	7.5	12	21	65.3	6.6	23.9	21	–	37.4	20	27	27	135	186 251	QSLV4-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	7.6	12	21	66.3	7.6	23.9	21	–	37.4	20	27	27	169	186 252	QSLV4-G $\frac{1}{2}$ -12	1

* Packaging unit quantity

Multiple distributors QSLV6, Quick Star

Technical data

FESTO


Multiple distributor QSLV6

6 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data																
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	H4	H5	L1	B1	1	2	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø										[g]			
R thread																
R $\frac{1}{8}$	2.5	4	10	57.4	8	16.1	14	53.4	22.2	10	14	–	45	153 241	QSLV6- $\frac{1}{8}$ -4	1
	2.9	6	12.4	57.4	8	16.1	14	53.4	26.2	12	14	–	51	153 242	QSLV6- $\frac{1}{8}$ -6	1
	4.1	8	14.4	61.3	8	17.6	15	57.3	29.1	14	17	–	76	153 244	QSLV6- $\frac{1}{8}$ -8	1
R $\frac{1}{4}$	2.9	6	12.4	60.4	11	17.1	14	54.4	26.2	12	14	–	54	153 243	QSLV6- $\frac{1}{4}$ -6	1
	4.1	8	14.4	64.3	11	18.5	15	58.3	29.1	14	17	–	79	153 245	QSLV6- $\frac{1}{4}$ -8	1
	5.2	10	17.6	75.8	12	22	18	69.8	33.5	17	22	–	134	153 247	QSLV6- $\frac{1}{4}$ -10	1
R $\frac{3}{8}$	4.2	8	14.4	65.3	12	19.2	15	59	29.1	14	17	–	84	153 246	QSLV6- $\frac{3}{8}$ -8	1
	5.2	10	17.6	76.8	15	22.7	18	70.5	33.5	17	22	–	140	153 248	QSLV6- $\frac{3}{8}$ -10	1
	7.6	12	21	89.5	12	27.3	21	83.2	37.4	20	27	–	214	153 249	QSLV6- $\frac{3}{8}$ -12	1
R $\frac{1}{2}$	7.6	12	21	92.5	15	28.4	21	84.3	37.4	20	27	–	221	153 250	QSLV6- $\frac{1}{2}$ -12	1
G thread with sealing ring																
G $\frac{1}{8}$	2.5	4	10	56.2	5.1	13.9	14	–	22.2	10	14	14	45	186 253	QSLV6-G $\frac{1}{8}$ -4	1
	2.9	6	12.4	56.2	5.1	13.9	14	–	26.2	12	14	14	50	186 254	QSLV6-G $\frac{1}{8}$ -6	1
	4.1	8	14.4	59.2	5.1	15.4	15	–	29.1	14	17	17	75	186 256	QSLV6-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	2.9	6	12.4	57.7	5.6	14.4	14	–	26.2	12	14	17	59	186 255	QSLV6-G $\frac{1}{4}$ -6	1
	4.1	8	14.4	59.7	5.6	15.4	15	–	29.1	14	17	17	77	186 257	QSLV6-G $\frac{1}{4}$ -8	1
	5.2	10	17.6	68.2	5.6	18.9	18	–	33.5	17	22	22	133	186 259	QSLV6-G $\frac{1}{4}$ -10	1
G $\frac{3}{8}$	4.2	8	14.4	61.2	6.6	15.9	15	–	29.1	14	17	19	116	186 258	QSLV6-G $\frac{3}{8}$ -8	1
	5.2	10	17.6	69.7	6.6	19.4	18	–	33.5	17	22	22	137	186 260	QSLV6-G $\frac{3}{8}$ -10	1
	7.6	12	21	79.3	6.6	23.9	21	–	37.4	20	27	27	179	186 261	QSLV6-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	7.6	12	21	80.3	7.6	23.9	21	–	37.4	20	27	27	213	186 262	QSLV6-G $\frac{1}{2}$ -12	1

* Packaging unit quantity

Multiple distributors QSQ, Quick Star

Technical data


FESTO

Multiple distributor QSQ


360° rotatable
Male thread
with external hex
4 outlets



R thread



G thread




Push-in connector QSQ

360° rotatable
4 outlets
reducing



Reducing



Dimensions and ordering data

Connection	Nominal size	Tubing O.D.	B1	D5 Ø	D6 Ø	D7 Ø	L1	L2	L3	L4	≈	Weight/ piece [g]	Part No.	Type	PU*
D1	[mm]	D2													
R thread															
R $\frac{1}{8}$	2	4	10	10.5	3.2	–	46	8	14	42	12	21.5	153 206	QSQ- $\frac{1}{8}$ -4	1
	2.1	6	13	13	3.2	–	50.5	8	16	56.5	12	29	153 208	QSQ- $\frac{1}{8}$ -6	1
R $\frac{1}{4}$	2	4	10	10.5	3.2	–	49	11	14	43	14	29.5	153 207	QSQ- $\frac{1}{4}$ -4	1
	2.1	6	13	13	3.2	–	53.5	11	16	48	16	–	153 288	QSQ- $\frac{1}{4}$ -6	1
G thread with sealing ring															
G $\frac{1}{8}$	1.4	4	10	10.5	3.2	–	44.7	5.1	14.2	–	13	22	186 220	QSQ-G $\frac{1}{8}$ -4	1
	3.4	6	13	13	3.5	–	49.3	5.1	15.8	–	14	28	186 222	QSQ-G $\frac{1}{8}$ -6	1
G $\frac{1}{4}$	1.3	4	10	10.5	3.2	–	46.2	5.6	14.2	–	17	31	186 221	QSQ-G $\frac{1}{4}$ -4	1
	3	6	13	13	3.5	–	50.8	5.6	15.8	–	17	37	186 263	QSQ-G $\frac{1}{4}$ -6	1
Reducing															
6	1.4	4	10	10.5	3.2	13	37.5	14	–	–	–	14	153 209	QSQ-6-4	1
8	3.2	6	13	13	3.2	14.5	42.5	16	–	–	–	20.5	153 210	QSQ-8-6	1

* Packaging unit quantity

Multiple distributors QST3, Quick Star

Technical data


FESTO

Multiple distributor QST3


360° rotatable
Male thread
with external hex
3 outlets



R thread



G thread




Push-in multiple distributor QST3

360° rotatable
reducing



Reducing



Dimensions and ordering data																		
Con- nec- tion	Nom- inal size	Tubing O.D.		D5 Ø	D6 Ø	D7 Ø	H1	H2	L1	L2	L3	L4	L5	⌀	Weight	Part No.	Type	PU*
D1	[mm]	D2	D3												[g]			
R thread																		
R $\frac{1}{8}$	2.5	6	4	13	3.3	10	18.5	8	68.5	8	64.5	34	20	12	23	153 200	QST3- $\frac{1}{8}$ -6-4	1
R $\frac{1}{4}$	3.5	8	6	15	3.3	13	20	9	81	11	75	40	24	14	36.5	153 201	QST3- $\frac{1}{4}$ -8-6	1
R $\frac{3}{8}$	4.9	10	8	18	3.3	15	24	10.5	93.5	12	87	46	28	17	39.5	153 202	QST3- $\frac{3}{8}$ -10-8	1
G thread with sealing ring																		
G $\frac{1}{8}$	2.5	6	4	13	3.3	10	18.4	8	67.4	5.1	–	34	20	13	24	186 217	QST3-G $\frac{1}{8}$ -6-4	1
G $\frac{1}{4}$	3.5	8	6	15	3.3	13	21.3	9	78.2	5.6	–	40.2	24	17	39	186 218	QST3-G $\frac{1}{4}$ -8-6	1
G $\frac{3}{8}$	4.9	10	8	17.5	3.3	15	23.7	10.5	90	6.6	–	46.2	28	19	59	186 219	QST3-G $\frac{3}{8}$ -10-8	1
Reducing																		
6	2.5	6	4	13	3.3	10	18.5	8	60	–	–	34	20	–	16	153 203	QST3-6-4	1
8	3.6	8	6	15	3.3	13	21	9	69.5	–	–	40	24	–	23	153 204	QST3-8-6	1
10	4.9	10	8	18	3.3	15	23.5	10.5	80	–	–	46	28	–	33	153 205	QST3-10-8	1

* Packaging unit quantity

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drives



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquihuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com