Silencer

Diecast Al

Type U-...-B U-...-B-NPT



Silencers are used to reduce the noise at the outlet ports of valves.


These slim, rugged, die-cast components are used where space is limited.

The silencing effect is achieved by reducing air speed. The silencers achieve a considerable reduction in exhaust air noise without affecting the speed of the piston rod of a cylinder.

Important: Clean silencers in kerosene or naptha (not with trichloroethylene).







SW = wrench size (mm)

Туре	D				
, , , , , , , , , , , , , , , , , , ,	diameter		L	L1	SW
	in / mm		in / mm	in / mm	in / mm
U-1/8-B	0.63 / 16.0	G 1/8 ISO	1.56 / 39.5	0.26 / 6.5	0.55 / 14
U-1/8-B-NPT	0.63 / 16.0	1/8 NPT	1.56 / 39.5	0.26 / 6.5	0.55 / 14
U-1/4-B	0.77 / 19.5	G 1/4 ISO	2.22 / 56.5	0.33 / 8.5	0.67 / 17
U-1/4-B-NPT	0.77 / 19.5	1/4 NPT	2.22 / 56.5	0.33 / 8.5	0.67 / 17
U-3/8-B	0.98 / 25.0	G 3/8 ISO	3.48 / 88.5	0.41 / 10.5	0.75 / 19
U-3/8-B-NPT	0.98 / 25.0	3/8 NPT	3.48 / 88.5	0.41 / 10.5	0.75 / 19
U-1/2-B	1.10 / 28.0	G 1/2 ISO	4.72 / 120.0	0.55 / 14	0.94 / 24
U-1/2-B-NPT	1.10 / 28.0	1/2 NPT	4.72 / 120.0	0.55 / 14	0.94 / 24
U-3/4-B	1.50 / 38.0	G 3/4 ISO	5.59 / 142.0	0.63 / 16	1.26 / 32
U-1-B	1.88 / 47.8	G1 ISO	7.06 / 179.4	0.59 / 15	1.42 / 36

Pressure Range		0 to 150 psi / 0 to 10 bar					
Temperature Range		-50°F to +158°F / -10°C to +70°C					
Order No Part No.	Туре	Thread	Noise level at 90 psi / 6 bar to atmosphere* dB (A)	Orifice size at inlet in / mm	C _V factor** C _V / I/min	Weight Ib / kg	Materials
6841	U-1/8-B	G 1/8 ISO	74	0.21 / 5.3	1.45 / 1450	0.018 / 0.008	Housing: Diecast
12638	U-1/8-B-NPT	1/8 NPT	74	0.21 / 5.3	1.45 / 1450	0.018 / 0.008	Aluminum
6842	U-1/4-B	G 1/4 ISO	78	0.30 / 7.5	3.00 / 3000	0.037 / 0.017	Insert: Plastic
12639	U-1/4-B-NPT	1/4 NPT	78	0.30 / 7.5	3.00 / 3000	0.037 / 0.017	
6843	U-3/8-B	G 3/8 ISO	80	0.35 / 9.0	4.50 / 4500	0.082 / 0.037	
12740	U-3/8-B-NPT	3/8 NPT	80	0.35 / 9.0	4.50 / 4500	0.082 / 0.037	
6844	U-1/2-B	G 1/2 ISO	80	0.55 / 14.0	6.00 / 6500	0.165 / 0.075	
12741	U-1/2-B-NPT	1/2 NPT	80	0.55 / 14.0	6.00 / 6500	0.165 / 0.075	
6845	U-3/4-B	G 3/4 ISO	81	0.67 / 17.0	11.0 / 11000	0.265 / 0.120	
151990	U-1-B	G 1 ISO	82	0.93 / 23.5	17.3 / 17300	0.514 / 0.233	

^{*} Measured at a distance of 3 ft / 1 m

^{**} At 90 psi / 6 bar

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation ComponentsComplete custom engineered solutions



Custom Control CabinetsComprehensive engineering support and on-site services



Complete SystemsShipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



ElectromechanicalElectromechanical actuators, motors, controllers & drives



PneumaticsPneumatic linear and rotary actuators, valves, and air supply



PLC's and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125 Earth City, MO 63045

For ordering assistance, or to find your nearest Festo Distributor, **Call:** 1.800.99.FESTO **Fax:** 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,
Call: 1.866.GO.FESTO
Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation 395 Moreland Road P.O. Box 18023 Hauppauge, NY 11788 www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N Greenville, WI 54942

Boston

120 Presidential Way, Suite 330 Woburn, MA 01801

Chicago

1441 East Business Center Drive Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600 Lewisville, TX 75057

Detroit - Automotive Engineering Center 2601 Cambridge Court, Suite 320 Auburn Hills, MI 48326

New York

395 Moreland Road Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.

Av. Ceylán 3, Col. Tequesquinahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00

Fax: 011 52 [55] 53 21 66 65

Email: festo.mexico@mx.festo.com

www.festo.com/mx



Canada

Headquarters

Festo Inc. 5300 Explorer Drive

Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000

Fax: 1.905.624.9000 Email: info.ca@ca.festo.com

www.festo.com/ca



Festo Worldwide

Argentina Australia Australia Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela