

## Filter regulators MS-LFR, MS series


**FESTO**



# Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

| Type                                                                                                              |                                                                                     | Size |                                       |                                | Pressure regulation range |                    |                 |                 |                  |                  | Grade of filtration |   |   |   |   |  |
|-------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------|---------------------------------------|--------------------------------|---------------------------|--------------------|-----------------|-----------------|------------------|------------------|---------------------|---|---|---|---|--|
|                                                                                                                   |                                                                                     |      |                                       |                                | [bar]                     |                    |                 |                 |                  |                  | [µm]                |   |   |   |   |  |
|                                                                                                                   |                                                                                     |      |                                       |                                | 0.05<br>...<br>0.7        | 0.05<br>...<br>2.5 | 0.1<br>...<br>4 | 0.3<br>...<br>7 | 0.1<br>...<br>12 | 0.5<br>...<br>16 |                     |   |   |   |   |  |
| Code                                                                                                              |                                                                                     |      | Pneumatic<br>connection in<br>housing | Connecting plate               | AG...                     | D2                 | D4              | D5              | D6               | D7               | D8                  | A | B | C | E |  |
| Service units                                                                                                     |                                                                                     |      |                                       |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
| MSB-FRC                                                                                                           |    | 4    | G1/8, G1/4                            | G1/8, G1/4, G3/8               | –                         | –                  | –               | ■               | ■                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | ■               | ■                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 9    | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
| Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9) |                                                                                     |      |                                       |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
| MSB                                                                                                               |    | 4    | G1/4                                  | G1/8, G1/4, G3/8               | –                         | –                  | –               | ■               | ■                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/2                                  | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | ■               | ■                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 9    | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
| Individual devices                                                                                                |                                                                                     |      |                                       |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
| Filter regulators<br>MS-LFR                                                                                       |  | 4    | G1/8, G1/4                            | G1/8, G1/4, G3/8               | –                         | –                  | ■               | ■               | ■                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | ■               | ■               | ■                | ■                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 9    | G3/4, G1                              | G1/2, G3/4, G1, G1 1/4, G1 1/2 | –                         | –                  | ■               | ■               | ■                | ■                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     | G1, G1 1/4, G1 1/2, G2         | –                         | –                  | –               | ■               | ■                | ■                | –                   | – | ■ | ■ |   |  |
| Filters<br>MS-LF                                                                                                  |  | 4    | G1/8, G1/4                            | G1/8, G1/4, G3/8               | –                         | –                  | –               | –               | –                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | –               | –                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 9    | G3/4, G1                              | G1/2, G3/4, G1, G1 1/4, G1 1/2 | –                         | –                  | –               | –               | –                | –                | –                   | – | ■ | ■ |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     | G1, G1 1/4, G1 1/2, G2         | –                         | –                  | –               | –               | –                | –                | –                   | – | ■ | ■ |   |  |
| Fine and micro<br>filters<br>MS-LFM                                                                               |  | 4    | G1/8, G1/4                            | G1/8, G1/4, G3/8               | –                         | –                  | –               | –               | –                | –                | ■                   | ■ | – | – |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | –               | –                | –                | ■                   | ■ | – | – |   |  |
|                                                                                                                   |                                                                                     | 9    | G3/4, G1                              | G1/2, G3/4, G1, G1 1/4, G1 1/2 | –                         | –                  | –               | –               | –                | –                | ■                   | ■ | – | – |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     | G1, G1 1/4, G1 1/2, G2         | –                         | –                  | –               | –               | –                | –                | ■                   | ■ | – | – |   |  |
| Activated carbon<br>filters<br>MS-LFX                                                                             |  | 4    | G1/8, G1/4                            | G1/8, G1/4, G3/8               | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
|                                                                                                                   |                                                                                     | 9    | G3/4, G1                              | G1/2, G3/4, G1, G1 1/4, G1 1/2 | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     | G1, G1 1/4, G1 1/2, G2         | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
| Water separators<br>MS-LWS                                                                                        |  | 4    | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |
|                                                                                                                   |                                                                                     | 6    | G1/4, G3/8, G1/2                      | G1/4, G3/8, G1/2, G3/4         | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
|                                                                                                                   |                                                                                     | 9    | G3/4, G1                              | G1/2, G3/4, G1, G1 1/4, G1 1/2 | –                         | –                  | –               | –               | –                | –                | –                   | – | – | – |   |  |
|                                                                                                                   |                                                                                     | 12   | –                                     |                                |                           |                    |                 |                 |                  |                  |                     |   |   |   |   |  |

# Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

| Type                                      | Size | Bowl guard                           |            | Condensate drains |                |                 |                                       | Pressure indicator                   |                              |                                           |                                           |                 | Security                                          |                                  | Options  |                                   | → Page/<br>Internet |
|-------------------------------------------|------|--------------------------------------|------------|-------------------|----------------|-----------------|---------------------------------------|--------------------------------------|------------------------------|-------------------------------------------|-------------------------------------------|-----------------|---------------------------------------------------|----------------------------------|----------|-----------------------------------|---------------------|
|                                           |      | Plastic bowl with plastic bowl guard | Metal bowl | Manual rotary     | Semi-automatic | Fully automatic | External, fully automatic, electrical | Cover plate (without pressure gauge) | Integrated MS pressure gauge | Adapter plate for EN pressure gauge G 1/8 | Adapter plate for EN pressure gauge G 1/4 | Pressure sensor | Rotary knob with detent, lockable via accessories | Rotary knob with integrated lock | Silencer | Flow direction from right to left |                     |
| Code                                      |      | R                                    | U          | M                 | H              | V               | E...                                  | VS                                   | AG                           | A8                                        | A4                                        | AD...           | AS                                                | E11                              | S        | Z                                 |                     |
| <b>Service units</b>                      |      |                                      |            |                   |                |                 |                                       |                                      |                              |                                           |                                           |                 |                                                   |                                  |          |                                   |                     |
| <b>MSB-FRC</b>                            | 4    | ■                                    | –          | ■                 | –              | ■               | –                                     | –                                    | ■                            | –                                         | –                                         | –               | ■                                                 | –                                | –        | ■                                 | msb4                |
|                                           | 6    | ■                                    | ■          | ■                 | –              | ■               | –                                     | –                                    | ■                            | –                                         | –                                         | –               | ■                                                 | –                                | –        | ■                                 | msb6                |
|                                           | 9    | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                           | 12   | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |
| <b>Service unit combinations</b>          |      |                                      |            |                   |                |                 |                                       |                                      |                              |                                           |                                           |                 |                                                   |                                  |          |                                   |                     |
| <b>MSB</b>                                | 4    | ■                                    | ■          | ■                 | –              | ■               | –                                     | –                                    | ■                            | –                                         | –                                         | –               | ■                                                 | –                                | –        | ■                                 | msb4                |
|                                           | 6    | ■                                    | ■          | ■                 | –              | ■               | –                                     | –                                    | ■                            | –                                         | –                                         | –               | ■                                                 | –                                | –        | ■                                 | msb6                |
|                                           | 9    | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                           | 12   | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |
| <b>Individual devices</b>                 |      |                                      |            |                   |                |                 |                                       |                                      |                              |                                           |                                           |                 |                                                   |                                  |          |                                   |                     |
| Filter regulators<br><b>MS-LFR</b>        | 4    | ■                                    | ■          | ■                 | ■              | ■               | –                                     | ■                                    | ■                            | ■                                         | ■                                         | ■               | ■                                                 | ■                                | –        | ■                                 | 8                   |
|                                           | 6    | ■                                    | ■          | ■                 | ■              | ■               | ■                                     | ■                                    | ■                            | –                                         | ■                                         | ■               | ■                                                 | ■                                | –        | ■                                 | 8                   |
|                                           | 9    | –                                    | ■          | ■                 | ■              | ■               | ■                                     | ■                                    | ■                            | –                                         | ■                                         | ■               | ■                                                 | ■                                | –        | ■                                 | 24                  |
|                                           | 12   | –                                    | ■          | ■                 | –              | ■               | ■                                     | ■                                    | ■                            | –                                         | ■                                         | –               | ■                                                 | ■                                | –        | ■                                 | 36                  |
| Filters<br><b>MS-LF</b>                   | 4    | ■                                    | ■          | ■                 | ■              | ■               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms4-lf              |
|                                           | 6    | ■                                    | ■          | ■                 | ■              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms6-lf              |
|                                           | 9    | –                                    | ■          | ■                 | ■              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms9-lf              |
|                                           | 12   | –                                    | ■          | ■                 | –              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms12-lf             |
| Fine and micro filters<br><b>MS-LFM</b>   | 4    | ■                                    | ■          | ■                 | ■              | ■               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms4-lfm             |
|                                           | 6    | ■                                    | ■          | ■                 | ■              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms6-lfm             |
|                                           | 9    | –                                    | ■          | ■                 | ■              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms9-lfm             |
|                                           | 12   | –                                    | ■          | ■                 | –              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms12-lfm            |
| Activated carbon filters<br><b>MS-LFX</b> | 4    | ■                                    | ■          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms4-lfx             |
|                                           | 6    | ■                                    | ■          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms6-lfx             |
|                                           | 9    | –                                    | ■          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms9-lfx             |
|                                           | 12   | –                                    | ■          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms12-lfx            |
| Water separators<br><b>MS-LWS</b>         | 4    | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                           | 6    | –                                    | ■          | –                 | –              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms6-lws             |
|                                           | 9    | –                                    | ■          | –                 | –              | ■               | ■                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | ■                                 | ms9-lws             |
|                                           | 12   | –                                    | –          | –                 | –              | –               | –                                     | –                                    | –                            | –                                         | –                                         | –               | –                                                 | –                                | –        | –                                 | –                   |

# Filter regulators MS-LFR, MS series

Product range overview – MS series service units

**FESTO**

| Type                                            | Size                                                                                | Pneumatic connection in housing | Connecting plate | Pressure regulation range [bar] |                    |                 |                 |                  |                  | Supply voltage                           |                                           |                                           |                                           |   |
|-------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------|------------------|---------------------------------|--------------------|-----------------|-----------------|------------------|------------------|------------------------------------------|-------------------------------------------|-------------------------------------------|-------------------------------------------|---|
|                                                 |                                                                                     |                                 |                  | 0.05<br>...<br>0.7              | 0.05<br>...<br>2.5 | 0.1<br>...<br>4 | 0.3<br>...<br>7 | 0.1<br>...<br>12 | 0.5<br>...<br>16 | 24 V DC, connection pattern to EN 175301 | 24 V DC, connection pattern M12 to DESINA | 110 V AC, connection pattern to EN 175301 | 230 V AC, connection pattern to EN 175301 |   |
| Code                                            |                                                                                     |                                 | AG...            | D2                              | D4                 | D5              | D6              | D7               | D8               | V24                                      | V24P                                      | V110                                      | V230                                      |   |
| <b>Individual devices</b>                       |                                                                                     |                                 |                  |                                 |                    |                 |                 |                  |                  |                                          |                                           |                                           |                                           |   |
| Pressure regulators<br><b>MS-LR</b>             |    | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | G3/4, G1         | G1/2, G3/4, G1, G1 1/4, G1 1/2  | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
| Pressure regulators<br><b>MS-LRB</b>            |    | 4                               | G1/4             | G1/8, G1/4, G3/8                | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/2             | G1/4, G3/8, G1/2, G3/4          | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Precision pressure regulators<br><b>MS-LRP</b>  |   | 4                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | ■                  | ■               | ■               | –                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Precision pressure regulators<br><b>MS-LRPB</b> |  | 4                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/2             | G1/4, G3/8, G1/2, G3/4          | ■                  | ■               | ■               | –                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Electrical pressure regulators<br><b>MS-LRE</b> |  | 4                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | ■               | ■                | ■                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Lubricators<br><b>MS-LOE</b>                    |  | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | G3/4, G1         | G1/2, G3/4, G1, G1 1/4, G1 1/2  | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Electrical on-off valves<br><b>MS-EM(1)</b>     |  | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | G3/4, G1         | G1/2, G3/4, G1, G1 1/4, G1 1/2  | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Electrical on-off valves<br><b>MS-EE</b>        |  | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | –               | –                | –                | ■                                        | –                                         | ■                                         | ■                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | ■                                        | –                                         | ■                                         | ■                                         | – |
|                                                 |                                                                                     | 9                               | G3/4, G1         | G1/2, G3/4, G1, G1 1/4, G1 1/2  | –                  | –               | –               | –                | –                | ■                                        | ■                                         | ■                                         | ■                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | –                | –                | ■                                        | ■                                         | ■                                         | ■                                         | – |
| Electrical soft-start valves<br><b>MS-DL</b>    |  | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
| Electrical soft-start valves<br><b>MS-DE</b>    |  | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –                  | –               | –               | –                | –                | ■                                        | –                                         | ■                                         | ■                                         | – |
|                                                 |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | ■                                        | –                                         | ■                                         | ■                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –                  | –               | –               | –                | –                | ■                                        | ■                                         | ■                                         | ■                                         | – |
| Soft start and exhaust valves<br><b>MS-SV</b>   |  | 4                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 6                               | G1/2             | G1/4, G3/8, G1/2, G3/4          | –                  | –               | –               | –                | –                | ■                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 9                               | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |
|                                                 |                                                                                     | 12                              | –                | –                               | –                  | –               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         | – |

# Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

| Type                                            | Size | Bowl guard                           |            | Pressure indicator                   |                              |                                          |                                          |                 | Security                                          |                                  | Options  |                                   | → Page/<br>Internet |
|-------------------------------------------------|------|--------------------------------------|------------|--------------------------------------|------------------------------|------------------------------------------|------------------------------------------|-----------------|---------------------------------------------------|----------------------------------|----------|-----------------------------------|---------------------|
|                                                 |      | Plastic bowl with plastic bowl guard | Metal bowl | Cover plate (without pressure gauge) | Integrated MS pressure gauge | Adapter plate for EN pressure gauge G1/8 | Adapter plate for EN pressure gauge G1/4 | Pressure sensor | Rotary knob with detent, lockable via accessories | Rotary knob with integrated lock | Silencer | Flow direction from right to left |                     |
| Code                                            |      | R                                    | U          | VS                                   | AG                           | A8                                       | A4                                       | AD...           | AS                                                | E11                              | S        | Z                                 |                     |
| <b>Individual devices</b>                       |      |                                      |            |                                      |                              |                                          |                                          |                 |                                                   |                                  |          |                                   |                     |
| Pressure regulators<br><b>MS-LR</b>             | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms4-lr              |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms6-lr              |
|                                                 | 9    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms9-lr              |
|                                                 | 12   | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | ■                                                 | ■                                | –        | ■                                 | ms12-lr             |
| Pressure regulators<br><b>MS-LRB</b>            | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms4-lrb             |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms6-lrb             |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
| Precision pressure regulators<br><b>MS-LRP</b>  | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 6    | –                                    | –          | ■                                    | –                            | ■                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms6-lrp             |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
| Precision pressure regulators<br><b>MS-LRPB</b> | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 6    | –                                    | –          | ■                                    | –                            | ■                                        | ■                                        | ■               | ■                                                 | ■                                | –        | ■                                 | ms6-lrpb            |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
| Electrical pressure regulators<br><b>MS-LRE</b> | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | –        | ■                                 | ms6-lre             |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 |      |                                      |            |                                      |                              |                                          |                                          |                 |                                                   |                                  |          |                                   |                     |
| Lubricators<br><b>MS-LOE</b>                    | 4    | ■                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | ■                                 | ms4-loe             |
|                                                 | 6    | ■                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | ■                                 | ms6-loe             |
|                                                 | 9    | –                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | ■                                 | ms9-loe             |
|                                                 | 12   | –                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | ■                                 | ms12-loe            |
|                                                 |      |                                      |            |                                      |                              |                                          |                                          |                 |                                                   |                                  |          |                                   |                     |
| Electrical on-off valves<br><b>MS-EM(1)</b>     | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | –                                                 | –                                | ■        | ■                                 | ms4-em1             |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                                 | –                                | ■        | ■                                 | ms6-em1             |
|                                                 | 9    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | ■        | ■                                 | ms9-em              |
|                                                 | 12   | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | ■        | ■                                 | ms12-em             |
| Electrical on-off valves<br><b>MS-EE</b>        | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | –                                                 | –                                | ■        | ■                                 | ms4-ee              |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                                 | –                                | ■        | ■                                 | ms6-ee              |
|                                                 | 9    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | ■        | ■                                 | ms9-ee              |
|                                                 | 12   | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | ■        | ■                                 | ms12-ee             |
| Electrical soft-start valves<br><b>MS-DL</b>    | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | –                                                 | –                                | –        | ■                                 | ms4-dl              |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                                 | –                                | –        | ■                                 | ms6-dl              |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | –        | ■                                 | ms12-dl             |
| Electrical soft-start valves<br><b>MS-DE</b>    | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | –                                                 | –                                | –        | ■                                 | ms4-de              |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                                 | –                                | –        | ■                                 | ms6-de              |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | –               | –                                                 | –                                | –        | ■                                 | ms12-de             |
| Soft start and exhaust valves<br><b>MS-SV</b>   | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                                 | –                                | ■        | ■                                 | ms6-sv              |
|                                                 | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |
|                                                 | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                                 | –                                | –        | –                                 | –                   |

# Filter regulators MS-LFR, MS series

Product range overview – MS series service units

**FESTO**

| Type                                    | Size                                                                                | Pneumatic connection in housing | Connecting plate | Pressure regulation range [bar] |                 |                  |                  | Supply voltage                           |                                           |                                           |                                           |
|-----------------------------------------|-------------------------------------------------------------------------------------|---------------------------------|------------------|---------------------------------|-----------------|------------------|------------------|------------------------------------------|-------------------------------------------|-------------------------------------------|-------------------------------------------|
|                                         |                                                                                     |                                 |                  | 0.1<br>...<br>4                 | 0.3<br>...<br>7 | 0.1<br>...<br>12 | 0.5<br>...<br>16 | 24 V DC, connection pattern to EN 175301 | 24 V DC, connection pattern M12 to DESINA | 110 V AC, connection pattern to EN 175301 | 230 V AC, connection pattern to EN 175301 |
| Code                                    |                                                                                     |                                 | AG...            | D5                              | D6              | D7               | D8               | V24                                      | V24P                                      | V110                                      | V230                                      |
| <b>Individual devices</b>               |                                                                                     |                                 |                  |                                 |                 |                  |                  |                                          |                                           |                                           |                                           |
| Membrane air dryers<br><b>MS-LDM1</b>   |    | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 9                               | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 12                              | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
| Branching modules<br><b>MS-FRM</b>      |    | 4                               | G1/8, G1/4       | G1/8, G1/4, G3/8                | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 6                               | G1/4, G3/8, G1/2 | G1/4, G3/8, G1/2, G3/4          | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 9                               | G3/4, G1         | G1/2, G3/4, G1, G1 1/4, G1 1/2  | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 12                              | –                | G1, G1 1/4, G1 1/2, G2          | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
| Distributor blocks<br><b>MS-FRM-FRZ</b> |   | 4                               | G1/4             | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 6                               | G1/2             | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 9                               | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 12                              | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
| Flow sensors<br><b>SFAM</b>             |  | 4                               | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 6                               | G1/2             | G1/2                            | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 9                               | –                | G1, G1 1/2                      | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |
|                                         |                                                                                     | 12                              | –                | –                               | –               | –                | –                | –                                        | –                                         | –                                         | –                                         |

# Filter regulators MS-LFR, MS series


**FESTO**

Product range overview – MS series service units

| Type                                    | Size | Bowl guard                           |            | Pressure indicator                   |                              |                                          |                                          |                 | Switch output                                |                                             | Options  |                                   | → Page/<br>Internet |
|-----------------------------------------|------|--------------------------------------|------------|--------------------------------------|------------------------------|------------------------------------------|------------------------------------------|-----------------|----------------------------------------------|---------------------------------------------|----------|-----------------------------------|---------------------|
|                                         |      | Plastic bowl with plastic bowl guard | Metal bowl | Cover plate (without pressure gauge) | Integrated MS pressure gauge | Adapter plate for EN pressure gauge G1/8 | Adapter plate for EN pressure gauge G1/4 | Pressure sensor | 2x PNP or NPN, 1 analogue output 4 ... 20 mA | 2x PNP or NPN, 1 analogue output 0 ... 10 V | Silencer | Flow direction from right to left |                     |
| Code                                    |      | R                                    | U          | VS                                   | AG                           | A8                                       | A4                                       | AD...           | 2SA                                          | 2SV                                         | S        | Z/R                               |                     |
| <b>Individual devices</b>               |      |                                      |            |                                      |                              |                                          |                                          |                 |                                              |                                             |          |                                   |                     |
| Membrane air dryers<br><b>MS-LDM1</b>   | 4    | –                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | ■                                 | ms4-ldm1            |
|                                         | 6    | –                                    | ■          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | ■                                 | ms6-ldm1            |
|                                         | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | –                   |
|                                         | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | –                   |
| Branching modules<br><b>MS-FRM</b>      | 4    | –                                    | –          | ■                                    | ■                            | ■                                        | ■                                        | ■               | –                                            | –                                           | –        | ■                                 | ms4-frm             |
|                                         | 6    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                            | –                                           | –        | ■                                 | ms6-frm             |
|                                         | 9    | –                                    | –          | ■                                    | ■                            | –                                        | ■                                        | ■               | –                                            | –                                           | –        | ■                                 | ms9-frm             |
|                                         | 12   | –                                    | –          | ■                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | ms12-frm            |
| Distributor blocks<br><b>MS-FRM-FRZ</b> | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | ■                                 | ms4-frm             |
|                                         | 6    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | ■                                 | ms6-frm             |
|                                         | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | –                   |
|                                         | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | –                   |
| Flow sensors<br><b>SFAM</b>             | 4    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | ■                                            | ■                                           | –        | ■                                 | –                   |
|                                         | 6    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | ■                                            | ■                                           | –        | ■                                 | sfam-62             |
|                                         | 9    | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | ■                                            | ■                                           | –        | ■                                 | sfam-90             |
|                                         | 12   | –                                    | –          | –                                    | –                            | –                                        | –                                        | –               | –                                            | –                                           | –        | –                                 | –                   |

## Peripherals overview

### Filter regulator MS4/MS6-LFR



### Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

## Filter regulators MS4/MS6-LFR, MS series

Peripherals overview

**FESTO**

| Mounting attachments and accessories |                                                                     |                          |                       |                          |                       |                     |
|--------------------------------------|---------------------------------------------------------------------|--------------------------|-----------------------|--------------------------|-----------------------|---------------------|
|                                      |                                                                     | Individual device        |                       | Combination              |                       | ➔ Page/Internet     |
|                                      |                                                                     | Without connecting plate | With connecting plate | Without connecting plate | With connecting plate |                     |
| 1                                    | Cover cap<br>MS4/6-END                                              | ■                        | –                     | ■                        | –                     | ms4-end,<br>ms6-end |
| 2                                    | Connecting plate<br>MS4/6-AG...                                     | –                        | ■                     | –                        | ■                     | ms4-ag,<br>ms6-ag   |
| 3                                    | Module connector<br>MS4/6-MV                                        | –                        | ■                     | ■                        | ■                     | ms4-mv,<br>ms6-mv   |
| 4                                    | Mounting bracket<br>MS4/6-WB                                        | ■                        | ■                     | –                        | –                     | ms4-wb,<br>ms6-wb   |
| 5                                    | Mounting bracket<br>MS4-WBM                                         | ■                        | ■                     | –                        | –                     | ms4-wbm             |
| 6                                    | Mounting bracket<br>MS4/6-WR                                        | ■                        | ■                     | –                        | –                     | ms4-wr,<br>ms6-wr   |
| 7                                    | Hex nut<br>MS4/6-WRS                                                | ■                        | ■                     | ■                        | ■                     | ms4-wrs,<br>ms6-wrs |
| 8                                    | Cover plate<br>VS                                                   | ■                        | ■                     | ■                        | ■                     | 22                  |
| 9                                    | Adapter plate for EN pressure gauge 1/8/1/4<br>A8/A4                | ■                        | ■                     | ■                        | ■                     | 22                  |
| 10                                   | Pressure gauge<br>MA                                                | ■                        | ■                     | ■                        | ■                     | 47                  |
| 11                                   | Pressure sensor without display<br>AD7 ... AD10                     | ■                        | ■                     | ■                        | ■                     | 22                  |
| 12                                   | Connecting cable<br>NEBU-M8...-LE3                                  | ■                        | ■                     | ■                        | ■                     | 47                  |
| 13                                   | Pressure sensor with display<br>AD1 ... AD4                         | ■                        | ■                     | ■                        | ■                     | 22                  |
| 14                                   | Connecting cable<br>NEBU-M8...-LE3/NEBU-M12...-LE4                  | ■                        | ■                     | ■                        | ■                     | 47                  |
| 15                                   | Fully automatic condensate drain, electrically<br>actuated E2/E3/E4 | ■                        | ■                     | ■                        | ■                     | 22                  |
| 16                                   | Padlock<br>LRVS-D                                                   | ■                        | ■                     | ■                        | ■                     | 47                  |
| –                                    | Mounting bracket<br>MS4/6-WP/WPB/WPE/WPM                            | –                        | ■                     | ■                        | ■                     | ms4-wp,<br>ms6-wp   |

## Filter regulators MS4/MS6-LFR, MS series

FESTO

Type codes

|                                  |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
|----------------------------------|------------------------------------------------------------|----|---|---|-----|---|-----|---|----|---|---|---|---|---|----|
|                                  |                                                            | MS | 6 | - | LFR | - | 1/2 | - | D7 | - | E | R | M | - | AS |
| <b>Series</b>                    |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| MS                               | Standard service unit                                      |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Size</b>                      |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 4                                | Grid dimension 40 mm                                       |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 6                                | Grid dimension 62 mm                                       |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Service function</b>          |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| LFR                              | Filter regulator                                           |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Pneumatic connection</b>      |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| MS4                              |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 1/8                              | Thread G1/8                                                |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 1/4                              | Thread G1/4                                                |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| MS6                              |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 1/4                              | Thread G1/4                                                |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 3/8                              | Thread G3/8                                                |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| 1/2                              | Thread G1/2                                                |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Pressure regulation range</b> |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| D6                               | Pressure regulation range 0.3 ... 7 bar                    |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| D7                               | Pressure regulation range 0.5 ... 12 bar                   |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Grade of filtration</b>       |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| C                                | 5 µm                                                       |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| E                                | 40 µm                                                      |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Bowl guard</b>                |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| R                                | Plastic bowl guard                                         |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| U                                | Integrated as metal bowl                                   |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Condensate drain</b>          |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| M                                | Manual rotary                                              |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| V                                | Fully automatic                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| <b>Security</b>                  |                                                            |    |   |   |     |   |     |   |    |   |   |   |   |   |    |
| AS                               | Standard rotary knob with detent, lockable via accessories |    |   |   |     |   |     |   |    |   |   |   |   |   |    |

Additional variants can be ordered using the modular system → 22


- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Secondary venting
- Rotary knob
- Security
- Type of mounting
- Alternative flow direction

# Filter regulators MS4/MS6-LFR, MS series


FESTO

Technical data

Manual rotary condensate drain,  
with pressure gauge



Semi or fully automatic condensate  
drain, with pressure gauge



With this device, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.

Flow rate  
850 ... 7,200 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0.8 ... 20 bar  
[www.festo.com/en/Spare\\_parts\\_service](http://www.festo.com/en/Spare_parts_service)

Wearing parts kits  
→ 21



- Good regulation characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- Available with or without secondary venting
- High flow rate
- Directly-actuated diaphragm regulator
- Four pressure regulation ranges: 0.3 ... 4 bar, 0.3 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Regulator lock for protecting the values against adjustment
- Two pressure gauge connections for different fitting options
- Return flow option for exhausting from output 2 to output 1 already integrated
- Optional pressure sensor
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 46

| General technical data       |          |                                                                                                           |      |                                        |           |
|------------------------------|----------|-----------------------------------------------------------------------------------------------------------|------|----------------------------------------|-----------|
| Size                         |          | MS4                                                                                                       |      | MS6                                    |           |
| Pneumatic connection 1, 2    |          | G1/8                                                                                                      | G1/4 | G1/4                                   | G3/8 G1/2 |
| Constructional design        |          | Filter regulator with/without pressure display                                                            |      |                                        |           |
| Regulating function          |          | Output pressure constant, with return flow action, with/without secondary venting                         |      |                                        |           |
| Type of mounting             |          | Via accessories                                                                                           |      |                                        |           |
|                              |          | In-line installation                                                                                      |      |                                        |           |
|                              |          | Front panel mounting                                                                                      |      |                                        |           |
| Mounting position            |          | Vertical ±5°                                                                                              |      |                                        |           |
| Grade of filtration [µm]     |          | 5 (air quality class at the output 3.7.– to DIN ISO 8573-1)                                               |      |                                        |           |
|                              |          | 40 (air quality class at the output 5.7.– to DIN ISO 8573-1)                                              |      |                                        |           |
| Bowl guard                   |          | Plastic bowl guard                                                                                        |      |                                        |           |
|                              |          | Integrated as metal bowl                                                                                  |      |                                        |           |
| Condensate drain             |          | Manual rotary                                                                                             |      |                                        |           |
|                              |          | Semi-automatic                                                                                            |      |                                        |           |
|                              |          | Fully automatic                                                                                           |      |                                        |           |
|                              |          | –                                                                                                         |      | Fully automatic, electrically actuated |           |
| Regulator lock               |          | Rotary knob with detent                                                                                   |      |                                        |           |
|                              |          | Rotary knob with detent, lockable via accessories                                                         |      |                                        |           |
|                              |          | Rotary knob with integrated lock                                                                          |      |                                        |           |
| Pressure regulation range    | D5 [bar] | 0.3 ... 4                                                                                                 |      |                                        |           |
|                              | D6 [bar] | 0.3 ... 7                                                                                                 |      |                                        |           |
|                              | D7 [bar] | 0.5 ... 12 (0.5 ... 10 with pressure sensor variant AD...)                                                |      |                                        |           |
|                              | D8 [bar] | –                                                                                                         |      | 0.5 ... 16                             |           |
| Max. hysteresis [bar]        |          | 0.25                                                                                                      |      |                                        |           |
| Pressure display             |          | Via pressure sensor for displaying output pressure via LCD display and electrical output                  |      |                                        |           |
|                              |          | Via pressure sensor for displaying output pressure via operational status indicator and electrical output |      |                                        |           |
|                              |          | Via pressure gauge for displaying output pressure                                                         |      |                                        |           |
| Max. condensate volume [cm³] |          | 19 (with plastic bowl guard)                                                                              |      | 38                                     |           |
|                              |          | 25 (with metal bowl)                                                                                      |      |                                        |           |

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS4/MS6-LFR, MS series

FESTO

Technical data

| Standard nominal flow rate $q_{nN}^{1)}$ [l/min] |                 |                     |                     |                     |                     |                     |
|--------------------------------------------------|-----------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| Size                                             | MS4             |                     |                     | MS6                 |                     |                     |
| Pneumatic connection                             | G $\frac{1}{8}$ | G $\frac{1}{4}$     |                     | G $\frac{1}{4}$     | G $\frac{3}{8}$     | G $\frac{1}{2}$     |
| D5 – Pressure regulation range 0.3 ... 4 bar     |                 |                     |                     |                     |                     |                     |
| Grade of filtration                              | 5 $\mu$ m       | 900 <sup>2)</sup>   | 1,800 <sup>2)</sup> | 2,000 <sup>2)</sup> | 5,500 <sup>2)</sup> | 6,900 <sup>2)</sup> |
|                                                  | 40 $\mu$ m      | 1,100 <sup>2)</sup> | 1,900 <sup>2)</sup> | 2,200 <sup>2)</sup> | 6,000 <sup>2)</sup> | 7,200 <sup>2)</sup> |
| D6 – Pressure regulation range 0.3 ... 7 bar     |                 |                     |                     |                     |                     |                     |
| Grade of filtration                              | 5 $\mu$ m       | 900                 | 1,500               | 2,700               | 5,000               | 5,600               |
|                                                  | 40 $\mu$ m      | 1,000               | 1,700               | 2,800               | 5,700               | 6,200               |
| D7 – Pressure regulation range 0.5 ... 12 bar    |                 |                     |                     |                     |                     |                     |
| Grade of filtration                              | 5 $\mu$ m       | 850                 | 1,200               | 2,200               | 3,500               | 4,000               |
|                                                  | 40 $\mu$ m      | 900                 | 1,500               | 2,500               | 4,000               | 4,500               |
| D8 – Pressure regulation range 0.5 ... 16 bar    |                 |                     |                     |                     |                     |                     |
| Grade of filtration                              | 5 $\mu$ m       | –                   | –                   | 2,000               | 3,300               | 3,800               |
|                                                  | 40 $\mu$ m      | –                   | –                   | 2,300               | 3,500               | 4,000               |

1) Measured at  $p_1 = 10$  bar and  $p_2 = 6$  bar,  $\Delta p = 1$  bar

2) Measured at  $p_1 = 10$  bar and  $p_2 = 3$  bar,  $\Delta p = 1$  bar

| Operating and environmental conditions              |                                                                                               |            |                |            |                 |          |                                           |
|-----------------------------------------------------|-----------------------------------------------------------------------------------------------|------------|----------------|------------|-----------------|----------|-------------------------------------------|
| Condensate drain                                    | Manual rotary                                                                                 |            | Semi-automatic |            | Fully automatic |          | Fully automatic,<br>electrically actuated |
|                                                     | M                                                                                             |            | H              |            | V               |          | E2/E3/E4                                  |
| Size                                                | MS4                                                                                           | MS6        | MS4            | MS6        | MS4             | MS6      | MS6                                       |
| Supply pressure [bar]                               | 0.8 ... 14                                                                                    | 0.8 ... 20 | 1.5 ... 12     | 1.5 ... 12 | 2 ... 12        | 2 ... 12 | 0.8 ... 16                                |
| Operating medium                                    | Filtered compressed air or inert gases, lubricated or unlubricated, grade of filtration 40 µm |            |                |            |                 |          |                                           |
| Ambient temperature [°C]                            | −10 ... +60                                                                                   |            | +5 ... +60     |            | +5 ... +60      |          | +1 ... +60                                |
| Ambient temperature with<br>pressure sensor AD...   | 0 ... +50                                                                                     |            | +5 ... +50     |            | +5 ... +50      |          | +1 ... +50                                |
| Temperature of medium [°C]                          | −10 ... +60                                                                                   |            | +5 ... +60     |            | +5 ... +60      |          | +1 ... +60                                |
| Temperature of medium with<br>pressure sensor AD... | 0 ... +50                                                                                     |            | +5 ... +50     |            | +5 ... +50      |          | +1 ... +50                                |
| Storage temperature [°C]                            | −10 ... +60                                                                                   |            | −10 ... +60    |            | −10 ... +60     |          | +1 ... +60                                |
| Corrosion resistance class CRC <sup>1)</sup>        | 2                                                                                             |            |                |            |                 |          |                                           |

1) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

## Filter regulators MS4/MS6-LFR, MS series


Technical data

**FESTO**

| Weight [g]                                                                                              |                             |                          |                             |                          |
|---------------------------------------------------------------------------------------------------------|-----------------------------|--------------------------|-----------------------------|--------------------------|
| Size                                                                                                    | MS4                         |                          | MS6                         |                          |
| Rotary knob                                                                                             | Without integrated lock E11 | With integrated lock E11 | Without integrated lock E11 | With integrated lock E11 |
| Filter regulator with plastic bowl guard R                                                              | 275                         | 400                      | 875                         | 1,145                    |
| Filter regulator with metal bowl U                                                                      | 475                         | 600                      | 1,087                       | 1,627                    |
| Filter regulator with metal bowl U and fully automatic condensate drain, electrically actuated E2/E3/E4 | –                           | –                        | 1,800                       | 2,070                    |

### Materials

Sectional view



| Filter regulator  |                                      |                                                  |
|-------------------|--------------------------------------|--------------------------------------------------|
| [1]               | Housing                              | Die-cast aluminium                               |
| [2]               | Rotary knob                          | PA/POM                                           |
|                   | Rotary knob with integrated lock E11 | Aluminium                                        |
| [3]               | Plastic bowl guard                   | PC                                               |
| [4]               | Metal bowl                           | Wrought aluminium alloy, die-cast aluminium      |
|                   | Inspection window                    | PA                                               |
| [5]               | Filter element                       | PE                                               |
| [6]               | Spin disc                            | POM                                              |
| [7]               | Filter holder                        | POM                                              |
| [8]               | Separating plate                     | POM                                              |
| [9]               | Stabilising disc                     | POM                                              |
| [10]              | Diaphragm                            | NBR                                              |
| [11]              | Spring                               | Steel                                            |
| –                 | Seals                                | NBR                                              |
| Note on materials |                                      | RoHS-compliant (not with variant E2, E3 or E4)   |
|                   |                                      | Free of copper and PTFE only with cover plate VS |

# Filter regulators MS4/MS6-LFR, MS series

Technical data

FESTO

## Standard flow rate $q_n$ as a function of output pressure $p_2$



Pressure regulation range D6 or D7

Grade of filtration 5  $\mu\text{m}$

Grade of filtration 40  $\mu\text{m}$



MS4-LFR-1/8

Primary pressure  $p_1 = 10$  bar



MS4-LFR-1/4

Primary pressure  $p_1 = 10$  bar



# Filter regulators MS4/MS6-LFR, MS series

FESTO

Technical data

## Standard flow rate $q_n$ as a function of output pressure $p_2$



Pressure regulation range D6 or D7

Grade of filtration 5  $\mu\text{m}$

Grade of filtration 40  $\mu\text{m}$



MS6-LFR-1/4

Primary pressure  $p_1 = 10$  bar





MS6-LFR-3/8

Primary pressure  $p_1 = 10$  bar



MS6-LFR-1/2

Primary pressure  $p_1 = 10$  bar



# Filter regulators MS4/MS6-LFR, MS series


Technical data

**FESTO**

## Dimensions – Standard

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated pressure gauge, display unit [bar], standard rotary knob with detent, manual rotary condensate drain



1 Installation dimensions

→ Flow direction

| Type        | B1 | B2 | B3             |                 | D1   | D2   | L1         |       | L2 | L3   | L4   | L5 | L6         |       | L7 |
|-------------|----|----|----------------|-----------------|------|------|------------|-------|----|------|------|----|------------|-------|----|
|             |    |    | Pressure gauge |                 |      |      | Bowl guard |       |    |      |      |    | Bowl guard |       |    |
|             |    |    | Standard scale | Red-green scale |      |      | Plastic    | Metal |    |      |      |    | Plastic    | Metal |    |
| MS4-LFR-1/8 | 40 | 21 | 57             | 58.5            | G1/8 | 37.2 | 140.6      | 158.2 | 27 | 51.1 | 58.5 | 25 | 17.7       | 17.7  | 2  |
| MS4-LFR-1/4 |    |    |                |                 | G1/4 |      |            |       |    |      |      |    |            |       |    |
| MS6-LFR-1/4 | 62 | 31 | 77             | 78.5            | G1/4 | 51   | 189        | 194.4 | 39 | 86   | 84   | 68 | 15.8       | 19    | 5  |
| MS6-LFR-3/8 |    |    |                |                 | G3/8 |      |            |       |    |      |      |    |            |       |    |
| MS6-LFR-1/2 |    |    |                |                 | G1/2 |      |            |       |    |      |      |    |            |       |    |

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS4/MS6-LFR, MS series

Technical data


**FESTO**

## Dimensions – Pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Cover plate VS

Adapter plate A8/A4 for EN pressure gauge 1/8/1/4, without pressure gauge



| Type               | B2 | B3   | D1   | D4   |
|--------------------|----|------|------|------|
| MS4-LFR-1/8-...-VS | 21 | 54   | G1/8 | –    |
| MS4-LFR-1/4-...-VS |    |      | G1/4 |      |
| MS4-LFR-1/8-...-A8 | 21 | 58.5 | G1/8 | G1/8 |
| MS4-LFR-1/4-...-A8 |    |      | G1/4 |      |
| MS4-LFR-1/8-...-A4 | 21 | 58.5 | G1/8 | G1/4 |
| MS4-LFR-1/4-...-A4 |    |      | G1/4 |      |
| MS6-LFR-1/4-...-VS | 31 | 76   | G1/4 | –    |
| MS6-LFR-3/8-...-VS |    |      | G3/8 |      |
| MS6-LFR-1/2-...-VS |    |      | G1/2 |      |
| MS6-LFR-1/4-...-A4 | 31 | 78.5 | G1/4 | G1/4 |
| MS6-LFR-3/8-...-A4 |    |      | G3/8 |      |
| MS6-LFR-1/2-...-A4 |    |      | G1/2 |      |

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS4/MS6-LFR, MS series

Technical data


**FESTO**

## Dimensions – Pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: [sde1](#)



Variant AD1:  
SDE1-D10-G2-MS-L-P1-M8 with  
3-pin plug M8x1, 1 switching  
output PNP


Variant AD2:  
SDE1-D10-G2-MS-L-N1-M8 with  
3-pin plug M8x1, 1 switching  
output NPN

Variant AD3:  
SDE1-D10-G2-MS-L-PI-M12 with  
4-pin plug M12x1, 1 switching  
output PNP and 4 ... 20 mA  
analogue

Variant AD4:  
SDE1-D10-G2-MS-L-NI-M12 with  
4-pin plug M12x1, 1 switching  
output NPN and 4 ... 20 mA  
analogue

Pressure sensor without LCD display (operational status indicator only) AD7 ... AD10

Technical data → Internet: [sde5](#)



Variant AD7:  
SDE5-D10-O-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/O contact

Variant AD8:  
SDE5-D10-C-...-P-M8 with 3-pin  
plug M8x1, threshold value  
comparator, 1 switching output PNP,  
N/C contact

Variant AD9:  
SDE5-D10-O3-...-P-M8 with 3-pin  
plug M8x1, window comparator,  
1 switching output PNP, N/O contact

Variant AD10:  
SDE5-D10-C3-...-P-M8 with 3-pin  
plug M8x1, window comparator,  
1 switching output PNP, N/C contact

| Type                             | B2 | B3   | D1   | D6    | L5   | L6   |
|----------------------------------|----|------|------|-------|------|------|
| MS4-LFR-1/8-...-AD1/AD2          | 21 | 82.6 | G1/8 | M8x1  | 35.1 | 46.7 |
| MS4-LFR-1/4-...-AD1/AD2          |    |      | G1/4 |       |      |      |
| MS4-LFR-1/8-...-AD3/AD4          | 21 | 82.6 | G1/8 | M12x1 | 35.1 | 55.8 |
| MS4-LFR-1/4-...-AD3/AD4          |    |      | G1/4 |       |      |      |
| MS4-LFR-1/8-...-AD7/AD8/AD9/AD10 | 21 | 59.1 | G1/8 | M8x1  | -    | -    |
| MS4-LFR-1/4-...-AD7/AD8/AD9/AD10 |    |      | G1/4 |       |      |      |
|                                  |    |      |      |       |      |      |
| MS6-LFR-1/4-...-AD1/AD2          | 31 | 103  | G1/4 | M8x1  | 35.1 | 46.7 |
| MS6-LFR-3/8-...-AD1/AD2          |    |      | G3/8 |       |      |      |
| MS6-LFR-1/2-...-AD1/AD2          |    |      | G1/2 |       |      |      |
| MS6-LFR-1/4-...-AD3/AD4          | 31 | 103  | G1/4 | M12x1 | 35.1 | 55.8 |
| MS6-LFR-3/8-...-AD3/AD4          |    |      | G3/8 |       |      |      |
| MS6-LFR-1/2-...-AD3/AD4          |    |      | G1/2 |       |      |      |
| MS6-LFR-1/4-...-AD7/AD8/AD9/AD10 | 31 | 79   | G1/4 | M8x1  | -    | -    |
| MS6-LFR-3/8-...-AD7/AD8/AD9/AD10 |    |      | G3/8 |       |      |      |
| MS6-LFR-1/2-...-AD7/AD8/AD9/AD10 |    |      | G1/2 |       |      |      |

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS4/MS6-LFR, MS series

Technical data

**FESTO**

## Dimensions – Rotary knob


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

For installation into control panel

Standard rotary knob with detent


Standard rotary knob with detent,  
lockable via accessories AS

Rotary knob with integrated lock  
E11



Long rotary knob with detent LD

Long rotary knob with detent,  
lockable via accessories LD-AS



| Type              | B4   | B5   | D2   | D3<br>+1 | L3    | L8 | L9 | L10   |
|-------------------|------|------|------|----------|-------|----|----|-------|
| MS4-LFR-...       | –    | –    | 37.2 | 30       | 51.1  | 13 | 6  | –     |
| MS4-LFR-...-AS    | 48.3 | 29.7 |      |          | 60.2  |    |    |       |
| MS4-LFR-...-E11   | –    | –    |      |          | 76    |    |    |       |
| MS4-LFR-...-LD    | –    | –    | 37.2 | –        | 51.1  | –  | –  | 76.8  |
| MS4-LFR-...-LD-AS | 48.3 | 29.7 |      |          | 60.2  |    |    | 85.7  |
| MS6-LFR-...       | –    | –    | 51   | 44       | 86    | 22 | 14 | –     |
| MS6-LFR-...-AS    | 64.4 | 39   |      |          | 95.5  |    |    |       |
| MS6-LFR-...-E11   | –    | –    |      |          | 112.1 |    |    |       |
| MS6-LFR-...-LD    | –    | –    | 51   | –        | 86    | –  | –  | 139   |
| MS6-LFR-...-LD-AS | 64.4 | 39   |      |          | 95.5  |    |    | 148.5 |



## Filter regulators MS4/MS6-LFR, MS series

**FESTO**

Technical data

| Ordering data                                                                                                                                      |                  |            |                          |                     |                           |                     |
|----------------------------------------------------------------------------------------------------------------------------------------------------|------------------|------------|--------------------------|---------------------|---------------------------|---------------------|
| Pressure regulation range 0.3 ... 7 bar, integrated pressure gauge, display unit [bar], standard rotary knob with detent, lockable via accessories |                  |            |                          |                     |                           |                     |
| Size                                                                                                                                               | Condensate drain | Connection | Grade of filtration 5 µm |                     | Grade of filtration 40 µm |                     |
|                                                                                                                                                    |                  |            | Part No.                 | Type                | Part No.                  | Type                |
| Plastic bowl guard                                                                                                                                 |                  |            |                          |                     |                           |                     |
| MS4                                                                                                                                                | Manual rotary    | G½         | 529160                   | MS4-LFR-½-D6-CRM-AS | 529164                    | MS4-LFR-½-D6-ERM-AS |
|                                                                                                                                                    |                  | G¼         | 529144                   | MS4-LFR-¼-D6-CRM-AS | 529148                    | MS4-LFR-¼-D6-ERM-AS |
|                                                                                                                                                    | Fully automatic  | G½         | 529162                   | MS4-LFR-½-D6-CRV-AS | 529166                    | MS4-LFR-½-D6-ERV-AS |
|                                                                                                                                                    |                  | G¼         | 529146                   | MS4-LFR-¼-D6-CRV-AS | 529150                    | MS4-LFR-¼-D6-ERV-AS |
| MS6                                                                                                                                                | Manual rotary    | G¼         | 529196                   | MS6-LFR-¼-D6-CRM-AS | 529200                    | MS6-LFR-¼-D6-ERM-AS |
|                                                                                                                                                    |                  | G¾         | 529216                   | MS6-LFR-¾-D6-CRM-AS | 529220                    | MS6-LFR-¾-D6-ERM-AS |
|                                                                                                                                                    |                  | G½         | 529176                   | MS6-LFR-½-D6-CRM-AS | 529180                    | MS6-LFR-½-D6-ERM-AS |
|                                                                                                                                                    | Fully automatic  | G¼         | 529198                   | MS6-LFR-¼-D6-CRV-AS | 529202                    | MS6-LFR-¼-D6-ERV-AS |
|                                                                                                                                                    |                  | G¾         | 529218                   | MS6-LFR-¾-D6-CRV-AS | 529222                    | MS6-LFR-¾-D6-ERV-AS |
|                                                                                                                                                    |                  | G½         | 529178                   | MS6-LFR-½-D6-CRV-AS | 529182                    | MS6-LFR-½-D6-ERV-AS |
|                                                                                                                                                    |                  |            |                          |                     |                           |                     |
|                                                                                                                                                    |                  |            |                          |                     |                           |                     |

| Ordering data                                                                                                                                       |                  |            |                          |                       |                           |                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|------------------|------------|--------------------------|-----------------------|---------------------------|-----------------------|
| Pressure regulation range 0.5 ... 12 bar, integrated pressure gauge, display unit [bar], standard rotary knob with detent, lockable via accessories |                  |            |                          |                       |                           |                       |
| Size                                                                                                                                                | Condensate drain | Connection | Grade of filtration 5 µm |                       | Grade of filtration 40 µm |                       |
|                                                                                                                                                     |                  |            | Part No.                 | Type                  | Part No.                  | Type                  |
| Plastic bowl guard                                                                                                                                  |                  |            |                          |                       |                           |                       |
| MS4                                                                                                                                                 | Manual rotary    | G1/8       | 529168                   | MS4-LFR-1/8-D7-CRM-AS | 529172                    | MS4-LFR-1/8-D7-ERM-AS |
|                                                                                                                                                     |                  | G1/4       | 529152                   | MS4-LFR-1/4-D7-CRM-AS | 529156                    | MS4-LFR-1/4-D7-ERM-AS |
|                                                                                                                                                     | Fully automatic  | G1/8       | 529170                   | MS4-LFR-1/8-D7-CRV-AS | 529174                    | MS4-LFR-1/8-D7-ERV-AS |
|                                                                                                                                                     |                  | G1/4       | 529154                   | MS4-LFR-1/4-D7-CRV-AS | 529158                    | MS4-LFR-1/4-D7-ERV-AS |
| MS6                                                                                                                                                 | Manual rotary    | G1/4       | 529204                   | MS6-LFR-1/4-D7-CRM-AS | 529208                    | MS6-LFR-1/4-D7-ERM-AS |
|                                                                                                                                                     |                  | G3/8       | 529224                   | MS6-LFR-3/8-D7-CRM-AS | 529228                    | MS6-LFR-3/8-D7-ERM-AS |
|                                                                                                                                                     |                  | G1/2       | 529184                   | MS6-LFR-1/2-D7-CRM-AS | 529188                    | MS6-LFR-1/2-D7-ERM-AS |
|                                                                                                                                                     | Fully automatic  | G1/4       | 529206                   | MS6-LFR-1/4-D7-CRV-AS | 529210                    | MS6-LFR-1/4-D7-ERV-AS |
|                                                                                                                                                     |                  | G3/8       | 529226                   | MS6-LFR-3/8-D7-CRV-AS | 529230                    | MS6-LFR-3/8-D7-ERV-AS |
|                                                                                                                                                     |                  | G1/2       | 529186                   | MS6-LFR-1/2-D7-CRV-AS | 529190                    | MS6-LFR-1/2-D7-ERV-AS |
|                                                                                                                                                     |                  |            |                          |                       |                           |                       |
|                                                                                                                                                     |                  |            |                          |                       |                           |                       |
| Integrated as metal bowl                                                                                                                            |                  |            |                          |                       |                           |                       |
| MS4                                                                                                                                                 | Manual rotary    | G1/8       | 535702                   | MS4-LFR-1/8-D7-CUM-AS | 535708                    | MS4-LFR-1/8-D7-EUM-AS |
|                                                                                                                                                     |                  | G1/4       | 535718                   | MS4-LFR-1/4-D7-CUM-AS | 535724                    | MS4-LFR-1/4-D7-EUM-AS |
|                                                                                                                                                     | Fully automatic  | G1/8       | 535704                   | MS4-LFR-1/8-D7-CUV-AS | 535706                    | MS4-LFR-1/8-D7-EUV-AS |
|                                                                                                                                                     |                  | G1/4       | 535720                   | MS4-LFR-1/4-D7-CUV-AS | 535722                    | MS4-LFR-1/4-D7-EUV-AS |
| MS6                                                                                                                                                 | Manual rotary    | G1/4       | 530342                   | MS6-LFR-1/4-D7-CUM-AS | 529212                    | MS6-LFR-1/4-D7-EUM-AS |
|                                                                                                                                                     |                  | G3/8       | 530346                   | MS6-LFR-3/8-D7-CUM-AS | 529232                    | MS6-LFR-3/8-D7-EUM-AS |
|                                                                                                                                                     |                  | G1/2       | 530338                   | MS6-LFR-1/2-D7-CUM-AS | 529192                    | MS6-LFR-1/2-D7-EUM-AS |
|                                                                                                                                                     | Fully automatic  | G1/4       | 530344                   | MS6-LFR-1/4-D7-CUV-AS | 529214                    | MS6-LFR-1/4-D7-EUV-AS |
|                                                                                                                                                     |                  | G3/8       | 530348                   | MS6-LFR-3/8-D7-CUV-AS | 529234                    | MS6-LFR-3/8-D7-EUV-AS |
|                                                                                                                                                     |                  | G1/2       | 530340                   | MS6-LFR-1/2-D7-CUV-AS | 529194                    | MS6-LFR-1/2-D7-EUV-AS |
|                                                                                                                                                     |                  |            |                          |                       |                           |                       |

| Ordering data – Wearing parts kits |          |         |
|------------------------------------|----------|---------|
| Size                               | Part No. | Type    |
| MS4                                | 673647   | MS4-LFR |
| MS6                                | 673648   | MS6-LFR |

# Filter regulators MS4/MS6-LFR, MS series

Ordering data – Modular products

**FESTO**

| M Mandatory data → |        |         |          |                                                         |                           |                     |         |                                    |
|--------------------|--------|---------|----------|---------------------------------------------------------|---------------------------|---------------------|---------|------------------------------------|
| Module No.         | Series | Size    | Function | Connection size                                         | Pressure regulation range | Grade of filtration | Bowl    | Condensate drain                   |
| 526489<br>526490   | MS     | 4,<br>6 | LFR      | 1/8, 1/4, 3/8,<br>1/2,<br>AGA, AGB,<br>AGC, AGD,<br>AGE | D5,<br>D6,<br>D7,<br>D8   | E,<br>C             | R,<br>U | M,<br>H,<br>V,<br>E2,<br>E3,<br>E4 |
| Order example      |        |         |          |                                                         |                           |                     |         |                                    |
| 526489             | MS     | 4       | - LFR    | - AGA                                                   | - D6                      | - C                 | - R     | - M                                |

| Ordering table      |                                       |                                      |                       |             |      |            |
|---------------------|---------------------------------------|--------------------------------------|-----------------------|-------------|------|------------|
| Grid dimension [mm] |                                       | 40                                   | 62                    | Condition s | Code | Enter code |
| M                   | Module No.                            | 526489                               | 526490                |             |      |            |
|                     | Series                                | Standard                             |                       |             | MS   | MS         |
|                     | Size                                  | 4                                    | 6                     |             | ...  |            |
|                     | Function                              | Filter regulator                     |                       |             | -LFR | -LFR       |
|                     | Connection size                       | Thread G1/8                          | –                     |             | -1/8 |            |
|                     |                                       | Thread G1/4                          | Thread G1/4           |             | -1/4 |            |
|                     |                                       | –                                    | Thread G3/8           |             | -3/8 |            |
|                     |                                       | –                                    | Thread G1/2           |             | -1/2 |            |
|                     |                                       | Connecting plate G1/8                | –                     |             | -AGA |            |
|                     |                                       | Connecting plate G1/4                | Connecting plate G1/4 |             | -AGB |            |
|                     |                                       | Connecting plate G3/8                | Connecting plate G3/8 |             | -AGC |            |
|                     |                                       | –                                    | Connecting plate G1/2 |             | -AGD |            |
|                     |                                       | –                                    | Connecting plate G3/4 |             | -AGE |            |
|                     | Pressure regulation range             | 0.3 ... 4 bar                        |                       |             | -D5  |            |
|                     |                                       | 0.3 ... 7 bar                        |                       |             | -D6  |            |
|                     |                                       | 0.5 ... 12 bar                       |                       |             | -D7  |            |
|                     |                                       | –                                    | 0.5 ... 16 bar        |             | -D8  |            |
|                     | Grade of filtration                   | 40 µm                                |                       |             | -E   |            |
|                     |                                       | 5 µm                                 |                       |             | -C   |            |
|                     | Bowl                                  | Plastic bowl with plastic bowl guard |                       |             | -R   |            |
|                     |                                       | Metal bowl                           |                       |             | -U   |            |
|                     | Condensate drain                      | Manual                               |                       |             | -M   |            |
|                     |                                       | Semi-automatic (P1 max. 12 bar)      |                       | 1           | -H   |            |
|                     |                                       | Fully automatic (P1 max. 12 bar)     |                       | 1           | -V   |            |
|                     | External, fully automatic, electrical | –                                    | 110 V AC, terminals   | 2           | -E2  |            |
|                     |                                       | –                                    | 230 V AC, terminals   | 2           | -E3  |            |
|                     |                                       | –                                    | 24 V DC, terminals    | 2           | -E4  |            |

1 H, V Not with pressure regulation range D8

2 E2, E3, E4 Only with metal bowl U

Transfer order code

|  |    |  |   |     |   |  |   |  |   |  |   |  |   |  |
|--|----|--|---|-----|---|--|---|--|---|--|---|--|---|--|
|  | MS |  | - | LFR | - |  | - |  | - |  | - |  | - |  |
|--|----|--|---|-----|---|--|---|--|---|--|---|--|---|--|

# Filter regulators MS4/MS6-LFR, MS series

FESTO

Ordering data – Modular products

| 0 Options                                             |                                  |                   |             |            |                                  |                            |
|-------------------------------------------------------|----------------------------------|-------------------|-------------|------------|----------------------------------|----------------------------|
| Pressure gauge alternatives                           | Alternative pressure gauge scale | Secondary venting | Rotary knob | Security   | Type of mounting                 | Alternative flow direction |
| VS,<br>A8, A4,<br>RG,<br>AD1 ... AD4,<br>AD7 ... AD10 | PSI,<br>MPa                      | OS                | LD          | AS,<br>E11 | WR,<br>WP,<br>WPM,<br>WB,<br>WBM | Z                          |
| - A8                                                  | -                                | -                 | - LD        | - AS       | - WPM                            | - Z                        |

| Ordering table                |                                                                                                    |    |    |             |       |            |
|-------------------------------|----------------------------------------------------------------------------------------------------|----|----|-------------|-------|------------|
| Grid dimension                | [mm]                                                                                               | 40 | 62 | Condition s | Code  | Enter code |
| 0 Pressure gauge alternatives | Cover plate                                                                                        |    |    |             | -VS   |            |
|                               | Adapter plate for EN pressure gauge 1/8, without pressure gauge                                    |    |    |             | -A8   |            |
|                               | Adapter plate for EN pressure gauge 1/4, without pressure gauge                                    |    |    |             | -A4   |            |
|                               | Integrated pressure gauge, red-green scale                                                         |    |    | 4           | -RG   |            |
|                               | Pressure sensor with display, plug M8, 1 switching output PNP, 3-pin                               |    |    | 5           | -AD1  |            |
|                               | Pressure sensor with display, plug M8, 1 switching output NPN, 3-pin                               |    |    | 5           | -AD2  |            |
|                               | Pressure sensor with display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA |    |    | 5           | -AD3  |            |
|                               | Pressure sensor with display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA |    |    | 5           | -AD4  |            |
|                               | Pressure sensor without display, plug M8, threshold value comparator, PNP, N/O contact             |    |    | 5           | -AD7  |            |
|                               | Pressure sensor without display, plug M8, threshold value comparator, PNP, N/C contact             |    |    | 5           | -AD8  |            |
|                               | Pressure sensor without display, plug M8, window comparator, PNP, N/O contact                      |    |    | 5           | -AD9  |            |
|                               | Pressure sensor without display, plug M8, window comparator, PNP, N/C contact                      |    |    | 5           | -AD10 |            |
|                               | Alternative pressure gauge scale                                                                   |    |    |             |       |            |
|                               | psi                                                                                                |    |    | 6           | -PSI  |            |
|                               | MPa                                                                                                |    |    | 6           | -MPa  |            |
| Secondary venting             | Without secondary venting                                                                          |    |    |             | -OS   |            |
| Rotary knob                   | Long rotary knob                                                                                   |    |    | 7           | -LD   |            |
| Security                      | Lockable via accessories                                                                           |    |    |             | -AS   |            |
|                               | With integrated lock                                                                               |    |    |             | -E11  |            |
| Type of mounting              | Mounting bracket with knurled nut for regulator head                                               |    |    | 8           | -WR   |            |
|                               | Mounting bracket                                                                                   |    |    | 9           | -WP   |            |
|                               | Mounting bracket                                                                                   |    |    | 9           | -WPM  |            |
|                               | Mounting bracket                                                                                   |    |    |             | -WB   |            |
|                               | Mounting bracket                                                                                   |    |    |             | -WBM  |            |
| Alternative flow direction    | Flow direction from right to left                                                                  |    |    |             | -Z    |            |

4 RG Alternative pressure gauge scale PSI serves only as an auxiliary scale

5 AD1 ... AD4, AD7 ... AD10  
Measuring range max. 10 bar  
Not with pressure regulation range D8

6 PSI, MPa Not with pressure gauge alternatives VS, A8, A4, AD1 ... AD4, AD7 ... AD10

7 LD Not with security E11

8 WR Not with long rotary knob LD

9 WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE


Transfer order code

- - - - -

## Filter regulators MS9-LFR, MS series

Peripherals overview

**FESTO**



### Note

Additional accessories:

- Module connector for combinations with size MS6, MS9 or MS12 → Internet: rmv, armv

| Mounting attachments and accessories |                                                                      |                           |                                  |             |                 |
|--------------------------------------|----------------------------------------------------------------------|---------------------------|----------------------------------|-------------|-----------------|
|                                      |                                                                      | Individual unit           |                                  | Combination | ➔ Page/Internet |
|                                      |                                                                      | Without connecting thread | With connecting thread<br>¾ or 1 |             |                 |
| 1                                    | Connecting plate<br>MS9-AG...                                        | ■                         | –                                | ■           | ms9-ag          |
| 2                                    | Module connector<br>MS9-MV                                           | ■                         | –                                | ■           | ms9-mv          |
| 3                                    | Mounting bracket<br>MS9-WP                                           | ■                         | ■                                | ■           | ms9-wp          |
| 4                                    | Mounting bracket<br>MS9-WPB                                          | ■                         | ■                                | ■           | ms9-wp          |
| 5                                    | Mounting bracket<br>MS9-WPM                                          | ■                         | –                                | ■           | ms9-wp          |
| 6                                    | MS pressure gauge<br>AG                                              | ■                         | ■                                | ■           | 34              |
| 7                                    | Cover plate<br>VS                                                    | ■                         | ■                                | ■           | 34              |
| 8                                    | Pressure sensor without display<br>AD7 ... AD10                      | ■                         | ■                                | ■           | 34              |
| 9                                    | Connecting cable<br>NEBU-M8...-LE3                                   | ■                         | ■                                | ■           | 47              |
| 10                                   | Adapter plate for EN pressure gauge ¼<br>A4                          | ■                         | ■                                | ■           | 34              |
| 11                                   | Pressure gauge<br>MA                                                 | ■                         | ■                                | ■           | 47              |
| 12                                   | Padlock<br>LRVS-D                                                    | ■                         | ■                                | ■           | 47              |
| 13                                   | Condensate drain, fully automatic, electrically<br>actuated E2/E3/E4 | ■                         | ■                                | ■           | 34              |

## Filter regulators MS9-LFR, MS series

Type codes

|                                                 |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
|-------------------------------------------------|------------------------------------------------------------|----|---|---|-----|---|---|---|----|---|---|---|---|---|----|---|----|---|-----|---|----|
|                                                 |                                                            | MS | 9 | - | LFR | - | G | - | D6 | - | E | U | M | - | DI | - | AG | - | BAR | - | AS |
| <b>Series</b>                                   |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| MS                                              | Standard service unit                                      |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Size</b>                                     |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| 9                                               | Grid dimension 90 mm                                       |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Service function</b>                         |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| LFR                                             | Filter regulator                                           |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Connection size</b>                          |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| G                                               | Module without connecting thread, without connecting plate |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Pressure regulation range/operation mode</b> |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| D6                                              | 0.5 ... 7 bar, manually operated                           |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| D7                                              | 0.5 ... 12 bar, manually operated                          |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Grade of filtration</b>                      |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| C                                               | 5 µm                                                       |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| E                                               | 40 µm                                                      |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Bowl guard</b>                               |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| U                                               | Integrated as metal bowl                                   |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Condensate drain</b>                         |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| M                                               | Manual rotary                                              |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| V                                               | Fully automatic                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Regulator type</b>                           |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
|                                                 | Piloted                                                    |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| DI                                              | Directly actuated (only with pressure regulation range D6) |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Pressure gauge</b>                           |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| AG                                              | MS pressure gauge                                          |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Pressure gauge scale</b>                     |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| BAR                                             | Bar                                                        |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| <b>Security</b>                                 |                                                            |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |
| AS                                              | Rotary knob with detent, can be locked using accessories   |    |   |   |     |   |   |   |    |   |   |   |   |   |    |   |    |   |     |   |    |


Additional variants can be ordered using the modular system → 34

- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Secondary venting
- Security lock
- Type of mounting
- Alternative flow direction


## Filter regulators MS9-LFR, MS series

Technical data

Manual rotary condensate drain, with pressure gauge



Semi or fully automatic condensate drain, with pressure gauge



With this component, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.

Flow rate  
8,000 ... 23,000 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
1 ... 20 bar



- Good regulation characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- Piloted or directly actuated filter-diaphragm regulator
- High flow rates
- Available with or without secondary venting
- Four pressure regulation ranges: 0.5 ... 4 bar, 0.5 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Actuator lock to protect set values against adjustment
- Pressure gauge connection for different fitting options
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Optional pressure sensor
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 46

| General technical data                   |                   |                                                                                                               |    |                                           |                                 |
|------------------------------------------|-------------------|---------------------------------------------------------------------------------------------------------------|----|-------------------------------------------|---------------------------------|
| Pneumatic connection 1, 2                |                   | G3/4                                                                                                          | G1 | G1½ ... G1½ (with connecting plate AG...) | – (without connecting thread G) |
| Design                                   |                   | Piloted filter-diaphragm regulator                                                                            |    |                                           |                                 |
|                                          |                   | Directly actuated filter-diaphragm regulator                                                                  |    |                                           |                                 |
| Regulator type                           | Piloted           | Output pressure constant, with return flow action, with primary pressure compensation, with secondary venting |    |                                           |                                 |
|                                          | Directly actuated | Output pressure constant, with return flow action, with/without secondary venting                             |    |                                           |                                 |
| Type of mounting                         |                   | Via accessories                                                                                               |    |                                           |                                 |
|                                          |                   | In-line installation                                                                                          |    |                                           |                                 |
| Mounting position                        |                   | Vertical ±5°                                                                                                  |    |                                           |                                 |
| Grade of filtration                      | [µm]              | 5 (air quality class at the output 3.7.– to DIN ISO 8573-1)                                                   |    |                                           |                                 |
|                                          |                   | 40 (air quality class at the output 5.7.– to DIN ISO 8573-1)                                                  |    |                                           |                                 |
| Bowl guard                               |                   | Integrated as metal bowl                                                                                      |    |                                           |                                 |
| Condensate drain                         |                   | Manual rotary                                                                                                 |    |                                           |                                 |
|                                          |                   | Semi-automatic                                                                                                |    |                                           |                                 |
|                                          |                   | Fully automatic                                                                                               |    |                                           |                                 |
|                                          |                   | Fully automatic, electrically actuated                                                                        |    |                                           |                                 |
| Security                                 |                   | Rotary knob with detent                                                                                       |    |                                           |                                 |
|                                          |                   | Rotary knob with detent, can be locked using accessories                                                      |    |                                           |                                 |
|                                          |                   | Rotary knob with integrated lock                                                                              |    |                                           |                                 |
| Pressure regulation range/operation mode | D5 [bar]          | 0.5 ... 4, manually operated                                                                                  |    |                                           |                                 |
|                                          | D6 [bar]          | 0.5 ... 7, manually operated                                                                                  |    |                                           |                                 |
|                                          | D7 [bar]          | 0.5 ... 12, manually operated (0.5 ... 10 with pressure sensor variant AD...)                                 |    |                                           |                                 |
|                                          | D8 [bar]          | 0.5 ... 16, manually operated (0.5 ... 10 with pressure sensor variant AD...)                                 |    |                                           |                                 |
| Max. pressure hysteresis [bar]           |                   | 0.4                                                                                                           |    |                                           |                                 |
| Pressure display                         |                   | Via pressure sensor for displaying output pressure via operational status indicator and electrical output     |    |                                           |                                 |
|                                          |                   | Via pressure gauge for displaying output pressure                                                             |    |                                           |                                 |
|                                          |                   | Via pressure gauge with red/green scale for displaying output pressure                                        |    |                                           |                                 |
|                                          |                   | G¾ prepared                                                                                                   |    |                                           |                                 |
| Max. condensate volume [ml]              |                   | 220                                                                                                           |    |                                           |                                 |

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS9-LFR, MS series

Technical data

| Standard nominal flow rate $q_{nN}^{1)}$ [l/min] |                                    |                        |                        |                                                 |                        |
|--------------------------------------------------|------------------------------------|------------------------|------------------------|-------------------------------------------------|------------------------|
| Design                                           | Piloted filter-diaphragm regulator |                        |                        | Directly actuated filter-diaphragm regulator DI |                        |
| Pneumatic connection                             | G $\frac{3}{4}$                    | G1                     |                        | G $\frac{3}{4}$                                 | G1                     |
| D5 – Pressure regulation range 0.5 ... 4 bar     |                                    |                        |                        |                                                 |                        |
| Grade of filtration                              | 5 $\mu$ m                          | 16,000 $\pm 15\%^{2)}$ | 20,000 $\pm 15\%^{2)}$ | 8,000 $\pm 15\%^{2)}$                           | 19,000 $\pm 15\%^{2)}$ |
|                                                  | 40 $\mu$ m                         | 19,000 $\pm 15\%^{2)}$ | 23,000 $\pm 15\%^{2)}$ | 8,000 $\pm 15\%^{2)}$                           | 19,000 $\pm 15\%^{2)}$ |
| D6 – Pressure regulation range 0.5 ... 7 bar     |                                    |                        |                        |                                                 |                        |
| Grade of filtration                              | 5 $\mu$ m                          | 13,000 $\pm 15\%$      | 18,000 $\pm 15\%$      | 18,000 $\pm 15\%$                               | 13,000 $\pm 15\%$      |
|                                                  | 40 $\mu$ m                         | 15,000 $\pm 15\%$      | 20,000 $\pm 15\%$      | 14,000 $\pm 15\%$                               | 13,000 $\pm 15\%$      |
| D7 – Pressure regulation range 0.5 ... 12 bar    |                                    |                        |                        |                                                 |                        |
| Grade of filtration                              | 5 $\mu$ m                          | 13,000 $\pm 15\%$      | 18,000 $\pm 15\%$      | –                                               | –                      |
|                                                  | 40 $\mu$ m                         | 19,000 $\pm 15\%$      | 20,000 $\pm 15\%$      | –                                               | –                      |
| D8 – Pressure regulation range 0.5 ... 16 bar    |                                    |                        |                        |                                                 |                        |
| Grade of filtration                              | 5 $\mu$ m                          | 10,000 $\pm 15\%$      | 18,000 $\pm 15\%$      | –                                               | –                      |
|                                                  | 40 $\mu$ m                         | 19,000 $\pm 15\%$      | 20,000 $\pm 15\%$      | –                                               | –                      |

1) Measured at  $p_1 = 10$  bar and  $p_2 = 6$  bar,  $\Delta p = 1$  bar

2) Measured at  $p_1 = 10$  bar and  $p_2 = 4$  bar,  $\Delta p = 1$  bar

| Operating and environmental conditions             |                                                                                     |                |                 |                                        |
|----------------------------------------------------|-------------------------------------------------------------------------------------|----------------|-----------------|----------------------------------------|
| Condensate drain                                   | Manual rotary                                                                       | Semi-automatic | Fully automatic | Fully automatic, electrically actuated |
|                                                    | M                                                                                   | H              | V               | E2/E3/E4                               |
| Operating pressure [bar]                           | 1 ... 20                                                                            | 1.5 ... 12     | 2 ... 12        | 1 ... 16                               |
| Operating medium                                   | Air quality class 5:7:- to DIN ISO 8573-1                                           |                |                 |                                        |
| Operating medium with pressure sensor AD           | Filtered compressed air, lubricated or unlubricated, grade of filtration 40 $\mu$ m |                |                 |                                        |
| Ambient temperature [°C]                           | –10 ... +60                                                                         | +5 ... +60     | +5 ... +60      | +1 ... +60                             |
| Ambient temperature with pressure sensor AD [°C]   | 0 ... +50                                                                           | +5 ... +50     | +5 ... +50      | +1 ... +50                             |
| Temperature of medium [°C]                         | –10 ... +60                                                                         | +5 ... +60     | +5 ... +60      | +1 ... +60                             |
| Temperature of medium with pressure sensor AD [°C] | 0 ... +50                                                                           | +5 ... +50     | +5 ... +50      | +1 ... +50                             |
| Storage temperature [°C]                           | –10 ... +60                                                                         | +5 ... +60     | +5 ... +60      | +1 ... +60                             |
| Corrosion resistance class CRC <sup>1)</sup>       | 2                                                                                   |                |                 |                                        |

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

| Weight [g]                                                                                              |                             |                          |
|---------------------------------------------------------------------------------------------------------|-----------------------------|--------------------------|
| Rotary knob                                                                                             | Without integrated lock E11 | With integrated lock E11 |
| Filter regulator with metal bowl U                                                                      | 2,400                       | 2,700                    |
| Filter regulator with metal bowl U and fully automatic condensate drain, electrically actuated E2/E3/E4 | 2,800                       | 3,100                    |


## Filter regulators MS9-LFR, MS series

Technical data

**FESTO**

### Materials

Sectional view




### Filter regulator

|                   |                                                      |                                                |
|-------------------|------------------------------------------------------|------------------------------------------------|
| 1                 | Housing                                              | Die-cast aluminium                             |
| 2                 | Rotary knob                                          | PA                                             |
|                   | Rotary knob with integrated lock E11                 | Aluminium                                      |
| 3                 | Bowl                                                 | Wrought aluminium alloy                        |
|                   | Inspection window                                    | PA                                             |
| 4                 | Filter element                                       | PE                                             |
| 5                 | Spin disc                                            | POM                                            |
| 6                 | Filter holder                                        | POM                                            |
| 7                 | Separating plate                                     | POM                                            |
| 8                 | Diaphragm                                            | NBR                                            |
| 9                 | Valve stem                                           | Wrought aluminium alloy, NBR, POM              |
| –                 | Cover                                                | PA reinforced                                  |
| –                 | Connecting plate, module connector, mounting bracket | Die-cast aluminium                             |
| –                 | Seals                                                | NBR                                            |
| Note on materials |                                                      | RoHS-compliant (not with variant E2, E3 or E4) |


### Standard flow rate $q_n$ as a function of output pressure $p_2$ at operating pressure $p_1 = 10$ bar

Piloted filter-diaphragm regulator


Grade of filtration 5  $\mu\text{m}$ , pneumatic connection G $\frac{3}{4}$




Grade of filtration 40  $\mu\text{m}$ , pneumatic connection G $\frac{3}{4}$



Grade of filtration 5  $\mu\text{m}$ , pneumatic connection G1



Grade of filtration 40  $\mu\text{m}$ , pneumatic connection G1



— D5: 0.5 ... 4 bar      — D7: 0.5 ... 12 bar  
 - - - D6: 0.5 ... 7 bar      - - - D8: 0.5 ... 16 bar


## Filter regulators MS9-LFR, MS series

Technical data


Standard flow rate  $q_n$  as a function of output pressure  $p_2$  at operating pressure  $p_1 = 10$  bar

Directly actuated filter-diaphragm regulator DI


Grade of filtration  $5\ \mu\text{m}$ , pneumatic connection  $G\frac{3}{4}$




Grade of filtration  $40\ \mu\text{m}$ , pneumatic connection  $G\frac{3}{4}$



Grade of filtration  $5\ \mu\text{m}$ , pneumatic connection G1



Grade of filtration  $40\ \mu\text{m}$ , pneumatic connection G1



— D5: 0.5 ... 4 bar  
 - - - D6: 0.5 ... 7 bar

## Filter regulators MS9-LFR, MS series


Technical data

**FESTO**

### Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Without connecting thread G, cover plate VS, rotary knob with detent



| Type      | B1 | B2 | B3  | L1             |                      | L2             |                      | L3 | L4             |                      | L5  | L6   |
|-----------|----|----|-----|----------------|----------------------|----------------|----------------------|----|----------------|----------------------|-----|------|
|           |    |    |     | pilot actuated | directly actuated DI | pilot actuated | directly actuated DI |    | pilot actuated | directly actuated DI |     |      |
| MS9-LFR-G | 90 | 45 | 109 | 320            | 313                  | 69             | 62                   | 86 | 127            | 120                  | 150 | 34.5 |

# Filter regulators MS9-LFR, MS series


Technical data

## Dimensions – Connecting thread/connecting plate

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

With connecting thread 3/4 or 1

With connecting plate AG...



2 Mounting screw M6xmin.90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

→ Flow direction

| Type        | B4 | B5  | B6   | B7  | B8  | D1     | D4 | D5  | L7 | T1 | ≅  |
|-------------|----|-----|------|-----|-----|--------|----|-----|----|----|----|
| MS9-LFR-3/4 | 90 | 104 | 91.5 | -   | -   | G3/4   | 11 | 6.5 | 66 | 6  | -  |
| MS9-LFR-1   |    |     |      |     |     | G1     |    |     |    |    |    |
| MS9-LFR-AGD | -  | -   | -    | 112 | 132 | G1/2   | -  | -   | -  | -  | 30 |
| MS9-LFR-AGE |    |     |      |     | 132 | G3/4   |    |     |    |    | 36 |
| MS9-LFR-AGF |    |     |      |     | 142 | G1     |    |     |    |    | 41 |
| MS9-LFR-AGG |    |     |      |     | 162 | G1 1/4 |    |     |    |    | 50 |
| MS9-LFR-AGH |    |     |      |     | 176 | G1 1/2 |    |     |    |    | 55 |


Note: This product conforms to ISO 1179-1 and ISO 228-1

## Dimensions – Pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated MS pressure gauge with standard scale AG or red/green scale RG, display unit [bar]

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



→ Flow direction

| Type              | B2 | B3  | B9  | D2   |
|-------------------|----|-----|-----|------|
| MS9-LFR-...-AG/RG | 45 | 109 | -   | -    |
| MS9-LFR-...-A4    |    | -   | 110 | G1/4 |

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Filter regulators MS9-LFR, MS series

Technical data


**FESTO**

### Dimensions – Pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Pressure sensor without LCD display (operational status indicator only) AD7 ... AD10

Technical data → Internet: [sde5](http://sde5)



Variant AD7:  
SDE5-D10-O-...-P-M8 with  
3-pin plug M8x1, threshold  
value comparator,  
1 switching output PNP, N/O  
contact

Variant AD9:  
SDE5-D10-O3-...-P-M8 with  
3-pin plug M8x1, window  
comparator, 1 switching  
output PNP, N/O contact

Variant AD8:  
SDE5-D10-C-...-P-M8 with  
3-pin plug M8x1, threshold  
value comparator,  
1 switching output PNP, N/C  
contact

Variant AD10:  
SDE5-D10-C3-...-P-M8 with  
3-pin plug M8x1, window  
comparator, 1 switching  
output PNP, N/C contact

| Type                         | B2 | B11 | D3 |
|------------------------------|----|-----|----|
| MS9-LFR-...-AD7/AD8/AD9/AD10 | 45 | 112 | M8 |


### Dimensions – Rotary knob

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Rotary knob with detent

Rotary knob with detent, can be  
locked using accessories AS

Rotary knob with integrated lock  
E11



| Type            | B1 | D1 | L1  | L2  | L3 |
|-----------------|----|----|-----|-----|----|
| MS9-LFR         | –  | 52 | –   | 86  | –  |
| MS9-LFR-...-AS  | 65 | 52 | –   | 96  | –  |
| MS9-LFR-...-E11 | –  | 52 | 174 | 114 | 25 |


# Filter regulators MS9-LFR, MS series

Technical data

## Dimensions – Condensate drain


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

### Manual rotary M/fully automatic V




Barbed connector for plastic tubing PCN-4

### Semi-automatic H



QS connector for plastic tubing PUN-6/PAN-6

### Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: [pwea](http://pwea)


Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

| Type                 | B1 | D1 | H1   | L1  | L2  | L3 |
|----------------------|----|----|------|-----|-----|----|
| MS9-LFR-...-M/V      | –  | 5  | 34.5 | –   | –   | –  |
| MS9-LFR-...-H        |    | 6  |      |     |     |    |
| MS9-LFR-...-E2/E3/E4 | 72 | –  | 178  | 140 | 108 | 15 |

## Ordering data

Pressure regulation range 0.5 ... 7 bar, integrated pressure gauge, display unit [bar], rotary knob with detent, can be locked using accessories

| Size                                         | Condensate drain | Connection | Grade of filtration 5 µm |                               | Grade of filtration 40 µm |                               |
|----------------------------------------------|------------------|------------|--------------------------|-------------------------------|---------------------------|-------------------------------|
|                                              |                  |            | Part No.                 | Type                          | Part No.                  | Type                          |
| Piloted filter-diaphragm regulator           |                  |            |                          |                               |                           |                               |
| MS9                                          | Manual rotary    | –          | 564114                   | MS9-LFR-G-D6-CUM-AG-BAR-AS    | 564110                    | MS9-LFR-G-D6-EUM-AG-BAR-AS    |
|                                              | Fully automatic  | –          | 564115                   | MS9-LFR-G-D6-CUV-AG-BAR-AS    | 564111                    | MS9-LFR-G-D6-EUV-AG-BAR-AS    |
| Directly actuated filter-diaphragm regulator |                  |            |                          |                               |                           |                               |
| MS9                                          | Manual rotary    | –          | 564116                   | MS9-LFR-G-D6-CUM-DI-AG-BAR-AS | 564112                    | MS9-LFR-G-D6-EUM-DI-AG-BAR-AS |
|                                              | Fully automatic  | –          | 564117                   | MS9-LFR-G-D6-CUV-DI-AG-BAR-AS | 564113                    | MS9-LFR-G-D6-EUV-DI-AG-BAR-AS |

## Ordering data

Pressure regulation range 0.5 ... 12 bar, integrated pressure gauge, display unit [bar], rotary knob with detent, can be locked using accessories

| Size                               | Condensate drain | Connection | Grade of filtration 5 µm |                            | Grade of filtration 40 µm |                            |
|------------------------------------|------------------|------------|--------------------------|----------------------------|---------------------------|----------------------------|
|                                    |                  |            | Part No.                 | Type                       | Part No.                  | Type                       |
| Piloted filter-diaphragm regulator |                  |            |                          |                            |                           |                            |
| MS9                                | Manual rotary    | –          | 564120                   | MS9-LFR-G-D7-CUM-AG-BAR-AS | 564118                    | MS9-LFR-G-D7-EUM-AG-BAR-AS |
|                                    | Fully automatic  | –          | 564121                   | MS9-LFR-G-D7-CUV-AG-BAR-AS | 564119                    | MS9-LFR-G-D7-EUV-AG-BAR-AS |

## Filter regulators MS9-LFR, MS series

Ordering data – Modular products

**FESTO**

| M Mandatory data → |        |      |          |                                    |                               |                     |      |                     |
|--------------------|--------|------|----------|------------------------------------|-------------------------------|---------------------|------|---------------------|
| Module No.         | Series | Size | Function | Connection size                    | Pressure range/operation mode | Grade of filtration | Bowl | Condensate drain    |
| 562531             | MS     | 9    | LFR      | 3/4, 1, AGD, AGE, AGF, AGG, AGH, G | D5, D6, D7, D8                | E, C                | U    | M, H, V, E2, E3, E4 |
| Ordering example   |        |      |          |                                    |                               |                     |      |                     |
| 562531             | MS     | 9    | - LFR    | - G                                | - D5                          | - E                 | - U  | - M                 |

| Ordering table      |                                     |                                                            |  |             |      |
|---------------------|-------------------------------------|------------------------------------------------------------|--|-------------|------|
| Grid dimension [mm] |                                     | 90                                                         |  | Condition s | Code |
| M                   | Module No.                          | 562531                                                     |  |             |      |
|                     | Series                              | Standard                                                   |  |             | MS   |
|                     | Size                                | 9                                                          |  |             | 9    |
|                     | Function                            | Filter regulator                                           |  |             | -LFR |
|                     | Connection size                     | Thread G3/4                                                |  |             | -3/4 |
|                     |                                     | Thread G1                                                  |  |             | -1   |
|                     |                                     | Connecting plate G1/2                                      |  |             | -AGD |
|                     |                                     | Connecting plate G3/4                                      |  |             | -AGE |
|                     |                                     | Connecting plate G1                                        |  |             | -AGF |
|                     |                                     | Connecting plate G1 1/4                                    |  |             | -AGG |
|                     |                                     | Connecting plate G1 1/2                                    |  |             | -AGH |
|                     |                                     | Module without connecting thread, without connecting plate |  |             | -G   |
|                     | Pressure range/operation mode       | 0.5 ... 4 bar, manually operated                           |  |             | -D5  |
|                     |                                     | 0.5 ... 7 bar, manually operated                           |  |             | -D6  |
|                     |                                     | 0.5 ... 12 bar, manually operated                          |  |             | -D7  |
|                     |                                     | 0.5 ... 16 bar, manually operated                          |  |             | -D8  |
|                     | Grade of filtration                 | 40 µm                                                      |  |             | -E   |
|                     |                                     | 5 µm                                                       |  |             | -C   |
|                     | Bowl                                | Metal bowl                                                 |  |             | -U   |
|                     | Condensate drain                    | Manual                                                     |  |             | -M   |
|                     |                                     | Semi-automatic (P1 max. 12 bar)                            |  |             | -H   |
|                     |                                     | Fully automatic (P1 max. 12 bar)                           |  |             | -V   |
|                     |                                     | External, fully automatic, electric                        |  |             | -E2  |
|                     |                                     | 110 V AC, terminals (P1 max. 16 bar)                       |  |             | -E3  |
|                     |                                     | 230 V AC, terminals (P1 max. 16 bar)                       |  |             | -E4  |
|                     | 24 V DC, terminals (P1 max. 16 bar) |                                                            |  |             |      |

### Transfer order code

|        |    |   |   |     |   |  |   |  |   |  |   |   |   |  |
|--------|----|---|---|-----|---|--|---|--|---|--|---|---|---|--|
| 562531 | MS | 9 | - | LFR | - |  | - |  | - |  | - | U | - |  |
|--------|----|---|---|-----|---|--|---|--|---|--|---|---|---|--|

# Filter regulators MS9-LFR, MS series

Ordering data – Modular products

| Options        |                                            | Mandatory data                   |                   | Options  |                  |                            |  |
|----------------|--------------------------------------------|----------------------------------|-------------------|----------|------------------|----------------------------|--|
| Regulator type | Pressure gauge/pressure gauge alternatives | Alternative pressure gauge scale | Secondary venting | Security | Type of mounting | Alternative flow direction |  |
| DI             | AG, VS, A4, RG, AD7 ... AD10               | PSI, MPA, BAR                    | OS                | AS, E11  | WP, WPM, WPB     | Z                          |  |
| - DI           | - AG                                       | - BAR                            | - OS              | - AS     | -                | -                          |  |

| Ordering table |                                               |                                                                                        |             |                |              |               |
|----------------|-----------------------------------------------|----------------------------------------------------------------------------------------|-------------|----------------|--------------|---------------|
| Grid dimension |                                               | [mm]                                                                                   | 90          | Condition<br>s | Code         | Enter<br>code |
| <b>O</b>       | Regulator type                                | Directly actuated                                                                      |             | <b>1</b>       | <b>-DI</b>   |               |
| <b>M</b>       | Pressure gauge/pressure gauge<br>alternatives | MS pressure gauge                                                                      |             |                | <b>-AG</b>   |               |
|                |                                               | Cover plate                                                                            |             |                | <b>-VS</b>   |               |
|                |                                               | Adapter plate for EN pressure gauge 1/4, without pressure gauge                        |             |                | <b>-A4</b>   |               |
|                |                                               | Integrated pressure gauge, red/green scale                                             |             | <b>2</b>       | <b>-RG</b>   |               |
|                |                                               | Pressure sensor without display, plug M8, threshold value comparator, PNP, N/O contact |             | <b>3</b>       | <b>-AD7</b>  |               |
|                |                                               | Pressure sensor without display, plug M8, threshold value comparator, PNP, N/C contact |             | <b>3</b>       | <b>-AD8</b>  |               |
|                |                                               | Pressure sensor without display, plug M8, window comparator, PNP, N/O contact          |             | <b>3</b>       | <b>-AD9</b>  |               |
|                |                                               | Pressure sensor without display, plug M8, window comparator, PNP, N/C contact          |             | <b>3</b>       | <b>-AD10</b> |               |
|                | Alternative pressure gauge scale              | Psi                                                                                    |             | <b>4</b>       | <b>-PSI</b>  |               |
|                |                                               | MPa                                                                                    |             | <b>4</b>       | <b>-MPA</b>  |               |
| Bar            |                                               | <b>4</b>                                                                               | <b>-BAR</b> |                |              |               |
| <b>O</b>       | Secondary venting                             | Without secondary venting                                                              |             | <b>5</b>       | <b>-OS</b>   |               |
|                | Security                                      | Can be locked using accessories                                                        |             |                | <b>-AS</b>   |               |
|                |                                               | With integrated lock                                                                   |             |                | <b>-E11</b>  |               |
|                | Type of mounting                              | Mounting bracket                                                                       |             | <b>6</b>       | <b>-WP</b>   |               |
|                |                                               | Mounting bracket                                                                       |             | <b>6</b>       | <b>-WPM</b>  |               |
|                |                                               | Mounting bracket for large wall gap                                                    |             | <b>6</b>       | <b>-WPB</b>  |               |
|                | Alternative flow direction                    | Flow direction from right to left                                                      |             |                | <b>-Z</b>    |               |

- |                 |                                                                  |                |                             |
|-----------------|------------------------------------------------------------------|----------------|-----------------------------|
| 1 DI            | Not with pressure range D7, D8                                   | 5 OS           | Only with regulator type DI |
| 2 RG            | Not with alternative pressure gauge scale PSI                    | 6 WP, WPM, WPB | Not with module G           |
| 3 AD7 ... AD10  | Measuring range max. 10 bar                                      |                |                             |
| 4 PSI, MPA, BAR | Not with pressure gauge alternatives VS, A4, AD7, AD8, AD9, AD10 |                |                             |

Transfer order code


-  -  -  -  -  -  -

# Filter regulators MS12-LFR, MS series

Peripherals overview

**FESTO**

## Filter regulators MS12-LFR



### Note

Additional accessories:

- Module connector for combination with size MS9 → Internet: armv

## Mounting attachments and accessories

|   |                                         | → Page/Internet |
|---|-----------------------------------------|-----------------|
| 1 | Connecting plate<br>MS12-AG...          | ms12-ag         |
| 2 | Mounting bracket<br>MS12-WP             | ms12-wp         |
| 3 | Module connector<br>MS12-MV             | ms12-mv         |
| 4 | Padlock<br>LRVS-D                       | 47              |
| 5 | Cover plate<br>VS                       | 44              |
| 6 | Adapter for EN pressure gauge 1/4<br>A4 | 44              |
| 7 | Pressure gauge<br>MA                    | 47              |

## Filter regulators MS12-LFR, MS series

FESTO

Type codes

|                                  |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
|----------------------------------|-----------------------------------------------------------------------------------------------|----|----|---|-----|---|---|---|----|---|---|---|---|---|----|---|----|
|                                  |                                                                                               | MS | 12 | - | LFR | - | G | - | D7 | - | C | U | V | - | LD | - | AS |
| <b>Series</b>                    |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| MS                               | Standard service unit                                                                         |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Size</b>                      |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| 12                               | Grid dimension 124 mm                                                                         |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Service function</b>          |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| LFR                              | Filter regulator                                                                              |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Connection size</b>           |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| G                                | Module without connecting thread, without connecting plate<br>Connecting plates → Accessories |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Pressure regulation range</b> |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| D7                               | Pressure regulation range 0.5 ... 12 bar                                                      |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Grade of filtration</b>       |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| C                                | 5 µm                                                                                          |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| E                                | 40 µm                                                                                         |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Bowl guard</b>                |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| U                                | Integrated as metal bowl                                                                      |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Condensate drain</b>          |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| V                                | Fully automatic                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Rotary knob</b>               |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| LD                               | Long rotary knob                                                                              |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| <b>Security</b>                  |                                                                                               |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |
| AS                               | Rotary knob with detent, lockable via accessories                                             |    |    |   |     |   |   |   |    |   |   |   |   |   |    |   |    |

Further variants can be ordered using the modular system → 44


- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Security
- Type of mounting
- Alternative flow direction

# Filter regulators MS12-LFR, MS series


FESTO

Technical data

Function  
Condensate drain  
manual rotary  
with pressure gauge



Condensate drain  
fully automatic  
with pressure gauge



Flow rate  
11,000 ... 17,000 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0.8 ... 20 bar  
[www.festo.com/en/  
Spare\\_parts\\_service](http://www.festo.com/en/Spare_parts_service)

Wearing parts kits  
➔ 43

With this device, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.

- Good control characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- High flow rates
- Pilot actuated diaphragm regulator without intrinsic air consumption
- Three pressure regulation ranges: 0.3 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Pressure gauge connection for different fitting options
- Available with manual, fully automatic or fully automatic, electrically actuated condensate drain
- Regulator lock for protecting the values against adjustment
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges ➔ 46



| General technical data                  |      |                                                                                      |            |     |    |
|-----------------------------------------|------|--------------------------------------------------------------------------------------|------------|-----|----|
| Pneumatic connection 1, 2 <sup>1)</sup> |      | G1                                                                                   | G1¼        | G1½ | G2 |
| Design                                  |      | Filter regulator with/without pressure gauge                                         |            |     |    |
|                                         |      | Sintered filter with centrifugal separation                                          |            |     |    |
|                                         |      | Pilot actuated diaphragm regulator                                                   |            |     |    |
| Regulating function                     |      | Output pressure constant, with primary pressure compensation, with secondary venting |            |     |    |
| Type of mounting                        |      | Via accessories                                                                      |            |     |    |
|                                         |      | In-line installation                                                                 |            |     |    |
| Assembly position                       |      | Vertical ±5°                                                                         |            |     |    |
| Grade of filtration                     | [µm] | 5 (air purity class at the output 3.7.– to DIN ISO 8573-1)                           |            |     |    |
|                                         |      | 40 (air purity class at the output 5.7.– to DIN ISO 8573-1)                          |            |     |    |
| Bowl guard                              |      | Integrated as metal bowl                                                             |            |     |    |
| Condensate drain                        |      | Manual rotary                                                                        |            |     |    |
|                                         |      | Fully automatic                                                                      |            |     |    |
|                                         |      | Fully automatic, electrical actuated                                                 |            |     |    |
| Regulator lock                          |      | Rotary knob with detent                                                              |            |     |    |
|                                         |      | Rotary knob with detent, lockable via accessories                                    |            |     |    |
|                                         |      | Rotary knob with integrated lock                                                     |            |     |    |
| Pressure regulation range               | D6   | [bar]                                                                                | 0.3 ... 7  |     |    |
|                                         | D7   | [bar]                                                                                | 0.5 ... 12 |     |    |
|                                         | D8   | [bar]                                                                                | 0.5 ... 16 |     |    |
| Max. hysteresis                         |      | [bar]                                                                                | 0.4        |     |    |
| Pressure indicator                      |      | With pressure gauge                                                                  |            |     |    |
| Max. condensate volume                  |      | [cm <sup>3</sup> ]                                                                   | 400        |     |    |

1) Dependent on connecting plate selected, must be ordered separately as an accessory ➔ Internet: ms12-ag

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filter regulators MS12-LFR, MS series

FESTO

Technical data

| Standard nominal flow rate $q_{nN}^{1)}$ [l/min] |       |        |        |        |        |
|--------------------------------------------------|-------|--------|--------|--------|--------|
| Pneumatic connection                             |       | G1     | G1¼    | G1½    | G2     |
| Grade of filtration                              | 5 µm  | 11,000 | 11,500 | 12,000 | 14,000 |
|                                                  | 40 µm | 12,000 | 12,500 | 13,000 | 17,000 |

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag  
measured at  $p_1 = 10$  bar and  $p_2 = 6$  bar,  $\Delta p = 0.5$  bar


| Operating and environmental conditions |                                                           |                   |                                               |
|----------------------------------------|-----------------------------------------------------------|-------------------|-----------------------------------------------|
| Condensate drain                       | Manual rotary M                                           | Fully automatic V | Fully automatic, electrical actuated E2/E3/E4 |
| Input pressure [bar]                   | 0.8 ... 20                                                | 2 ... 12          | 0.8 ... 16                                    |
| Operating medium                       | Compressed air, air quality class 5.7.- to DIN ISO 8573-1 |                   |                                               |
| Ambient temperature [°C]               | -10 ... +60                                               | +5 ... +60        | +1 ... +60                                    |
| Temperature of medium [°C]             | -10 ... +60                                               | +5 ... +60        | +1 ... +60                                    |
| Storage temperature [°C]               | -10 ... +60                                               | -10 ... +60       | +1 ... +60                                    |
| Corrosion resistance CRC <sup>1)</sup> | 2                                                         |                   |                                               |

1) Corrosion resistance class 2 according to Festo standard 940 070  
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

| Weights [g]                                                                                             |                             |                          |
|---------------------------------------------------------------------------------------------------------|-----------------------------|--------------------------|
| Rotary knob                                                                                             | Without integrated lock E11 | With integrated lock E11 |
| Filter regulator with metal bowl U                                                                      | 7,000                       | 7,300                    |
| Filter regulator with metal bowl U and fully automatic, electrically actuated condensate drain E2/E3/E4 | 7,700                       | 8,000                    |

## Materials

Sectional view



| Filter regulator |                                      |                         |
|------------------|--------------------------------------|-------------------------|
| 1                | Body                                 | Die-cast aluminium      |
| 2                | Rotary knob                          | Polyamide               |
|                  | Rotary knob with integrated lock E11 | Aluminium               |
| 4                | Metal bowl                           | Wrought aluminium alloy |
| 6                | Filter element                       | Sintered bronze         |
| 7                | Spin disc                            | Polyacetate             |
| 8                | Filter holder                        | Polyacetate             |
| 9                | Separating plate                     | Polyacetate             |
| 10               | Stabilising disc                     | Polyacetate             |
| 11               | Diaphragm                            | Nitrile rubber          |
| 12               | Spring                               | Steel                   |
| -                | Seals                                | Nitrile rubber          |

# Filter regulators MS12-LFR, MS series

Technical data

FESTO

## Standard flow rate $q_n$ as a function of output pressure $p_2$

Grade of filtration 40  $\mu\text{m}$



With connecting plate MS12-AGF

Pneumatic connection G1

With connecting plate MS12-AGG

Pneumatic connection G1¼

Primary pressure  $p_1 = 10 \text{ bar}$





With connecting plate MS12-AGH

Pneumatic connection G1½

With connecting plate MS12-AGI

Pneumatic connection G2

Primary pressure  $p_1 = 10 \text{ bar}$



# Filter regulators MS12-LFR, MS series


Technical data

**FESTO**

## Dimensions

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Integrated pressure gauge, display unit [bar], long rotary knob with detent



1 Installation dimensions

→ Flow direction

| Type            | B1  | B2  | B3 | B4  | B5 | D5<br>Ø | L1  | L2 | L3 | L4  | L5  | L6 |
|-----------------|-----|-----|----|-----|----|---------|-----|----|----|-----|-----|----|
| MS12-LFR-...-LD | 124 | 122 | 61 | 148 | 52 | 40      | 460 | 88 | 86 | 168 | 250 | 16 |

# Filter regulators MS12-LFR, MS series

Technical data


**FESTO**

## Dimensions – Pressure gauge alternatives

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Cover plate VS

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



| Type            | B3 | B4  | D4   |
|-----------------|----|-----|------|
| MS12-LFR-...-VS | 61 | 148 | –    |
| MS12-LFR-...-A4 | 61 | 148 | G1/4 |

Note: This product conforms to ISO 1179-1 and ISO 228-1


## Dimensions – Rotary knob

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Long rotary knob with detent LD

Long rotary knob with detent,  
lockable via accessories LD-AS

Rotary knob with integrated lock  
E11



| Type               | B1 | D1 | L1  | L2  | L3 |
|--------------------|----|----|-----|-----|----|
| MS12-LFR-...-LD    | –  | 52 | –   | 86  | –  |
| MS12-LFR-...-LD-AS | 65 | 52 | –   | 96  | –  |
| MS12-LFR-...-E11   | –  | 52 | 174 | 114 | 25 |

# Filter regulators MS12-LFR, MS series


Technical data

**FESTO**

## Dimensions – Condensate drain


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

### Manual rotary M



Barbed fitting for plastic tubing  
PCN-4

### Fully automatic V




Barbed fitting for plastic tubing  
PCN-4

| Type           | L6 |
|----------------|----|
| MS12-LFR-...-M | 11 |

| Type           | L6 |
|----------------|----|
| MS12-LFR-...-V | 13 |

## Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: [pwea](http://pwea)



Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

## Ordering data

Pressure regulation range 0.5 ... 12 bar, metal bowl, integrated pressure gauge, display unit [bar], long rotary knob with detent, lockable via accessories

| Size | Condensate drain | Connection              | Grade of filtration 5 µm |                         | Grade of filtration 40 µm |                         |
|------|------------------|-------------------------|--------------------------|-------------------------|---------------------------|-------------------------|
|      |                  |                         | Part No.                 | Type                    | Part No.                  | Type                    |
| MS12 | fully automatic  | G1 ... G2 <sup>1)</sup> | 537150                   | MS12-LFR-G-D7-CUV-LD-AS | 537149                    | MS12-LFR-G-D7-EUV-LD-AS |

1) Connecting plate must be ordered separately as an accessory → Internet: [ms12-ag](http://ms12-ag)

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Ordering data – Wearing parts kits

| Size | Part No. | Type        |
|------|----------|-------------|
| MS12 | 673586   | MS12-LR/LFR |

## Filter regulators MS12-LFR, MS series

Ordering data – Modular products

**FESTO**

| M Mandatory data →   |        |      |          |                                   |                           |                     |      |
|----------------------|--------|------|----------|-----------------------------------|---------------------------|---------------------|------|
| Module No.           | Series | Size | Function | Connection sizes                  | Pressure regulation range | Grade of filtration | Bowl |
| 535022               | MS     | 12   | LFR      | AGF,<br>AGG,<br>AGH,<br>AGI,<br>G | D6,<br>D7,<br>D8          | E,<br>C             | U    |
| <b>Order example</b> |        |      |          |                                   |                           |                     |      |
| 535022               | MS     | 12   | - LFR    | - AGF                             | - D6                      | - C                 | - U  |

| Ordering table |                           |                                                            |     |             |      |            |      |
|----------------|---------------------------|------------------------------------------------------------|-----|-------------|------|------------|------|
| Grid dimension |                           | [mm]                                                       | 124 | Condition s | Code | Enter code |      |
| M              | Module No.                | 535022                                                     |     |             |      |            |      |
|                | Series                    | Standard                                                   |     |             | MS   |            | MS   |
|                | Size                      | 12                                                         |     |             | 12   |            | 12   |
|                | Function                  | Filter regulator                                           |     |             | -LFR |            | -LFR |
|                | Connection sizes          | Connecting plate G1                                        |     |             | -AGF |            |      |
|                |                           | Connecting plate G1¼                                       |     |             | -AGG |            |      |
|                |                           | Connecting plate G1½                                       |     |             | -AGH |            |      |
|                |                           | Connecting plate G2                                        |     |             | -AGI |            |      |
|                |                           | Module without connecting thread, without connecting plate |     |             | -G   |            |      |
|                | Pressure regulation range | 0.3 ... 7 bar                                              |     |             | -D6  |            |      |
|                |                           | 0.5 ... 12 bar                                             |     |             | -D7  |            |      |
|                |                           | 0.5 ... 16 bar                                             |     |             | -D8  |            |      |
|                | Grade of filtration       | 40 µm                                                      |     |             | -E   |            |      |
|                |                           | 5 µm                                                       |     |             | -C   |            |      |
| ↓              | Bowl                      | Metal bowl                                                 |     |             | -U   |            | -U   |

Transfer order code

|        |    |    |       |   |  |   |  |   |  |     |
|--------|----|----|-------|---|--|---|--|---|--|-----|
| 535022 | MS | 12 | - LFR | - |  | - |  | - |  | - U |
|--------|----|----|-------|---|--|---|--|---|--|-----|

# Filter regulators MS12-LFR, MS series

FESTO

Ordering data – Modular products

| Options                       |                             |                                  |             |            |                  |                            |
|-------------------------------|-----------------------------|----------------------------------|-------------|------------|------------------|----------------------------|
| Condensate drain              | Pressure gauge alternatives | Alternative pressure gauge scale | Rotary knob | Security   | Type of mounting | Alternative flow direction |
| M,<br>V,<br>E2,<br>E3,<br>E4, | VS,<br>A4                   | PSI,<br>MPA                      | LD          | AS,<br>E11 | WP               | Z                          |
| - E2                          | -                           | -                                | - LD        | - AS       | - WP             | - Z                        |

| Ordering table |                                  |                                                                                 |             |      |  |            |
|----------------|----------------------------------|---------------------------------------------------------------------------------|-------------|------|--|------------|
| Grid dimension | [mm]                             | 124                                                                             | Condition s | Code |  | Enter code |
| ↓<br>[M]       | Condensate drain                 | Manual                                                                          |             | -M   |  |            |
|                |                                  | Fully automatic (P1 max. 12 bar)                                                | [1]         | -V   |  |            |
|                |                                  | External fully automatic condensate drain, electrical, 110 V AC, terminal strip |             | -E2  |  |            |
|                |                                  | External fully automatic condensate drain, electrical, 230 V AC, terminal strip |             | -E3  |  |            |
|                |                                  | External fully automatic condensate drain, electrical, 24 V DC, terminal strip  |             | -E4  |  |            |
| [O]            | Pressure gauge alternatives      | Cover plate                                                                     |             | -VS  |  |            |
|                |                                  | Adapter plate for EN pressure gauge 1/4, without pressure gauge                 |             | -A4  |  |            |
|                | Alternative pressure gauge scale | psi                                                                             | [2]         | -PSI |  |            |
|                |                                  | MPa                                                                             | [2]         | -MPA |  |            |
|                | Rotary knob                      | Long rotary knob                                                                | [3] [4]     | -LD  |  |            |
|                | Security                         | Lockable via accessories                                                        |             | -AS  |  |            |
|                |                                  | With integrated lock                                                            | [3]         | -E11 |  |            |
|                | Type of mounting                 | Mounting bracket                                                                | [5]         | -WP  |  |            |
|                | Alternative flow direction       | Flow direction from right to left                                               |             | -Z   |  |            |

- [1] **V** Not with pressure regulation range D8  
 [2] **PSI, MPA** Not with pressure gauge alternatives VS, A4  
 [3] **LD, E11** Either rotary knob LD or security E11 must be selected  
 [4] **LD** Not with security E11  
 [5] **WP** Only with connecting plate AGF, AGG, AGH or AGI

Transfer order code

- [ ] - [ ] - [ ] - [ ] - [ ] - [ ] - [ ]

## Filter regulators MS-LFR, MS series

Accessories

**FESTO**

### Filter cartridges



| Ordering data |                             |          |                                                                                               |
|---------------|-----------------------------|----------|-----------------------------------------------------------------------------------------------|
| Size          | Grade of filtration<br>[µm] | Part No. | Type                                                                                          |
| MS4           | 5 (colour: blue)            | 534501   | MS4-LFP-C                                                                                     |
|               | 40 (colour: white)          | 534502   | MS4-LFP-E                                                                                     |
| MS6           | 5 (colour: blue)            | 534499   | MS6-LFP-C                                                                                     |
|               | 40 (colour: white)          | 534500   | MS6-LFP-E                                                                                     |
| MS9           | 5                           | 570309   | MS9-LFP-C  |
|               | 40                          | 570310   | MS9-LFP-E  |
| MS12          | 5                           | 537143   | MS12-LFP-C                                                                                    |
|               | 40                          | 537144   | MS12-LFP-E                                                                                    |

## Filter regulators MS-LFR, MS series

Accessories

**FESTO**

| Ordering data – Connecting cable NEBU-M8                                          |                       |                 |                  | Technical data → Internet: nebu |                     |
|-----------------------------------------------------------------------------------|-----------------------|-----------------|------------------|---------------------------------|---------------------|
|                                                                                   | Electrical connection | Number of wires | Cable length [m] | Part No.                        | Type                |
|  | M8x1, straight socket | 3               | 2.5              | 541333                          | NEBU-M8G3-K-2.5-LE3 |
|                                                                                   |                       |                 | 5                | 541334                          | NEBU-M8G3-K-5-LE3   |
|  | M8x1, angled socket   | 3               | 2.5              | 541338                          | NEBU-M8W3-K-2.5-LE3 |
|                                                                                   |                       |                 | 5                | 541341                          | NEBU-M8W3-K-5-LE3   |

| Ordering data – Connecting cable NEBU-M12                                         |                        |                 |                  | Technical data → Internet: nebu |                      |
|-----------------------------------------------------------------------------------|------------------------|-----------------|------------------|---------------------------------|----------------------|
|                                                                                   | Electrical connection  | Number of wires | Cable length [m] | Part No.                        | Type                 |
|  | M12x1, straight socket | 4               | 2.5              | 550326                          | NEBU-M12G5-K-2.5-LE4 |
|                                                                                   |                        |                 | 5                | 541328                          | NEBU-M12G5-K-5-LE4   |
|  | M12x1, angled socket   | 4               | 2.5              | 550325                          | NEBU-M12W5-K-2.5-LE4 |
|                                                                                   |                        |                 | 5                | 541329                          | NEBU-M12W5-K-5-LE4   |

| Ordering data – Pressure gauge MA                                                   |                                                       |                      |                  |           |                    |                               |
|-------------------------------------------------------------------------------------|-------------------------------------------------------|----------------------|------------------|-----------|--------------------|-------------------------------|
|                                                                                     | Nominal size                                          | Pneumatic connection | Indicating range |           | Part No.           | Type                          |
|                                                                                     |                                                       |                      | [bar]            | [psi]     |                    |                               |
|  | Pressure gauge MA, DIN EN 837-1                       |                      |                  |           |                    | Technical data ➔ Internet: ma |
|                                                                                     | 40                                                    | R1/4                 | 0 ... 16         | 0 ... 232 | 187080             | MA-40-16-R1/4-EN              |
|                                                                                     |                                                       |                      | 0 ... 25         | 0 ... 360 | 187081             | MA-40-25-R1/4-EN              |
|                                                                                     |                                                       | G1/4                 | 0 ... 16         | 0 ... 232 | 183901             | MA-40-16-G1/4-EN              |
|                                                                                     |                                                       |                      | 0 ... 25         | 0 ... 360 | 183902             | MA-40-25-G1/4-EN              |
|                                                                                     |                                                       |                      |                  |           |                    |                               |
|                                                                                     | Pressure gauge MA, DIN EN 837-1, with red-green range |                      |                  |           |                    | Technical data ➔ Internet: ma |
|                                                                                     | 40                                                    | R1/8                 | 0 ... 16         | –         | 525726             | MA-40-16-R1/8-E-RG            |
| 50                                                                                  | R1/4                                                  | 0 ... 16             | –                | 525729    | MA-50-16-R1/4-E-RG |                               |

| Ordering data – Padlock LRVS-D                                                      |            |               |
|-------------------------------------------------------------------------------------|------------|---------------|
|                                                                                     | Weight [g] | Part No. Type |
|  | 120        | 193786 LRVS-D |

## Product Range and Company Overview

### A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalnepantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)