

## Vacuum generators VAD-M

**FESTO**




# Vacuum generators

Key features

**FESTO**

## Product overview

**Vacuum generator**



All Festo vacuum generators have a single-stage design and operate according to the venturi principle. The product families described below

have been designed for a wide range of applications. The different performance classes of the individual

product families make it possible to select vacuum generators tailored to suit specific requirements.

## Standard and inline ejectors

VN-...

Datenblätter → Internet: vn



- Nominal size  
0.45 ... 3 mm
- Max. vacuum  
93%
- Temperature range  
0 ... +60 °C
- A range of extremely effective generators suitable for use directly in the workplace
- Available as straight or T-shaped housing
- Low space requirement
- Low-cost
- No wearing parts
- Extremely fast evacuation time
- Vacuum switch (optional)
- Optional with additional functions:
  - integrated eject pulse
  - electric control for vacuum ON/OFF
  - combination of eject pulse and control

VAD-.../VAK-...

Datenblätter → Internet: vad



- Nominal size  
0.5 ... 1.5 mm
- Max. vacuum  
80%
- Temperature range  
-20 ... +80 °C
- Range of vacuum generators with sturdy aluminium casing
- VAK-...: Built-in reservoir
- VAD-...: Connection for additional external reservoir
- Maintenance-free
- VAK-...: Reliable setting down of workpieces

# Vacuum generators

Key features

**FESTO**

## Compact ejectors

VADM-.../VADMI-...


Datenblätter → Internet: [vadm](#)



- Nominal size  
0.45 ... 3 mm
- Max. vacuum  
88%
- Temperature range  
0 ... +60 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VADMI-...: Additional built-in solenoid valve for ejector pulse
- Filter with display
- Air-saving circuit (optional)
- Vacuum switch (optional)
- Reliable setting down of workpieces

VAD-M-.../VAD-M-I-...

→ 6



- Nominal size  
0.7 ... 2 mm
- Max. vacuum  
85%
- Temperature range  
0 ... +40 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VAD-M-I-...: Additional built-in solenoid valve for ejector pulse
- Reliable setting down of workpieces

# Vacuum generators VAD-M

FESTO

Key features

## At a glance


- Compact and sturdy design
- Short switching times thanks to integrated solenoid valves
- With manual override
- Maintenance-free because there are no moving parts
- With integrated silencer for reducing exhaust noise

## Vacuum generators VAD-M...-I...

The compressed air supply of these vacuum generators is controlled by the built-in solenoid valve. When the electrical power supply is switched on, the valve is actuated and the flow of compressed air from 1 (P) to 3 (R) generates a vacuum at port 2, operating on the ejector principle.

Suction stops when the supply power to the valve is switched off. Workpieces with smooth, impervious surfaces are picked up and retained.

- Built-in solenoid valve for:
  - Vacuum ON/OFF




## Vacuum generator VAD-M...-I... with ejector pulse

With two integrated solenoid valves for vacuum ON/OFF and ejector pulse for rapid purging of vacuum, plus manual override

Compressed air enters the vacuum generator following the application of a voltage signal to the integrated solenoid valve, thereby creating a vacuum. Once the voltage is switched off at the vacuum valve (B) and switched on at the ejector valve (A), the vacuum is rapidly purged at connection 2 (V) as a result of the application of pressure.

- Two integrated solenoid valves:
  - Vacuum ON/OFF
  - Ejector pulse





# Vacuum generators VAD-M

Peripherals overview and type codes

FESTO

VAD-MYB

VAD-ME



Mounting attachments and accessories			
	VAD-MYB	VAD-ME	→ Seite/Internet
1 Push-in fitting QS	■	■	qs
2 Suction gripper ESG	■	■	esg
3 Plug socket with cable KMYZ-2	■	—	kmyz-2
4 Plug socket with cable KMYZ-4	■	—	kmyz-4
5 Plug socket with cable KME-1	—	■	kme-1
6 Plug socket MSSD-ZBZC	—	■	mssd-zbzc
7 Plug socket MSSD-E	—	■	mssd-e
8 Illuminating seal ME-LD	—	■	me-ld

Type		VAD	MYB	I	1/8
VAD	Vacuum generator, electrical				
Solenoid coils					
MYB	Solenoid coil				
ME	Solenoid coil				
Functions					
I	With ejector pulse				
Connection sizes					
1/8	G1/8 thread				
1/4	G1/4 thread				
3/8	G3/8 thread				


- - Note  
Possible combinations can be found in the ordering data.


# Vacuum generators VAD-M


Technical data


FESTO

## Function



-  - Temperature range  
0 ... +40 °C

-  - Operating pressure  
1.5 ... 8 bar



General technical data				
Type	VAD-MYB-...		VAD-ME-...	
Size	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$
Design	Slim rectangular			
Operating medium	Compressed air, dried, filtered and unlubricated			
Mounting position	Any			
Ejector features	High vacuum			
Type of mounting	Via female threads			
Pneumatic connection 1/2	M5/G $\frac{1}{8}$	G $\frac{1}{8}$ /G $\frac{1}{8}$	G $\frac{1}{8}$ /G $\frac{1}{4}$	G $\frac{1}{4}$ /G $\frac{3}{8}$
Nominal size of laval nozzle [mm]	0.7	0.95	1.4	2.0
Max. vacuum [%]	85			
Operating pressure [bar]	1.5 ... 8			
Duty cycle [%]	100			
Protection class	IP65			

Ambient conditions	
Variant	VAD-M...-...
Ambient temperature [°C]	0 ... +40
Corrosion resistance CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Weights [g]				
Type	VAD-MYB-...		VAD-ME-...	
Size	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$
VAD-M...	80	125	210	240
VAD-M...-I-...	135	160	250	280

# Vacuum generators VAD-M


Technical data

FESTO



Vacuum generators  
Electropneumatic

1.2



Vacuum  $\Delta p_u$  as a function of operating pressure  $p$




Evacuation time  $t$  [s] for 1 litre volume at 6 bar operating pressure



Air consumption  $Q$  as a function of operating pressure  $p$



Efficiency  $\eta$  as a function of vacuum  $\Delta p$  at  $P_{nom}$  6 bar



# Vacuum generators VAD-M


Technical data

FESTO

## Dimensions

VAD-MYB-1/8

VAD-ME-1/8/-1/4/-3/8



1 Socket type KMYZ-2-24-... with 2-wire cable, 2.5 or 5 m long, Ø 3.4 mm (2x 0.25 mm<sup>2</sup>)

2 Socket type KME-1-24-... with 2-wire cable, 2.5 or 5 m long, Ø 5.6 mm (2x 0.75 mm<sup>2</sup>)

3 Mounting thread  
4 Manual override  
5 Yellow LED

Type	B	D1	D2	D3	D4	D5	H1	H2	H3	H4
VAD-MYB-1/8	15	G1/8	M4	M5	4.2	—	62.5	12.7	7	22
VAD-ME-1/8	18	G1/8	M4	G1/8	4.2	3.2	93	14.2	6.5	20
VAD-ME-1/4	22	G1/4	M4	G1/8	4.2	4.2	106.8	8.7	9	33
VAD-ME-3/8	22	G3/8	M5	G1/4	5.2	5.2	113.1	11	10	39

Type	H5	H6	L1	L2	L3	L4	L5	L6	L7	L8
VAD-MYB-1/8	29	56	67.2	43.5	14	5.5	33.5	34.6	—	—
VAD-ME-1/8	36	64	76	61	27	19	30.5	48	32.5	58
VAD-ME-1/4	50	77.8	96.6	61	29	22.5	21.5	48	37	58
VAD-ME-3/8	56	84.1	101.8	61	32	23.5	21.5	48	39.5	58

# Vacuum generators VAD-M

Technical data

**FESTO**


Vacuum generators  
Electropneumatic

1.2

## Dimensions

VAD-MYB-I-1/8

VAD-ME-I-1/8/-1/4/-3/8



1 Socket type KMYZ-2-24-... with  
2-wire cable, 2.5 or 5 m long,  
Ø 3.4 mm (2x 0.25 mm<sup>2</sup>)

2 Socket type KME-1-24-... with  
2-wire cable,  
2.5 or 5 m long, Ø 5.6 mm  
(2x 0.75 mm<sup>2</sup>)

3 Mounting thread  
4 Manual override  
5 Yellow LED

Type	B1	D1	D2	D3	D4	D5	H1	H2	H3	H4
VAD-MYB-I-1/8	15	G1/8	M4	M5	4.2	–	67.5	12.7	7	22
VAD-ME-I-1/8	18	G1/8	M4	G1/8	4.2	3.2	93	14.2	6.5	20
VAD-ME-I-1/4	22	G1/4	M4	G1/8	4.2	4.2	106.8	8.7	9	33
VAD-ME-I-3/8	22	G3/8	M5	G1/4	5.2	5.2	113.1	11	10	39

Type	H5	H6	L1	L2	L3	L4	L5	L6	L7
VAD-MYB-I-1/8	34	58.5	80.2	67	26	5.5	33.5	70	45
VAD-ME-I-1/8	36	64	76	61	27	19	30.5	96	32.5
VAD-ME-I-1/4	50	77.8	96.6	61	29	22.5	21.5	96	37
VAD-ME-I-3/8	56	84	101.8	61	32	23.5	21.5	96	39.5

## Ordering data

Pneumatic connection	Solenoid coils	Without ejector pulse		With ejector pulse	
		Part No.	Type	Part No.	Type
G1/8	MYB	35 553	VAD-MYB-1/8	35 530	VAD-MYB-I-1/8
G1/8	ME	35 554	VAD-ME-1/8	35 531	VAD-ME-I-1/8
G1/4	ME	35 555	VAD-ME-1/4	35 532	VAD-ME-I-1/4
G3/8	ME	35 556	VAD-ME-3/8	35 533	VAD-ME-I-3/8

## Product Range and Company Overview

### A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices


### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)