




- Easy to insert
- Easy to release
- Up to 6 outlets
- 360° rotatable



Multiple distributors QS, Quick Star

Key features

FESTO

Application	Simply "plug and work"	Reliably connected	Captive seal
 Effortless selection of the right fitting. Quick Star offers a secure solution for every connection. The convenient push-in fitting system includes well over 1000 types of standard and function fittings.	 The stainless steel retaining ring within the fitting holds the tubing securely without damaging its surface. Vibration and pressure surges are safely absorbed. The tubing can be detached easily by pressing down the blue release ring. For your convenience, the appropriate outside tubing diameter is marked on the release ring.	 A nitrile rubber sealing ring guarantees a perfect seal between standard OD tubing and the body of the fitting. Standard tubing is suitable for use with compressed air and vacuum.	 All of the brass components included in Festo's push-in fittings are nickel plated and are thus highly resistant to corrosion. The tapered ISO R threads have a self-sealing PTFE coating, which allows the fitting to be re-used up to five times without the need for additional sealing components.

360° rotatable	360° rotatable, with ball bearing
 Alignment is performed during assembly. Tube movement is compensated during use.	 Permits rotating motion of up to 500 rpm during use.

Which fitting fits which thread?	
G thread to ISO 228-1 • Shorter thread • Constant installation depth • Replaceable sealing ring • Sealing at front • Can be re-used a number of times thanks to replaceable sealing ring	R thread to EN 10226-1 and ISO 7/1 • Self-sealing thread • Sealing on the threads • No additional sealing surface required • Smaller installation dimensions since there is no need for a rebate for the sealing surface • Can be re-used up to five times
 G male thread G female thread	 R male thread G female thread R female thread

Multiple distributors QS, Quick Star


Technical data

FESTO

General technical data		
Size	Standard	
Design structure	Push/pull principle	
Assembly position	Any	
Operating and environmental conditions		
Temperature dependent operating pressure	[bar]	−0.95 ... +14
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]	
Note on operating/pilot medium	Operation with lubricated medium possible	
Ambient temperature	[°C]	−10 ... +80
Corrosion resistance class CRC ¹⁾	1	
Certification	Germanischer Lloyd	


- 1) CRC1: Corrosion resistance class to Festo standard 940 070
Components with light corrosion exposure. Protection for transport and storage. Components without significant decorative function or surface, e.g. installed out of sight internally or behind covers.

Operating pressure p as a function of temperature t



Materials

Sectional view



Multiple distributor QS		
1	Release ring	POM (colour: blue)
2	Seal	NBR
3	Housing	PBT
4	Tube clamping segment	High alloy stainless steel
5	Threaded coupling	Nickel plated brass
Note on materials		RoHS-compliant

Multiple distributors QS, Quick Star

Technical data

FESTO

Max. tightening torque	
Connecting thread	Max. tightening torque [Nm]
R thread	
R1/8	7
R1/4	12
R3/8	22
R1/2	28
G thread	
G1/8	10
G1/4	15
G3/8	25
G1/2	40

Tubing insertion depth						
	Tubing O.D. [mm]	4	6	8	10	12
	Tubing insertion depth [mm]	15	17	18	20.5	23.5

Possible push-in fitting/tubing combinations					
Thread	Tubing O.D. [mm]				
	4	6	8	10	12
R1/8	+	++	+	–	–
R1/4	+	+	++	+	–
R3/8	–	–	+	++	+
R1/2	–	–	–	–	++
G1/8	+	++	+	–	–
G1/4	+	+	++	+	–
G3/8	–	–	+	++	+
G1/2	–	–	–	–	++

- + Possible thread/tubing O.D. combinations
- ++ Optimum thread/tubing O.D. combinations (with regard to flow)

Multiple distributors QS, Quick Star

Product range overview

FESTO

Shape	Design	Type	Connection D1			Connection D2	Connection D3	→ Page/ Internet
			R thread	G thread	Tubing O.D.	Tubing O.D.	Tubing O.D.	
L-shape	Multiple distributor, rotatable 360° – 2 outlets							
		QSLV2	R1/8	G1/8	–	4, 6, 8	–	6
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 3 outlets							
		QSLV3	R1/8	G1/8	–	4, 6, 8	–	7
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 4 outlets							
		QSLV4	R1/8	G1/8	–	4, 6, 8	–	8
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 6 outlets							
		QSLV6	R1/8	G1/8	–	4, 6, 8	–	9
			R1/4	G1/4		6, 8, 10		
			R3/8	G3/8		8, 10, 12		
			R1/2	G1/2		12		
	Multiple distributor, rotatable 360° – 4 outlets							
		QSQ	R1/8	G1/8	–	4, 6	–	10
			R1/4	G1/4		4, 6		
		QSQ reducing	–	–	6	4	–	10
					8	6		
T-shape	Multiple distributor, rotatable 360° – 3 outlets							
		QST3	R1/8	G1/8	–	6	4	11
			R1/4	G1/4		8	6	
			R3/8	G3/8		10	8	
		QST3 reducing	–	–	6	6	4	11
					8	8	6	
					10	10	8	

Multiple distributors QSLV2, Quick Star

Technical data

FESTO


Multiple distributor QSLV2

2 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data														
Connection	Nominal size [mm]	Tubing O.D. D2	D5 $\varnothing$	H1	H2	H3	H4	H5	L1	$\varnothing 1$	Weight/ piece [g]	Part No.	Type	PU*
R thread														
R $\frac{1}{8}$	2.4	4	10	41.6	8	15.5	13	37.6	22.2	14	26	153211	QSLV2- $\frac{1}{8}$ -4	1
	3.2	6	12.5	41.6	8	15.5	13	37.6	24.2	14	28	153212	QSLV2- $\frac{1}{8}$ -6	1
	4.2	8	14.5	46.6	8	17.5	15	42.6	27.7	17	44	153214	QSLV2- $\frac{1}{8}$ -8	1
R $\frac{1}{4}$	3.2	6	12.5	44.6	11	16.5	13	38.6	24.2	14	34	153213	QSLV2- $\frac{1}{4}$ -6	1
	4.3	8	14.5	49.6	11	18.5	15	43.6	27.7	17	47	153215	QSLV2- $\frac{1}{4}$ -8	1
	5.2	10	17.5	57.6	11	22	18	51.6	31.7	22	80	153217	QSLV2- $\frac{1}{4}$ -10	1
R $\frac{3}{8}$	4.3	8	14.5	50.6	12	19.2	15	44.3	27.7	17	54	153216	QSLV2- $\frac{3}{8}$ -8	1
	5.3	10	17.5	58.6	12	22.7	18	52.3	31.7	22	83	153218	QSLV2- $\frac{3}{8}$ -10	1
	6.3	12	21	68.8	12	27.5	21.6	62.5	36.7	27	139	153219	QSLV2- $\frac{3}{8}$ -12	1
R $\frac{1}{2}$	6.4	12	21	71.8	15	28.6	21.6	63.6	36.7	27	149	153220	QSLV2- $\frac{1}{2}$ -12	1
G thread with sealing ring														
G $\frac{1}{8}$	2.4	4	10	40.6	5.1	13.4	13	—	22.2	14	25	186223	QSLV2-G $\frac{1}{8}$ -4	1
	3.2	6	12.5	40.6	5.1	13.4	13	—	24.2	14	27	186224	QSLV2-G $\frac{1}{8}$ -6	1
	4.2	8	14.5	45.6	5.1	15.4	15	—	27.7	17	43	186226	QSLV2-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	3.2	6	12.5	42.1	5.6	14.4	13	—	24.2	17	36	186225	QSLV2-G $\frac{1}{4}$ -6	1
	4.3	8	14.5	46.1	5.6	15.4	15	—	27.7	17	44	186227	QSLV2-G $\frac{1}{4}$ -8	1
	5.2	10	17.5	54.1	5.6	18.9	18	—	31.7	22	77	186229	QSLV2-G $\frac{1}{4}$ -10	1
G $\frac{3}{8}$	4.3	8	14.5	47.6	6.6	15.9	15	—	27.7	19	53	186228	QSLV2-G $\frac{3}{8}$ -8	1
	5.3	10	17.5	55.6	6.6	19.4	18	—	31.7	22	79	186230	QSLV2-G $\frac{3}{8}$ -10	1
	6.3	12	21	65.8	6.6	24.2	21.6	—	36.7	27	135	186231	QSLV2-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	6.4	12	21	66.8	7.6	24.2	21.6	—	36.7	27	140	186232	QSLV2-G $\frac{1}{2}$ -12	1

* Packaging unit quantity

Multiple distributors QSLV3, Quick Star

FESTO

Technical data


Multiple distributor QSLV3

3 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data														
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	H4	H5	L1	$\varnothing C1$	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø								[g]			
R thread														
R $\frac{1}{8}$	2.4	4	10	54.7	8	15.5	13	50.7	22.2	14	33	153221	QSLV3- $\frac{1}{8}$ -4	1
	3.2	6	12.5	54.7	8	15.5	13	50.7	24.2	14	35	153222	QSLV3- $\frac{1}{8}$ -6	1
	4.3	8	14.5	61.7	8	17.5	15	57.7	27.7	17	56	153224	QSLV3- $\frac{1}{8}$ -8	1
R $\frac{1}{4}$	3.2	6	12.5	57.7	11	16.5	13	51.7	24.2	14	41	153223	QSLV3- $\frac{1}{4}$ -6	1
	4.2	8	14.5	64.7	11	18.5	15	58.7	27.7	17	59	153225	QSLV3- $\frac{1}{4}$ -8	1
	5.2	10	17.5	75.7	11	22	18	69.7	31.7	22	99	153227	QSLV3- $\frac{1}{4}$ -10	1
R $\frac{3}{8}$	4.3	8	14.5	65.7	12	19.2	15	59.4	27.7	17	66	153226	QSLV3- $\frac{3}{8}$ -8	1
	5.3	10	17.5	76.7	12	22.7	18	70.4	31.7	22	102	153228	QSLV3- $\frac{3}{8}$ -10	1
	6.4	12	21	90.5	12	27.5	21.6	84.2	36.7	27	171	153229	QSLV3- $\frac{3}{8}$ -12	1
R $\frac{1}{2}$	6.5	12	21	93.5	15	28.6	21.6	85.3	36.7	27	180	153230	QSLV3- $\frac{1}{2}$ -12	1
G thread with sealing ring														
G $\frac{1}{8}$	2.4	4	10	53.7	5.1	13.4	13	–	22.2	14	32	186233	QSLV3-G $\frac{1}{8}$ -4	1
	3.2	6	12.5	53.7	5.1	13.4	13	–	24.2	14	35	186234	QSLV3-G $\frac{1}{8}$ -6	1
	4.3	8	14.5	60.7	5.1	15.4	15	–	27.7	17	55	186236	QSLV3-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	3.2	6	12.5	55.2	5.6	14.4	13	–	24.2	17	43	186235	QSLV3-G $\frac{1}{4}$ -6	1
	4.2	8	14.5	61.2	5.6	15.4	15	–	27.7	17	56	186237	QSLV3-G $\frac{1}{4}$ -8	1
	5.2	10	17.5	72.2	5.6	18.9	18	–	31.7	22	96	186239	QSLV3-G $\frac{1}{4}$ -10	1
G $\frac{3}{8}$	4.3	8	14.5	62.7	6.6	15.9	15	–	27.7	19	65	186238	QSLV3-G $\frac{3}{8}$ -8	1
	5.3	10	17.5	73.3	6.6	19.4	18	–	31.7	22	98	186240	QSLV3-G $\frac{3}{8}$ -10	1
	6.4	12	21	87.5	6.6	24.2	21.6	–	36.7	27	167	186241	QSLV3-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	6.5	12	21	88.5	7.6	24.2	21.6	–	36.7	27	171	186242	QSLV3-G $\frac{1}{2}$ -12	1

* Packaging unit quantity

Multiple distributors QSLV4, Quick Star



FESTO

Technical data

Multiple distributor QSLV4

4 outlets

360° rotatable



Dimensions and ordering data															
Connection	Nominal size [mm]	Tubing O.D. D2	D5 Ø	H1	H2	H3	H4	H5	L1	B1	⌀1	Weight/ piece [g]	Part No.	Type	PU*
R thread															
R1/8	2.3	4	10	41.6	8	15.5	13	37.6	22.2	10	14	31	153231	QSLV4-1/8-4	1
	2.9	6	12.5	41.6	8	15.5	13	37.6	24.2	12	14	35	153232	QSLV4-1/8-6	1
	4	8	14.5	46.6	8	17.5	15	42.6	27.7	14	17	54	153234	QSLV4-1/8-8	1
R1/4	2.9	6	12.5	44.6	11	16.5	13	38.6	24.2	12	14	40	153233	QSLV4-1/4-6	1
	4.1	8	14.5	49.6	11	18.5	15	43.6	27.7	14	17	56	153235	QSLV4-1/4-8	1
	5	10	17.5	57.6	11	22	18	51.6	31.7	17	22	95	153237	QSLV4-1/4-10	1
R3/8	4.1	8	14.5	50.6	12	19.2	15	44.3	27.7	14	17	64	153236	QSLV4-3/8-8	1
	5.1	10	17.5	58.6	12	22.7	18	52.3	31.7	17	22	98	153238	QSLV4-3/8-10	1
	6	12	21	68.8	12	27.5	21.6	62.5	36.7	20	27	162	153239	QSLV4-3/8-12	1
R1/2	6.2	12	21	71.8	15	28.6	21.6	63.6	36.7	20	27	171	153240	QSLV4-1/2-12	1
G thread with sealing ring															
G1/8	2.3	4	10	40.6	5.1	13.4	13	—	22.2	10	14	30	186243	QSLV4-G1/8-4	1
	2.9	6	12.5	40.6	5.1	13.4	13	—	24.2	12	14	34	186244	QSLV4-G1/8-6	1
	4	8	14.5	45.6	5.1	15.4	15	—	27.7	14	17	53	186246	QSLV4-G1/8-8	1
G1/4	2.9	6	12.5	42.1	5.6	14.4	13	—	24.2	12	17	42	186245	QSLV4-G1/4-6	1
	4.1	8	14.5	46.1	5.6	15.4	15	—	27.7	14	17	54	186247	QSLV4-G1/4-8	1
	5	10	17.5	54.1	5.6	18.9	18	—	31.7	17	22	92	186249	QSLV4-G1/4-10	1
G3/8	4.1	8	14.5	47.6	6.6	15.9	15	—	27.7	14	19	63	186248	QSLV4-G3/8-8	1
	5.1	10	17.5	55.6	6.6	19.4	18	—	31.7	17	22	94	186250	QSLV4-G3/8-10	1
	6	12	21	65.8	6.6	24.2	21.6	—	36.7	20	27	158	186251	QSLV4-G3/8-12	1
G1/2	6.2	12	21	66.8	7.6	24.2	21.6	—	36.7	20	27	162	186252	QSLV4-G1/2-12	1

* Packaging unit quantity

Multiple distributors QSLV6, Quick Star

FESTO

Technical data


Multiple distributor QSLV6

6 outlets


360° rotatable



R thread



G thread



Dimensions and ordering data															
Connection	Nominal size	Tubing O.D.	D5	H1	H2	H3	H4	H5	L1	B1	≈C1	Weight/ piece	Part No.	Type	PU*
D1	[mm]	D2	Ø									[g]			
R thread															
R $\frac{1}{8}$	2.3	4	10	54.7	8	15.5	13	50.7	22.2	10	14	40	153241	QSLV6- $\frac{1}{8}$ -4	1
	2.9	6	12.5	54.7	8	15.5	13	50.7	24.2	12	14	45	153242	QSLV6- $\frac{1}{8}$ -6	1
	4	8	14.5	61.7	8	17.5	15	57.7	27.7	14	17	71	153244	QSLV6- $\frac{1}{8}$ -8	1
R $\frac{1}{4}$	2.9	6	12.5	57.7	11	16.5	13	51.7	24.2	12	14	51	153243	QSLV6- $\frac{1}{4}$ -6	1
	4	8	14.5	64.7	11	18.5	15	58.7	27.7	14	17	73	153245	QSLV6- $\frac{1}{4}$ -8	1
	5.2	10	17.5	75.7	11	22	18	69.7	31.7	17	22	122	153247	QSLV6- $\frac{1}{4}$ -10	1
R $\frac{3}{8}$	4.1	8	14.5	65.7	12	19.2	15	59.4	27.7	14	17	81	153246	QSLV6- $\frac{3}{8}$ -8	1
	5.2	10	17.5	76.7	12	22.7	18	70.4	31.7	17	22	126	153248	QSLV6- $\frac{3}{8}$ -10	1
	6.3	12	21	90.5	12	27.5	21.6	84.2	36.7	20	27	205	153249	QSLV6- $\frac{3}{8}$ -12	1
R $\frac{1}{2}$	6.3	12	21	93.5	15	28.6	21.6	85.3	36.7	20	27	214	153250	QSLV6- $\frac{1}{2}$ -12	1
G thread with sealing ring															
G $\frac{1}{8}$	2.3	4	10	53.7	5.1	13.4	13	—	22.2	10	14	39	186253	QSLV6-G $\frac{1}{8}$ -4	1
	2.9	6	12.5	53.7	5.1	13.4	13	—	24.2	12	14	45	186254	QSLV6-G $\frac{1}{8}$ -6	1
	4	8	14.5	60.7	5.1	15.4	15	—	27.7	14	17	70	186256	QSLV6-G $\frac{1}{8}$ -8	1
G $\frac{1}{4}$	2.9	6	12.5	55.2	5.6	14.4	13	—	24.2	12	17	53	186255	QSLV6-G $\frac{1}{4}$ -6	1
	4	8	14.5	61.2	5.6	15.4	15	—	27.7	14	17	71	186257	QSLV6-G $\frac{1}{4}$ -8	1
	5.2	10	17.5	72.2	5.6	18.9	18	—	31.7	17	22	119	186259	QSLV6-G $\frac{1}{4}$ -10	1
G $\frac{3}{8}$	4.1	8	14.5	62.7	6.6	15.9	15	—	27.7	14	19	80	186258	QSLV6-G $\frac{3}{8}$ -8	1
	5.2	10	17.5	73.7	6.6	19.4	18	—	31.7	17	22	122	186260	QSLV6-G $\frac{3}{8}$ -10	1
	6.3	12	21	87.5	6.6	24.2	21.6	—	36.7	20	27	201	186261	QSLV6-G $\frac{3}{8}$ -12	1
G $\frac{1}{2}$	6.3	12	21	88.5	7.6	24.2	21.6	—	36.7	20	27	205	186262	QSLV6-G $\frac{1}{2}$ -12	1

* Packaging unit quantity



Multiple distributors QSQ, Quick Star

Technical data

FESTO


Multiple distributor QSQ

360° rotatable
Male thread
with external hex
4 outlets



Push-in connector QSQ

360° rotatable
4 outlets
reducing



Dimensions and ordering data															
Connection	Nominal size	Tubing O.D.	B1	D5 Ø	D6 Ø	D7 Ø	L1	L2	L3	L4	≡	Weight/ piece [g]	Part No.	Type	PU*
D1	[mm]	D2													
R thread															
R ¹ / ₈	2	4	10	10.5	3.2	–	46	8	14	42	12	21.5	153206	QSQ- ¹ / ₈ -4	1
	2.1	6	13	13	3.2	–	50.5	8	16	56.5	12	29	153208	QSQ- ¹ / ₈ -6	1
R ¹ / ₄	2	4	10	10.5	3.2	–	49	11	14	43	14	29.5	153207	QSQ- ¹ / ₄ -4	1
	2.1	6	13	13	3.2	–	53.5	11	16	48	16	29	153288	QSQ- ¹ / ₄ -6	1
G thread with sealing ring															
G ¹ / ₈	1.4	4	10	10.5	3.2	–	44.7	5.1	14.2	–	13	22	186220	QSQ-G ¹ / ₈ -4	1
	3.4	6	13	13	3.5	–	49.3	5.1	15.8	–	14	28	186222	QSQ-G ¹ / ₈ -6	1
G ¹ / ₄	1.3	4	10	10.5	3.2	–	46.2	5.6	14.2	–	17	31	186221	QSQ-G ¹ / ₄ -4	1
	3	6	13	13	3.5	–	50.8	5.6	15.8	–	17	37	186263	QSQ-G ¹ / ₄ -6	1
Reducing															
6	1.4	4	10	10.5	3.2	13	37.5	14	–	–	–	14	153209	QSQ-6-4	1
8	3.2	6	13	13	3.2	14.5	42.5	16	–	–	–	20.5	153210	QSQ-8-6	1

* Packaging unit quantity

Multiple distributors QST3, Quick Star

FESTO


Technical data

Multiple distributor QST3


360° rotatable
Male thread
with external hex
3 outlets



R thread



G thread




Push-in multiple distributor QST3

360° rotatable
reducing



Reducing



Dimensions and ordering data																		
Connec- tion	Nom- inal size [mm]	Tubing O.D.		D5 Ø	D6 Ø	D7 Ø	H1	H2	L1	L2	L3	L4	L5	≈	Weight [g]	Part No.	Type	PU*
D1		D2	D3															
R thread																		
R ¹ / ₈	2.5	6	4	13	3.3	10	18.5	8	68.5	8	64.5	34	20	12	23	153200	QST3- ¹ / ₈ -6-4	1
R ¹ / ₄	3.5	8	6	15	3.3	13	20	9	81	11	75	40	24	14	36.5	153201	QST3- ¹ / ₄ -8-6	1
R ³ / ₈	4.9	10	8	18	3.3	15	24	10.5	93.5	12	87	46	28	17	59.5	153202	QST3- ³ / ₈ -10-8	1
G thread with sealing ring																		
G ¹ / ₈	2.5	6	4	13	3.3	10	18.4	8	67.4	5.1	–	34	20	13	24	186217	QST3-G ¹ / ₈ -6-4	1
G ¹ / ₄	3.5	8	6	15	3.3	13	21.3	9	78.2	5.6	–	40.2	24	17	39	186218	QST3-G ¹ / ₄ -8-6	1
G ³ / ₈	4.9	10	8	17.5	3.3	15	23.7	10.5	90	6.6	–	46.2	28	19	59	186219	QST3-G ³ / ₈ -10-8	1
Reducing																		
6	2.5	6	4	13	3.3	10	18.5	8	60	–	–	34	20	–	16	153203	QST3-6-4	1
8	3.6	8	6	15	3.3	13	21	9	69.5	–	–	40	24	–	23	153204	QST3-8-6	1
10	4.9	10	8	18	3.3	15	23.5	10.5	80	–	–	46	28	–	33	153205	QST3-10-8	1

* Packaging unit quantity