

# Connecting cables NEBV, for valves

Technical data

## Connecting cable NEBV-H1G2

- Connecting cable for VUVG valves
- Pre-assembled
- Cable lengths 0.5 to 5 m
- For connecting to electrical connection box VAVE-L1-...H
- Suitable for valves with MH connection



General technical data		
Electrical connection		Socket, 2-pin
Nominal operating voltage	[V DC]	0 ... 30
Wire insulation colour code	Pin1	Red
	Pin3	Black
Type of mounting		Clip
Mounting position		Any
Protection class to EN 60529		IP40

Materials		
Type	NEBV-H1G2-KN	NEBV-H1G2-P
Housing	POM	POM
Housing colour	Black	Black
Pin contact	Tin-plated copper alloy	Tin-plated copper alloy
Cable sheath	-	PUR
Cable sheath colour	-	Grey
Insulating sheath	PVC	PVC
Cable properties	-	Suitable for use with energy chains
Note on materials	RoHS-compliant	RoHS-compliant

Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +60

Circuitry (view of socket)		
	Pin	Wire colour
	1	Red
	2	-
	3	Black

# Connecting cables NEBV, for valves


Technical data

**FESTO**


## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

### NEBV-H1G2-KN



### NEBV-H1G2-P



Type	B1	H1	L1	L2
NEBV-H1G2-KN-0.5-N-LE2	8.3	8.4	500	13
NEBV-H1G2-KN-1-N-LE2			1000	
NEBV-H1G2-KN-2.5-N-LE2			2500	
NEBV-H1G2-KN-5-N-LE2			5000	

Type	B1	D1	H1	L1	L2	L3	L4
NEBV-H1G2-P-0.5-N-LE2	9	3.4	8.4	500	50	33.2	9
NEBV-H1G2-P-1-N-LE2				1000			
NEBV-H1G2-P-2.5-N-LE2				2500			
NEBV-H1G2-P-5-N-LE2				5000			

## Ordering data

Electrical connection	Cable composition	Product weight [g]	Length [m]	Part No.	Type
Straight socket, 2-pin	2 individual cables	4	0.5	<b>566654</b>	<b>NEBV-H1G2-KN-0.5-N-LE2</b>
		7	1	<b>566655</b>	<b>NEBV-H1G2-KN-1-N-LE2</b>
		17	2.5	<b>566656</b>	<b>NEBV-H1G2-KN-2.5-N-LE2</b>
		31	5	<b>566657</b>	<b>NEBV-H1G2-KN-5-N-LE2</b>
	2-wire cable	8	0.5	<b>566658</b>	<b>NEBV-H1G2-P-0.5-N-LE2</b>
		16	1	<b>566659</b>	<b>NEBV-H1G2-P-1-N-LE2</b>
		35	2.5	<b>566660</b>	<b>NEBV-H1G2-P-2.5-N-LE2</b>
		70	5	<b>566661</b>	<b>NEBV-H1G2-P-5-N-LE2</b>