


Spiral plastic tubing





FESTO



Spiral plastic tubing

Product range overview

FESTO

Version	Type	Ø [mm]	Colour			Operating medium		
			Blue	Black	Blue/black	Compressed air	Vacuum	Water (not drinking water)
Spiral tubing		Outside Ø						
	PUN-S Polyurethane	4, 6, 8, 10, 12	■	■	-	■	■	-
	PUN-S-DUO Polyurethane Tubing pair	4, 6, 8, 10, 12	-	-	■	■	■	-
Spiral tubing, pre-assembled		Inside Ø						
	PUN-SG Polyurethane	6.4; 7.9	■	-	-	■	■	■
	PPS Polyamide	4.75; 6.35	■	-	-	■	■	■

Spiral plastic tubing

Product range overview

FESTO

Type	Halogen-free	PWIS-free to FN 942 010	Suitable for chain link trunking	Approved by German Technical Control Board	Resistance							➔ Page/ Internet
					Chemicals	Microbes	UV radiation	Hydrolysis	Stress cracks	Corrosion resistance class	Shore hardness	
Spiral tubing												
PUN-S	■	■	■	■	-	-	++ ¹⁾	+	++	-	D 52	6
PUN-S-DUO	■	■	■	■	-	-	+	+	+	-	D 52	8
Spiral tubing, pre-assembled												
PUN-SG	■	■	-	-	+	++	+	++	+	1 ²⁾	A 87	9
PPS	■	■	■	-	+	++	+	+	+	1 ²⁾	D 60	10

++ Well suited

+ Limited suitability (upon request)

– Unsuitable

1) Applies for black colour

2) Corrosion resistance class 1 to Festo standard 940 070

Components with light corrosion exposure. Protection for transport and storage. Components without significant decorative function or surface, e.g. installed out of sight internally or behind covers.


Spiral plastic tubing

Technical data


FESTO

Measuring methods

Flow-relevant bending radius R_d



The tubing is bent in the direction of its inherent flexion until a 5% flattening of the tubing O.D. occurs. The R_d is then calculated. There is no reduction in the flow rate up until the R_d is reached.




Cross section flattened as a result of bended tubing

d = non deformed tubing OD

$d1$ = deformed tubing OD

Minimum bending radius R_{min}





The tubing attached to a movable plate is bent until the deformation results in a kink. The measured value is the minimum bending radius R_{min} . This R_{min} leads to considerable reductions in flow.

Spiral plastic tubing

Type codes

FESTO

		PUN	-	8	x	1.25	-	S	-	1	-	DUO	-	BS
Material														
PUN	Polyurethane													
PPS	Polyamide													
Outside Ø [mm]														
Wall thickness [mm]														
Design														
S	Spiral													
Working length [m]														
Twin tubing														
DUO	Twin tubing													
Colour														
SW	Black													
BL	Blue													
BS	Blue/black													

Length specifications		
	Working length	With tensile load, 80% of the maximum section length
	Block length	Without tensile load

Note

The working length represents 80% of the maximum permissible expansion. This maximum expansion is the limiting value before permanent deformation takes place.

Spiral plastic tubing PUN-S

Technical data

FESTO

Spiral plastic tubing PUN-S

Highly flexible plastic tubing.

-Q- Ambient temperature
-35 ... +60 °C


Pressure
operating pressure
-0.95 ... +10 bar

Material:
Polyurethane

Note on material:
Free of copper and PTFE



Operating pressure p as a function of temperature t



Possible fittings



Push-in fitting QS,
Quick Star¹⁾
→ Internet: qs



Quick connector CK
→ Internet: ck



Push-in fitting QS-F,
Quick Star, metal
→ Internet: qs-f

1) Recommended fitting

Dimensions and ordering data									
O.D. [mm]	I.D. [mm]	Winding Ø [mm]	Number of windings	Working length [m]	Block length [m]	Weight [g/m]	Colour	Part No.	Type
4	2.6	25	20	0.5	0.184	13	Blue	197 587	PUN-4x0,75-S-0,5-BL
							Black	197 602	PUN-4x0,75-S-0,5-SW
			45	1	0.284	27	Blue	197 588	PUN-4x0,75-S-1-BL
							Black	197 603	PUN-4x0,75-S-1-SW
			70	1.5	0.384	42	Blue	197 589	PUN-4x0,75-S-1,5-BL
							Black	197 604	PUN-4x0,75-S-1,5-SW
6	4	46	23	1	0.344	51	Blue	197 590	PUN-6x1-S-1-BL
							Black	197 605	PUN-6x1-S-1-SW
			52	2	0.518	110	Blue	197 591	PUN-6x1-S-2-BL
							Black	197 606	PUN-6x1-S-2-SW
			168	6	1.214	350	Blue	197 592	PUN-6x1-S-6-BL
							Black	197 607	PUN-6x1-S-6-SW
8	5.7	60	12	1	0.304	650	Blue	197 593	PUN-8x1,25-S-1-BL
							Black	197 608	PUN-8x1,25-S-1-SW
			27	2	0.424	140	Blue	197 594	PUN-8x1,25-S-2-BL
							Black	197 609	PUN-8x1,25-S-2-SW
			87	6	0.904	440	Blue	197 595	PUN-8x1,25-S-6-BL
							Black	197 610	PUN-8x1,25-S-6-SW

Spiral plastic tubing PUN-S

Technical data

FESTO

Dimensions and ordering data									
O.D.	I.D.	Winding Ø	Number of windings	Working length	Block length	Weight	Colour	Part No.	Type
[mm]	[mm]	[mm]		[m]	[m]	[g/m]			
10	7	80	9.5	1	0.305	110	Blue	197 596	PUN-10x1,5-S-1-BL
							Black	197 611	PUN-10x1,5-S-1-SW
			22	2	0.43	250	Blue	197 597	PUN-10x1,5-S-2-BL
							Black	197 612	PUN-10x1,5-S-2-SW
			70	6	0.91	760	Blue	197 598	PUN-10x1,5-S-6-BL
							Black	197 613	PUN-10x1,5-S-6-SW
12	8	95	9	1	0.32	200	Blue	197 599	PUN-12x2-S-1-BL
							Black	197 614	PUN-12x2-S-1-SW
			20	2	0.452	420	Blue	197 600	PUN-12x2-S-2-BL
							Black	197 615	PUN-12x2-S-2-SW
			64	6	0.98	1300	Blue	197 601	PUN-12x2-S-6-BL
							Black	197 616	PUN-12x2-S-6-SW

Spiral plastic tubing PUN-S-DUO

Technical data

FESTO

DUO spiral plastic tubing PUN-S-DUO

-Q- Ambient temperature
-35 ... +60 °C

Highly flexible paired plastic tubing.
Two lengths of tubing are fused
together into a tubing pair. For fitting,
the paired tubing is separated as
required at both ends.


Pressure
operating pressure
-0.95 ... +10 bar

Material:
Polyurethane

Note on material:
Free of copper and PTFE



Operating pressure p as a function of temperature t



Possible fittings



Push-in fitting QS,
Quick Star¹⁾
→ Internet: qs



Quick connector CK
→ Internet: ck



Push-in fitting QS-F,
Quick Star, metal
→ Internet: qs-f

1) Recommended fitting

Dimensions and ordering data									
O.D. [mm]	I.D. [mm]	Winding Ø [mm]	Number of windings	Working length [m]	Block length [m]	Weight [g/m]	Colour	Part No.	Type
4	2.6	25	20	0.5	0.268	25	Blue/black	197 617	PUN-4x0,75-S-0,5-DUO-BS
			45	1	0.468	55		197 618	PUN-4x0,75-S-1-DUO-BS
			70	1.5	0.668	84		197 619	PUN-4x0,75-S-1,5-DUO-BS
6	4	46	23	1	0.488	102	Blue/black	197 620	PUN-6x1-S-1-DUO-BS
			52	2	0.836	230		197 621	PUN-6x1-S-2-DUO-BS
			168	6	2.228	700		197 622	PUN-6x1-S-6-DUO-BS
8	5.7	60	12	1	0.408	130	Blue/black	197 623	PUN-8x1,25-S-1-DUO-BS
			27	2	0.648	280		197 624	PUN-8x1,25-S-2-DUO-BS
			87	6	1.608	870		197 625	PUN-8x1,25-S-6-DUO-BS
10	7	80	9.5	1	0.41	220	Blue/black	197 626	PUN-10x1,5-S-1-DUO-BS
			22	2	0.66	490		197 627	PUN-10x1,5-S-2-DUO-BS
			70	6	1.62	1520		197 628	PUN-10x1,5-S-6-DUO-BS
12	8	95	9	1	0.44	390	Blue/black	197 629	PUN-12x2-S-1-DUO-BS
			20	2	0.704	830		197 630	PUN-12x2-S-2-DUO-BS
			64	6	1.76	2600		197 631	PUN-12x2-S-6-DUO-BS

Spiral plastic tubing PUN-SG, pre-assembled

Technical data

FESTO

Spiral plastic tubing PUN-SG

-Q- Ambient temperature
-40 ... +60 °C

Highly flexible and hydrolysis
resistant pneumatic tubing with fabric
reinforcing and captive rotatable
fittings.


Pressure
operating pressure
-0.95 ... +15 bar

Material:
Polyurethane, nickel plated brass,
polyacetate

Note on material:
Free of copper and PTFE



Operating pressure p as a function of temperature t



- 1 PUN-10x1,5-SG
- 2 PUN-12x2-SG

Dimensions and ordering data

O.D.	I.D.	Pneumatic connection	Flow-relevant bending radius	Winding Ø	Number of windings	Working length	Block length	Weight	Colour	Part No.	Type
[mm]	[mm]		[mm]	[mm]		[m]	[m]	[g/m]			
9.5	6.4	G $\frac{1}{4}$	50	42	21	2.4	0.889	180	Blue	533 463	PUN-10x1,5-SG-2,4-BL- $\frac{1}{4}$
					50	4.8	1.165	340		533 464	PUN-10x1,5-SG-4,8-BL- $\frac{1}{4}$
					66	6	1.317	430		533 465	PUN-10x1,5-SG-6-BL- $\frac{1}{4}$
11.7	7.9	G $\frac{3}{8}$	65	51	41	4.8	1.172	480		533 466	PUN-12x2-SG-4,8-BL- $\frac{3}{8}$
					53	6	1.312	560		533 467	PUN-12x2-SG-6-BL- $\frac{3}{8}$

Spiral plastic tubing PPS, pre-assembled

Technical data

FESTO

Spiral plastic tubing PPS

This hydrolysis resistant plastic tubing demonstrates high thermal and mechanical load capacities. The tubing is supplied ready for use with 2 rotatable screw connectors and captive OL sealing rings. Kinks at the tubing ends are prevented with the anti-kinking springs.

-Q- Ambient temperature
-30 ... +80 °C


Pressure
operating pressure
-0.95 ... +21.2 bar

Material:
Polyamide, brass, galvanised steel

Note on material:
Conforms to RoHS




Operating pressure p as a function of temperature t



- 1 PPS-4
- 2 PPS-6

Dimensions and ordering data										
O.D.	I.D.	Pneumatic connection	Winding Ø	Number of windings	Working length	Block length	Weight	Colour	Part No.	Type
[mm]	[mm]		[mm]		[m]	[m]	[g/m]			
6.3	4.7	G¼	75	44	7.5	0.34	249	Blue	19 798	PPS-4-7,5-¼-BL
				90	15	0.67	367		19 799	PPS-4-15-¼-BL
7.8	6.2			43	7.5	0.43	298		19 796	PPS-6-7,5-¼-BL
				86	15	0.80	500		19 797	PPS-6-15-¼-BL



- 1 Kink protection spring
- 2 Captive seal

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com